

RIDGID

WD1680 Blower Vac Wet/Dry Vac

RIDGID
FULL LIFETIME WARRANTY
Against Material Defects
& Workmanship

This RIDGID® 16 Gallon Wet/Dry Vac is a multifunctional powerhouse. Its powerful motor and large drum size allow it to perform extremely well as a conventional vac. In addition, the vacuum's power head detaches and quickly converts into a 190 peak MPH handheld blower with a locking blowing wand that outperforms most dedicated leaf blowers. The quick-release cord wrap lets you spend less time unwrapping the 20' cord, and more time on the job. The caddy conveniently keeps your accessories and hose close at hand. It's like two incredible tools in one.

FEATURES	BENEFITS
• Detachable Hand Held Blower	Provides 190 MPH airstream for removing debris from walkways, decks, yards, driveways, job sites, tools, etc. Performance meets or exceeds that of many dedicated lawn & garden leaf blowers.
• 6.5 Peak HP Motor	Provides maximum power for the heavy-duty pickup of water & debris in the shop, basement, garage or on the job.
• Sound Reduction Technology	Scroll Noise Reduction® is a patented feature that provides quiet operation by precisely controlling the flow of air through the vac.
• Four Swivel Casters	Provides 360° maneuverability. Freewheeling movement of vac when pushed or pulled in any direction.
• Dual-Flex® Locking Hose	Resists collapsing and adds 180° flexibility at both hose ends. Hose locks onto vac.
• Innovative Accessory Storage	Unique built-in accessory caddy - Conveniently stores accessories and hose quick at hand. No more searching or fumbling to find the accessories you need.
• 1-Layer Standard Filter	Pleated paper filter captures common everyday dirt.
• 20' Power Cord	Extra long to accommodate convenient wide area cleaning.
• Large Built-In Drain	Drain located at lowest point of drum for complete emptying of water.
• Included Accessories	2-1/2" x 7' Dual-Flex® Locking Hose, 2 Extension Wands, Utility Nozzle, Car Nozzle, Wet Nozzle, & Locking Blower Nozzle



SPECIFICATIONS

Drum Size	16 gal.
Motor	
- Peak Horsepower	6.5
- Air Watts	286
- Voltage	120
- Amps	12.0
Cord Length	20'
Construction	High Impact Polypropylene
U.L. Listed	Yes
Filter Surface Area	1,600 sq. in.
Replacement Filters	VF4000 VF5000 VF6000
Optional Wet Filter	VF7000
Optional Filter Bag	VF3502
Accessory Size	2-1/2"
Shipping Weight	29 lbs.
Net Weight	24.5 lbs.



Dual-Flex® Locking Hose



Accessory & Hose Storage Caddy



Vac with Accessories & Filter



Removable Lawn & Leaf Blower