

# RIDGID

## WD6425 6 Gallon Stainless Steel Wet/Dry Vac

RIDGID  
**FULL LIFETIME WARRANTY**  
Against Material Defects  
& Workmanship

This RIDGID® 6 Gallon Stainless Steel Wet/Dry Vac is designed to deliver great suction and rugged construction in a compact package. The high performance 4.25 peak horsepower motor easily handles tough job site clean-up tasks. The top handle with integrated cord wrap, stainless steel construction, caster feet with accessory storage all make this wet/dry vacuum ideal for the demands of the Pro or DIY homeowner.

### FEATURES

- 4.25 Peak HP Motor
- 6 Gallon Stainless Steel Drum
- 4 Swivel Casters
- On-board Accessory Storage
- Lower Center of Gravity
- 1-Layer Standard Filter
- 1-7/8" x 7' Locking Hose
- Top Carry Handle/Cord Wrap
- Included Accessories

### BENEFITS

- High performance vacuum with integral blowing port for added versatility.
- Offers durable construction and a high-gloss shine.
- Provide easy 360° mobility.
- Four built-in accessory storage pockets – 1 on each caster foot. No more searching or fumbling to find accessories.
- Design lowers the center of gravity to help prevent tipping. Compact design stores more easily.
- Pleated paper filter captures common everyday dirt.
- Resists collapsing. Hose locks onto vac and can be stored on-board.
- Large carrying handle provides an area for storage of the power cord.
- 1-7/8" x 7' Locking Hose, 2 Extension Wands, Utility Nozzle, Wet Nozzle, & 1-Layer Paper Pleated Filter



### SPECIFICATIONS

Drum Size	6 gal.
Motor	
- Peak Horsepower	4.25
- Air Watts	177
- Voltage	120
- Amps	8.3
Cord Length	10'
Construction	Stainless Steel
U.L. Listed	Yes
Filter	Pleated Paper
Replacement Filters	VF4000 VF5000 VF6000
Optional Wet Filter	VF7000
Accessory Size	1-7/8"
Shipping Weight	15 lbs.
Net Weight	13 lbs.



Qwik Lock Filter Fastening System



Wet Pick-up - Basements, etc.



Vac with Accessories & Filter



Dry Pick-up - Workshop, Garage etc.