



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO.: 2025010305749802

NAME AND ADDRESS OF THE APPLICANT

TopWorx Inc.
3300 Fern Valley Road, Louisville, KY 40213, USA

NAME AND ADDRESS OF THE MANUFACTURER

TopWorx Inc.
3300 Fern Valley Road, Louisville, KY 40213, USA

NAME AND LOCATION OF THE FACTORY

TopWorx Inc.
3300 Fern Valley Road, Louisville, KY 40213, USA

PRODUCT NAME,MODEL AND SPECIFICATION

Magnet switch
MTS, MTSM; Ui:300V, Uimp:1.5kV; Ith:3A; AC-12:120VAC/0.5A,120VAC/1.5A,120VAC/3A;
DC-12:24VDC/1A, 24VDC/2A ; Enclosure protection class:IP66/67;See the appendix

STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

Valid from: Jan.16,2025

Valid until: Jan.15,2030

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

CERTIFICATE NO. : 2025010305749802

Appendix: Page 1 of 1

型号的解释:

Switch Model No: MTS - 2 2 B N xxxx

① ② ③ ④ ⑤ ⑥

① Model 型号

MTS: 5/8"-18 Mounting Thread, 1/2" NPT Conduit Entry

5/8"-18 公螺纹, 1/2"NPT 压接接头

MTSM: M18 Mounting Thread, M20 Conduit Entry

M18 公螺纹, M20 压接接头

② Contact Form 触头

1: 250mA MAX, SPDT (Form C), Hermetically Sealed 250mA MAX, SPDT (C型),

密封

2: 1A MAX, SPDT (Form C), Hermetically Sealed 1A MAX, SPDT (C型), 密封

3: 3A MAX, SPDT (Form C), Hermetically Sealed 3A MAX, SPDT (C型), 密封

③ Area Classification 区域分类

1: Hazardous Locations, Global cULus; ATEX/IECEX 危险场所

2: General Purpose, Global cULus, CE 通用

④ Termination 接线端子

A: Flying Leads, 2 Meters 飞线, 2米

B: PVC Cable, 2 Meters PVC 电缆, 2米

S: Silicone Cable, 2 Meters 硅胶电缆, 2米

⑤ Regional Certification 区域认证 (可选)

B: InMetro (Brazil) 巴西

K: KCs/KOSHA (Korea) 韩国

N: NEPSI/CCCEX (China) 中国

P: CCoE/PESO (India) 印度

R: EAC/GOST (Eurasian Union, Russia) 俄罗斯

⑥ Custom Number 客户编码 (可选)

May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use, does not affect product safety or production process. 可能包含 4 个数字, 表示自定义报价 不影响保护方法。4 个自定义编号仅用于商业用途, 不影响产品安全或生产过程。

This page is attached to the certificate and should be used at the same time as the certificate page.



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.