

### Features

- Solid state electronic timer used to automatically control ASCO solenoid valves
- Typically used with ASCO Solenoid Valves for automatic draining of condensate in compressed air systems
- Selectable timing ranges (2-40 seconds "on"; 30 seconds to 45 minutes "off")
- Manual override for test/reset
- LED lights to indicate timing phase

### Technical Specifications

<b>Supply Voltage</b>	24 - 240V AC/DC 50/60 Hz
<b>Current Consumption</b>	4 mA max.
<b>Operating Temperature</b>	14°F - 122°F
<b>Environmental Protection</b>	Type 4
<b>Switch Capacity</b>	1 Amp
<b>Inrush Current Capacity</b>	10 Amps for 10 mSec
<b>Duty Cycle</b>	100%
<b>Repeat Accuracy</b>	± 0.1%
<b>Scale Accuracy</b>	± 10%
<b>Reset/Test</b>	Manual Touch Switch
<b>Printed Circuit Board</b>	UL 94V0
<b>Connection</b>	DIN 43650 ISO-4400/6952
<b>Indicators</b>	LEDs to indicate phases
<b>On Time</b>	Adjustable from 2 to 40 sec.
<b>Off Time</b>	Adjustable from 30 sec to 45 min.



### Timer and Accessories Kit Numbers

<b>Timer Catalog Number:</b>	272839-001 272839-009**
<b>Power Cord* Kit Number:</b>	272852
<b>DIN Connector Kit Number:</b>	272873
* 6' power cord has DIN connector and 3-prong plug for wall outlet. ** For use with DIN 11 CDV Assemblies.	

Dimensions inches (mm)

