

Rosemount™ Custom Liquid Data Sheet

BOLD = Required Value
★ = Default value

Only one of the listed items can be selected.
 One or more of the listed items can be selected.

Customer Information		
Customer: _____	Contact Name: _____	
Phone No.: _____	Fax No./Email: _____	
Tagging		
Instrument Tag: _____		
Operating and Reference Conditions		
Fill in the following fields to match the Process Information and Base Conditions on the DP Flow CDS.		
Operating Temperature:		
Normal: _____	Minimum: _____	Maximum: _____
Units: <input type="radio"/> °F <input type="radio"/> °C		
Reference Conditions: Temperature: _____ 60 °F★		
Viscosity		
Select the Viscosity Units, then enter the viscosity values at the corresponding temperature value.		
Viscosity:	Temperature Value:	Viscosity Value (minimum 3 points required):
<input type="radio"/> Centipoise	Min. Operating Temp. = _____	_____
<input type="radio"/> Lbs/Ft Sec.	[¹ /4 (max-min)]+min = _____	_____
<input type="radio"/> Pascal Sec.	[¹ /2 (max-min)]+min = _____	_____
	[³ /4 (max-min)]+min = _____	_____
	Max. Operating Temp. = _____	_____
Density		
Select the Density Units, then fill in the Density value at the Reference Temperature and Pressure Conditions listed above.		
Density:		Reference Density: _____
<input type="radio"/> Density in Kg/CuM		
<input type="radio"/> Density in Lbs/CuFt		
Fill in the Density values at the corresponding temperature values.		
Temperature Values:		Density:
Temperature 1 : Min. Operating Temp. = _____		_____
Temperature 2 : [¹ /6 (max-min)]+min= _____		_____
Temperature 3 : [¹ /3 (max-min)]+min= _____		_____
Temperature 4 : [¹ /2 (max-min)]+min= _____		_____
Temperature 5 : [² /3 (max-min)]+min= _____		_____
Temperature 6 : [⁵ /6 (max-min)]+min= _____		_____
Temperature 7 : Max. Operating Temp. = _____		_____



Emerson Automation Solutions

6021 Innovation Blvd.
Shakopee, MN 55379, USA
☎ +1 800 999 9307 or +1 952 906 8888
☎ +1 952 949 7001
✉ RFQ.RMD-RCC@Emerson.com

Emerson Automation Solutions

8200 Market Blvd.
Chanhassen, MN 55317, USA
☎ +1 800 999 9307 or +1 952 906 8888
☎ +1 952 949 7001
✉ RMT-NA.RCCRFQ@Emerson.com

Emerson Automation Solutions

1300 Concord Terrace, Suite 400
Sunrise, FL 33323, USA
☎ +1 954 846 5030
☎ +1 954 846 5121
✉ RFQ.RMD-RCC@Emerson.com

Emerson Automation Solutions Europe GmbH


Neuhofstrasse 19a P.O. Box 1046
CH 6340 Baar
Switzerland
☎ +41 (0) 41 768 6111
☎ +41 (0) 41 768 6300
✉ RFQ.RMD-RCC@Emerson.com

Emerson Automation Solutions Asia Pacific Pte Ltd

1 Pandan Crescent
Singapore 128461
☎ +65 6777 8211
☎ +65 6777 0947
✉ Enquiries@AP.Emerson.com


Emerson Automation Solutions

Emerson FZE P.O. Box 17033
Jebel Ali Free Zone - South 2
Dubai, United Arab Emirates
☎ +971 4 8118100
☎ +971 4 8865465
✉ RFQ.RMTMEA@Emerson.com

 [Linkedin.com/company/Emerson-Automation-Solutions](https://www.linkedin.com/company/Emerson-Automation-Solutions)

 [Twitter.com/Rosemount_News](https://twitter.com/Rosemount_News)

 [Facebook.com/Rosemount](https://www.facebook.com/Rosemount)

 [Youtube.com/user/RosemountMeasurement](https://www.youtube.com/user/RosemountMeasurement)

Emerson Terms and Conditions of Sale are available upon request.
The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount is a mark of one of the Emerson family of companies. All other marks are the property of their respective owners.
© 2020 Emerson. All rights reserved.