



FOR DETAILED REQUIREMENTS ON STILL PIPE INSTALLATION, VERIFICATION PIN AND REFLECTOR KIT SEE DOCUMENT D7000005-484.

**IMPORTANT:**  
VERIFICATION PIN MUST BE DIRECTED TOWARDS ONE BOLT HOLE IN CUSTOMERS FLANGE. MARKING MUST BE DONE TO INDICATE THE POSITION OF THE VERIFICATION PIN AND THE CORRESPONDING FLANGE HOLE WITHIN 5°. THIS MARKING IS TO BE USED DURING MOUNTING OF THE RLG.

1. ALL DIMENSION IS VALID AT 20°C.
2. GENERAL RECOMMENDATION:  
FOR 6" L= 1800mm, MIN. DISTANCE 2000mm AND MAX. DISTANCE 2500mm  
FOR 4" L= 1200mm, MIN. DISTANCE 1000mm AND MAX. DISTANCE 2500mm  
GENERAL RECOMMENDATION FOR FULL CONTAINMENT TANKS 4000mm.  
REFER D7000005-337 FOR POSITIONING OF THE REF. PIN AT SUSPEND DECK.
3. FOR SIL INSTALLATION: MIN. 500 MM

POS	ITEM DESCRIPTION	QTY	REMARK	SUPPLIER
06	OUTER SLEEVE	1	STAINLESS STEEL	CUSTOMER
05	REFLECTOR KIT	1	STAINLESS STEEL	RTR
04	VERIFICATION PIN KIT	1	STAINLESS STEEL	RTR
03	FOOT	3	STAINLESS STEEL	CUSTOMER
02	MOVING JOINT	4	STAINLESS STEEL	CUSTOMER
01	STILL PIPE	1	STAINLESS STEEL	CUSTOMER

ISSUED BY EMe-BL	WEEK 1236	PRODUCT CODE 5900	FILE ACAD	INSTALLATION DRAWING TITLE MECHANICAL INSTALLATION DWG 5900 LPG/LNG STILL PIPE ATTACHED TO VESSEL BOTTOM
APPROVED BY EMe-MH	WEEK 1238	ORIGINAL DWG NO. -	SCALE	

**ROSEMOUNT**

1 ST ANGLE

DOC TYPE  
2

DWG NO.  
D7000001-466

ISSUE  
03

SHEET  
1/1

THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN.