

8

7

6

5

4

3

2

1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)


REVISIONS						
REV	ECN	DESCRIPTION OF CHANGE	DRAWN	CHKD	APVD	DATE

D

D

Transmitter:


1500B
2500B



MODEL 1500/2500

4-WIRE IS Cable
1000 ft [300 m]
(maximum cable length)

CUSTOMER SUPPLIED CABLE
MAXIMUM LENGTH:
1000 ft (300m) OF 18 AWG(0.8 mm²)
300 ft (100m) OF 22 AWG(0.35 mm²)



C

C

Sensor Terminals:


Sensor Models:

DH025	DL025	DS150
DH038	DL050	DS300
DH100	DL065	
DH150	DL100	
DH300	DL200	

1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Violet
8	Gray
9	White

9-WIRE IS Cable
60 ft [18 m]
(maximum cable length)

NOTE:
Prepare IS Cable per the instructions
provided with the cable.



9-WIRE Remote Core Processor
(supplied with transmitter)

GROUND SCREW
BLACK

BROWN
VIOLET
YELLOW

RED
GREEN
WHITE

GROUND SCREW

BLUE
GRAY
ORANGE

B

B

A

A

8

7

6

5

4

3

2

1

COPYRIGHT 2005 MICRO MOTION, INC.
ALL RIGHTS RESERVED

ITEM	DESCRIPTION		PART OR REF. NO.	MATL. OR MFR	QTY.
			 MICRO MOTION, INC. BOULDER, COLORADO		
			WIRING, D/DL TO 1500B/2500B		
NAME		DATE			
DRAWN	LLR	6/2/03		SIZE DWG. NO.	REV.
CHKD.	JLA	6/3/03		D EW-20001164	C
APVD.	JLA	6/3/03		SCALE NONE	DO NOT SCALE DRAWING SHEET 1 OF 1