


56-3000 and 56-3200 Series

TESCOM Product Manual



56-3000 SERIES



56-3200 SERIES



Do not attempt to select, install, use
or maintain this product until you have
read and fully understand this manual.

Contents

Section 1: Symbols 4

 1.1 Symbols 4

Section 2: Safety, Installation and Operations Precautions..... 4

 2.1 Regulators and Valves 4

 2.2 Installation 6

 2.3 Repair Service 6

Section 3: Introduction 7

Section 4: Specifications..... 8

Section 5: Drawings..... 8

 5.1 Installation Diagram for 56-3000 Series 8

 5.2 Installation Diagram for 56-3200 Series 9

Section 6: Installation and Start-Up Procedures..... 10

Section 1: Symbols

1.1 Symbols

WARNING

Paragraphs highlighted by the **CAUTION** icon contain information that must be followed to maintain a safe and successful operating environment.

CAUTION

Paragraphs highlighted by the **WARNING** icon contain information about practices or circumstances that can lead to personal injury or death, property damage or economic loss.

Section 2: Safety, Installation and Operations Precautions

2.1 Regulators and Valves

WARNING



Do not attempt to select, install, use or maintain this regulator, valve or accessory until you have read and fully understand these instructions.

Be sure this information reaches the operator and stays with the product after installation.

Do not permit untrained personnel to install, use or maintain this regulator, valve or accessory.

Improper selection, improper installation, improper maintenance, misuse or abuse of regulators, valves or related accessories can cause death, serious injury and/or property damage.

Oxygen service requires special expertise and knowledge of system design and material compatibility in order to minimize the potential for death, serious injury and/or property damage.

Possible consequences include but are not limited to:

- High velocity fluid (gas or liquid) discharge
- Parts ejected at high speed
- Contact with fluids that may be hot, cold, toxic or otherwise injurious
- Explosion or burning of the fluid
- Lines/hoses whipping dangerously
- Damage or destruction to other components or equipment in the system.

⚠ CAUTION

Safety Precautions

1. Inspect the regulators, valves, accessories and assembly before each use.
2. Never connect regulators, valves, accessories and assembly to a supply source having a pressure greater than the maximum rated pressure of the regulator, valve or accessory.
3. Refer to product label (model specific) for maximum inlet pressures. If this rated pressure cannot be found, contact your local TESCO representative for the rated pressure prior to installation and use. Verify the designed pressure rating of all equipment (e.g., supply lines, fittings, connections, filters, valves, gauges, etc.) in your system. All must be capable of handling the supply and operating pressure.
4. Clearly establish flow direction of the fluid before installation of regulators, valves and accessories. It is the responsibility of the user to install the equipment in the correct direction.
5. Remove pressure from the system before tightening fittings, gauges or components.
6. Never turn regulator or valve body. Instead hold regulator or valve body and turn fitting nut.
7. If a regulator or valve leaks or malfunctions, take it out of service immediately.
8. Do not modify equipment or add attachments not approved by the manufacturer.
9. Apply pressure to the system gradually, avoiding a sudden surge of fluid or pressure shock to the equipment in the system.
10. Regulators are not shut-off devices. Install a pressure relief device downstream of the regulator to protect the process equipment from overpressure conditions. Shut off the supply pressure when the regulator is not in use.
11. Periodic inspection and scheduled maintenance of your equipment is required for continued safe operation.
12. The frequency of servicing is the responsibility of the user based on the application. Positive seal/tied diaphragm regulators require the downstream pressure to be vented before turning the hand knob counterclockwise to reduce the outlet pressure. Damage may occur to the regulator if this procedure is not followed.
13. Never allow problems or lack of maintenance to go unreported.
14. Read and follow precautions on compressed gas cylinder labels.
15. It is important that you analyze all aspects of your application and review all available information concerning the product or system. Obtain, read and understand the Material Safety Data Sheet (MSDS) for each fluid used in your system.
16. Never use materials for regulators, valves or accessories that are not compatible with the fluids being used.
17. Users must test components for material compatibility with the system operating conditions prior to use in the system.

18. Vent fluids to a safe environment and in an area away from employees. Be sure that venting and disposal methods are in accordance with Federal, State and Local requirements. Locate and construct vent lines to prevent condensation or gas accumulation. Make sure the vent outlet is not obstructed by rain, snow, ice, vegetation, insects, birds, etc. Do not interconnect vent lines; use separate lines if more than one vent is needed.
19. Do not locate regulators, valves or accessories controlling flammable fluids near open flames or any other source of ignition.
20. Some fluids when burning do not exhibit a visible flame. Use extreme caution when inspecting and/or servicing systems using flammable fluids to avoid death or serious injury to employees. Provide a device to warn employees of these dangerous conditions.
21. Many gases can cause suffocation. Make certain the area is well ventilated. Provide a device to warn employees of lack of oxygen.
22. Never use oil or grease on these regulators, valves or accessories. Oil and grease are easily ignited and may combine violently with some fluids under pressure.
23. Have emergency equipment in the area if toxic or flammable fluids are used.
24. Upstream filters are recommended for use with all fluids.
25. Do not bleed system by loosening fittings unless specified by the product manual.
26. Prevent icing of the equipment by removing excess moisture from the gas.
27. Always use proper thread lubricants and sealants on tapered pipe threads.

2.2 Installation

CAUTION

Do not open packaging until ready for installation or in a clean environment. Product is cleaned in accordance with CGA 4.1 and ASTM G93, Verification Type 1, Tests 1 and 2. With periodic verification of cleaning process to MIL-STD-1330D.

WARNING

Make sure that the components and materials used in the fluid handling system are compatible with the fluid and have the proper pressure rating. Failure to do so can result in death, serious injury and/or property damage.

Inspect the regulator, valve, accessories and assembly for physical damage and contamination. Do not connect the regulator, valve, accessory or assembly if you detect oil, grease or damaged parts. If the regulator, valve, accessory or assembly is damaged, contact your local TESCOM representative to have the regulator cleaned or repaired.

2.3 Repair Service

If a regulator or valve leaks or malfunctions, take it out of service immediately. You must have instructions before doing any maintenance. Do not make any repairs you do not understand. Have qualified personnel make the repairs. Return any equipment in need of service to your

equipment supplier for evaluation and prompt service. Equipment is restored to the original factory performance specifications, if repairable. There are flat fee repair charges for each standard model. The original equipment warranty applies after a complete overhaul.

⚠ CAUTION

Proper Component Selection

1. Consider the total system design when selecting a component for use in a system.
2. The user is responsible for assuring all safety and warning requirements of the application are met through his/her own analysis and testing.
3. TESCO may suggest material for use with specific media upon request. Suggestions are based on technical compatibility resources through associations and manufacturers. TESCO does NOT guarantee materials to be compatible with specific media -- THIS IS THE RESPONSIBILITY OF THE USER!
4. Due to the varying composition, viscosity, corrosiveness and density of chemical fluids, the fluid media and full system must be considered by the user when selecting a product. This is required to ensure regulator performance, user safety, flow capability and system level performance.
5. Component function, adequate ratings, proper installation, operation and maintenance are the responsibilities of the system user.
6. Temperature Set Button (Only with Optional Display). This button is located on the temperature display. See Figure 3.
When pressed down the display will show the heater set temperature.

⚠ WARNING

Do not modify equipment or add attachments not approved by the manufacturer. Doing so can result in death, serious injury and/or property damage.

ASSEMBLY/INSTALLATION DRAWINGS AND BILLS OF MATERIAL drawings and parts lists for your product may be obtained by contacting TESCO. Tescom will provide these by email, fax or mail. Your local TESCO representative can provide additional assistance. Be sure to have your complete model number ready.

Section 3: Introduction

TESCOM 56-3000 and 56-3200 Series chemical injection flow control devices are specifically designed for offshore chemical injection applications. The 56-3000 and 56-3200 Series utilize pressure regulators in conjunction with a closed-loop electronic controller which allow for precise control of large flow ranges at pressures up to 15,000 psig / 1034 bar.


Section 4: Specifications

Maximum Inlet Pressure 56-3000 Series:	15,000 psig / 1034 bar
Maximum Inlet Pressure 56-3200 Series:	8000 psig / 551 bar
Maximum Outlet Pressure 56-3000 Series:	15,000 psig / 1034 bar
Maximum Outlet Pressure 56-3200 Series:	8000 psig / 551 bar
Operating Temperature (All):	0 to 165°F / -18 to 73°C
Weight 56-3000 Series:	Approximately 34.8 lbs / 15.8 kg
Weight 56-3200 Series:	Approximately 43.0 lbs / 19.5 kg

Section 5: Drawings


5.1 Installation Diagram for 56-3000 Series

Letter call-outs are referenced in the Installation and Start-Up Procedures section of this manual.



5.2 Installation Diagram for 56-3200 Series

Letter call-outs are referenced in the Installation and Start-Up Procedures section of this manual.



Section 6: Installation and Start-Up Procedures

WARNING

Failure to follow these instructions or to properly install and maintain this equipment could result in an explosion, fire and/or chemical contamination causing property damage and personal injury or death.

TESCOM regulators must be installed, operated and maintained in accordance with federal, state and local codes, rules and regulations.

If the regulator vents gas or a leak develops in the system, service to the unit may be required. Failure to correct trouble could result in a hazardous condition.

Installation, operation and maintenance procedures performed by unqualified personnel may result in improper adjustment and unsafe operation. Either condition may result in equipment damage or personal injury. Call qualified personnel when installing, operating, and maintaining the 56-3000 and 56-3200 Series regulator.

WARNING

Personal injury, equipment damage or leakage due to escaping fluid may result if needle valves are used to isolate the pressure reducing regulator. It is strongly recommended that block valves be used to properly isolate the regulator from system.

Personal injury, equipment damage or leakage due to escaping accumulated fluid or bursting of pressure-containing parts may result if this regulator is:

- Over-pressured
- Used with incompatible process fluid
- Installed where service conditions could exceed the limits given in the specifications section and on the appropriate nameplate
- Where conditions exceed any ratings of adjacent piping or piping connections. To avoid such injury or damage, provide pressure-relieving or pressure-limiting devices to prevent service conditions from exceeding those limits

Confirm with gauges that there is zero pressure in the system prior to installation:

Note: Refer to the Installation Diagram for additional information.

1. Re-tighten fittings on assembly as they may have loosened during shipping.
2. If the ER5000 Series was shipped detached from the air-loaded regulator, assemble the ER5000 Series onto the top of the regulator using the fittings provided with the ER5000 Series (1/8-in. NPT to 1/4-in. adapter, 1/2 to 1/4-in. compression fitting).
3. Install the ER5000 Series electronics according to the instructions provided in the Quick Start Manual provided with the ER5000 Series or using the instructions listed in the “Getting Started” section of the ER5000 Series Product Manual.
 - a. Do not supply power to the ER5000 Series until instructed to do so by the manual.

4. Install the ERTune software per the instructions listed in the “Install the ERTune Program” section of the Quick Start Manual or the “The ERTune Program” section of the ER5000 Series Product Manual.
5. Check that the pre-populated PIDs displayed in the “Tab” area of the ERTune software match the product PIDs listed below. If they do not, adjust them according to your product part number.
 - a. 56-3000 Series
Set 513
External Feedback
Proportional: 125
Derivative: 300
Integral: 150
Maximum: 50
Minimum: -5
Deadband: 0.00
Refresh Rate: 200 ms
 - b. 56-3200 Series
Set 514
External Feedback
Proportional: 200
Derivative: 500
Integral: 1000
Maximum: 64
Minimum: -64
Deadband: 0.00
Refresh Rate: 200 ms
6. Close the inlet (C) and outlet (A) block and bleed valves on each side of the regulator, and pressurize the supply (inlet) side of the system.
7. Install the regulator and valve assembly with the inlet port connected to the supply or inlet piping of the system, and connect the outlet port to the downstream piping in the system using plumbing supplier-specified torque values.
8. Slowly open the inlet block valve to apply pressure to the inlet of the 56-3X00 Series assembly regulator (D).
9. Verify the correct inlet pressure to the regulator (F).
10. Slowly open the outlet block valve (A) to allow pressurized flow through the system.
11. Verify the outlet pressure from the regulator and valve assembly (G) to determine if there is any leakage. If there is leakage, remove the 56-3X00 Series assembly for inspection and repair. If no leakage is noted, proceed to step 12.
12. Verify and record the flow rate and system pressure over time.

**Emerson Process Management
Regulator Technologies Inc.
TESCOM**

AMERICAS
12616 Industrial Blvd.
Elk River, MN 55330 USA
T +1 800 447 1250
+1 763 241 3238
F +1 763 241 3224
na.tescom@emerson.com
www.tescom.com

EUROPE
An der Trave 23-25
23923 Selmsdorf, Germany
T +49 (0) 3 88 23/31-287
F +49 (0) 3 88 23/31-140
eu.tescom@emerson.com
www.tescom-europe.com

Brandon House
23-25 Brandon Street
Hamilton ML3 6DA
South Lanarkshire, UK
T +44 1698 424 254
F +44 1698 459 299
uk.tescom@emerson.com
www.tescom.com

ASIA PACIFIC
3/F, Building #2 No. 1277
Xin Jin Qiao Road Jinqiao E.P.Z.
Pudong Shanghai 201206 China
T +86 21 2892 9970
F +86 21 2892 9001
ap.tescom@emerson.com
www.tescom.com

MIDDLE EAST & AFRICA
PO Box 17033 Jebel Ali Free Zone-South
(Zone 2)
Dubai, UAE
T +971 4 811 8443
F +971 4 886 5465
mea.tescom@emerson.com
www.tescom.com

DOPSM2105X012 ©TESCOM Corporation, 2016; All Rights Reserved.
TESCOM is a business unit of Emerson Process Management Regulator
Technologies, Inc. Trademarks are property of divisions of Emerson
Process Management.

The contents of this publication are presented for information purposes
only, and while effort has been made to ensure their accuracy, they are not
to be construed as warranties or guarantees, express or implied, regarding
the products or services described herein or their use or applicability.
All sales are governed by our terms and conditions, which are available
on request. We reserve the right to modify or improve the designs or
specifications of our products at any time without notice.

TESCOM™


EMERSON™
Process Management