numatics[®]

TJ Series

3 Jaw Gripper





www.numatics.com



Table of Contents

TJ Series

TJ30 Series	3-5
Features and Benefits	3
Specifications	3
How to Order	3
TJ30 Dimensions and Performance Data	4
TJ200 Series	5-8
Features and Benefits	5
Specifications	
How to Order	5
TJ200 Dimensions and Performance Data	6
TJ30 & TJ200 Series Switch Information	7-8



TJ30 Series 3 Jaw Gripper

TJ30 3 jaw gripper provides high grip force in a compact design. Stripper plate option provides 9 lbs. of linear spring force to facilitate part insertion when gripper jaws release part.

A. Jaws

Jaws are T-Slot bearing supported to prevent Jaw breakage and offer superior load bearing performance.

B. Flexible Mounting

Flexible mounting, thru hole for Socket Head Cap Screws (SHCS), tapped from opposite side.

C. Dowel Holes

Dowel holes for locating.

D. Body


Hardcoated aluminum body.

E. Sensing Tracks

Sensing tracks for Hall effect switches sensing.

F. Stripper Plate


Optional Stripper Plate.



Specifications

Series	Grip Force Close 100 PSI	Stroke	Weight	Displacement	Maximum Operating Pressure
TJ30	36 lbs.	0.300	9 oz	0.35 cu. in.	120 PSI


How To Order




Switch Description	Standard Cord Set Part No.	Quick Disconnect Part No.
Hall PNP	P494A0022300A00	P494A0022600A00
Hall NPN	P494A0022400A00	P494A0022700A00
90° 5 Meter Cable	N/A	PXC90
Straight 5 Meter Cable	N/A	PXCST



Dimensions: Inches (mm)



Performance Data



Grip Force VS. Finger Length

L (Finger Length)	Close For	ce @ 80 PSI
1 inch	24 lbs	10.8 Kgf
2 inches	21 lbs	9.5 Kgf

Maximum Load Ratings


TJ30	Static	Dynamic
C- Compression	300 lbs. (1332N)	100 lbs (444N)
T - Tension	300 lbs. (1332N)	100 lbs (444N)
Mx	250 in/lbs. (2.8 Nm)	75 in/lbs (8.5 Nm)
Му	150 in/lbs. (17 Nm)	75 in/lbs (8.5 Nm)
Mz	250 in/lbs. (2.8 Nm)	75 in/lbs (8.5 Nm)





Sensing Part Numbers

P494A0022300A00



ELECTRICAL DESIGN	DC PNP
OUTPUT	Normally Open
OPERATING VOLTAGE	10-30 VDC
CURRENT RATING	100 mA
SHORT-CIRCUIT PROTECTION	Yes
OVERLOAD PROTECTION	Yes
REVERSE POLARITY PROTECTION	Yes
VOLTAGE DROP	< 2.5 V
CURRENT CONSUMPTION	< 12 mA
REPEATABILITY	< .2mm
POWER-ON DELAY TIME	< 30 ms
SWITCH FREQUENCY	> 3000 Hz
AMBIENT TEMPERATURE	-25°C to 85°C
PROTECTION	IP 67, III

HOUSING MATERIAL	PA (Polyamide) Black; Fastening Clamp:
	Stainless Steel

FL	JNCTION DISPLAY	Yellow LED
SV	VITCHING STATUS	reliow LED

CONNECTION	Flying Leads, Pur Cable (2m Long, 3 x26 Gauge
	Wire)

	Clamping Screw with Combined Slot/Hexagon
REMARKS	Socket Head AF 1.5
	cULus - Class 2 Source Required

Rubber Placehold, Cable Clip, and Cut Sheet **ACCESSORIES** To Be Provided with Every Switch

AGENCY APPROVALS

HYSTERESIS

TRAVEL SPEED

MAGNETIC SENSITIVITY




1.0mm

2.0 mT

> 10 m/s

P494A0022600A00



ELECTRICAL DESIGN	DC PNP
OUTPUT	Normally Open
OPERATING VOLTAGE	10-30 VDC
CURRENT RATING	100 mA
SHORT-CIRCUIT PROTECTION	Yes
OVERLOAD PROTECTION	Yes
REVERSE POLARITY PROTECTION	Yes
VOLTAGE DROP	< 2.5 V
CURRENT CONSUMPTION	< 12 mA
REPEATABILITY	< .2mm
POWER-ON DELAY TIME	< 30 ms
SWITCH FREQUENCY	> 3000 Hz
AMBIENT TEMPERATURE	-25°C to 85°C
PROTECTION	IP 67, III
HYSTERESIS	1.0mm
MAGNETIC SENSITIVITY	2.0 mT
TRAVEL SPEED	> 10 m/s

HOUSING MATERIAL	PA (Polyamide) Black; Fastening Clamp:
HOUSING WATERIAL	Stainless Steel

FUNCTION DISPLAY	LAY	
SWITCHING STATUS	Yellow LED	

CONNECTION	M8 Connector Pur Cable (3 m)

	Clamping Screw with Combined Slot/Hexagon
REMARKS	Socket Head AF 1.5
	cULus - Class 2 Source Required

Rubber Placehold, Cable Clip, and Cut Sheet **ACCESSORIES** To Be Provided with Every Switch








In-Line Sensors



Sensing Part Numbers





TJ200 Series 3 Jaw Gripper

Provides high grip force in a compact design. Shielded design makes the TJ ideal for machine loading and unloading. Compact design to grip force ratio are ideal for confined work areas.

A. Jaws

Jaws are T-Slot bearing supported to prevent Jaw breakage and offer superior load bearing performance.

B. Flexible Mounting

Flexible mounting, thru hole for Socket Head Cap Screws (SHCS), tapped from opposite side.

C. Dowel Holes

Dowel holes for locating.

D. Body

Hardcoated aluminum body.

E. Sensing


Sensing tracks for Hall effect switches sensing.



Specifications


Series	Grip Force Close 100 PSI	Stroke	Weight	Maximum Operating Pressure
TJ200	250 lbs	0.330	2.3 oz	120 psi

How To Order








Dimensions: Inches (mm)



Performance Data







Grip Force VS. Finger Length

L (Finger Length)	Close For	ce @ 80 PSI
1 inch	175 lbs.	79 Kgf.
2 inches	160 lbs.	72 Kgf.
3 inches	140 lbs.	63 Kgf.

Maximum Load Ratings


TJ200	Static	Dynamic
C- Compression	1250 lbs. (5560N)	400 lbs. (1780N)
T - Tension	1250 lbs. (5560N)	400 lbs. (1780N)
Mx	1000 in/lbs. (113 Nm)	400 in/lbs. (113 Nm)
My	900 in/lbs. (113 Nm)	300 in/lbs. (101 Nm)
Mz	1000 in/lbs. (113 Nm)	400 in/lbs. (113 Nm)





Switch Information

Electro Switch (PNP NO) Flying Lead - CS-18-TP



Sensor Type Switching Logic

Output

Operating Voltage Switching Current Power Rating* Voltage Drop

Current Consumption Leakage Current

LED Indicator Cable

Operating Frequency Magnetic Requirement

Magnetic Requirement Temperature Range

Shock / Vibration

Enclosure Classification Protection Circuit

Set Screw Max. Torque

Solid State Output Normally Open

PNP Current Sourcing

5-30 VDC 50mA max. 1.5 Watts

0.5 V @ 25 mA max. 12 mA @ 24 VDC max.

0.01 mA max.

Red

1000 Hz

40 Gauss parallel 14 to 158°F (-10 to 70°C)


50G/9G

IEC 529 IP67 (NEMA 6) Reverse Polarity, Surge

Suppression

que 1.77 in-lbs (0.2 N-m)

Electro Switch (PNP NO) Flying Lead - CS-18T-QD



Sensor Type Switching Logic

Output

Operating Voltage Switching Current Power Rating* Voltage Drop Current Consumption

Leakage Current
LED Indicator
Cable

Operating Frequency Magnetic Requirement Temperature Range Shock / Vibration Enclosure Classification Protection Circuit

Set Screw Max. Torque

Solid State Output Normally Open PNP Current Sourcing

5-30 VDC 50mA max. 1.5 Watts

1.5 V @ 25 mA max. 12 mA @ 24 VDC max.

0.01 mA max.

Green

Abrasion resistant polyurethane (PUR) jacket, PVC insulation

1000 Hz

40 Gauss parallel

14 to 158°F (-10 to 70°C)

50G/9G

IEC 529 IP67 (NEMA 6) Reverse Polarity, Surge

Suppression


1.77 in-lbs (0.2 N-m)

^{*}Switches are not designed for wet environments. Please see your distributor for additional information.

3 Jaw Gripper




TJ200 Series Gripper



Sensor Description	Standard Cord Set	Quick Disconnect
Hall PNP	CS-18-TP	CS-18T-QD
Hall NPN	CS-20TN	CS-18N-QD

Switch Information

Electro Switch (NPN NO) Flying Lead - CS-20TN



Sensor Type Switching Logic

Output

Operating Voltage Switching Current Power Rating* Voltage Drop

Current Consumption Leakage Current

LED Indicator

Cable

Operating Frequency Magnetic Requirement Temperature Range Shock / Vibration Enclosure Classification Protection Circuit Set Screw Max. Torque

Solid State Output Normally Open NPN Current Sinking

5-30 VDC 50mA max. 1.5 Watts

0.5 V @ 25 mA max. 12 mA @ 24 VDC max.

0.01 mA max.

Red

1000 Hz 40 Gauss parallel

14 to 158°F (-10 to 70°C)


50G/9G

IEC 529 IP67 (NEMA 6) Reverse Polarity, Surge

Suppression

1.77 in-lbs (0.2 N-m)

Electro Switch (NPN NO) 8 mm Connector - CS-18N-QD



Sensor Type Switching Logic

Output

Operating Voltage Switching Current Power Rating*

Voltage Drop Current Consumption

Leakage Current LED Indicator

Cable

Operating Frequency Magnetic Requirement

Temperature Range Shock / Vibration **Enclosure Classification**

Protection Circuit

Set Screw Max. Torque

Solid State Output Normally Open NPN Current Sinking

5-30 VDC 50mA max. 1.5 Watts

0.5 V @ 25 mA max. 12 mA @ 24 VDC max.

0.01 mA max.

Red

1000 Hz

40 Gauss parallel

14 to 158°F (-10 to 70°C)

50G/9G

IEC 529 IP67 (NEMA 6) Reverse Polarity, Surge

Suppression

1.77 in-lbs (0.2 N-m)

numatics°

World Class Supplier of Pneumatic Components



World Headquarters

USA Numatics, Incorporated 46280 Dylan Drive Novi, Michigan 48377

P: 248-596-3200 F: 248-596-3201 **Canada Numatics, Ltd** P: 519-758-2700 F: 519-758-5540

México - Ascomatica SA de CV P: 52 55 58 09 56 40 (DF y Area metropolitana) P: 01 800 000 ASCO (2726) (Interior de la República) F: 52 55 58 09 56 60 **Brazil Ascoval Ind.e Comercio Ltda** P: (55) 11-4208-1700 F: (55) 11-4195-3970