Contact bridges with cable, series CON-CB







Contact bridges, series CON-CB

- Socket, mini-DIN, 8-pin, straight

- Number of solenoid coils 1



Technical data

Ambient temperature min./max. Protection class Protective circuit Operational voltage Valve LED status display Mounting screw Tightening torque for mounting screws [+0,05] Weight -15 ... 50 °C IP65 43 V bi-directional 24 V DC

Yellow M2.5 with slot 0.25 Nm

See table below The delivered product may vary from that in the illustration.

Part No.	Electrical connectio 1	n Electrical connection 2				Cable length	
5763533113	open cable ends 9-p	in	Socket, form C, 2-pin, with cable, straight				5 m
5763533103	Plug 8-pin straight 18	30°		Socket, form C, 2-p	in, straight		0.2 m
Part No. Cable-Ø n-Wi		n-Wir		Wire cross-section	Weight		Fig
		11- V VII	e		weight		Fig.
5763533113 4.8 mm 9			0.128 mm ²	0.2 kg	F	ig. 1	
5763533103 4.8 mm 9		0.14 mm ²	0.037 kg	F	ig. 2		

Technical information

Contact bridge 5763533113 actuates a valve system (Fig. 1). Variant 5763533103 connects the 8 solenoid coils (Fig. 2).


Technical information

Material		
Housing	Polyester amide	
Cable	Polyurethane	
Seals	Fluorocaoutchouc	



Dimensions

Fig. 1



- 1) mounting space for name plate
- 2) Valve LED

3a) sealing cap for manual override, not removable

- 3b) sealing cap for manual override, removable
- 4) captive seal and screw

5) Tightening torque for mounting screws: 0,25 Nm + 0,05

Wire allocation:

Black = magnet 1 Brown = magnet 2 Orange = magnet 3 Yellow = magnet 4 Green = magnet 5 Purple = magnet 6 White = magnet 7 Pink = magnet 8 Blue = 0 V


Assignment scheme

Color	black		brown	/n Orange			green	
Allocation	llocation solenoid 1		solenoid 2	solenoid 3	solenoid 4		solenoid 5	
violet		white	pink			blue		
solenoid 6		solenoid 7	solenoi	d 8		Ground		



Dimensions

Fig. 2



- 1) mounting space for name plate
- 2) Valve LED
- 3a) sealing cap for manual override, not removable
- 3b) sealing cap for manual override, removable
- 4) captive seal and screw
- 5) Tightening torque for mounting screws: 0,25 Nm + 0,05
- 6) additional possibility of grounding




Round plug connector, Series CON-RD

- Socket Snap Ø8 3-pin with detent straight 180°
- open cable ends
- with cable
- unshielded



48 V AC/DC
IP65
0.25 mm ²
0.058 kg



Technical data

Part No.	Max. current	Number of wires	Cable-Ø	Cable length
8946016112	3 A	3	4.5 mm	2.5 m

Technical information

The specified protection class is only valid in assembled and tested state.

Technical information


Material	
Cable sheath	Polyvinyl chloride

Page 6 | AVENTICS



Dimensions


Dimensions



L = length

Pin assignments

Pin assignment, socket




(1) BN=brown(2) BK=black

(3) BU=blue



Adapter, Series CON-VP

- from form A to form C
- Socket, straight, 180°
- Plug, straight, 180°
- unshielded



Ambient temperature min./max.	-25 50 °C
Operational	42 V DC
voltage	
Protection class	IP65
Protection class	IP65
Weight	0.013 kg

Technical data


Part No.	Version	Max. current
8946053622	from form A to form C	0.5 A


Technical information

Material	
Housing	Polyamide

Dimensions

Dimensions





1) $\begin{vmatrix} \overline{z} \\ \overline{z} \\ 2 \\ 2 \\ 2 \\ 2 \end{vmatrix}$ 2)

1) contact as per DIN EN 175301-803, form A

2) contact as per DIN EN 175301-803, form C

Page 8 | AVENTICS



AVENTICS



Blanking plug, series CON-CB



Ambient temperature min./max.	-15 50 °C
Protection class	IP65
Weight	0.006 kg

Technical data


Part No.	Туре
5763500414	for series CD01-PL

Technical information

Material	
Housing	Polyoxymethylene

Dimensions

Dimensions





Protective cap



Weight

0.001 kg


Technical data

Part No.	Thread connection
8941350294	M12x1

Technical information

Material		
Housing	Polyamide	

Dimensions





Sealing cap for manual override

Weight



0.003 kg The delivered product may vary from that in the illustration.


Technical data

Part No.	Delivery unit
8980122904	10 piece

Technical information

laterial	
Housing	Polyamide

Dimensions



Efficient pneumatic solutions, our program: cylinders and drives, valves and valve systems, air supply management



Visit us: Emerson.com/Aventics

Your local contact: Emerson.com/contactus

- C Emerson.com
 - Facebook.com/EmersonAutomationSolutions
- in LinkedIn.com/company/Emerson-Automation-Solutions
 - Twitter.com/EMR_Automation

An example configuration is depicted on the title page. The delivered product may thus vary from that in the illustration. Subject to change. This Document, as well as the data, specifications and other information set forth in it, are the exclusive property of AVENTICS GmbH. It may not be reproduced or given to third parties without its consent. Only use the AVENTICS products shown in industrial applications. Read the product documentation completely and carefully before using the product. Observe the applicable regulations and laws of the respective country. When integrating the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that the products are subject to a natural process of wear and aging.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Brand logotype are registered trademarks of one of the Emerson family of companies. All other marks are the property of their respective owners. © 2017 Emerson Electric Co. All rights reserved. 2019-03



CONSIDER IT SOLVED