

1 **EU - TYPE EXAMINATION CERTIFICATE**

2 **Equipment or Protective System Intended for use in Potentially Explosive Atmospheres
Directive 2014/34/EU**

3 EU - Type Examination Certificate **Baseefa16ATEX0139X – Issue 1**
Number:

3.1 In accordance with Article 41 of Directive 2014/34/EU, EC-Type Examination Certificates referring to 94/9/EC that were in existence prior to the date of application of 2014/34/EU (20 April 2016) may be referenced as if they were issued in accordance with Directive 2014/34/EU. Supplementary Certificates to such EC-Type Examination Certificates, and new issues of such certificates, may continue to bear the original certificate number issued prior to 20 April 2016.

4 Product: **K5 and K7 Series Control Centre**

5 Manufacturer: **Topworx Incorporated**

6 Address: **3300 Fern Valley Road, Louisville, Kentucky, 40213
United States of America**

7 This re-issued certificate extends EC Type Examination Certificate No. **Baseefa16ATEX0139** to apply to product designed and constructed in accordance with the specification set out in the Schedule of the said certificate but having any variations specified in the Schedule attached to this certificate and the documents therein referred to.

8 SGS Fimko Oy, Notified Body number 0598, in accordance with Article 17 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this product has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of products intended for use in potentially explosive atmospheres given in Annex II to the Directive.

8.1 The original certificate was issued by SGS Baseefa Ltd (UK Notified Body 1180). It, and any supplements previously issued by SGS Baseefa Ltd have been transferred to the supervision of SGS Fimko Oy (EU Notified Body 0598). The original certificate number is retained.

The examination and test results are recorded in confidential Report No. **See Certificate History**

9 Compliance with the Essential Health and Safety Requirements has been assured by compliance with:

EN IEC 60079-0: 2018 EN 60079-11: 2012 EN 60079-31: 2014

except in respect of those requirements listed at item 18 of the Schedule.

10 If the sign “X” is placed after the certificate number, it indicates that the product is subject to the Specific Conditions of Use specified in the schedule to this certificate.

11 This EU - TYPE EXAMINATION CERTIFICATE relates only to the design and construction of the specified product. Further requirements of the Directive apply to the manufacturing process and supply of this product. These are not covered by this certificate.

12 The marking of the product shall include the following:

 **See Certificate Schedule**

SGS Fimko Oy Customer Reference No. **2191**

Project File No. **21/0357**

This document is issued by the Company subject to their General Conditions for Certification Services accessible at <http://www.sgs.com/en/Terms-and-Conditions.aspx>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained herein reflects the Company's findings at the time of their intervention only and within the limits of Client's instructions, if any. It does not necessarily indicate that the equipment may be used in particular industries or circumstances. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, schedule included, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

SGS Fimko Oy

Takomotie 8
FI-00380 Helsinki, Finland
Telephone +358 (0)9 696 361
e-mail sgs.fimko@sgs.com
web site www.sgs.fi

Business ID 0978538-5 Member of the SGS Group (SGA SA)



Mikko Välimäki
SGS Fimko Oy

13

Schedule

14

Certificate Number Baseefa16ATEX0139X – Issue 1

15 Description of Product

The K7 Series Control Centre comprises an aluminium or stainless steel enclosure containing up to two sets of terminal block, up to four voltage free switches or up to four certified proximity sensors in any combination and up to two solenoid valves activated by a rotary mechanism. The K5 Series Control Centre is of a similar construction to the K7 but is housed in a low profile enclosure. Both K5 & K7 versions may include an optional mechanical visual indicator. External electrical connections are made via up to four tapped holes.

Models of the equipment with a 'D' in the model number are gas and dust certified. The installation of the external connections and plugging of the unused entries in these variants must be carried out using appropriately certified IP6X cable glands and blanking plugs.

Other models of the equipment marked with a 'G' in the model number are only gas certified. The installation of the external connections and plugging of the unused entries in these variants must be carried out using appropriate cable glands and blanking plugs with a minimum ingress protection of at least IP20. These variants may also be optionally fitted with plug and socket connections fitted to the entries of the enclosure.

The following tables list the markings and parameters of the model covered by the certificate:

Models of the Gas & Dust Certified Rotary Drive K5 & K7 Series Control Centre containing up to four voltage free (VF) contacts and two solenoid valves are designated as follows:

Type C-M-D/** where /** defines which type of solenoid is fitted (see table 1)

No indicator or indicator $\leq 20\text{cm}^2$ surface area

	Ex ia IIC T6 Gb (-10°C \leq Ta \leq +40°C)
⊕ II 2 GD	Ex tb IIIC T85°C Db (-10°C \leq Ta \leq +40°C)
VF Contacts	$U_i = 28\text{V}$ $I_i = 120\text{mA}$ $P_i = 1.3\text{W}$ $C_i = 0$ $L_i = 0$
Each Solenoid	$U_i = **\text{V}$ $I_i = ***\text{mA}$ $P_i = **\text{W}$ $C_i = **$ $L_i = **$

Models of the Gas & Dust Certified Rotary Drive K5 & K7 Series Control Centre that contain up to four proximity sensors and two solenoid valves are designated as follows:

Type C-P-D/** where /** defines which type of solenoid is fitted (see table 1)

No indicator or indicator $\leq 20\text{cm}^2$ surface area

	Ex ia IIC T5 Gb (-10°C \leq Ta \leq +50°C)
⊕ II 2 GD	Ex tb IIIC T100°C Db (-10°C \leq Ta \leq +50°C)
	Ex ia IIC T6 Gb (-10°C \leq Ta \leq +40°C)
⊕ II 2 GD	Ex tb IIIC T85°C Db (-10°C \leq Ta \leq +40°C)
Each Sensor	$U_i = 15\text{V}$ $I_i = 50\text{mA}$ $P_i = 0.12\text{W}$ $C_i = 150\text{nF}$ $L_i = 550\mu\text{H}$
Each Solenoid	$U_i = **\text{V}$ $I_i = ***\text{mA}$ $P_i = **\text{W}$ $C_i = **$ $L_i = **$

Models of the Gas & Dust Certified Rotary Drive K5 & K7 Series Control Centre containing up to four proximity sensors NCB2-V3-N0 in the 2:1 mode (AC function), are designated as follows:

Type C-A-D/ where /** defines which type of solenoid is fitted (see table 1)**

No indicator or indicator $\leq 20\text{cm}^2$ surface area

	Ex ia IIC T5 Gb (-10°C \leq Ta \leq +50°C)				
⊕ II 2 GD	Ex tb IIIC T100°C Db (-10°C \leq Ta \leq +50°C)				
	Ex ia IIC T6 Gb (-10°C \leq Ta \leq +40°C)				
⊕ II 2 GD	Ex tb IIIC T85°C Db (-10°C \leq Ta \leq +40°C)				
Each Sensor	$U_i = 15\text{V}$	$I_i = 50\text{mA}$	$P_i = 0.12\text{W}$	$C_i = 200\text{nF}$	$L_i = 200\mu\text{H}$
Each Solenoid	$U_i = **\text{V}$	$I_i = ***\text{mA}$	$P_i = **\text{W}$	$C_i = **$	$L_i = **$

Models of the Gas & Dust Certified Rotary Drive K5 & K7 Series Control Centre that contain volt-free contacts, proximity sensors and two solenoid valves are designated as follows:

Type C-MP-D/ where /** defines which type of solenoid is fitted (see table 1)**

No indicator or indicator $\leq 20\text{cm}^2$ surface area

	Ex ia IIC T5 Gb (-10°C \leq Ta \leq +50°C)				
⊕ II 2 GD	Ex tb IIIC T100°C Db (-10°C \leq Ta \leq +50°C)				
	Ex ia IIC T6 Gb (-10°C \leq Ta \leq +40°C)				
⊕ II 2 GD	Ex tb IIIC T85°C Db (-10°C \leq Ta \leq +40°C)				
VF Contacts	$U_i = 28\text{V}$	$I_i = 120\text{mA}$	$P_i = 1.3\text{W}$	$C_i = 0$	$L_i = 0$
Sensor	$U_i = 15\text{V}$	$I_i = 50\text{mA}$	$P_i = 0.12\text{W}$	$C_i = 150\text{nF}$	$L_i = 550\mu\text{H}$
Solenoid	$U_i = **\text{V}$	$I_i = ***\text{mA}$	$P_i = **\text{W}$	$C_i = **$	$L_i = **$

Models of the Gas Only Certified Rotary Drive K5 & K7 Series Control Centre containing up to four voltage free (VF) contacts and two solenoid valves are designated as follows:

Type CC-M-G/ where /** defines which type of solenoid is fitted (see table 1)**

No indicator or indicator $\leq 20\text{cm}^2$ surface area

	Ex ia IIC T6 Gb (-10°C \leq Ta \leq +40°C)				
⊕ II 2 G					
VF Contacts	$U_i = 28\text{V}$	$I_i = 120\text{mA}$	$P_i = 1.3\text{W}$	$C_i = 0$	$L_i = 0$
Each Solenoid	$U_i = **\text{V}$	$I_i = ***\text{mA}$	$P_i = **\text{W}$	$C_i = **$	$L_i = **$

Models of the Gas Only Certified Rotary Drive K5 & K7 Series Control Centre that contain up to four proximity sensors and two solenoid valves are designated as follows:

Type CC-P-G/ where /** defines which type of solenoid is fitted (see table 1)**

No indicator or indicator $\leq 20\text{cm}^2$ surface area

	Ex ia IIC T5 Gb (-10°C \leq Ta \leq +50°C)				
⊕ II 2 G	Ex ia IIC T6 Gb (-10°C \leq Ta \leq +40°C)				
Each Sensor	$U_i = 15\text{V}$	$I_i = 50\text{mA}$	$P_i = 0.12\text{W}$	$C_i = 150\text{nF}$	$L_i = 550\mu\text{H}$
Each Solenoid	$U_i = **\text{V}$	$I_i = ***\text{mA}$	$P_i = **\text{W}$	$C_i = **$	$L_i = **$

Models of the Gas Only Certified Rotary Drive K5 & K7 Series Control Centre containing up to four proximity sensors NCB2-V3-N0 in the 2:1 mode (AC function), are designated as follows:

Type CC-A-G/ where /** defines which type of solenoid is fitted (see table 1)**

No indicator or indicator $\leq 20\text{cm}^2$ surface area

	Ex ia IIC T5 Gb (-10°C \leq Ta \leq +50°C)				
⊕ II 2 G	Ex ia IIC T6 Gb (-10°C \leq Ta \leq +40°C)				
Each Sensor	$U_i = 15\text{V}$	$I_i = 50\text{mA}$	$P_i = 0.12\text{W}$	$C_i = 200\text{nF}$	$L_i = 200\mu\text{H}$
Each Solenoid	$U_i = **\text{V}$	$I_i = ***\text{mA}$	$P_i = **\text{W}$	$C_i = **$	$L_i = **$

Models of the Gas Only Certified Rotary Drive K5 & K7 Series Control Centre that contain volt-free contacts, proximity sensors and two solenoid valves are designated as follows:

Type CC-MP-G/ where /** defines which type of solenoid is fitted (see table 1)**

No indicator or indicator $\leq 20\text{cm}^2$ surface area

⊕ II 2 G	Ex ia IIC T5 Gb (-10°C ≤ Ta ≤ +50°C)				
⊕ II 2 G	Ex ia IIC T6 Gb (-10°C ≤ Ta ≤ +40°C)				
VF Contacts	$U_i = 28\text{V}$	$I_i = 120\text{mA}$	$P_i = 1.3\text{W}$	$C_i = 0$	$L_i = 0$
Sensor	$U_i = 15\text{V}$	$I_i = 50\text{mA}$	$P_i = 0.12\text{W}$	$C_i = 150\text{nF}$	$L_i = 550\mu\text{H}$
Solenoid	$U_i = **\text{V}$	$I_i = **\text{mA}$	$P_i = **\text{W}$	$C_i = **$	$L_i = **$

Table 1 – Solenoid Types

	U_i	I_i	P_i	C_i	L_i
*****/01	18V	74mA	~	0	0.5mH
*****/02	28V	37mA	~	0	0.5mH
*****/03	30V	200mA	0.9W	0	0
*****/04	16V	330mA	~	0	0
*****/05	30V	330mA	~	0	0
*****/06	16V	840mA	~	0	0
*****/07	30V	840mA	~	0	0
*****/08	28V	300mA	1.6W	0	0

16 Report Number

See Certificate History

17 Specific Conditions of Use

- The cable glands used as entries to the enclosure must be suitably certified cable glands to the requirements of EN IEC 60079-0: 2018, including Annex A, with a minimum IP rating of IP6X in order to comply with the requirements of EN 60079-31: 2014.
- Any unused entries must be fitted with a suitably certified blanking plug certified to the requirements of EN IEC 60079-0: 2018 with a minimum IP rating of IP6X in order to comply with the requirements of EN 60079-31: 2014.

18 Essential Health and Safety Requirements

In addition to the Essential Health and Safety Requirements (EHSRs) covered by the standards listed at item 9, the following are considered relevant to this product, and conformity is demonstrated in the report:

Clause	Subject
1.2.7	LVD type requirements
1.2.8	Overloading of equipment (protection relays, etc.)
1.4.1	External effects
1.4.2	Aggressive substances, etc.

19 Drawings and Documents

New drawings submitted for this issue of certificate:

Number	Sheet	Issue	Date	Description
CERT-ES-09203-1*	1 of 10	AC	2023-10-05	K5L/K7L Control Centre – Ex ia Certification Label – II 2 GD
CERT-ES-09203-1*	2 of 10	AC	2023-10-05	K5L/K7L Control Centre – Ex ia Certification Label – II 2 G
CERT-ES-09203-1	3 of 10	AC	2023-10-05	K5L/K7L Control Centre – Ex ia Product with Optional Connectors
CERT-ES-09203-1	4 of 10	AC	2023-10-05	K5L/K7L Control Centre – Ex ia Enclosure Detail
CERT-ES-09203-1	5 of 10	AC	2023-10-05	K5L/K7L Control Centre – Ex ia Sensors
CERT-ES-09203-1	6 of 10	AC	2023-10-05	K5L/K7L Control Centre – Ex ia Circuit Detail
CERT-ES-09203-1	7 of 10	AC	2023-10-05	K5L/K7L Control Centre – Ex ia Typical Termination Label
CERT-ES-09203-1	8 of 10	AC	2023-10-05	K5L/K7L Control Centre – Ex ia Linear Drive Details
CERT-ES-09203-1	9 of 10	AC	2023-10-05	K5L/K7L Control Centre – Ex ia Indicator Options for Gas and Dust
CERT-ES-09203-1	10 of 10	AC	2023-10-05	K5L/K7L Control Centre – Ex ia Linear Drive

*These drawings are also common to BAS21UKEX0672X

No current drawings remained unaffected by this issue:

20 Certificate History

Certificate No.	Date	Comments
Baseefa16ATEX0139	17 January 2017	The release of the prime certificate. The associated test and assessment against the requirements of EN 60079-0: 2012 + A11: 2013, EN 60079-11: 2012 and EN 60079-31, Edition 2 is documented in ATEX Test Report 16(C)0386/2 and held with Project No. 16/0386.
Baseefa16ATEX0139X Issue 1	10 November 2023	This issue of the certificate confirms the current design meets the requirements of EN IEC 60079-0: 2018, EN 60079-11: 2012 and EN 60079-31, Edition 2 including the revision of the equipment marking in accordance with these standards. The test and assessment is documented in ATEX Test Report 21(C)0357/02 and held with Project No. 21/0357.
For drawings applicable to each issue, see original of that issue.		