



제2024-017388-01-1 호

안전인증서

ASCO Valve (Shanghai) Co., Ltd.

No.480 Xin Miao, No.3 Road Xin Qiao Town, Song Jiang District, Shanghai, 201612, China

위 사업장에서 제조하는 아래의 품목이 「산업안전보건법」 제84조 및 같은 법 시행규칙 제110조제1항에 따른 안전인증 심사 결과 안전·보건기준에 적합하므로 안전인증표시의 사용을 인증합니다.

품 목

Switchboxes

형식·모델(용량·등급) / 인증번호

DXP(Ex db IIC T6...T3 Gb) / 24-KA4BO-0260X

인증기준

고용노동부고시 제2021-22호

인증조건

1. 제조공장

·본 인증서는 'No.480 Xin Miao, No.3 Road Xin Qiao Town, Song Jiang District, Shanghai, 201612, China'에서 생산하는 제품에 한함.

2. 제품개요

·제품개요: 당 기기는 알루미늄으로 제작된 덮개와 베이스로 구성되어 있는 스위치박스임.
·제품정격: 250 V 이하, 15 A 이하, 10 W 이하
·사용주위온도: $-60\text{ }^{\circ}\text{C} \leq T_a \leq +60\text{ }^{\circ}\text{C}$ (T6) / $+75\text{ }^{\circ}\text{C}$ (T5) / $+110\text{ }^{\circ}\text{C}$ (T4) / $+175\text{ }^{\circ}\text{C}$ (T3)

3. 인증범위: 본 인증서는 위의 형식번호에 한하여 유효함.

4. 안전한 사용을 위한 조건

·화염접합면은 임의로 수리하지 말 것.
·당 기기는 이황화탄소 분위기가 형성된 곳에서 사용하지 말 것.
·사용하지 않는 케이블 인입부에는 KCS 인증받은 블랭킹 엘리먼트를 사용할 것.
·정전기 위험-사용설명서를 볼 것(용기 외부의 비금속 부품의 접촉에 주의).
·관련 IECEx 인증서(IECEx SIR 07.0093X issue No.18) 3 페이지 SPECIFIC CONDITIONS OF USE 참조

5. 인증(변경)사항: 없음.

6. 그 밖의 사항

·안전인증품의 품질관리, 확인심사 수검, 변경사항 신고 등 인증 받은 자의 의무 준수
·본 안전인증서는 반드시 관련 IECEx 인증서(IECEx SIR 07.0093X issue No.18)와 함께 사용할 것.

2024 년 04 월 22 일

한국산업기술시험원장





No. 2024-017388-01-1

안전인증서

Certificate of Safety

ASCO Valve (Shanghai) Co., Ltd.

No.480 Xin Miao, No.3 Road Xin Qiao Town, Song Jiang District, Shanghai, 201612, China

The following product manufactured by the above company has been authorized for the use of safety certification mark as the product has satisfied the safety and health requirements under Article 84 of OCCUPATIONAL SAFETY AND HEALTH ACT and paragraph 1 of Article 110 of ENFORCEMENT ORDINANCE OF the same ACT.

Electrical Equipment

Switchboxes

Model (Marking) / Certificate No.

DXP(Ex db IIC T6...T3 Gb) / 24-KA4BO-0260X

Applied standards

Announcement No. 2021-22 of Ministry of Employment and Labor

Conditions of Certification

1. Manufacturing location(s)

·This certificate is valid only for the specified products produced at 'No.480 Xin Miao, No.3 Road Xin Qiao Town, Song Jiang District, Shanghai, 201612, China'.

2. Description of equipment

·The switchbox comprises a rectangular base and cover manufactured in aluminium.
·Ratings: Max. 250 V, Max. 15 A, Max. 10 W
·Ambient Temperature: $-60\text{ }^{\circ}\text{C} \leq T_a \leq +60\text{ }^{\circ}\text{C}$ (T6) / $+75\text{ }^{\circ}\text{C}$ (T5) / $+110\text{ }^{\circ}\text{C}$ (T4) / $+175\text{ }^{\circ}\text{C}$ (T3)

3. Scope of certification: This certificate is valid only for the models as above.

4. Special conditions for safe use

·Do not repair the Flamproof joints arbitrarily.
·The enclosure are excluded from use in carbon disulphide atmospheres.
·The plugging of the unused entry must be carried out using KCs certified blanking components.
·WARNING - POTENTIAL ELECTROSTATIC CHARGING HAZARD - SEE INSTRUCTIONS.
·See Specific Conditions of Use on IECEx certificate(IECEx SIR 07.0093X issue No.18).

5. Details of certificate changes: None.

6. Details of the others

·Manufacturer shall take the responsibility including maintaining quality requirements for the certified products, receiving factory surveillance and informing any changes to the certified products.
·This certificate shall be used with the related IECEx certificate (IECEx SIR 07.0093X issue No.18).

Date of Issue: 2024-04-22

한국산업기술시험원장
KOREA TESTING LABORATORY

