

Config600 Compatibility Matrix

Config600 Configuration Software is constantly updated with new features available in new versions of the software. The Config600 version and S600+ binary.app version must be compatible to take advantage of all features present in new versions of the software.

Note

- For a description of the functionality in each version of binary.app, please refer to the version history file available on SupportNet.
- Use Config600 version 3.0 and the associated binary.app version when porting an S600 configuration to an S600+.
- A full system test is recommended after you perform a firmware upgrade.
- Binary.app version 06.30a or later requires either kernel file 2016, 2021, or later.

Table 1. Config600 Compatibility Matrix

Config600 Version	Binary.app Version	Main Changes (see respective release notes for further details)
Version 3.0		
3.0.3.0	06.04	First S600+ release.
	06.09 (all variants)	
	06.09p (Gas and Liquid MID)	Totalisation fix.
3.0 (all variants)	06.09q (Gas and Liquid MID)	Edge browser support, fix for missing periodic reports, various bug fixes.
	06.09r (Gas and Liquid MID)	Fix for internal timer rollover (affecting web server, flowing time and totals integration over time).
Version 3.1		
3.1.0.0	06.13	Weighted mode for ADC, Hart, PRT / TCPIP firewall. Aramco reporting.
3.1.1.7	06.13	Bug fixes.
3.1.1.8	06.13	NORSOK statistical proving.
3.1.1.9	06.13	Bug fixes.

Config600 Compatibility Matrix

D301853X012

October 2024

Config600 Version	Binary.app Version	Main Changes (see respective release notes for further details)
3.1 (all variants)	06.13a	Totalisation fix. Microsoft Edge browser support, fix for missing periodic reports.
	06.13b	Fix for internal timer rollover (affecting web server, flowing time and totals integration over time).
Version 3.2		
3.2.0.5	06.20	AGA3 2012, NORSOK WIO, network printing. CFX reports.
3.2.0.9	06.20	CFX user interface.
3.2.1.0	06.21	CFX licensing.
3.2.2.0	06.21	Stop Windows 7 crashing.
3.2.3.0	06.21	Bug fixes.
3.2.4.0	06.21 (all variants)	Bug fixes.
3.2.5.0	06.22 (all variants)	Aramco prover history now supports FRN and MFB on a product basis. Aramco batching now copies the selected product table settings from the selected product table after a cold start.
3.2.6.0	06.24 (all variants)	IAPWS-IF97.
3.2.8.0	06.25	Installation location change for permissions issues. Addition of ISO17089 for Daniel USM.
3.2 (all variants up to and including 3.2.8)	06.25a	Totalisation fix, Microsoft Edge browser support, fix for missing periodic totals.
	06.25b	Fix for internal timer rollover (affecting web server, flowing time and totals integration over time).
3.2.9.0	06.26 (Liquid MID)	Aramco reports layout (batching, proving), GOST check sum.
	06.26a (Liquid MID)	Optimize memory allocation for reports, select start or end timestamp for reports, check for big increments.
3.2.9.1	06.26b (all variants)	Fix message queue issue when constant log printed from front panel.
	06.26b (Liquid MID)	
3.2.9 (all variants)	06.28a	Totalisation fix.

Config600 Version	Binary.app Version	Main Changes (see respective release notes for further details)
	06.28b (Gas and Liquid MID)	Fix for internal timer rollover (affecting web server, flowing time and totals integration over time). Microsoft Edge browser support. Various bug fixes.
Version 3.3		
3.3.0.0	06.27	AGA8 Part 1 2017, ISO6976 2016.
	06.28a	Totalisation fix.
3.3.1.0	06.28 (Gas and Liquid MID)	AGA8 Part 2 2017, support for liquid CALDON meters.
	06.28a (Gas and Liquid MID)	Totalisation fix.
	06.28b (Gas and Liquid MID)	Fix for internal timer rollover (affecting web server, flowing time and totals integration over time). Microsoft Edge browser support. Various bug fixes.
3.3.2.0	06.29	Totalisation fix / Coriolis fixes and additional atmospheric / base pressure.
3.3.3.0	06.30	Secondary engineering units, gas meter proving (AGA 6), station dual gas chromatographs, serial to pulse auto switchover for gas and liquid ultrasonic meters, IAPWS-IF97 phase options for water and steam.
3.3.5.0	06.30a	Microsoft Edge browser support, addition of gateway for second Ethernet port, fix for missing periodic reports, various bug fixes.
	06.30b (Gas and Liquid MID)	Fix for slow web browser, various bug fixes.
	06.30c (Gas and Liquid MID)	Fix for internal timer rollover (affecting web server, flowing time and totals integration over time).
3.3.6.0	06.31	TFWA x 12 configuration option, Wobbe Index for gas calculations, GPA2172-09 (ASTM-D3588) SUP/INF calculation at 14.65 psia, various bug fixes.
Version 3.4		
3.4.0.0	06.32	Added support for 6-path Gas Ultrasonic (Elster Qsonic Plus) and 8-path Gas Ultrasonic meters (FlowSic600-XT and

Config600 Compatibility Matrix

D301853X012

October 2024

Config600 Version	Binary.app Version	Main Changes (see respective release notes for further details)
		Rosemount). Improved exback functionality. Added daily and monthly tabular reports. Added support for Southern hemisphere DST. Various bug fixes.
	06.32a	Various bug fixes.
	06.32b (Gas and Liquid MID)	Fix for internal timer rollover (affecting web server, flowing time and totals integration over time).
Version 3.5		
3.5.0.0	06.34	Updates for Aramco Gas Proving Reports. Added webserver enhancements. Added support for AGA5 Mass HV. Changed to use InstallShield for Config600. Various bug fixes.
3.5.0.1	06.34	Fix for Config600 installer.
3.5.1.0	06.34a	Various bug fixes for tabular reports, Gas local KF Selection, Calc explorer, Batch recalculation using CTSm / CPSm. Removal of Remote access functionality

For customer service and technical support, visit [Emerson.com/Guardian](https://www.emerson.com/Guardian).

North America and Latin America:

Emerson Energy and Transportation
Solutions
6005 Rogerdale Road
Houston, TX 77072 U.S.A.
T +1 281 879 2699 | F +1 281 988 4445
[Emerson.com/SCADAforEnergy](https://www.emerson.com/SCADAforEnergy)

United Kingdom:

Emerson Process Management Limited
Fosse House, 6 Smith Way
Grover Park, Enderby
Leicester LE19 1SX UK
T +44 0 870 240 1987

Europe:

Emerson S.R.L
Regulatory Compliance Shared Services
Department
Company No. J12/88/2006
Emerson 4 Street
Parcul Industrial Tetarom 11
Romania
T +40 374 132 000

Middle East/Africa:

Emerson Energy and Transportation
Solutions
Emerson FZE
P.O. Box 17033
Jebel Ali Free Zone – South 2
Dubai U.A.E.
T +971 4 8118100 | F +971 4 8865465

Asia-Pacific:

Emerson Energy and Transportation
Solutions
1 Pandan Crescent
Singapore 128461
T +65 6777 8211 | F +65 6777 0947

© 2018–2024 Bristol Inc. All rights reserved.

This publication is for informational purposes only. While every effort has been made to ensure accuracy, this publication shall not be read to include any warranty or guarantee, express or implied, including as regards the products or services described or their use or applicability. Bristol Inc. (hereinafter “Energy and Transportation Solutions” or ETS) reserves the right to modify or improve the designs or specifications of its products at any time without notice. All sales are governed by ETS terms and conditions which are available upon request. ETS accepts no responsibility for proper selection, use or maintenance of any product, which remains solely with the purchaser and/or end-user. Emerson and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.