

Electric gripper GE

GE-25-P



Table of contents: GE

Electric gripper GE-25-P	Page
GE-25-P	285


Electric gripper GE

GE-25-P



13

- Compact design
- Fast reaction/cycle times
- Highest performance density





GE-25-P	
Attachment grid	20 mm
Attachment thread	M3
Operating temperature (min./max.)	5 - 55 °C
Storage temperature	5 - 55 °C
Humidity	< 90 %

Type	GE-25-P
Order number	50538537
Jaw stroke	2 x 3 mm
Net weight	0.11 kg
Recommended workpiece weight	0.2 kg
Gripping force min. 100%	40 N
Gripping force max. 50%	20 N
Max. admissible finger length	32 mm
Max. admissible mass per finger	0.02 kg
Closing/opening time	0.09/0.09 sec.
Noise level	< 70 dB(A)
Protection class IP (mechanical)	30
Protection class IP (electrical)	40
Repeat accuracy	+/- 0.02 mm
Supply voltage (min./max.)	21.6 / 26.4 VDC
Rated current	0.14 A
Min. supply current (power supply)*	1.0 A
Max. current input**	1 A
Current input in blocked state***	0.07 / 0.14 A
Controller electronics	integrated
Communication interface	digital inputs
Number of digital I/O	2/-
Mounting position	

* minimum supply current for reliable operation of product.

** maximum current input in the acceleration phase (max. t = 50 ms).

*** Current input in blocked state (in gripper end position or while gripping a workpiece) with active command „OpenGripper“ or „Close Gripper“.

Cleanroom class ISO 14644-1, class ISO 7

Included in the delivery

(Catalogue HT accessories)


- 2x Centering bushing Ø5x2.5
- 2x Special screw M3x23 5/6

Accessories

(Catalogue HT accessories)











- Sensor-actuator cable-S3
- INI d4x25-Sn1.0-PNP-NC-M8x1
- INI d4x25-Sn1.0-PNP-NO-M8x1

ES20	1 3 1,3	< direct > VP 107 VP 151	1 1 2
SA-1	1,2 1,2	< direct > VP 101	1 2
RE-50	3 3	VP 107 VP 151	1 2
SREH-50	3 3	direct VP 151	1 2
RA-40	3	VP 50486393 50596647*	1,2
CS 8	1,3 1,3	< direct > VP 101	1 2
CS 12	1,3 1,3	VP 107 VP 151	1 2
CS 16	1,3 1,3	VP 107 VP 151	1 2
LM 12	1	VW 305	1
LM 16	1	VW 305	1
CR 12	3 3	< direct > VP 151	1 2
CR 16	3 3	< direct > VP 151	1 2




* Verbindungskabel
/ Câble de connexion
/ Connection cable

Mounting areas

CS, ES	LM	HM	SA	UG, GM, SG, DG, PG, GE, SGE
				
PMP, PMP-c	PEZ, PDZ	PEL, PDL	RM, RE	CR, RM 32, RE, SREH, RA
				


Note that there might be different mounting positions from one module to another one.
The required connection elements and the range of support columns are depicted in the catalogue HT accessories.

Type	GE-25-P
Max. static torque M_x	0.50 Nm
Max. static torque M_y	0.42 Nm
Max. static torque M_z	1.50 Nm
Max. static force F_z	70 N




Gripping force diagrams

Gripping force diagram (GE-25-P 50%)



Gripping force diagram (GE-25-P 100%)



Maximum permissible cantilever

