

GMX-L20A 4000W


Overview

Emerson's Branson™ Ultraweld® L20 system is designed and built to assure you the highest degree of reliability and weld quality.

Emerson is the world leader in ultrasonic metal joining through our portfolio of Branson products. We have partnered with industries in many markets including photovoltaic, medical, automotive, battery, refrigeration, electrical and appliance. Our many years of experience have given us a broad base of applications knowledge.

Ultrasonic metal welding provides our customers with a sound solution, superior performance, improved throughput, and reduced maintenance.

Branson welding systems are designed and built to ensure the highest degree of reliability and weld quality.



Key features

- **Precision roller bearing slide** assures smooth operation and extreme accuracy.
- **Precise adjustments** for accurate setting of both upper and lower positive stops.
- **Dovetail mounting** allows quick change fixturing.
- **Solid steel horns** for fast set up and minimum tooling cost—or- Titanium horns with economical replaceable tips.
- **Optional vortex cooling** allows high-speed operation without heat buildup.

ADVANTAGES OF ULTRASONIC WELDING	
Process control	Ultrasonic welding monitored through time, energy, power and height limits
Cost and environmental savings	Elimination of consumables such as solder, flux, crimp connectors and braze materials
Speed	Typical weld cycles under 0.5 seconds
Low operating costs	Less than 1/30 of the energy of resistance welding
Tool life	Precision machined, multi-lobe tools manufactured with high-quality tool steel provide long life, simple setup and precise weld accuracy
Insulation dispersal	In most cases, high frequency scrubbing action eliminates the need to pre-clean parts or strip insulation from magnet wire
Low operating temperature	Minimal heat generation, therefore metal parts will not anneal and there is no need for cooling water
Automation potential	Efficient size, minimal maintenance and orientation flexibility make Branson ultrasonic equipment the best choice for automatic assembly

For more information:
www.Emerson.com/Branson

BRANSON™







GMX-L20 Series

Specifications

SPECIFICATIONS	
Frequency	20kHz
Compressed air	80 psi (5.5 bar) clean, dry air


Power	Nominal AC Input	Current Rating
4.0kW	200-230V, 50-60 Hz, Single Phase	25 Amp Max.@200V / 25 Amp fuse



Features

Attribute	GMX-L20A
Connectivity	Ethernet 1000/100/10 Mbps for direct Branson Insights connection with MES
	Recipe remote recall via Ethernet
OS System	Industry Leading real-time OS
UI App	Modern & Smart design user-friendly
Time to start	Fast cycle start up
Display	7" Polychrome, capacitive LCD
	Optional for extended display (additional monitor)
Result Display	3 Graphs by Power, Height, Frequency
Language	Multiple Languages
Actuator	Optimized pneumatics for better safety
Height Encoder	Digital encoder, 5µm resolution, covers full cylinder stroke
Height Calibration	Simplified process with accuracy correction

Examples of HMI Screens & Recipes



The Emerson logo is a trademark and service mark of Emerson Electric Co. Branson logotype are registered trademarks of one of the Emerson family of companies. All other marks are the property of their respective owners. © 2023 Emerson Electric Co. All rights reserved.