


ANDERSON GREENWOOD AMAL LIR/LIRE FLAME ARRESTERS

In-line deflagration flame arresters designed to prevent the propagation of subsonic flames.



FEATURES

- Concentric and eccentric model variants available.
- Fabricated housings.
- Advanced crimped stainless steel element construction as standard. Other materials available.
- Mounted vertically or horizontally.
- Uni-directional.
- Can be used in combination with a Marvac pressure/vacuum valve.
- Independently tested and certified.
- Manufactured to ISO 9001:2015.

GENERAL APPLICATION

The Types LIR/LIRE are used in applications with subsonic flames and mounted in process or vent lines. They can be located in the pipeline or at the end of the pipe vent.

TECHNICAL DATA

Materials:	Carbon steel, stainless steel
Sizes:	DN 6 to 400 (1/8" to 16")
Connections:	Threaded, flanged or plain
Temperature range:	-20 to 165°C (-4 to 329°F)
Gas groups:	IIA, IIB1, IIB2, IIB3, IIB, IIC ¹⁾
Certification:	ATEX Directive 2014/34/EU; PED 2014/68/EU; ISO 16852

1. Up to and including DN 150 (6")

ANDERSON GREENWOOD AMAL LIR/LIRE FLAME ARRESTERS

MATERIALS AND CONNECTION OPTIONS

Materials

Carbon steel and stainless steel.

Connection pipe size

Threaded DN 6 to 80 (1/8" to 3")
 Flanged DN 15 to 400 (1/2" to 16")
 Plain DN 20 to 150 (3/4" to 6")


Gas groups

- IIA
- IIB1
- IIB2
- IIB3
- IIB
- IIC¹⁾


NOTE

Accessories, special materials and connections are available on request.

TYPE LIR FLANGED²⁾ (LF VERSION)



TYPE LIR SCREWED (LR VERSION)



TEMPERATURE RANGE

Type	Connection	Gas group	Size range	Short burn	Max. temperature	Element
LIR/LIRE	Flanged	IIA	DN 12 to 400	Yes	-20/60°C [-4/140°F]	1 x 0.8 mm [0.039 x 0.031"]
LIR/LIRE	Flanged	IIB1/IIB3	DN 12 to 400	Yes	-20/60°C [-4/140°F]	1 x 0.8/0.6 mm [0.039 x 0.031/0.024"]
LIR/LIRE	Flanged	IIB	DN 12 to 400	Yes	-20/60°C [-4/140°F]	1 x 0.45 mm [0.039 x 0.018"]
LIR/LIRE	Flanged	IIC	DN 12 to 400	Yes	-20/60°C [-4/140°F]	1 x 0.15 mm [0.039 x 0.006"]
LIR/LIRE	Flanged	IIA	DN 12 to 400	No	-20/165°C [-4/329°F]	1 x 0.6 mm [0.039 x 0.024"]
LIR/LIRE	Flanged	IIB1/IIB3	DN 12 to 400	No	-20/165°C [-4/329°F]	1 x 0.38 mm [0.039 x 0.015"]
LIR/LIRE	Flanged	IIB	DN 12 to 400	No	-20/165°C [-4/329°F]	1 x 0.3 mm [0.039 x 0.012"]
LIR/LIRE	Flanged	IIC	DN 12 to 500	No	-20/165°C [-4/329°F]	1 x 0.15 mm [0.039 x 0.006"]
LIR	Screwed	IIA	DN 6 to 40 (1/8" to 1 1/2")	Yes	-20/60°C [-4/140°F]	1 x 0.8 mm [0.039 x 0.031"]
LIR	Screwed	IIB1/IIB3	DN 6 to 40 (1/8" to 1 1/2")	Yes	-20/60°C [-4/140°F]	1 x 0.8/0.6 mm [0.039 x 0.031/0.024"]
LIR	Screwed	IIB	DN 6 to 40 (1/8" to 1 1/2")	Yes	-20/60°C [-4/140°F]	1 x 0.45 mm [0.039 x 0.018"]
LIR	Screwed	IIC	DN 6 to 40 (1/8" to 1 1/2")	Yes	-20/60°C [-4/140°F]	1 x 0.15 mm [0.039 x 0.006"]
LIR	Screwed	IIA	DN 6 to 40 (1/8" to 1 1/2")	No	-20/165°C [-4/329°F]	1 x 0.6 mm [0.039 x 0.024"]
LIR	Screwed	IIB1/IIB3	DN 6 to 40 (1/8" to 1 1/2")	No	-20/165°C [-4/329°F]	1 x 0.38 mm [0.039 x 0.015"]
LIR	Screwed	IIB	DN 6 to 40 (1/8" to 1 1/2")	No	-20/165°C [-4/329°F]	1 x 0.3 mm [0.039 x 0.012"]
LIR	Screwed	IIC	DN 6 to 40 (1/8" to 1 1/2")	No	-20/165°C [-4/329°F]	1 x 0.15 mm [0.039 x 0.006"]

NOTES

All sizing and selection must be conducted by the factory.

Standard elements are double the pipe size.

1. Only available up to and including DN 150 (6")

2. Eccentric variants are available.

ANDERSON GREENWOOD AMAL LIR/LIRE FLAME ARRESTERS

SELECTION GUIDE

Example:	LIR	50	LF	100	19	60	S3	S3
Model								
LIR								
LIRE								
Connection diameter								
Threaded								
DN 6 to 40 (1/8" to 1 1/2") - Type LIR only								
DN 50 to 80 (2" to 3")								
DN 20 to 50 (3/4" to 2") - Type LIR only								
Flanged								
DN 15 to 400 (1/2" to 16")								
DN 20 to 50 (3/4" to 2")								
Plain								
DN 20 to 150 (3/4" to 6") - Type LIR only								
Element code								
LF								
Element diameter								
DN 25 to 50 (1" to 2")								
DN 40 to 600 (1 1/2" to 24")								
DN 50 to 300 (2" to 12")								
Element width								
19 19 mm (0.75")								
38 38 mm (1.5")								
76 76 mm (3.0")								
Cell height								
80 0.80 mm (0.032")								
60 0.60 mm (0.024")								
45 0.45 mm (0.018")								
38 0.38 mm (0.015")								
15 0.15 mm (0.006")								
Element material								
S3 Stainless steel								
C Carbon steel								
Body material								
S3 Stainless steel								
C Carbon steel								

VCTDS-03783-EN © 2017, 2023 Emerson Electric Co. All rights reserved 09/23. Anderson Greenwood is a mark owned by one of the companies in the Emerson Automation Solutions business unit of Emerson Electric Co. The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are property of their respective owners.

The contents of this publication are presented for informational purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.

Emerson Electric Co. does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any Emerson Electric Co. product remains solely with the purchaser.

Emerson.com