

1

2

3

A


A

B

B

C

C



- 03 L0 = ROUTING DISTANCE FROM 2240 FLANGE TO LEAK TEMPERATURE SENSOR ELEMENT, WHERE SLACK IS TYPICALLY 2000mm
- 02 614 MINIMUM/SMALLEST POSSIBLE BENDING RADIUS = 100mm
- 01 2240 MOUNTED ON CONICAL CONNECTION OR REMOTE JUNCTION BOX

ISSUED BY TP-HH		DRAWN WEEK 1917	PRODUCT CODE 5900	 LAYOUTVAGEN 1, 435 33 MÖLNLYCKE, SWEDEN
APPROVED BY TT-CH		APP'D WEEK 1917	DOCUMENT TYPE 02	
ORIGINAL DRAWING NO. 9261085-036	SIZE A3	1 ST ANGLE 	SCALE 1:1	INSTALLATION DRAWING TITLE GENERAL ARRANGEMENT COOL DOWN TEMP. SENSORS
CAD MAINTAINED, (ACAD)		DO NOT SCALE PRINT		DRAWING NO. 9261085-036
THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN				ISSUE 03
				SHEET 1/1

1

2

3

INST DWG A3 120605

2019-06-25 Electronic Master - Printed Copies Uncontrolled - Emerson Proprietary