


BOX REMOTE SIDE VIEW



1 DRILL PATTERN FOR MOUNTING OF THE DISPLAY UNIT AT PLATE SUPPLIED BY CUSTOMER. FOUR M4 SCREWS ARE REQUIRED. MAXIMUM DEPTH OF HOLES IS 10mm. 4 PCS M4X12 SUPPLIED BY RTR.

	GU-CK APPROVED BY GST-TK	MEEN	PRO/5600 original dwg no. 9150074—		ACAD SCALE	MECH/ 2210	ANICAL DISPLY	INSTALL UNIT /	ATION D RDU 40)WG)	
	ROSE	MO	UNT'	1 ST /	NGLE	DOC TYPE		0074-	·921	ISSUE 3	SHEET 1 /1
THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS.THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN.											

INSTALLATION DRAWING TITLE