



1 **EU-TYPE EXAMINATION CERTIFICATE**

2 Equipment intended for use in Potentially Explosive Atmospheres Directive 2014/34/EU

3 Certificate Number: **Sira 16ATEX1158X** Issue: **6**

4 Equipment: **CT5100 Laser Gas Analyser**

5 Applicant: **Emerson Process Management Limited**

6 Address: **2 Hunt Hill
Cumbernauld
Glasgow, G68 9LF**

7 This equipment and any acceptable variation thereto is specified in the schedule to this certificate and the documents therein referred to.

8 CSA Group Netherlands B.V., notified body number 2813 in accordance with Articles 17 and 21 of Directive 2014/34/EU of the European Parliament and of the Council, dated 26 February 2014, certifies that this equipment has been found to comply with the Essential Health and Safety Requirements relating to the design and construction of equipment intended for use in potentially explosive atmospheres given in Annex II to the Directive.

The examination and test results are recorded in the confidential reports listed in Section 14.2.

9 Compliance with the Essential Health and Safety Requirements, with the exception of those listed in the schedule to this certificate, has been assured by compliance with the following documents:

EN IEC 60079-0:2018 EN 60079-1:2014 EN 60079-2:2014 EN 60079-11:2012
EN 60079-28:2015

10 If the sign 'X' is placed after the certificate number, it indicates that the equipment is subject to Specific Conditions of Use identified in the schedule to this certificate.

11 This EU-Type Examination Certificate relates only to the design and construction of the specified equipment. If applicable, further requirements of this Directive apply to the manufacture and supply of this equipment.

12 The marking of the equipment shall include the following:



II 3 (1) G
Ex db ia op is pzc [ia Ga] IIC T3 Gc
Tamb = -20°C to +55°C

Signed: M Halliwell

Title: Director of Operations



Project Number 80122741

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE


EU-TYPE EXAMINATION CERTIFICATE

Sira 16ATEX1158X

Issue 6

13 DESCRIPTION OF EQUIPMENT

The CT5100 laser gas analyser and monitoring system consists of two metal enclosures, the upper enclosure being a naturally ventilated stainless steel structure with an aluminium top plate, housing the gas sampling chamber and the lower enclosure being a sealed stainless steel enclosure with approximate dimensions 406mm x 516mm x 295mm and an internal volume of 40 litres. The upper enclosure has no IP rating and the lower an IP66 rating, achieved with silicone and Viton seals.



The lower enclosure is the only pressurized part of the equipment, this contains the electronics, purge controller and local control system (HMI). The enclosure has a hinged door in the front and gland plates on the upper and lower sides. Apertures have been made in the front entry panel for mounting of the HMI and purge controller interfaces. The enclosure is fitted with two small glass windows on the upper gland plate to allow exit and entry of the laser beam, both windows being completely covered by a bolted metallic assembly containing a mirror. The glass windows are fitted into individual metal housings and form part of the lower, pressurized enclosure.

The upper enclosure contains a gas sampling cell into which the sampled atmosphere is introduced by fixed pipes. The upper enclosure and sampling cell are not pressurized. Attached to the gas sampling cell is a certified flameproof heater and a certified pressure transducer.

Electronics Enclosure

The electronics enclosure uses the purge and pressurisation protection method. It houses one 12V and one 24V power supply, the purge controller, Human-Machine Interface (HMI), IS barriers, terminals, relays and various electronic modules and boards.

The HMI and purge controller both have touchscreen displays for user operation, which penetrate the main enclosure and are mounted using the OEM supplied sealing arrangement. The HMI and purge controller are both pre-certified.

Ratings

100-120/250Vac, 50-60Hz, single phase, 600W.

Project Number 80122741

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE

EU-TYPE EXAMINATION CERTIFICATE

Sira 16ATEX1158X
Issue 6

Variation 1 - This variation introduced the following changes:

- i. An alternative cell assembly arrangement was permitted to allow a laser path length of 15 metres.
- ii. A change of sealing material on the gas line bulkhead assembly was authorised.
- iii. The addition of Velcro flaps to the cell insulation jacket is approved.
- iv. Changes to nameplate drawing to consolidate markings for ATEX, IECEx and North America was acknowledged.

Variation 2 - This variation introduced the following changes:

- i. To permit the introduction of an alternative cell assembly arrangement to allow laser path lengths of 0.2 metres and 2 metres.
- ii. To permit the removal of intermediate terminal wiring to the purge controller. All designs being directly wired to the purge controller.
- iii. To permit the introduction of alternative electrical components in the purged enclosure.
- iv. To permit the introduction of an alternative seal material for the cell assembly.
- v. To permit the introduction of an alternative PT100 fitting for the cell assembly.
- vi. To permit the introduction of an alternative marking label, which removes markings from the certification outside the scope of the ATEX certification.
- vii. The recognition of minor drawing modifications, including; additional detail, detail re-named and amended notes. These amendments are administrative or involve changes to the design that do not affect the aspects of the product that are relevant to explosion safety.

Variation 3 - This variation introduced the following changes:

- i. Recognise the Intrinsically safe modules in the CT5100 Laser Gas Analyser and carry out an IS assessment of the modules. Subsequently the IS standard, EN 60079-11:2012 was added and the marking was amended to include IS marking.
- ii. The IS pressure sensor, 'BD Sensor DMP331P' was removed.
- iii. The PT100 sensor on the top enclosure has been removed out of scope of this certificate and to permit connection to a suitable temperature sensor, the following IS parameters have been declared for the connections emerging from the purged enclosure.

$$U_o = 12.4V \quad I_o = 17.4mA \quad P_o = 54mW \quad C_i = 0 \quad L_i = 0$$

The capacitance and either the inductance or L/R of the load connected to hazardous area terminals of the apparatus must not exceed the following values for Group IIC:

$$\text{Capacitance} = 1.24\mu F, \text{ Inductance} = 117 \text{ mH and L/R ratio} = 597 \mu H/\text{ohm}.$$

The above parameters apply when one of the two conditions below is given:

- The total L_i of the external circuit (excluding the cable) is $< 1\%$ of the L_o value or
- The total C_i of the external circuit (excluding the cable) is $< 1\%$ of the C_o value.

The above parameters are reduced to 50% when both of the two conditions below are given:

- The total L_i of the external circuit (excluding the cable) is $\geq 1\%$ of the L_o value or
- The total C_i of the external circuit (excluding the cable) is $\geq 1\%$ of the C_o value.

Note : the reduced capacitance of the external circuit(including cable) shall not be greater than 600nF for Group IIC.

Project Number 80122741

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE

EU-TYPE EXAMINATION CERTIFICATE

**Sira 16ATEX1158X
Issue 6**

Variation 4 - This variation introduced the following change:

- i. The certificate holder and manufacturer's name and address were changed:

From:	To:
Cascade Technologies Ltd	Emerson Process Management Limited
Glendevon House	2 Hunt Hill
Castle Business Park	Cumbernauld
Stirling Scotland, FK9 4TZ	Glasgow, G68 9LF

Variation 5 - This variation introduced the following change:

- i. Following appropriate assessment to demonstrate compliance with the requirements of the latest standards, EN 60079-0:2012/A11:2013 and EN 60079-1:2007 are replaced with EN IEC 60079-0:2018 and EN 60079-1:2014. As a result, the marking was changed.
- ii. Removal of label drawing M-1000-2539.
- iii. Acknowledgement of use of suitably certified cable entry devices. As a result, the Specific Conditions of Use were changed.
- iv. Minor drawing modifications.
- v. It was noted that the certificate was on an incorrect template, this has resulted in the certificate being updated from a 'Type Examination Certificate' to a 'EU-Type Examination Certificate'.
- vi. A Condition of Manufacture regarding incorporated previously certified equipment/component was introduced retrospectively.

14 DESCRIPTIVE DOCUMENTS

14.1 Drawings

Refer to Certificate Annexe.

14.2 Associated Reports and Certificate History

Issue	Date	Report number	Comment
0	25 January 2017	R70044219A	The release of the prime certificate.
1	19 July 2017	R70133344A	The introduction of Variation 1.
2	13 March 2019	R70204981A	The introduction of Variation 2.
3	15 October 2019	0840	Transfer of certificate Sira 16ATEX1158X from Sira Certification Service to CSA Group Netherlands B.V.
4	06 January 2020	R80000620A	The introduction of Variation 3.
5	01 April 2022	R80107020A	The introduction of Variation 4.
6	30 June 2022	R80122740A	The introduction of Variation 5.

15 SPECIFIC CONDITIONS OF USE (denoted by X after the certificate number)

- 15.1 The purge controller keypad mounted on the front of the equipment shall not be exposed to direct UV light sources or direct sunlight. Example methods of protection include, but are not limited to, indoor applications away from UV sources and outdoor locations under shading. As part of regular inspections, if damage to or deterioration of the membrane keypad is detected the unit is to be taken out of service for repair or replacement.

Project Number 80122741

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE

EU-TYPE EXAMINATION CERTIFICATE

Sira 16ATEX1158X
Issue 6

- 15.2 The purge controller bypass function shall only be enabled during setup or maintenance and only when the area is known to be non-hazardous.
- 15.3 The equipment shall be installed in an area of not more than pollution degree 2 as defined in EN 60664-1.
- 15.4 The CT5100 purge controller automatically monitors the internal pressure of the enclosure and will output any fault conditions onto contact K2. It is the responsibility of the end user to connect this contact to a suitable facility such as an alarm, indicator or an automatic shutdown system.
- 15.5 For correct operation the on-site pressurising air supply must be capable of providing at least 25 l/min for leakage compensation.
- 15.6 The equipment shall be installed and operated only in an environment of overvoltage category II or better according to IEC 60664-1.
- 16 **ESSENTIAL HEALTH AND SAFETY REQUIREMENTS OF ANNEX II (EHSRs)**
The relevant EHSRs that are not addressed by the standards listed in this certificate have been identified and individually assessed in the reports listed in Section 14.2.
- 17 **CONDITIONS OF MANUFACTURE**
- 17.1 The use of this certificate is subject to the Regulations Applicable to Holders of CSA Group Netherlands B.V. certificates.
- 17.2 Holders of EU-Type Examination Certificates are required to comply with the conformity to type requirements defined in Article 13 of Directive 2014/34/EU.
- 17.3 The purge controller shall exhibit the following characteristics:
- Maintain an overpressure of ≥ 0.5 mbar within the purged enclosure.
 - Purge with air or any suitable inert gas for a duration of at least 2 minutes 30 seconds at a flow rate of at least 280 L/min before energisation.
 - Prevent the internal overpressure exceeding 10 mbar.
 - In addition, the manufacturer shall take all reasonable steps to ensure that the user/installer complies with any restrictions and special conditions for certification associated with the purge controller; they shall also provide an appropriate copy of the certificate that is applicable to the device.
- 17.4 The system comprising the CT5100 laser gas analyser and the installed purge controller shall be tested by the manufacturer after assembly to check the operation of all features necessary for safe use, particularly:
- Under pressure - The low pressure switch shall operate if the enclosure overpressure falls below the minimum specified above.
 - Purge flow failure - The purging system (including the timer) shall reset to the beginning of the purge cycle if the purging air flow rate (measured at the outlet) falls below the minimum specified above.
 - Supply pressure failure - The low pressure switch shall operate when or before the enclosure overpressure falls below the minimum specified above.

Project Number 80122741

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands



SCHEDULE

EU-TYPE EXAMINATION CERTIFICATE

Sira 16ATEX1158X
Issue 6

- 17.5 Each CT5100 laser gas analyser shall be subjected to a routine overpressure test of 15 mbar for a period of 2 min ± 10 s, in accordance with Clause 16.2 of EN 60079-2:2014. There shall be no permanent deformation.
- 17.6 Each CT5100 laser gas analyser shall be subjected to a routine leakage test, in accordance with Clause 16.3 of EN 60079-2:2014. The leakage flow rate shall not exceed 25 litre/min.
- 17.7 There shall be no intervening valves between the overpressure safety device and the enclosure and it shall be located such that it is possible to show correct operation.
- 17.8 The equipment incorporates various previously certified equipment/component. It is therefore the responsibility of the manufacturer to continually monitor the status of the certification associated with these devices. The manufacturer shall inform CSA of any modifications to the devices that may impinge upon the explosion safety design of the equipment.

Manufacturer Product	Type	Certificate	Relevant standards	Relevant Ex marking
Pepperl & Fuchs Purge control unit	P5500	DEMKO 14ATEX1282X issue 4	EN IEC 60079-0:2018 EN 60079-2:2014 EN IEC 60079-7:2015 +A1:2018 EN 60079-11:2012 EN IEC 60079-15:2019	Ex ic ec nC [ic Gc] [pzc Gc] IIC T4 Gc
Nass Magnet Solenoid	5500-MAN-EX01 (Pepperl & Fuchs)	PTB 03ATEX2018X issue 4	EN 60079-0:2009 EN 60079-18:2009	Ex mb IIC T5
Beka Serial text display	BA 488C	ITS 02ATEX2036X issue 1	IEC 60079-0:2011 IEC 60079-11:2011	Ex ia IIC T5 Ga
Beka Communications isolator	BA 201	ITS 07ATEX25602 issue 1	EN IEC 60079-0:2018 EN 60079-11:2012	[Ex ia Ga] IIC
ESI Technology Pressure transducer	PR3110	TRAC 12ATEX0060X issue 1	EN 60079-0:2012 EN 60079-11:2012	Ex ia IIC T4 Ga
Pepperl & Fuchs Resistance repeater	KCD2-RR-EX1	Baseefa 10ATEX0061 issue 3	EN IEC 60079-0:2018 EN 60079-11:2012	[Ex ia Ga] IIC
Pepperl & Fuchs Galvanically isolated barrier	KCD2-STC-EX1	CESI 06ATEX021 issue 2	EN 60079-0:2012 EN 60079-11:2012	[Ex ia Ga] IIC
Intertec-Hess Heater	SL ***THERM DLA T3 BI	PTB 02ATEX1116X issue 1	EN IEC 60079-0:2018 EN 60079-1:2014	Ex db IIC T3 Gb
Elmess Heater	DHK58M05-T160 PTC	BVS 14ATEXE155U issue 1	EN IEC 60079-0:2018 EN 60079-1:2014	Ex db IIC Gb

Project Number 80122741

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands

Certificate Annexe



Certificate Number: Sira 16ATEX1158X

Equipment: CT5100 Laser Gas Analyser

Applicant: Emerson Process Management Limited

Issue 0

Drawing	Sheets	Rev.	Date (Sira Stamp)	Title
M-1000-2480	1 to 5	B	07 Nov 16	Top Cover
M-1000-2482	1 of 1	A	07 Nov 16	Top Cover Gasket
M-1000-2536	1 of 1	B	07 Nov 16	Gas Line Gasket
M-1000-2539	1 of 1	E	09 Dec 16	Nameplate
M-1000-2540	1 of 1	A	07 Nov 16	Purge Valve IP Gasket
M-1000-2573	1 of 1	B	07 Nov 16	Window Mount
M-1000-3037	1 of 1	B	07 Nov 16	CT5100 Mounting Bracket
M-1000-3054	1 to 2	A	07 Nov 16	Front Panel
M-3000-0934	1 to 5	B	07 Nov 16	General Assembly
M-3000-0934_Appendix C	1 to 2	A	07 Nov 16	Non-Metallic Materials
M-3000-0938	1 of 1	B	07 Nov 16	Window Mount
M-3000-0970	1 of 1	C	07 Nov 16	Main Enclosure
M-3000-1121	1 to 8	D	07 Nov 16	Main Enclosure Assembly
M-3000-1374	1 to 2	A	07 Nov 16	Purge Vent Assembly
W-2000-0037-A	1 of 2	01	07 Nov 16	Component List
W-2000-0037-B	2 of 2	01	07 Nov 16	Component List
W-2000-0039-A	1 of 3	-	07 Nov 16	Electronic Layout
W-2000-0039-B	2 of 3	-	07 Nov 16	Electronic Layout
7.5.1.00224-39	1 to 6	A	07 Nov 16	Laser Information

Issue 1

Drawing	Sheets	Rev.	Date (Sira stamp)	Title
S-8000-0001	1 of 9	A	23 Jun 17	Baseplate Assembly
S-8000-0001	2 of 9	A	23 Jun 17	Baseplate Assembly
S-8000-0001	3 of 9	A	23 Jun 17	Base Plate Assembly
S-8000-0001	4 of 9	A	23 Jun 17	Cell Assembly
S-8000-0001	5 of 9	A	23 Jun 17	Baseplate
S-8000-0001	6 of 9	A	23 Jun 17	Baseplate
S-8000-0001	7 of 9	A	23 Jun 17	Gas Line Bulkhead Assembly
S-8000-0001	8 of 9	A	23 Jun 17	Insulation Jacket
S-8000-0001	9 of 9	A	23 Jun 17	Drawing Amendment Sheet
M-1000-2539	1 of 1	G	23 Jun 17	Nameplate
M-3000-0934	1 to 7	C	23 Jun 17	General Assembly
M-3000-1121	1 to 8	E	23 Jun 17	Main Enclosure Assembly

Issue 2

Drawing	Sheets	Rev.	Date (Sira stamp)	Title
M-1000-3037	1 to 2	C	21 Feb 19	CT5100 Mounting Spar
M-1000-3954	1 to 2	A	21 Feb 19	CT5100 Nameplate (IEC/ATEX)
M-3000-0934 Appendix C	1 to 3	D	22 Feb 19	CT5100 Non-metallic Materials
M-3000-0934	1 to 8	D	28 Feb 19	CT5100 General Assembly
M-3000-0970	1 to 2	D	21 Feb 19	CT5100 Enclosure Assembly
M-3000-1121	1 to 9	F	21 Feb 19	CT5100 Modified Enclosure
M-3000-1543	1 to 2	B	21 Feb 19	Baseplate IR Window Assembly
S-8000-0015	1 to 3	A	28 Feb 19	CT5100 Optical Paths
W-2000-037	1 to 3	C	21 Feb 19	CT5100 Index Drawing
W-2000-039	1 to 5	C	21 Feb 19	CT5100 Wiring/User Connection Drawing

Project Number 80122741

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands

Certificate Annexe



Certificate Number: Sira 16ATEX1158X
Equipment: CT5100 Laser Gas Analyser
Applicant: Emerson Process Management Limited

Issue 3 - No new drawings were introduced.

Issue 4

Drawing	Sheets	Rev.	Date (Sira stamp)	Title
M-1000-2539	1 to 2	H	09 Oct 19	CT5100 Rating plate
W-2000-0037	1 to 3	D	09 Oct 19	CT5100 Cert Index Drawing
W-2000-0097	1 to 2	A	09 Oct 19	CT5100 IS System Diagram

Issue 5

Drawing	Sheets	Rev.	Date (Sira stamp)	Title
M-1000-3954	1 to 3	C	09 Mar 22	CT5100 Rating Plate, ATEX IECEx
M-1000-2539	1 to 3	I	09 Mar 22	CT5100 Rating Plate, Universal

Issue 6

Drawing	Sheets	Rev.	Date (Stamp)	Title
M-1000-3954	1 to 3	D	07 Jun 22	CT5100 Nameplate, ATEX IECEx
W-2000-0037	1 to 3	E	07 Jun 22	CT5100 Cert Index Drawing

The following drawing no longer forms part of the certification documentation:

Drawing	Sheets	Rev.	Date (Stamp)	Title
M-1000-2539	1 to 3	I	09 Mar 22	CT5100 Rating plate, Universal

Project Number 80122741

This certificate and its schedules may only be reproduced in its entirety and without change
CSA Group Netherlands B.V. Utrechtseweg 310, Building B42, 6812AR Arnhem, The Netherlands