



ROSEMOUNT 9295 PROCESS FLOW METER DROP-IN SOLUTION FOR DEMANDING APPLICATIONS

Challenge

Specifying plant instrumentation, analyzing instrument performance, and ensuring that processes run efficiently and safely can be costly, time consuming, and often require multiple products. Straight run piping requirements also add additional challenges and installation constraints.

Our Solution

Streamline procurement, installation, operation, and maintenance with the Rosemount™ 9295 Process Flow Meter, an integrated differential pressure flow meter solution that arrives assembled, configured and leak-checked.

How It Works

- Conditioning Orifice Plate technology increases installation flexibility by eliminating straight pipe run requirements, allowing for installation at grade level or in difficult piping configurations
- Roddable close coupled design increases uptime by allowing impulse line blockages to be removed without a process shutdown
- Fully welded spool section design decreases installation time and costs by offering a simple drop-in solution
- Optional integral temperature sensor provides a fully compensated flow measurement without the need for additional pipe penetrations or wake frequency calculations

Key Features

- Ideal for liquid, gas, or steam
- All-welded design eliminates potential leak points
- Flow turndown of 10:1 or better
- Redundant transmitter assemblies available for SIS applications
- Ruggedized isolation valves improve process safety



Rosemount 9295 Process Flow Meter

To learn more about our Differential Pressure (DP)
Flow Measurement solutions, [click here.](#)

Key Product Specifications

Line Size	2 to 6 in (50 to 150 mm)
Maximum Operating Pressure	ASME/ANSI B16.5 900#
Process Wetted Material	316 SST, Carbon Steel
Bore Size	Standard bores in 0.40, 0.50, and 0.65 betas; custom bores available
Primary Isolation Valves	½" Class 800 Full-Port Gate Valves conforming to API 602 Meters built with Class 900 Flanges receive Class 1500 valve
Compatibility	Compatible with Rosemount 305 Integral Manifolds and all Rosemount DP Transmitters*
Available Quality Checks	Hydrostatic Test, Positive Material Identification (PMI), Flow Calibration, Dye Penetrant Exam, Radiography (flange welds only), Weld Qualification Results (PQRs), Visual and Dimensional Exam

* The Rosemount 9295 Process Flow Meter can be specified with multiple transmitters, providing redundant measurements for Safety Instrumented Systems (SIS). Consult your local Emerson Sales Representative for more information.

Associated Products



Rosemount 3051S DP Flow Transmitter



Rosemount 305 Integral Manifold



The Emerson logo is a trademark and service mark of Emerson Electric Co. Brand logotype are registered trademarks of one of the Emerson family of companies. All other marks are the property of their respective owners. © 2024 Emerson Electric Co. All rights reserved.

For more information, visit [Emerson.com/DPFlow](https://www.emerson.com/DPFlow)

00807-0100-4485 Rev AB