

Options

PressureMatic™ High/Low Pressure Pilot

PressureMatic senses pipeline or process pressure and outputs a pneumatic or hydraulic signal, responding to high or low pressure conditions. It operates under maximum working pressures to 6,000 psig with field adjustable high set points to 4,450 psig and low set points to 20 psig, determined according to piston size, spring rate and mechanism adjustments. Available as automatic reset pilot valve (P-AR) or manual reset pilot valve (P-MR).



ISO Test Valve

The ISO Test Valve used with the PressureMatic, enables its calibration without shutting down the flow line. It is compact, safe and has a blowout proof stem that prevents removal when the valve is under pressure. The ISO test Valve has a maximum working pressure range of 3,000 psig to 6,000 psig.



Bettis PressureGuard™ is manufactured to these worldwide standards as follows:



ISO – 9001
Cert. Num 93-13



Accredited by the Dutch Council
for certification

Emerson brands for most common control accessories:

Digital Valve Controllers:	Fisher®
Positioners:	Fisher®
Regulators:	Fisher®
Switch boxes:	TopWorx
Wireless position monitor:	TopWorx
Solenoid valves:	ASCO Numatics™

World Area Configuration Centers (WACC) offer sales support, service, inventory and commissioning to our global customers. Choose the WACC or sales office nearest you:

NORTH & SOUTH AMERICA

19200 Northwest Freeway
Houston, TX 77065
USA
T +1 281 477 4100
F +1 281 477 2809

Av. Hollingsworth,
325, Iporanga Sorocaba
SP 18087-105
Brazil
T +55 15 3238 3788
F +55 15 3228 3300

ASIA PACIFIC

No. 9 Gul Road
#01-02 Singapore 629361
T +65 6501 4600
F +65 6268 0028

No. 1 Lai Yuan Road
Wuqing Development Area
Tianjin 301700
P.R.China
T +86 22 8212 3300
F +86 22 8212 3308

MIDDLE EAST & AFRICA

P. O. Box 17033
Dubai
United Arab Emirates
T +971 4 811 8100
F +971 4 886 5465

P. O. Box 10305
Jubail 31961
Saudi Arabia
T +966 3 340 8650
F +966 3 340 8790

24 Angus Crescent
Longmeadow Business Estate
East P.O. Box 6908;
Greenstone; 1616
Modderfontein, Extension 5
South Africa
T +27 11 451 3700
F +27 11 451 3800

EUROPE

Berenyi u. 72-100
Videoton Industry Park
Building #230
Székesfehérvár 8000
Hungary
T +36 22 53 09 50
F +36 22 54 37 00

For complete list of sales and manufacturing sites, please visit www.emerson.com/actuationtechnologieslocations
Or contact us at info.actuationtechnologies@emerson.com

PressureGuard™

Self-Contained Hydraulic Emergency Shutdown Systems
For Rotary or Non API 6A Linear Valves



www.emerson.com/bettis

©2018 Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Bettis is a mark of the Emerson family of companies. All other marks are property of their respective owners.

The contents of this publication are presented for information purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice.



BETTIS™
DOC.6P.BPG.UK Rev G 06-18

www.emerson.com/bettis

EMERSON

BETTIS™

EMERSON

Design and Construction

Emerson – Actuation Technologies has been providing reliable solutions for the pipeline, process and production segments of the energy industry and myriad other industries for more than 55 years. They have established themselves as an innovator, with products that fully automate valves under the most rigorous conditions and in some of the most remote areas in the world. Our product quality is supported by ISO 9001 designations indicating full compliance with global standards for quality and documentation.

PressureGuard™ Self-Contained Hydraulic Emergency Shutdown (ESD) Systems provide reliable valve shutdown capability when an external power source is either not available or not dependable. They can be used with rotary hydraulic operators to provide a fail-safe system for use with ball, plug and other quarter-turn valves, as well as non 6A linear operated valves.


Benefits

- Suitable for remote, unmanned, unpowered and critical service.
- Standard hydraulic model available for all valve sizes and configurations.
- Modular design to simplify maintenance.
- Eliminates need for plant air, fuel gas, electricity or nitrogen backup.
- High pressure, zero leakage control.
- Minimum of working parts
- Adaptable for use with SCADA systems or remote signals.
- Fail safe design.



Product Features – Control System Module

The PressureGuard self-contained hydraulic control systems are supplied with a basic manifolded control package that provides a one-way local control using the handpump. In addition to its reliability, it provides quick and simple maintenance.



Hydraulic Fluid Reservoir

Available in 200-5,000 cu. in. displacements. Fitted with snubber and level indicator.

Hand Pump

Manually transfers hydraulic fluid from the reservoir to force it under pressure into the actuator and control system.

Pressure Gauges

High pressure (top) gauge monitors hydraulic pressure supplied to the actuator. Low pressure (bottom) monitors pressure in the low pressure control circuit.

Pressure Regulator

Reduces actuator high pressure to 100 psig for use of low pressure control components.

LP Accumulator


Prevents cyclic transfer of hydraulic fluid from high pressure to low pressure circuits.

Manual Reset Valve

Used to bypass the shutdown device, allowing use of hand pump even when shutdown device is in fail position.



PressureGuard Operation



The PressureGuard self-contained hydraulic module operates in tandem with the Bettis actuator and control signal devices.

Emerson - Actuation Technologies is a recognized leader in automated valve control in remote areas of the world.

Bettis™ actuators provide THE reliable solution for Emergency Shutdown (ESD) service.

PressureGuard™ ESD systems do not depend on an external power source.