

MAS 2600

Tank Contents Transmitter



Advantages

- Titanium housing and diaphragm
- Resistant to sea water and chemicals
- Silicon strain gauge sensor
- EMI protected
- Interchangeable with existing transmitters
- Programmable from 0.2 to 35 mH₂O
- Strong, light and extremely corrosion resistant

Description

The MAS 2600 tank contents transmitter is an electronic based transmitter designed for tank contents measuring application.

The MAS 2600 is a 2-wire 4-20 mA level transmitter consisting of a transducer and an amplifier connected via a 6-core vented cable.

The transducer is fully welded, housed in titanium with a titanium diaphragm and is submersible (IP68).

The amplifier is housed in a sea water-resistant polyester casing (IP56). The transducer is a pressure sensitive silicon micro strain gauge sensor mounted in a glass to metal seal. The sensor is

protected by an isolation diaphragm, electron beam welded to the transducer housing, with an oil filling between the sensor and the diaphragm.


Pressure changes in the front of the diaphragm will bring about a resistance change in the Whetstone bridge of the transducer. This change in the Whetstone bridge will be transmitted to the amplifier as a change in the electrical signal.

The MAS 2600 is manufactured in 4 programmable ranges from 0-3.5 mH₂O to 0-35 mH₂O, and available with a built-in Pt100 sensor.

Application


The MAS 2600 has been developed for level measuring in ballast, oil, service and fresh water tanks as well as tanks containing media which are not hostile to titanium.

For further information about the two controls please see separate data sheets.



Power Supply


The Power Supply can vary from 17 to 33 VDC. Permissible load resistance is shown graphically below.



Technical Specification

Transducer ranges	0-3.5 / 0-7 / 0-16 / 0-35 m H ₂ O gauge 0.8 - 2.0/0.8-3.5 bar absolute
Programmable measuring ranges	Each transducer range programmable in 8 steps
Accuracy	±0.25% F.S. at 20° C
TEB (Total Error Band)	±0.4% F.S. at 0 to +50° C ±2.0% F.S. at -20 to +80° C
Overload Capability	Minimum 4 x transducer range with no changes in calibration
Burst Pressure	6 x transducer range
Built-in Temperature Sensor Pt100	Optional
Diaphragm	Titanium
Sensor Housing	Titanium
Output Current	4-20 mA DC, 2-wire system
Power Supply	17-33 VDC $R_{\text{loop max. (Kohm)}} = (U_{\text{loop}} - 17V)/32 \text{ mA}$
Current Limiting: Typically Maximum	25 mA 32 mA
Operating Temperature Ranges: Transducer Amplifier	-20 to +80° C (125 c for H-version) -40 to + 85° C
Protection Class: Transducer Amplifier	IP 68 IP 56
Intrinsic Safety	Ex ia IIC T4 compliant

Dimension Drawing



Intrinsically Safe in Hazardous Areas

The MAS 2600 has been approved for use with standard transmitter zener barriers and is Ex ia.IIC T4 compliant in accordance with CENELEC EN 50020.

Approvals

MAS 2600 meets the strict requirements to marine equipment and is type approved by major classification societies as:

- DNV, GL, LRS, BV, RINA, KRS, ABS

Emerson Automation Solutions

Damcos A/S
Aaderupvej 41
DK-4700 Naestved
T +45 5578 7200
F +45 5578 7272

www.Emerson.com/marine

Emerson Automation Solutions

Rosemount Tank Radar AB
Box 150
SE-435 23 Mölnlycke
T +46 31 337 00 00
F +46 31 25 30 22

www.Emerson.com/marine

©2020 Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount and the Rosemount logotype are registered trademarks of Rosemount Inc. Damcos and the Damcos logotype are registered trademarks of Damcos A/S. TankRadar is a trademark of Rosemount Tank Radar AB. Rosemount Tank Radar AB and Damcos A/S are members of the Emerson family of companies. All other marks are the property of their respective owners.

The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, expressed or implied, regarding the products or services described herein or their use or applicability. Standard Terms and Conditions of Sale can be issued by contacting Damcos A/S or Rosemount Tank Radar AB. We reserve the right to modify or improve the designs and specifications of our products at any time without notice. Damcos A/S and Rosemount Tank Radar AB accepts no responsibility for any errors that may appear in this publication.