



5. MINIMUM NOZZLE HEIGHT 200mm.
4. THE PROBE FROM 3308 INSIDE TANK MUST NOT PROTRUDE LONGER THAN TANK ROOF LEGS OR IT WILL BE DAMAGED WHEN LANDING THE FLOATING ROOF. IT SHALL STOP AT LEAST 100mm BEFORE PIPE ENDS.
3. IF NOZZLE IS NOT VENTILATED, 3308 FLUSHING CONNECTION RING SHOULD BE USED TO AVOID PRESSURE BUILDUP IN NOZZLE.
2. SEE WIRELESS BEST PRACTICES DOCUMENTATION FOR RECOMMENDATIONS REGARDING WIRELESS INSTALLATION.
1. PROBE LENGTH/CONNECTION SIZE MUST BE SELECTED CONSIDERING BLIND ZONES AND NOZZLE REQUIREMENTS. CHECK MECHANICAL INSTALLATION REQUIREMENTS IN THE FLOATING ROOF MONITORING REFERENCE MANUAL AND 3308 SERIES WIRELESS GUIDED WAVE RADAR REFERENCE MANUAL.

ISSUED BY EMe-PB	DRAWN WEEK 1802	PRODUCT CODE 5900	 LAYOUTVÄGEN 1, 435 33 MÖLNLYCKE, SWEDEN
APPROVED BY EMe-MH	APP'D WEEK 1804	DOCUMENT TYPE 02	
ORIGINAL DRAWING NO. D7000004-603	SIZE A3	1 ST ANGLE 	SCALE -
CAD MAINTAINED, (PRO/E)	DO NOT SCALE PRINT		
<small>THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN</small>			INSTALLATION DRAWING TITLE <b>FLOATING ROOF MONITORING-ROOF MOUNTING</b>
DRAWING NO. D7000004-603		ISSUE 02	SHEET 1/1

2018-05-29 Electronic Master - Printed Copies Uncontrolled - Emerson Proprietary