



DETAIL A

DEPENDING ON TURBULENCE IN TANK AND MOUNTING ANGLE THE PROBE MAY NEED TO BE ANCHORED OR SUPPORTED.  
ENSURE MID PROBE HAS NO CONTACT WITH WALL. MIN DISTANCE 15 [0,6].

FOR MORE INFO, SEE REFERENCE MANUAL

1. P/T-RATING FOR FLANGE; SEE REF. MANUAL.

POS	ITEM DESCRIPTION	QTY	REMARK	SUPPLIER
04	GASKET	1	ACC. TO BSP-G THREAD STD.	CUSTOMER
03	GASKET	1	SOFT GASKET T=MIN 1.6 (ANSI B16.5/1c, EN1514-1/1BC). SEE NOTE 1.	CUSTOMER
02	SCREW/NUT/WASHER	-	ACC. TO FLANGE STD. SEE NOTE 1.	CUSTOMER
01	FLANGE	1	DIM. ACC. TO ANSI B 16.5/EN 1092-1. OTHER ON REQUEST. P/T RATING, SEE NOTE 1.	RMT

ISSUED BY	REV	PRODUCT CODE	FILE	INSTALLATION DRAWING TITLE
Eme-HW-C	0909	3300	PRO/E	MECHANICAL INSTALLATION DWG
APPROVED BY	REV	ORIGINAL DWG. NO.	SCALE	
Eme-HF	0909	9150077-971	-	FLEXIBLE TWIN LEAD
<b>ROSEMOUNT</b> <small>THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK-RADAR AB, SWEDEN.</small>				T-ST ANGLE 
				DOC TYPE   DWG NO.   ISSUE   SHEET 2   9150077-971   04   1/1