FB1100 Flow Computer

The FB1100 is a cost-effective, low-power explosionproof flow computer that measures and monitors gas flow for a single differential pressure meter run. As well as bringing a new level of measurement confidence, the FB1100 can run independently without external power, for up to one year, making it an ideal replacement for chart recorders.

The FB1100 is part of Emerson's new field mount flow computer family that delivers a convenient approach to remote oil and gas sites by addressing challenges to power, safety, measurement reliability, and accuracy.

Designed for simple configuration and ease of use, the cost effective FB1100 flow computer is focused on metering applications where control is not required.

The FB1100 provides a full audit trail, including enhanced history, alarm and event logs as well as providing a discrete output that can be used to drive an odorizer.

The FB1100 includes power options for the most remote sites and has flexible communication capabilities, including FBxWifi[™], for both remote and networked sites.

The new flow computers also come with the latest Rosemount[™] multivariable measurement sensor technology, providing high accuracy differential pressure and static pressure measurement with long term stability to help improve measurement confidence and production efficiency.

Features

The FB1100 flow computer includes the following key features:

- Increased measurement confidence, reduced measurement uncertainty
- Measurement and I/O capability focused on metering applications
- Industry leading differential and static pressure measurement including 0.05% of reading accuracy and 5-year stability
- High accuracy temperature measurement including curve matching via the Callendar-Van Dusen equation
- Reduced need to re-calibrate resulting in less time spent on site

- Simplified configuration and set-up with the FBxConnectTM configuration software tool
- Cost-effective alternative to chart recorders
- Flexible design with power and communication options to meet site needs
- Standard firmware supports global calculations for DP metering including orifice, cone, Venturi, nozzle, and conditioning orifice
- Standard firmware supports Properties Calculations for Natural Gas and Pure Gas
- Simple selection of engineering units to suit local requirements
- Global Hazardous Area Approvals Class 1 Div 1 & 2, ATEX & IEC Ex d & Ex ec
- FBxWifi allows secure local wireless access from safe area
- Ease of integration with support for Modbus, ROC, BSAP and DNP3 protocols
- Enhanced security helps prevent unauthorized access
- Enhanced alarming and historical data storage, improved audit trail
- Superior performance gives better control of your operations and maximizes profits
- API 21.1 compliant



Aluminum Housing

Stainless Steel Housing

FB1100



Energy and Transportation Solutions

FBxWifi™

The optional FBxWifi communications enables you to connect your laptop or tablet to the flow computer through a secure wireless connection. Once connected wirelessly, you can use FBxConnect configuration software to view process values, edit configuration parameters, and collect logs stored in the flow computer – all from within the safe area.

Power Options

The FB1100 has the following power options:

- External DC supply
- External DC supply with internal battery back-up
- Solar panel charging internal battery, FB1100 has internal solar regulator
- Autonomous mode with internal battery powering the FB1100 for 12 months

In "autonomous mode" the FB1100 runs from a single battery for up to 12 months without recharging. The 12-month battery life is based on the FB1100 running in low power mode on a typical remote application with a local collection of history and the use of the optional display for up to 30 minutes per month. This option is an ideal replacement for chart recorders, significantly reducing measurement uncertainty and providing a complete electronic audit trail. The 12month battery life is achieved under an ambient temperature of 25°C/77°F; refer to the table on page 10.

The solar powered option provides up to 25 days of autonomous operation if configured to operate under Low Power Mode. Refer the *Power Modes* section of the data sheet for more details.

Note: Internal battery option is not available with ATEX and IECEx approvals.

Firmware

The base firmware in the FB1100 flow computer measures static pressure, differential pressure, and temperature for a single meter run. The flow computer performs gas flow calculations based on those inputs in either U.S., metric, or other user-selectable units based on the calculation type.

The firmware supports the following flow calculations:

- AGA 3 1992/2013 (volume, mass/density, and mass/relative density)
- ISO 5167 1991/1998/2003 (orifice, Venturi, and nozzle)

- Rosemount[®] 405C Compact Orifice and 1595 Conditioning Orifice Plate
- McCrometer V-Cone[®] and Wafer Cone[®]
- NUFLO™ Cone
- AGA 9(Multipath Ultrasonic)

The firmware supports the following property calculations:

- AGA 8 1994 (Detailed, Gross 1 and Gross 2)
 - AGA 8 2017 Part 1 and Part 2 (GERG 2008) **Note:** AGA 8 Part 2 / GERG 2008 provides support for the following pure gases (100%) as well as any mixtures (0% to 100%): Nitrogen, Carbon Dioxide, Hydrogen, Oxygen, Carbon Monoxide, Water Vapor, Hydrogen Sulfide, Helium, and Argon
- Speed of Sound calculated via AGA 10 and AGA 8 2017 Part 2
- NX-19 1962, MOD, VDI/VDE 2040, Miller
- ISO 12213 2006 (parts 2 and 3)
- SGERG 1991 (Std., Alt 1, Alt 2, and Alt 3)
- GPA 2172 2009 (including saturated vapor calculation)
- ISO 6976 1995 (superior and inferior, incorporating Technical Corrigendum 2 [1997] and 3 [1999])
- AGA 5 2009

Regarding gas composition, the flow computer can:

- Receive updated gas composition from SCADA
- Receive manual updates for gas composition through FBxConnect; or
- Use a fixed gas composition

The firmware includes the following flow rates and totals:

- Uncorrected volume
- Corrected (standard) volume
- Mass
- Energy

In addition to the normal totals, the firmware also supports the following fault totals which can be enabled for a gas meter. The conditions to trigger the fault totals are user configurable:

- Uncorrected volume fault totals
- Corrected volume fault totals
- Mass fault totals
- Energy fault totals

The firmware supports a fallback mode when a process variable's value is questionable. The fallback options can be one of the following:

- Use last good value
- Use a fixed fallback value

Alarms and Events

The flow computer supports extensive alarming capability to enhance operational efficiency and improve the audit trail. Alarms are pre-allocated to meter runs for standard values such as pressure, temperature, and differential pressure as well as meter run flow rates. In addition to these standard alarms, the FB1100 provides a number of user alarms that you can assign to other database parameters simply by "filling in the blanks" in user alarm templates in the FBxConnect configuration tool. Storage is provided for the most recent 1000 alarms in the alarm log.

The event log stores the significant events during operation and can be configured to either store all events in a single log of 2000 events or the user can select to store the metrology/legal events in a separate log from the operational events. With the latter option the event log capacity is 1000 metrology events and 1000 operation events.

Automated Checksum Verification (ACV)

As an extended auditing feature, the flow computer provides an option to perform online integrity checks by generating firmware and configuration checksums. The checksum is a 32-bit CRC number which is routinely calculated and compared against the last verified checksum. If a newly calculated checksum does not match with the last verified checksum, the system generates a checksum error and the flow computer goes into an unverified state.

History

The FB1100 features expanded and flexible history capability to ensure measurement confidence and meet the increasing demands for secure data.

The flow computer has four standard periodic logs available providing hourly, daily, weekly, and monthly history. These logs can contain up to 110 variables including flow weighted average data, totals, and gas composition. For averaging, the FB1100 supports either flow weighted or flow dependent which can be linear or formulaic.

The FB1100 can store the following standard periodic logs for 35 variables. With the flexible history design, the number of variables and the time duration for different periodic logs can be adjusted to meet the application requirement.

- Hourly logs
- Daily logs

.

- 12 months or 365 records
- 12 months or 52 records
- Weekly logsMonthly logs
- 60 months or 60 records

62 days or 1500 records

Note: This is only the initial default history. With the flexible history design, the number of variables and the time duration for different periodic logs can be adjusted to meet the application requirement.

The flow computer also supports two user periodic logs, the duration or period of each is user selectable between 1 minute and 200 hours. The first user periodic logs include 10 parameters over 4,000 periods and the second contains 20 parameters over 500 periods.

The flow computer with FBxConnect provides preformatted EFM reports for hours and days. The format of the reports can be .csv, .pdf, or secure pdf.

In addition to the above reports, the flow computers can produce FLOWCAL-complaint .cfx files through the FBxConnect tool as well as calibration reports which contain U.S. Bureau of Land Management specific parameters.

Housing

The FB1100 includes an explosion-proof and flameproof enclosure made of die-cast aluminum or stainless steel that can operate in an unprotected outdoor environment. Wiring for I/O, communications, and power enters the enclosure through the four conduit fittings. The front-end cap provides a viewing window for the optional LCD. The rear end cap provides access to the screw terminals. The end caps can also be fitted with wire security seals.

Hazardous Area Certifications

The FB1100 has the following Global Hazardous Area Approvals:

- North American certification for Class I Division 1 Groups C and D (explosion proof) and Class I Division 2 Groups A, B, C and D
- ATEX and IECEx certification for Exd Zone 1 (flame proof) and Ex n Zone 2 hazardous locations

Configuration Software

Emerson's new FBxConnect tool is a Microsoft[®] Windows[®]-based tool that enables you to easily monitor, configure, service, and calibrate the FB1100 flow computer. Designed for ease of use, FBxConnect provides at-a-glance monitoring, quick access to commonly performed tasks, and a guided configuration process to quickly get your measurement up and running.

The wizard-driven approach simplifies configuration and ensures that you only need to enter the required data once. Whether you are an experienced engineer or a new technician, you can be confident configuration is done correctly the first time.

FBxConnect runs on a Windows PC or tablet. You connect securely to the flow computer using one of its serial ports or optionally through the FBxWifi wireless connection. For more information, refer to product data sheet *FBxConnect* (D301789X012).

Multivariable Sensor

Enabled by superior sensor technology and engineered for optimal flow performance, the MVS on the FB1100 delivers unparalleled accuracy over a wide range of operating conditions and industry leading stability. Pressure inputs on the sensor are used to measure differential (up to 1000" of water) and static (absolute or gauge) pressure with an operating range of up to 3600 psi and accuracies of up to 0.05% of reading.

)					-	
File Monitor	Configure 🏻 🔏 Se	rvices 🗋 Reports i	🚨 FilbxVue 🛛 🙀 Help				
Main	👌 Gas 🔹 -	🗊 History	Events	R Comm Ports			
ю	HM Display	(B) Alarma					
	View		History	Communications			
			M	onitor Meter			
P Mir_1							
	Differential Pressure		Flow	sing Pressure	Flowing Temperature		
8 8 9	-	Live 25 50	400 0	Live 2000 2400 2000 2	40 10 10 10 10 10 10 10 10 10 1	Live	
	Override Active	-	Overr	ide Active 🏼 🚽	Override Active	->	
	Normal			Normal	Normal		i
Corrected Volume Flo	w Rete	16724.32 MCF/d					
Corrected Volume Flo Mass Flow Rate : Energy Flow Rate :		710.1 MIb/d 16964.0 MMBtu/d					
Mass Flow Rate :							
Mass Flow Rate : Energy Flow Rate :	Units		Previous Day				
Mass Flow Rate : Energy Flow Rate :	Units	16964.0 MM8huld	Previous Day				
Mass Flow Rate : Energy Flow Rate : — Current Totals —	Units	16964.0 MM8hu/d Current Day					
Mass Row Rate : Energy Flow Rate : — Current Totals — Corrected Volume	Units e MC/	Current Day 69.582	0.0				
Mass Row Rate : Energy Row Rate : — Current Totals – Corrected Volume Mass	Units e MC ^r	16964.0 MM8huld Current Day 69.362 2.934	0.0 0.0				
Mass Row Rate : Energy Row Rate : — Current Totals – Corrected Volume Mass	Units e MC ^r	16964.0 MM8huld Current Day 69.362 2.934	0.0 0.0				

Monitor Screen

File 🖬 Monit										1
	or Oconfigure	X Services	Reports a		() Help					
Homo P Guided Setup	C Engr Units	✓ 10 Setup	Contract Select	Eluid Part Resonance		Ration ∑ Told	44 • (#) Ala @ Ho		PD Loops Math Block D Action Blocks D Effects	ka
Me	-	10	-		Manurerer			Laon	Control	
Mtr.1		*			D	P Meter				
eneral	Advanced	_			5	meter				
	DP Mtr_1		21	ition Assignm	ent: 3	lation_1		->	Diagnostics 71 Rates & Tota	als 7
cription :			Els.	id Properties	Reference : R	luid Prop_1		-•		
ial Number :			Flo	w Alerm Obje	sct : /	Nerm_10		-		
15:	Normal									
Meter Type				- Me	eter Sizing —		No Flo	w Cut-off Limit	- Flow Direction	_
leter Type :		3A3 Orifice (Flange			e Diameter :		n 0.0	inH2O	Forward	
VEA 3 Calculation	Selection : Al	5A3 2013 Volume	,	Pipe D	Nameter :	8.0	n No Row S	tatus : Rowing	O Reverse	
Howing Pressure		Press_1-1	••• •	Override ¥	224.8	224.8	psi(a)	Alarms		
Meter Inputs										
Flowing Pressure		Press_1-1	••• -	Override ¥	224.8	224.8	psi(a)	Alarms		
Rowing Tempera	iture	RTD_1+1	••• 🔹	Override T	86.4	86.4	7	Alarms		
Corrected Vo	olume Rate Alarr	n			Last Meter In	spection Time				
Corrected Vo	olume Rate Alarr Limit	n	Status		- Last Meter In 01/01/00 12:00:0]	
	Limit		Status]	
4igh High Alarm	Limit 10000	0 MCF/d								
sigh High Alarm Sigh Alarm Limit	Limit 10000	0 MCF/d	Normal							
- Corrected Vo righ High Alarm Figh Alarm Limit Low Alarm Limit Low Low Alarm L	Limit 10000 1 10000 1 0.0	0 MCF/d 0 MCF/d	Normal							
tigh High Alarm Tigh Narm Limit Low Alarm Limit	Limit 10000 t 10000 0.0 Limit 0.0	0 MCF/d 0 MCF/d MCF/d	Normal Normal Normal]	

FB1100

DP Meter

Temperature Input (RTD/PRT)

With industry-leading measurement accuracy, the temperature measurement of the FB1100 will ensure that you minimize your measurement uncertainty in all operating conditions. The input accepts two-, three-, or four-wire connections reducing any field wiring induced errors and also supports sensor curve matching utilizing the optional Callendar Van-Dusen constants to define the unique characteristics of the RTD/PRT to further improve process temperature measurement uncertainty.

The FB1100 flow computer's superior static pressure, differential pressure (DP) and temperature measurement performance and stability ensures you meet standards and regulations so you can avoid fines, penalties, leaseholder disputes, and lost revenue. With the advanced measurement, you're getting the most accurate flow reading to ensure you meet your company and regulatory performance requirements.

Discrete Output

The FB1100 includes a single discrete output (DO) which provides the ability to control various discrete output field devices. The DO channel is a solid-state, normally open switch rated at 500 mA, enough to directly drive most odorizers or samplers. The DO channel can be software configured as a latched, toggled, momentary, timed duration output (TDO), or scaled pulse output.

Communications

The FB1100 has three serial communications ports with support for RS-232, RS-422, and/or RS-485 operation, and one port that supports optional FBxWifi (802.11 b/g) communications using DNP3 protocol.

- COM1 4-wire serial communications. Software selectable for EIA-232 (RS-232), EIA-422 (RS-422), or EIA-485 (RS-485) operation.
- COM2 2-wire serial communications. Software selectable for EIA-232 (RS-232) or EIA-485 (RS-485) operation.
- COM3 2-wire serial communications. Software selectable for EIA-232 (RS-232) or EIA-485 (RS-485) operation.
- COM4 –FBxWifi (802.11 b/g) communications (optional).

Communications Protocols

The FB1100 supports DNP3, Modbus slave (ASCII and RTU), BSAP, and ROC protocols on the three serial ports and DNP3 on the FBxWifi port.

Mounting Options

The flow computer supports either direct mount to a manifold on the pipeline or indirect mounting on a two-inch pipe or pole. A mounting bracket and bolts are available for use with a traditional flange or coplanar flange.

Security

To secure your valuable process and data, the FB1100 provides multi-level role-based access, user account authentication, and password encryption.

The system administrator can set a minimum password length (up to 20 characters) that accommodates lower case, upper case, numbers, and symbols, as well as configure a user lock-out feature that locks out invalid users after a defined number of failed login attempts.

Additionally, the DNP3 protocol lends itself to an added layer of security through Secure Authentication (SA). SA version 5 (SAv5) is available in the FB1100 Flow Computer as a selection in the firmware. SAv5 authenticates the devices which significantly improves resistance to outside influence. **CPU Module** Processor

Memory

Clock

Diagnostics

Communications

		sing unit (CPU) of the fl tex® M4 processor.	ow computer is an NXP [®] Kinetis [®] K61 series CPU
	SRAM	8 MB, holds current st	ates of all variables and historical archives.
	Flash	128 MB, holds firmwa	re image and configuration files.
	Туре	Real-time clock	
	Accuracy	0 °C to 40 °C	60 seconds/year
		–40 °C to 80 °C	110 seconds/year
	Watchdog Timer	1175 milliseconds	
	Battery voltage m	onitor, external voltage	monitor, SRAM battery status
s			

COM1	4-wire serial communications. Software-selectable for RS-232, RS-422, or RS-485 operation.		
COM2	2-wire serial communications. Software-selectable for RS-232 or RS-485 operation.		
СОМЗ	2-wire serial communications. Software-selectable for RS-232 or RS-485 operation.		
COM4	FBxWifi (optional) 802.11 b/g		
Serial ports support DNP3, Modbus slave (ASCII and RTU), BSAP, and ROC Wi-Fi supports DNP3 DNP3 includes level 3 protocol subset			
	COM2 COM3 COM4 Serial ports s Wi-Fi suppor		

Inputs/Outputs

The base FB1100 includes the following I/O:

- 1 multivariable sensor, measures differential pressure and static pressure
- 1 process temperature input (PRT/RTD)
- 1 discrete output (DO)

The I/O of the FB1100 is focused on a standard metering application with a DO that is typically used to drive an odorizer.

Multivariable Sensor

The standard Rosemount[™] MultiVariable[™] sensor has a stainless steel coplanar flange, a stainless steel (316L) diaphragm, and silicone fill fluid. Optional versions include:

- A Hastelloy[®] C-276 sensor diaphragm, a Hastelloy C-276 coplanar flange, with either NACE MRO175/ISO 15156 or MRO103 certification
- Stainless steel traditional flange, a stainless steel diaphragm, and silicon fill fluid.

Differential Pressure	DP Range 1	–25 to 25 Inches H ₂ O (–62.16 to 62.16 mbar)		
Input		Reference Accuracy	± 0.1% span; For spans less than 5:1, ± (0.025+0.015 [USL/Span]) % span	
		Stability	±0.2% USL for 1 year	

	Ambient Temperature Effect per 50°5	from 1:1 to 30:1	± (0.2% USL + 0.25% span)			
	Effect per 50°F (28°C)	from 30:1 to 50:1	± (0.24% USL + 0.15% span)			
	Static Pressure	Zero Error	± 0.25% USL per 1000 psi (69 bar)			
	Effects	Span Error	± 0.4% of reading per 1000 psi (69 bar)			
	Over Pressure Limit	SP Range G4/A4	2000 psi (137.89 bar)			
	Burst Pressure 10,000 psi (689.47 bar) Limit					
	 Notes: 25-inch sensor is only available with static pressure SP Range G4/A4, maximum pressure limited to 2000 psi. 25-inch sensor is only available with stainless steel sensor and coplanar flange. 					
DP Range 2:	0 to 250 inches H	H ₂ O (623 mbar	·)			
Standard	Reference Accuracy	± 0.1% span For spans le	; ss than 10:1, ± (0.01 [USL/Span]) % span			
	Stability	ability ± 0.1% USL for 1 year				
	Ambient Temperature	from 1:1 to 30:1	± (0.15% USL)			
	Effect per 50°F (28°C)	from 30:1 to 50:1	± (0.20% USL)			
	Static Pressure Effects	Zero Error	± 0.1% USL per 1000 psi (69 bar) For Static Pressures above 2000 psi: ± [0.2 + 0.0001 * (Ps - 2000)] % /1000 ps			
		Span Error	± 0.2% of reading per 1000 psi (69 bar)			
	Over Pressure Limit	SP Range G6/A6	1600 psi (110.32 bar)			
		SP Range G7/A7	3626 psi (250.00 bar)			
		SP Range G4/A4	3626 psi (250.00 bar)			
	Burst Pressure Limit	All SP ranges	10,000 psi (689.47 bar)			
	Note: 0.1% Ac	curacy is not a	available on traditional flange.			
DP Range 2:	0 to 250 inches H	H₂O (623 mbar	·)			
Enhanced	Reference Accuracy	± 0.075% sp For spans le % span	an; ss than 10:1, ± (0.025 +0.005 [USL/Span])			

	Stability	For ±50 °F (2	L for 5 years; 28 °C) temperature changes, up to 1000 r) line pressure				
	Ambient Temperature Effect per 50°F (28°C)	hperature ± (0.035% USL + 0.125% span) from 5:1 to 100 ect per 50°F °C)					
	Static Pressure Effects	Zero Error	± 0.05% USL per 1000 psi (69 bar) For Static Pressures above 2000 psi: ± [0.1 + 0.0001 * (Ps - 2000)] % /1000 psi				
		Span Error	± 0.2% of reading per 1000 psi (69 bar)				
	Over Pressure Limit	SP Range G6/A6	1600 psi (110.32 bar)				
		SP Range G7/A7	3626 psi (250.00 bar)				
		SP Range G4/A4	3626 psi (250.00 bar)				
	Burst Pressure Limit	All SP ranges	10,000 psi (689.47 bar)				
DP Range 2: Enhanced for Flow	0 to 250 inches H	l₂O (623 mbai	r)				
	Reference Accuracy	±0.05% of reading; For readings less than 8:1, ± [0.05 + 0.0023(USL / Rdg)] % reading					
	Stability	±0.125% USL for 5 years; For ±50 °F (28 °C) temperature changes, up to 1000 psi (68.9 bar) line pressure					
	Ambient Temperature Effect per 50°F (28°C)	±0.13% of reading from 1:1 to 5:1, ± [0.13 + 0.04 (USL / RDG)] % of reading from 5:1 to 100:1					
	Static Pressure Effects	Zero Error	± 0.05% USL per 1000 psi (69 bar) For Static Pressures above 2000 psi: ± [0.1 + 0.0001 * (Ps - 2000)] % per 1000 psi				
		Span Error	± 0.2% of reading per 1000 psi (69 bar)				
	Over Pressure Limit	SP Range G6/A6	1600 psi (110.32 bar)				
		SP Range G7/A7	3626 psi (250.00 bar)				
		SP Range G4/A4	3626 psi (250.00 bar)				

	Burst Pressure Limit	All SP ranges	10,000 psi (689.47 bar)			
DP Range 2: Extended	0 to 250 inches I	l₂O (623 mbai	r)			
	Reference Accuracy		span for spans 25 to 250 in H₂O; s above span, ±0.15% reading			
	Stability	For ±50 °F (2	5L for 5 years; 28 °C) temperature changes, up to 1000 r) line pressure			
	Ambient Temperature Effect per 50°F (28°C)	0.125% spar For pressur	anned 75 to 250 in H ₂ O, \pm (0.025% MSL + h) es between span and 250 in H ₂ O, \pm L + 0.125% reading)			
		0.03% span)	es between span and 250 in H_2O , ± (0.09%			
		For pressure reading	e readings above 250 in H_2O , ± 0.15%			
	Static Pressure Effects	Zero Error	± 0.05% USL per 1000 psi (69 bar) For Static Pressures above 2000 psi: ± [0.1 + 0.0001 * (Ps - 2000)] % per 1000 psi			
		Span Error	± 0.2% of reading per 1000 psi (69 bar)			
	Over Pressure Limit	SP Range G6/A6	1600 psi (110.32 bar)			
		SP Range G7/A7	3626 psi (250.00 bar)			
	Burst Pressure Limit	All Span ranges	10,000 psi (689.47 bar)			
DP Range 3:	0 to 1000 inches H ₂ O (2.5 bar)					
Standard	Reference Accuracy	± 0.1% span For spans le	; sss than 10:1, ± (0.01 [USL/Span]) % span			
	Stability	±0.1% USL f	or 1 year			
	Ambient Temperature	from 1:1 to 30:1	± (0.15% USL)			
	Effect per 50°F (28°C)	from 30:1 to 50:1	± (0.20% USL)			
	Static Pressure Effects	Zero Error	± 0.1% USL per 1000 psi (69 bar) For Static Pressures above 2000 psi: ± [0.2 + 0.0001 * (Ps - 2000)] % /1000 psi			
		Span Error	± 0.2% of reading per 1000 psi (69 bar)			

	Over Pressure Limit	SP Range G7/A7	3626 psi (250.00 bar)				
		SP Range G4/A4	3626 psi (250.00 bar)				
	Burst Pressure Limit	All Span ranges	10,000 psi (689.47 bar)				
	Note: 0.1% Accu	racy is not av	ailable on traditional flange.				
DP Range 3:	0 to 1000 inches H_2O (2.5 bar)						
Enhanced	Reference Accuracy	± 0.075% sp For spans le % span	an; ess than 10:1, ± (0.025 +0.005 [USL/Span])				
	Stability	For ±50 °F (2	L for 5 years; 28 °C) temperature changes, up to 1000 r) line pressure				
	Ambient Temperature Effect per 50°F (28°C)	± (0.0175% USL + 0.1% span) from 1:1 to 5:1, ± (0.035% USL + 0.125% span) from 5:1 to 100:1					
	Static Pressure Effects	Zero Error	± 0.05% USL per 1000 psi (69 bar) For Static Pressures above 2000 psi: ± [0.1 + 0.0001 * (Ps - 2000)] % /1000 psi				
		Span Error	± 0.2% of reading per 1000 psi (69 bar)				
	Over Pressure Limit	SP Range G7/A7	3626 psi (250.00 bar)				
	_	SP Range G4/A4	3626 psi (250.00 bar)				
	Burst Pressure Limit	All Span ranges	10,000 psi (689.47 bar)				
	Note: 1000" DP Range 1)	-	available with 300 psi static pressure (SP				
DP Range 3: Enhanced for Flow	0 to 1000 inches	H ₂ O (2.5 bar)					
	Reference	± 0.05% of r	eading;				
	Accuracy	for readings % reading	s less than 8:1, ± [0.05 + 0.0023(USL / Rdg)]				
	Stability	For ± 50 °F (5L for 5 years; (28 °C) temperature changes, up to 1000 r) line pressure				
	Ambient Temperature Effect per 50°F (28°C)		eading from 1:1 to 5:1, 4 (USL / RDG)] % of reading from 5:1 to				

	Static Pressure Effects	Zero Error	± 0.05% USL per 1000 psi (69 bar) For Static Pressures above 2000 psi: ± [0.1 + 0.0001 * (Ps - 2000)] % per 1000 psi		
	Over Pressure	Span Error	± 0.2% of reading per 1000 psi (69 bar)		
	Over Pressure Limit	SP Range G7/A7	3626 psi (250.00 bar)		
		SP Range G4/A4	3626 psi (250.00 bar)		
	Burst Pressure Limit	All Span ranges	10,000 psi (689.47 bar)		
	Note: 1000" DP range is not available with 300 psi static pressure (SP Range 1).				
DP Range 4: Standard	0 to 2000 psi (137.89 bar)				
	Reference Accuracy	± 0.1% of sp for spans le	an; ss than 10:1, ± [0.01(USL / span)] % span		
			ss than 10:1, ± [0.01(USL / span)] % span		
	Accuracy	for spans let ± 0.1% USL 1	ss than 10:1, ± [0.01(USL / span)] % span		
	Accuracy Stability Ambient Temperature Effect per 50°F	for spans let ± 0.1% USL 1	ss than 10:1, ± [0.01(USL / span)] % span for 1 year		
	Accuracy Stability Ambient Temperature Effect per 50°F (28°C) Static Pressure	for spans le ± 0.1% USL 1 ± (0.225% of	 ss than 10:1, ± [0.01(USL / span)] % span for 1 year f USL) from 1:1 to 50:1 ± 0.2% USL per 1000 psi (69 bar) For Static Pressures above 2000 psi: ± [0.4 + 0.0002* (Ps - 2000)] % per 1000 		
	Accuracy Stability Ambient Temperature Effect per 50°F (28°C) Static Pressure	for spans let ± 0.1% USL 1 ± (0.225% of Zero Error	ss than 10:1, ± [0.01(USL / span)] % span for 1 year ^E USL) from 1:1 to 50:1 ± 0.2% USL per 1000 psi (69 bar) For Static Pressures above 2000 psi: ± [0.4 + 0.0002* (Ps - 2000)] % per 1000 psi		

Static Pressure Input

The following details are for the static pressure measurement of the MultiVariable sensor

•				
SP Range 1	Gauge – G6	–14.7 to 300 psig (–1.01 to 20.7 barg)		
	Absolute – A6	0 to 300 psia (–1.01 to 20.7 bara)		
SP Range 2	Gauge – G7	–14.7 to 1500 psig (–1.01 to 103.4 barg)		
	Absolute – A7	0 to 1500 psia (–1.01 to 103.4 bara)		
SP Range 3	Gauge – G4	–14.7 to 3600 psig (–1.01 to 250 barg)		
	Absolute – A4	0 to 3600 psia (–1.01 to 250 bara)		
Reference Accuracy	Standard	± 0.1% span; For spans less than 5:1, ± [0.017 (USL/Span)] % span		

		Enhanced	± 0.075% span; For spans less than 5:1, ± [0.013 (USL/Span)] % span		
		Enhanced for Flow	± 0.05% span; For spans less than 5:1, ± [0.006 (USL/Span)] % span		
	Stability	Standard	± 0.1% USL for 1 year		
		Enhanced	± 0.125% USL for 5 years		
		Enhanced for Flow	± 0.125% USL for 5 years		
	Ambient Temperature	Standard	± (0.175% USL) from 1:1 to 10:1, ± (0.225% USL) from 10:1 to 25:1		
	Effects per 28°C (50°F)	Enhanced	± (0.050% USL + 0.125% span) from 1:1 to 10:1, ± (0.060% USL + 0.175% span) from 10:1 to 25:1		
		Enhanced for Flow	± (0.040% USL + 0.060% span) from 1:1 to 10:1, ± (0.050% USL + 0.150% span) from 10:1 to 40:1		
Inputs					
Temperature Input (RTD/PRT)	Туре	Pt100 2-, 3-, or 4-wire (software selectable)			
	Measuring Range	–200 to +850°C (–328 to +1562 °F)			
	Reference Accuracy	+/- 0.1°C from –60 to 200 °C (±0.18 °F from –76 to +392 °F) +/- 0.07°C from –30 to 60 °C (±0.126 °F from –22 to +140 °F)			
	Ambient Temperature Effect	–30 to 60 °C	+/- 0.017 °C per 10 °C (+/- 0.03 °F per 18 °F) from the calibration temperature		
		–60 to 200 °C	+/- 0.034 °C per 10 °C (+/- 0.06 °F per 18 °F) from the calibration temperature		
	Calculation Type	User selectable	Callendar–Van Dusen		
		between	IEC 751/DIN 43760 (α 0.00385/°C)		
		-	IEC (α 0.003920/°C)		
	Scan Rate	1 second			
	Voltage Input Impedance	Greater than 3 M	Ω DC		
	Excitation Current	205 µA			
	Surge Suppression	36 Vdc			
	Common Mode Rejection	100 dB at DC			
	Normal Mode Rejection	100 dB at 50/60 H	lz		
Outputs					

	Current Mode 500 mA maximum					
	Operating 3 Voltage Range	30 Vdc maximum				
	Frequency 5	50 Hz maximum				
	Output Type L	Latched, momentary, toggle, TDO, or scaled pulse				
	Surge 3 Suppression	30 Vdc				
	Fault Mode U	User-entered default value or last good value				
Power						
External DC Power Supply	5.7 Vdc to 30 Vdc exte	ternal supply (Max power at 10 watts)				
Optional	Internal mounted 4.5	.5 Ah 6.0 Vdc battery				
Rechargeable Lead Acid Battery	The battery can power the unit for up to 25 days without any solar charging depending on display and communications usage, and can be charged by a 6-watt solar panel or from a DC supply for backup					
	Note: This option is available with Class 1 Div1 and Class 1 Div 2 approvals only.					
Lithium Battery Pack	10 Vdc, 41 Ah					
	Required when using autonomous measurement mode					
	Allows operation for one year in autonomous measurement mode with monthly data collection and 30 minutes per month of display use. Battery life is affected by ambient temperature, as shown in the following table:					
	Ambient Temper	erature Typical Impact on Battery Life				
	25°C	0%				
	-30°C	23%				
	0°C	19%				
	55°C	34%				
	72°C	38%				
	Note: This option is available only with Class 1 Div1 and Class 1 Div 2 approvals. Lithium battery shipping restrictions apply.					
Solar Panel	If ordered with the rechargeable battery option, the FB1100 includes an integral solar regulator					
	Can be supplied with an optional 6-watt 6 Vdc solar power					
	The solar panel input is rated to a maximum of 30V and 1.5A. A minimum of 8V is required to charge the battery.					
	Note: This option is a	available only with Class 1 Div1 and Class 1 Div 2 approvals.				
SRAM Battery	Lithium coin cell type	e BR2335 or BR2330				
	Typical battery life 5-7 years with power; 10,000 hours without power					

Power Modes

To keep power consumption to a minimum, especially for remote sites, the FB1100 can run in two different power modes, low and standard. The FB1100 normally runs in low power mode for standard metering applications.

When running in low power mode, the radio power control function is used to switch to standard power mode and enable the serial ports. During communication periods, the unit uses the standard power mode and then automatically reverts to low power mode when the communication period is over.

The local display and FBxWifi can be configured to switch off after a period of inactivity (configurable between 1 and 60 minutes) or be permanently left on.

When running in low power mode, if you need to use more than the default number of data points for logging, consult the *Emerson FB1100 Flow Computer Instruction Manual* (D301752X012) to determine the possible impact on power consumption.

The figures below are typical power values in mW measured at room temperature.

Low Power Mode		egral multivariable erature measureme	36 mW @ 6Vdc				
	Additional Load	Display and Back	klight active	296 mW @ 6Vdc			
	Options	FBxWifi		315 mW @ 6Vdc			
		FBxWifi and Disp	olay active	340 mW @ 6Vdc			
		DO active (1 Hz, no load)	50:50 duty cycle,	10 mW @ 6Vdc			
Standard Power Mode	Base unit with integral 209 mW @ 6 multivariable DP and pressure sensor and temperature measurement		209 mW @ 6Vdc	224 mW @ 265 mW @ 12Vdc 24Vdc			
	Additional Load Options	Display and Backlight active	162 mW @ 6Vdc	168 mW @ 12Vdc	178 mW @ 24Vdc		
		FBxWifi	189 mW @ 6Vdc	185 mW @ 12Vdc	200 mW @ 24Vdc		
		FBxWifi and Display active	204 mW @ 6Vdc	207 mW @ 12Vdc	221 mW @ 24Vdc		
		DO active (1 Hz, 50:50 duty cycle, no load)	21 mW @ 6Vdc	23 mW @ 12Vdc	20 mW @ 24Vdc		
Physical							
Construction	Die-cast aluminum, painted, with wire sealable end caps, or Stainless steel (AISI 316/ASTM CF8M), unpainted, with wire sealable end caps						
Ingress Protection	IEC 60529 IP66 & I	NEMA 4X					
Dimensions	11.715 in. H by 6.0	in. W by 9.426 in. I	D (297.7 mm H by 1	52.4 mm W by 239.4	4 mm D)		
Mounting	2 in. pipe or direct	manifold					
Wiring	Size 12 to 28 Ame	rican Wire Gauge (/	AWG) (0.3 to 2.0 mr	n diameter)			
Wiring Access		4 conduit entry points 3/4 in. NPT (standard) M20 (optional)					

Weight	FB1100 aluminum housing with MVS coplanar flange sensor: 6.75 Kg (14.9 lb)				
	FB1100 stainless s	teel housing with MVS copl	anar flange sensor: 13.27 Kg (29.5 lb)		
	Optional Lead Acid	d battery: 0.86 Kg (1.9 lb)			
	Optional Lithium	Battery: 0.95 Kg (2.1 lb)			
Display	Optional backlit lic	quid crystal display			
HMI	20 characters per	line; 4 lines in display			
Environmental					
Operating Temperature	 -40 °C to +80 °C (-40°F to +176 °F) (see ambient temps in Approvals section) Note: Check Approvals section for any restrictions. The display exhibits increased response time and decreased contrast at temperatures below -30°C (-22 °F). 				
Storage Temperature	–40 °C to +85 °C (-	-40°F to +185 °F)			
Operating Humidity	5 to 95%, non-con	densing			
Conformal Coating	All boards are con environments.	formal coated with a coatir	ng that complies with ANSI/ISA 71.04 Class G3		
Environmental Rating	Product conforms to ANSI/ISA 71.04 Class G3 environmental standards with all conduit openings sealed.				
Electro Magnetic Compatibility	The following EMC Emissions and Immunity are evaluated per EMC directive 2014/30/EU. Harmonized standards used:				
	EN 61326-2-3-2013 Immunity EN 61326-1-2013 Emissions				
Immunity	EN 61000-4-3 (Rad EN 61000-4-4 (Fast EN 61000-4-5 (Sur EN 61000-4-6 (Con EN 61000-4-8 (Pow EN 61000-4-17 (Vo EN 61000-4-29 (Vo *Meets CE complian	ges) nducted RF) ver Frequency Magnetic Fie ltage Ripple) ltage Dips and Interrupts)	ents (deviations < 1% span for RTD and Pressure		
Radiated Emissions	EN 55022 Class A				
Vibration	2g over 10 to 150 l 1g over 150 to 200				
Approvals					
Product Markings for Hazardous Locations	UL	Class 1, Div 1 Groups C, D, Temperature Code, T6 Class 1, Div 2 Groups A, B, C, D, Temperature Code T4			
		Ambient Temperature	Aluminum enclosure -40 °C to +80°C (-40 °F to +176 °F) (no battery) -40 °C to +80°C (-40 °F to +176 °F) (with rechargeable lead acid battery) -40 °C to +80°C (-40 °F to +176 °F) (with integral lithium battery		

		Evaluated per Approval	Per Class 1, Div 1:
		Standards	UL 1203 5 th Ed.
			UL/IEC 61010-1 Part 1 3 rd Ed.
			CSA C22.2 No. 30-M1986
			CSA C22.2 No. 61010-1-12 Part 1 3 rd Ed.
			Per Class 1, Div 2:
			ANSI/ISA 12.12.01-2015
			CSA C22.2 No. 213-15 CSA C22.2 NO. 61010-1-12 Part 1 3 rd Ed
			UL61010-1 Part 1 3 rd Ed
	UL	ATEX Cert: DEMKO 15 ATEX	(1349)
	-	IECEx Cert: IECEx UL 15.002	
		Ex db IIB T4 Gb, –40°C to +8	80°C
		UL22UKEX2397X	
		Ambient Temperature	–40 °C to +80 °C (–40 to +176 °F)
		(کیکر _{II 2 G.}	
		UK CA	EMC Directive 2016
		Evaluated per Approval	Directive 2014/34/EU
		Standards:	EN IEC 60079-0:2018
			EN 60079-0:2017
			EN 60079-1:2014
		ATEX Cert: DEMKO 15 ATEX IECEx Cert: UL 15.0044X Ex ec IIC T4 Gc UL22UKEX2396X	X 1367X
		Ambient Temperature	–40 °C to +80 °C (–40 to +176 °F)
		Ex III 3 G.	
		Evaluated per Approval	Directive 2014/34/EU
		Standards:	IEC 60079-0:2017
			IEC 60079-7:2017
			EN IEC 60079-0:2018 EN IEC 60079-7:2015 + A1:2018
			proval requires the use of an external DC power
		supply.	
roduct Markings for Aetrology	Measurement (Industry) Canada	Device Type: Conversion De Approval Type: Category 3, Approved For: Natural Gas	Туре В
/liscellaneous opprovals	Customs Union	EAC	
		TR CU 004/2011, TR CU 020 Conforms to the requireme Customs Union	/2011 ents of the technical regulations of the

RoHS2	Device with integral MVS or SP Sensor : RoHS (2) EU Directive 2011/65/EU: This product may be considered out- of-scope when used for the intended design purpose in a Large Scale Fixed Installation (LSFI). Consult <i>https://www.emerson.com/compliance</i> for up-to-date product
	information.
RoHS	
NEPSI China	NEPSU NEPSU
	National Supervision and Inspection Centre for Explosion Protection and Safety of Instrumentation Cert. No. GYJ18.1015X Ex d IIB T4 Gb
	Cert. No. GYJ17.1350X Ex Na IIC T4 Gc
CCOE India	
	Chief Controller of Explosives Approval No. A/P/HQ/MH/104/7674 (P568673) Ex db IIB T4 Gb
	Approval No. A/P/HQ/MH/104/5887 (P420946) Ex Na IIC T4 Gc
KOREA (KC)	EMC - Broadcasting and communication Equipment Cert. No. C1E5-0B70-8AB8-9CBC
NMi	Mİ
	Report Numbers: NMi-1901499-02 & 1901499-01 API Chapter 21.1:2013 compliance for "Flow measurement using Electronics Metering Systems – Electronic Gas Measurement" and independent verification for natural gas properties and flow calculations Report Number: NMi-3646138-04 API Chapter 21.2:2016
	Compliance for (Flow measurement using Electronic Metering System – Electronic Liquid Volume Measurement using positive displacement and turbine meters

Model/Seg	Description	Approval	Selection
Flow Compu	Jter		
00	FB1100 Flow Computer		FB1100
Hazardous	Area Approvals		
10	Class 1 Div1 cULus		A1
	IECEx/UKCA Ex db Flameproof		A2
	ATEX/UKCA Ex db Flameproof		A3
	Class 1 Div2 cULus		A4
	IECEx/UKCA Ex ec		A5
	ATEX/UKCA Ex ec		A6
Metrology A	Approvals		
20	Not required		B0
	Measurement Canada	A1, A4	B1
	Notes : Available only with the following sensor options:		
	 DP Range of 250" H2O (B222, B122) and 1000" H2O (B223, B123) 		
	• SP Range of 1500 psi (G7, A7) and 3600 psi (G4, A4)		
Housing Op	tions		
30	Coated aluminum with sensor, ¾" NPT conduit	A1, A2, A3, A4, A5, A6	C1
	Coated aluminum with sensor, 20mm conduit	A1, A2, A3, A4, A5, A6	C2
	Stainless steel with sensor, ¾" NPT conduit	A1, A2, A3, A4, A5, A6	С3
	Stainless steel with sensor, 20mm conduit	A1, A2, A3, A4, A5, A6	C4
Power Opti	ons		
40	DC supply with internal 6V 4.5 Ah lead acid re-chargeable back-up battery and solar regulator (solar panel supply by others)	A1, A4	D1
	DC supply (no internal battery)	A1, A2, A3, A4, A5, A6	D2
	Standalone lithium battery only, "unplugged"	A1, A4	D3
	Remote-mount 6W solar panel, 10 feet cable, internal solar regulator, and internal battery (C1 D2) Note:	A1, A4	D4
	The 6W solar panel has C1 D2 approval only, so if option D4 is ordered with C1 D1 approval, the solar panel must still be installed in a C1 D2 area.		
	Integral mount solar panel and internal battery (C1 D2)	A4	D5
Local Opera	itor Interface Display		
50	Not required	A1, A2, A3, A4, A5, A6	E0

Model/Seg	Description	Approval	Selection
	Display included	A1, A2, A3, A4, A5, A6	E1
Measureme	nt Type/Pressure Sensors		
60	Integral Multivariable; DP & Static P	A1, A2, A3, A4, A5, A6	F1
Multivariab	le Sensor (includes Differential P, Static P, and Material/Flar	nge Selections)	
70	Multivariable Sensor (includes Differential P, Static P, and Mat	erial/Flange Type Selections	5)
Differential	Pressure Range & Accuracy		
71	25 Inches H2O (62.3 mbar) DP, 0.1% Accuracy Note :	A1, A2, A3, A4, A5, A6	B221
	25" DP option B221 is available only with static pressure options G4 or A4 and the maximum pressure is limited to 2000 psi.		
	250 Inches H2O (623 mbar) DP, 0.1% Accuracy	A1, A2, A3, A4, A5, A6	B222
	250 Inches H2O (623 mbar) DP, 0.075% Accuracy	A1, A2, A3, A4, A5, A6	B122
	250 Inches H2O (623 mbar) DP, 0.05% Reading Accuracy, Enhanced for Flow	A1, A2, A3, A4, A5, A6	B322
	Note:		
	Enhanced For Flow sensor with the SP ranges G6, A6, G7, A7 (300/1500 psi) is only available with the Stainless Steel option 2E12 or Traditional Flange option 2F12. It is not available in the Hastelloy option 3E13. SP Range G4, A4 (3600 psi) is available in all material and flange types.		
	250 Inches H2O (623 mbar) Extended Range DP, 0.075% Accuracy	A1, A2, A3, A4, A5, A6	B12A
	Note:		
	250" Extended Range is only available with SP range G6, A6, G7, A7 and not available with SP range G4, A4		
	1000 Inches H2O (2.5 bar) DP, 0.1% Accuracy	A1, A2, A3, A4, A5, A6	B223
	Note:		
	1000" DP range is not available with 300 psi static pressure.		
	1000 Inches H2O (2.5 bar) DP, 0.075% Accuracy	A1, A2, A3, A4, A5, A6	B123
	Note : 1000" DP range is not available with 300 psi static pressure.		
	1000 Inches H2O (2.5 bar) DP, 0.05% Reading Accuracy,	A1, A2, A3, A4, A5, A6	B323
	Enhanced for Flow Notes:		
	 1000" DP range is not available with 300 psi static pressure. 		
	 Enhanced For Flow sensor with the SP ranges G6, A6, G7, A7 (300/1500 psi) is only available with the Stainless- Steel option 2E12 or Traditional Flange option 2F12. It is not available in the Hastelloy option 3E13. SP Range G4, A4 (3600 psi) is available in all material and flange types. 		

Model/Seg	Description	Approval	Selection
	2000 psi (137.9 bar) DP, 0.1% Accuracy	A1, A2, A3, A4, A5, A6	B225
	Note:		
	2000 psi DP range is only available with SP range G4 3626 psi and Hastelloy Diaphragm 3E13. Any other SP Range		
	including A4 is not available.		
Static Press	ure Range (for use with multivariable sensor B22 <i>n</i> or B12 <i>n</i> a	bove)	
72	MV 300 psi gauge (20.7 barg)	A1, A2, A3, A4, A5, A6	G6
	Note:		
	 1000" DP range is not available with 300 psi static pressure 		
	• Enhanced For Flow sensor with the SP ranges G6, A6, G7, A7 (300/1500 psi) is only available with the Stainless- Steel option 2E12 or Traditional Flange option 2F12. It is not available in the Hastelloy option 3E13. SP Range G4, A4 (3600 psi) is available in all material and flange types.		
	MV 300 psi absolute (20.7 bara)	A1, A2, A3, A4, A5, A6	A6
	Note:		
	 1000" DP range is not available with 300 psi static pressure 		
	• Enhanced For Flow sensor with the SP ranges G6, A6, G7, A7 (300/1500 psi) is only available with the Stainless- Steel option 2E12 or Traditional Flange option 2F12. It is not available in the Hastelloy option 3E13. SP Range G4, A4 (3600 psi) is available in all material and flange types.		
	MV 1500 psi gauge (103.4 barg)	A1, A2, A3, A4, A5, A6	G7
	Note:		
	Enhanced For Flow sensor with the SP ranges G6, A6, G7, A7 (300/1500 psi) is only available with the Stainless-Steel option 2E12 or Traditional Flange option 2F12. It is not available in the Hastelloy option 3E13. SP Range G4, A4 (3600 psi) is available in all material and flange types.		
	MV 1500 psi absolute (103.4 bara)	A1, A2, A3, A4, A5, A6	A7
	Note:		
	Enhanced For Flow sensor with the SP ranges G6, A6, G7, A7 (300/1500 psi) is only available with the Stainless-Steel option 2E12 or Traditional Flange option 2F12. It is not available in the Hastelloy option 3E13. SP Range G4, A4 (3600 psi) is available in all material and flange types.		
	MV 3600 psi gauge (250 barg)	A1, A2, A3, A4, A5, A6	G4
	Note:		
	When used with 25" DP option, maximum working pressure is 2000 psi/137.9 Bar.		
	MV 3600 psi absolute (250 bara)	A1, A2, A3, A4, A5, A6	A4
	Note:		

Model/Seg	Description	Approval	Selection	
	When used with 25" DP option, maximum working pressure is 2000 psi/137.9 Bar.			
Sensor Mat	erial and Flange Type			
73	Stainless steel sensor and coplanar flange	A1, A2, A3, A4, A5, A6	2E12	
	Hastelloy [®] diaphragm and Hastelloy coplanar flange Note :	A1, A2, A3, A4, A5, A6	3E13	
	Not available with 25" H2O DP range and 300/1500 psi range with 0.05% reading accuracy enhanced for flow options			
	Stainless steel sensor and traditional flange Note :	A1, A2, A3, A4, A5, A6	2F12	
	Traditional Flange is not available with 0.1% Accuracy sensor			
Sensor Mat	erial Certificates			
74	Not required	A1, A2, A3, A4, A5, A6	Q0	
	3.1 B Traceability certs to EN 10204	A1, A2, A3, A4, A5, A6	Q8	
	NACE MRO 175/ISO 15156 requires Hastelloy Diaphragm Option Note : Available only with 3E13	A1, A2, A3, A4, A5, A6	Q15	
	NACE MRO 103 - requires Hastelloy Diaphragm Option Note : Available only with 3E13	A1, A2, A3, A4, A5, A6	Q25	
Base Inputs	s & Outputs			
80	PRT/RTD input (2, 3, or 4 wire) and Single Discrete Output	A1, A2, A3, A4, A5, A6	G1	
Reserved				
90	Not required		H0	
FBxWifi™				
100	Not required	A1, A2, A3, A4, A5, A6	JO	
	FBxWifi with internal antenna (mounted inside enclosure)	A1, A2, A3, A4, A5, A6	J1	
	FBxWifi with local antenna mounted on conduit entry (C1 D2, IEC Ex N, & ATEX Ex N)	A4, A5, A6	J2	
Reserved				
110	Not required		К0	
Reserved				
120	Not required		LO	
Sensor Cali	bration Certificates			
130	Not required	A1, A2, A3, A4, A5, A6	M0	
	Pressure/MVS (DP &/or Static P) Sensor & PRT/RTD input	A1, A2, A3, A4, A5, A6	M1	

Model/Seg	Description	Approval	Selection
140	Not required		N0
Reserved			
150	Not required		P0
Mounting B	racket		
160	Not required		R0
	2" Pipe & panel mounting bracket & bolts (stainless steel) for coplanar flange, options 2E12 & 3E13	A1, A2, A3, A4, A5, A6	R1
	2" Pipe mounting bracket & bolts (stainless steel) for traditional flange, for use with option 2F12	A1, A2, A3, A4, A5, A6	R2
	2" Pipe mounting bracket & bolts (carbon steel) for traditional flange, for use with option 2F12	A1, A2, A3, A4, A5, A6	R3
Meter Runs	(Streams)		
170	Single Stream	A1, A2, A3, A4, A5, A6	S1
Fluid Types	& Calculations		
180	Natural Gas	A1, A2, A3, A4, A5, A6	T1
Reserved			
190	Not required		U0
Reserved			
200	Not required		V0
Reserved			
210	Not enabled		W0

Sensor Summary for FB1000 and FB2000 Series Flow Computers

The following table identifies the available possible sensor combinations for the FB1000 and FB2000 Series Flow Computers.

			Coplanar Flange		Coplanar Flange		Traditional Flange	
DP		SP	Stainle	ess Steel	Hast	telloy	Stainle	ss Steel
Range	Accuracy	Range	e Gauge	Absolute	Gauge	Absolute	Gauge	Absolute
25″	0.1%	2000 psi	Available	Available	N/A	N/A	N/A	N/A
250"	0.1%	300 psi	Available	Available	Available	Available	N/A	N/A
		1500 psi	Available	Available	Available	Available	N/A	N/A
		3626 psi	Available	Available	Available	Available	N/A	N/A
250"	0.075%	300 psi	Available	Available	Available	Available	Available	Availabl
		1500 psi	Available	Available	Available	Available	Available	Availabl
		3626 psi	Available	Available	Available	Available	Available	Availabl
250"		300 psi	Available	Available	N/A	N/A	Available	Available
Enhanced for	0.05% of Reading	1500 psi	Available	Available	N/A	N/A	Available	Available
Flow	Reading	3626 psi	Available	Available	Available	Available	Available	Available
250"		300 psi	Available	Available	Available	Available	Available	Available
Extended	0.075%	1500 psi	Available	Available	Available	Available	Available	Available
1000″	0.1%	1500 psi	Available	Available	N/A	N/A	N/A	N/A
		3626 psi	Available	Available	N/A	N/A	N/A	N/A
1000″	0.075%	1500 psi	Available	Available	Available	Available	Available	Availabl
		3626 psi	Available	Available	Available	Available	Available	Availabl
1000"	0.05% of	1500 psi	Available	Available	N/A	N/A	Available	Available
Enhanced for Flow	Reading	3626 psi	Available	Available	Available	Available	Available	Available
2000 psi	0.1%	3626 psi	N/A	N/A	Available	N/A	N/A	N/A

For customer service and technical support, visit *Emerson.com/Guardian*.

North America and Latin America:

Emerson Energy and Transportation Solutions 6005 Rogerdale Road Houston, TX 77072 U.S.A. T +1 281 879 2699 | F +1 281 988 4445 *Emerson.com/SCADAforEnergy*

United Kingdom:

Emerson Process Management Limited Fosse House, 6 Smith Way Grove Park, Enderby Leicester LE19 1SX UK T +44 0 870 240 1978

Europe:

Emerson S.R.L Regulatory Compliance Shared Services Department Company No. J12/88/2006 Emerson 4 Street Parcul Industrial Tetarom 11 Romania T +40 374 132 000

Middle East/Africa:

Emerson Energy and Transportation Solutions Emerson FZE P.O. Box 17033 Jebel Ali Free Zone – South 2 Dubai U.A.E. T +971 4 8118100 | F +971 4 8865465

Asia-Pacific:

Emerson Energy and Transportation Solutions 1 Pandan Crescent Singapore 128461 T +65 6777 8211| F +65 6777 0947 © 2017-2024 Bristol Inc. All rights reserved.

This publication is for informational purposes only. While every effort has been made to ensure accuracy, this publication shall not be read to include any warranty or guarantee, express or implied, including as regards the products or services described or their use or applicability. Bristol Inc. (hereinafter "Energy and Transportation Solutions" or ETS) reserves the right to modify or improve the designs or specifications of its products at any time without notice. All sales are governed by ETS terms and conditions which are available upon request. ETS accepts no responsibility for proper selection, use or maintenance of any product, which remains solely with the purchaser and/or end-user. Emerson and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

