

# Emerson™ Smart Wireless Gateway 1552WU



- Gateway connects wireless self-organizing networks with any host system with integrated Wi-Fi backhaul
- Easy configuration and management of *WirelessHART*® self-organizing networks
- Easy integration into control systems and data applications through Wireless LAN connections
- Seamless integration into AMS™ Device Manager and DeltaV™ automation system
- Greater than 99% reliability of field wireless data integrity with industry proven security
- Smart Wireless capabilities extends the full benefit of PlantWeb™ architecture to previously inaccessible locations
- Secure field wireless communications built into *WirelessHART*
- Secure Wi-Fi communications provided by defense-in-depth wireless intrusion prevention solution from Cisco®

# Smart Wireless Gateway and Access Point

## Gain real-time process information with greater than 99% wireless field wireless data reliability

- The Smart Wireless Gateway 1552WU automatically manages wireless communications in constantly changing environments for both Wi-Fi and *WirelessHART*.
- Native integration with DeltaV and Ovation™ automation systems provides simple and fast commissioning for wireless field networks.
- Connect to data historians, legacy host systems, and other via a LAN applications through Ethernet, Modbus®, OPC, EtherNet/IP™, and HART® outputs.



### Guarantee system availability with redundant gateway access points

- Never lose the wireless network with hot standby capability and automatic fault detection.
- Gateway access points function as a single system, eliminating the need for duplicate host integration.
- One click configuration of the Gateway redundancy feature

### Complete *WirelessHART* network configuration tools provided with each Gateway access point

- The integrated web interface allows easy configuration of the wireless network and data integration without the need to install additional software.
- Complimentary AMS Wireless Configurator software provides Emerson Device Dashboards to configure devices and view diagnostic data.
- Drag and drop device provisioning enables a secure method to add new wireless devices to the wireless field network.



## Contents

Emerson’s Smart Field Wireless Solution . . . . .	page 3	Specifications . . . . .	page 7
Emerson’s Smart Plant Wireless Solution . . . . .	page 4	Product Certifications . . . . .	page 10
Ordering Information . . . . .	page 6		

# Emerson's Smart Field Wireless Solution

## IEC 62591 (WirelessHART)... the industry standard

### Self-organizing, adaptive mesh routing

- No wireless expertise required; network automatically finds the best communication paths
- The self-organizing, self-healing network manages multiple communication paths for any given device. If an obstruction is introduced into the network, data will continue to flow because the device already has other established paths. The network will then lay in more communication paths as needed for that device.

### Reliable wireless architecture

- Standard IEEE 802.15.4 radios
- 2.4 GHz ISM band sliced into 15 radio-channels
- Time synchronized channel hopping to avoid interference from other radios, Wi-Fi, and EMC sources and increase reliability
- Direct sequence spread spectrum (DSSS) technology delivers high reliability in challenging radio environment

## Emerson's Smart Wireless

### Seamless integration via a LAN to all existing host systems


- Native integration into DeltaV and Ovation is transparent and seamless
- Gateways interface with existing host systems via a LAN, using industry standard protocols including OPC, Modbus TCP/IP, and EtherNet/IP

### Layered security keeps your network safe

- Ensures that data transmissions are received only by the Smart Wireless Gateway
- Network devices implement industry standard encryption, authentication, verification, anti-jamming, and key management
- Third party security verification including Achilles and FIPS197- user based login and enforced password strength. Password strength monitoring, user based log in, password reset requirements, automatic lockout, password expiration requirements. Based on guidelines from ISA99.03.03 standard approved level two.

### SmartPower™ Solutions

- Optimized Emerson instrumentation, both hardware and software, to extend power module life
- SmartPower technologies enable predictable power life



# Emerson's Smart Plant Wireless Solution

## Scalable

Emerson Process Management can provide a wireless network solution that exactly meets your needs today, while providing flexibility for future wireless mesh infrastructure growth as your needs expand. Emerson's Smart Wireless Plant Solutions can also scale to the types of applications you utilize in your wireless plant. For example, each Wi-Fi mesh node installed to backhaul *WirelessHART* data can also be used as a "hot spot" for your mobile workers to access live plant data, to wirelessly stream video data, or track personnel with Wi-Fi RFID tags.

## Reduced cost

When compared to the cost of engineering and trenching or pulling a fiber optic cable to each of the *WirelessHART* gateways, a fully integrated wireless backhaul solution can be deployed for less cost when the field network is separated from the control room by large distances, difficult terrain, or bodies of water.

## Safer deployment

Trenching or pulling a fiber optic cable in a live process area puts workers in the process area for long periods of time - exposing them to potential hazards and risking disruptions to process operations.

## Secure and reliable communications

All communications on the wireless plant network are fully secure using AES 128-bit encryption. The integrity of the wireless communication network is continuously monitored and alerts can be sent to administrators if degradation of the wireless signal is detected.

Wi-Fi defense-in-depth provided by Cisco's wireless intrusion prevention solution secures the Wi-Fi network from hackers, eavesdroppers, and ensures only authorized personnel have access to the resources they need.

## Wireless engineering services

Wireless engineering services are critical to the success of a wireless plant network deployment. Emerson offers a comprehensive services portfolio to help you design and deploy a wireless solution.

## Site assessment (wireless FEED)

A site assessment is not needed for the *WirelessHART* field instrumentation network, but one will be required for the Wi-Fi network communications equipment being installed to provide good Wi-Fi coverage for the desired plant area.

For the Wi-Fi wireless FEED, Emerson engineers visit your plant site to conduct a Radio Frequency (RF) study, determine access point locations and collect other on-site information.

## Network design and planning

Based on the site survey results and your control system requirements, Emerson engineers design the overall wireless mesh architecture including the detailed network infrastructure, network monitoring tools, and integrated security.

## Physical network installation management

Engineers work with you to install the wireless mesh network equipment based on the detailed network design.

## System commissioning

The wireless mesh network is brought online and commissioned onsite. Complete site acceptance testing is performed with your engineers.

## Training

Emerson will work with you to specify a training curriculum that meets your specific needs.

## Support

Emerson delivers SureService wireless life-cycle services through our engineering centers and global service organizations. Emerson's wireless life cycle services are designed to help you maintain system uptime, apply wireless technology for better business results and preserve your intellectual and capital investment.

## Additional wireless plant solutions

### Mobile worker

Depending on your needs, Emerson can provide Wi-Fi access throughout your process plant or just in specific locations to connect field personnel with Wi-Fi enabled PDAs or laptops to plant or office network applications.

### Video

Easily add video cameras in remote areas of your plant to monitor the process or site for emissions, safety and security.

### Safety mustering

Instead of taking a time-consuming role call in an emergency, a safety mustering solution can electronically determine the mustered status of all personnel in the process plant.

### Location tracking

Plant personnel can be tracked throughout the plant site with varying degrees of accuracy depending on your site's needs. Emerson's location tracking solution is flexible to provide a good, better, or best capability depending on your site's needs and budget.

Obsolete

## Ordering Information

For inquiries and ordering information, contact your local Emerson sales office. Prior to order acceptance, Emerson Process Management will issue a written proposal for your review and approval to ensure that scope, deliverables, timing, and budget meet your needs and expectations.

For more information, visit our website at [EmersonProcess.com/SmartWireless](http://EmersonProcess.com/SmartWireless).

Obsolete

# Specifications

## Functional specifications

### Input power

24VDC 2.5 Amp nominal (19–30 VDC), 39 watts

12VDC nominal (11.4–15 VDC) non-hazardous installations only

### Environmental

#### Operating temperature

-40 to 55 °C (-40 to 131 °F) plus Solar Loading

#### Storage temperature

-50 to 85 °C (-58 to 185 °F)

#### Humidity

0-100% (condensing)

#### Wind resistance

- Up to 100 MPH sustained winds
- Up to 165 MPH wind gusts

### Environmental ratings

- IP67
- NEMA® Type 4

### Compliance

#### Safety

- UL 60950-1, 2nd edition
- CAN/CSA-C22.2 No. 60950-1, 2nd edition
- IEC 60950-1, 2nd edition
- EN 60950-1, 2nd edition
- ANSI/ISA 12.12.01
- CSA C22.2 No 213
- IEC/EN 60079-0
- IEC/EN 60079-15
- CSA: Class I, Division 2, Groups A, B, C and D
- ATEX: Class I, Zone 2; Ex nA II, T5

### Immunity

- ≤ 5 mJ for 6kV/3kA @ 8/20 ms waveform
- ANSI/IEEE C62.41
- EN61000-4-5 Level 4 AC Surge Immunity
- EN61000-4-4 Level 4 Electrical Fast Transient Burst Immunity
- EN61000-4-3 Level 4 EMC Field Immunity
- EN61000-4-2 Level 4 ESD Immunity
- EN60950 Overvoltage Category IV

### Radio approvals

- FCC Part 15.247, 15.407
- FCC Bulletin OET-65C
- RSS-210
- RSS-102
- AS/NZS 4268.2003
- EN 300 328
- EN 301 893

### EMI and susceptibility

- FCC part 15.107, 15.109
- ICES-003
- EN 301 489-1, -17

## Communication specifications

### Wiring

Cat5E shielded cable

### Wiring distance

328 ft (100 m)

### Ethernet

10/100/1000BASE-T Ethernet, autosensing (RJ-45)

### Maximum transmit power for Wi-Fi

#### 2.4 GHz

- 802.11b (Complementary Code Keying [CCK])
  - 28 dBm with two antennas
- 802.11g (non HT duplicate mode)
  - 28 dBm with two antennas

- 802.11n (HT20)
  - 28 dBm with two antennas
- 802.15.4
  - 18 dBm with one antenna

#### 5 GHz

- 802.11a
  - 28 dBm with two antennas
- 802.11n non-HT duplicate (802.11a duplicate) mode
  - 28 dBm with two antennas
- 802.11n (HT20)
  - 27 dBm with two antennas
- 802.11n (HT40)
  - 27 dBm with two antennas

#### Maximum transmit power from *WirelessHART*

Maximum of 10 mW (10 dBm) EIRP

#### EMC performance

Meets all industrial environment requirements of EN61326 and NAMUR NE-21. Maximum deviation <1% span during EMC disturbance.<sup>(1)</sup>

#### Wi-Fi antenna options

The 1552WU has six external type N connectors for Wi-Fi antennas: Three for 2.4 GHz and three for 5 GHz. These IP66 rated antennas may be connected directly, or via an appropriate cable. The following Cisco antennas are supported:

- AIR-ANT2480V-N (2.4 GHz, 8 dBi, omni, 19.5-in. long)
- AIR-ANT5180V-N (5 GHz, 8 dBi, omni, 11-in. long)
- AIR-ANT5114P2M-N= (5 GHz, 14 dBi, dual polarized patch)

#### *WirelessHART* antenna

Remote mount Omnidirectional antenna (2.4GHz, 6 dBi) connected with a 50 ft low loss cable.

## Physical specifications

### Dimensions (W × L × H)

12.0-in. × 7.8-in. × 6.4-in. (30.48 cm × 19.81 cm × 16.26 cm)  
(including antenna mount)

### Weight

1552WU: 17.6 lb (8 kg)

Pole mounting bracket: 6.1 lb (2.8 kg)

### Material of construction

#### Housing

Aluminum, NEMA 4

#### Paint

Powder coat paint over Alodine finish plating

#### Cover gasket

Silicone tube

#### Remote antenna

Fiber glass

### Certifications

- CSA: Class I, Division 2, Groups A, B, C and D
- ATEX: Class I, Zone 2; Ex nA II, T5

### 802.11n capabilities

2 × 3 multiple-input multiple-output (MIMO) with two spatial streams

Legacy beamforming

20- and 40-MHz channels

PHY data rates up to 300 Mbps

Packet aggregation: A-MPDU (Tx/Rx), A-MSDU (Tx/Rx)

802.11 dynamic frequency selection (DFS)

Cyclic shift diversity (CSD) support

1. During surge event device may exceed maximum EMC deviation limit or reset; however, device will self-recover and return to normal operation with specified start-up time.



## Self-organizing field network specifications

### Protocol

IEC 62591 (*WirelessHART*), 2.4 - 2.5 GHz DSSS

### Maximum network size

100 wireless devices @ eight sec. or higher

50 wireless devices @ four sec.

25 wireless devices @ two sec.

12 wireless devices @ one sec.

### Supported device update rates

1, 2, 4, 8, 16, 32 seconds or 1 - 60 minutes

### Network size/latency

100 Devices: less than 10 sec.

50 Devices: less than 5 sec.

### Data reliability

> 99%

### Gateway protocols

#### Modbus

Supports Modbus TCP with 32-bit floating point values, integers, and scaled integers.

Modbus Registers are user-specified.

#### OPC

OPC server supports OPC DA v2, v3

#### EtherNet/IP

Supports EtherNet/IP protocol with 32-bit Floating Point values and Integers.

EtherNet/IP Assembly Input-Output instances are user configurable.

EtherNet/IP specifications are managed and distributed by ODVA.

### Wi-Fi security

#### Security

- Wireless bridging/mesh
  - X.509 digital certificates
  - MAC address authentication
  - Advanced Encryption Standards (AES), Temporal Key Integrity Protocol (TKIP)

- Wireless access
  - 802.11i, Wi-Fi Protected Access (WPA2), WPA
  - 802.1X authentication, including Extensible Authentication Protocol and Protected EAP (EAP-PEAP), EAP Transport Layer Security (EAP-TLS), EAP-Tunneled TLS (EAP-TTLS), and Cisco LEAP
  - Advanced Encryption Standards (AES), Temporal Key Integrity Protocol (TKIP)
  - VPN passthrough
  - IP Security (IPsec), Layer 2 Tunneling Protocol (L2TP)
  - MAC address filtering

## Gateway system security specifications

### Ethernet

Secure Sockets Layer (SSL) - enabled (default) TCP/IP communications

### Smart Wireless Gateway access

Role-based Access Control (RBAC) including Administrator, Maintenance, Operator, and Executive. Administrator has complete control of the gateway and connections to host systems and the self-organizing network.

### Self-organizing network

AES-128 Encrypted *WirelessHART* including individual session keys. Drag and drop device provisioning, including unique join keys and white listing.

### Internal firewall

User Configurable TCP ports for communications protocols, including Enable/Disable and user specified port numbers. Inspects both incoming and outgoing packets.

### Third party certification

Worldtech: Achilles Level 1 certified for network resiliency

National Institute of Standards and Technology (NIST): Advanced Encryption Standard (AES) Algorithm conforming to Federal Information Processing Standard Publication 197 (FIPS-197)

## Product Certifications

### Telecommunications Compliance

All wireless devices require certification to ensure that they adhere to regulations regarding the use of the RF spectrum. Nearly every country requires this type of product certification. Emerson and Cisco are working with governmental agencies around the world to supply fully compliant products and remove the risk of violating country directives or laws governing wireless device usage.

### FCC and IC

This device complies with Part 15 of the FCC Rules. Operation is subject to the following conditions. This device may not cause harmful interference. This device must accept any interference received, including interference that may cause undesired operation. This device must be installed to ensure a minimum antenna separation distance of 20 cm from all persons.

### Ordinary Location Certification for CSA

As standard, the 1552WU has been examined and tested to determine that the design meets basic electrical, mechanical, and fire protection requirements by CSA, a nationally recognized testing laboratory (NRTL) as accredited by the Federal Occupational Safety and Health Administration (OSHA).

#### North America

CSA Division 2, Non-Incendive  
Certificate: 1945576  
Suitable for Class I, Division 2, Groups A, B, C, and D.  
Ambient Temperature: T5(-40 °C to +55 °C)  
CSA Enclosure Type 4

### European Union Directive Information

The EC declaration of conformity for all applicable European directives for this product can be found on the Emerson website at [www.emerson.com](http://www.emerson.com). A hard copy may be obtained by contacting your local sales representative.

#### Europe

ATEX Type n  
Certificate: Sira 11ATEX4253  
ATEX Marking: II 3 G  
Ex nA II T5(T<sub>a</sub> = -40 °C to +55 °C)

#### **Special Condition for Safe Use (X):**

1. The surface resistivity of the antenna is greater than one gigaohm. To avoid electrostatic charge build-up, it must not be rubbed or cleaned with solvents or a dry cloth.

Obsolete

## Global Headquarters

### Emerson Process Management

6021 Innovation Blvd.  
Shakopee, MN 55379, USA  
+1 800 999 9307 or +1 952 906 8888  
+1 952 949 7001  
RFQ.RMD-RCC@EmersonProcess.com

## North America Regional Office

### Emerson Process Management

8200 Market Blvd.  
Chanhassen, MN 55317, USA  
+1 800 999 9307 or +1 952 906 8888  
+1 952 949 7001  
RMT-NA.RCCRFQ@Emerson.com

## Latin America Regional Office

### Emerson Process Management

1300 Concord Terrace, Suite 400  
Sunrise, FL 33323, USA  
+1 954 846 5030  
+1 954 846 5121  
RFQ.RMD-RCC@EmersonProcess.com

## Europe Regional Office

### Emerson Process Management Europe GmbH

Neuhofstrasse 19a P.O. Box 1046  
CH 6340 Baar  
Switzerland  
+41 (0) 41 768 6111  
+41 (0) 41 768 6300  
RFQ.RMD-RCC@EmersonProcess.com

## Asia Pacific Regional Office

### Emerson Process Management Asia Pacific Pte Ltd

1 Pandan Crescent  
Singapore 128461  
+65 6777 8211  
+65 6777 0947  
Enquiries@AP.EmersonProcess.com

## Middle East and Africa Regional Office

### Emerson Process Management

Emerson FZE P.O. Box 17033,  
Jebel Ali Free Zone - South 2  
Dubai, United Arab Emirates  
+971 4 8118100  
+971 4 8865465  
RFQ.RMTMEA@Emerson.com



Linkedin.com/company/Emerson-Process-Management



Twitter.com/Rosemount\_News



Facebook.com/Rosemount



Youtube.com/user/RosemountMeasurement



Google.com/+RosemountMeasurement

Standard Terms and Conditions of Sale can be found at:  
[Emerson.com/en-us/pages/Terms-of-Use.aspx](http://Emerson.com/en-us/pages/Terms-of-Use.aspx)

The Emerson logo is a trademark and service mark of Emerson Electric Co. AMS, SmartPower, PlantWeb, DeltaV, Ovation, Rosemount and Rosemount logotype are trademarks of Emerson Process Management. Cisco is a registered trademark of Cisco Systems, Inc. HART and WirelessHART are registered trademarks of FieldComm Group. EtherNet/IP is a trademark of ControlNet International under license by ODVA.

Modbus is a registered trademark of Gould Inc. NEMA is a registered trademark and service mark of the National Electrical Manufacturers Association.

All other marks are the property of their respective owners.  
© 2016 Emerson Process Management. All rights reserved.