

# RIDGID

## WD0671 6 Gallon High Performance Wet/Dry Vac



The RIDGID® 6 Gallon High Performance Wet/Dry Vac is designed for DIY'ers who want a traditionally styled, compact vac that delivers the powerful performance and rugged durability required for job site clean-up. This vacuum has a 6 gallon drum size that results in a more compact design that requires less storage space on a service truck or in a work shop or garage. And its top carry handle makes transporting easier than ever. It features the Patented Qwik Lock® Filter Fastening System that makes installing or removing your filter quick, easy & secure.

FEATURES	BENEFITS
<ul style="list-style-type: none"><li>• 2.5 Peak HP Motor</li><li>• 6 Gallon Drum</li><li>• 4 Swivel Casters</li><li>• On-board Accessory Storage</li></ul>	<p>Delivers the required power for efficient clean up of large messes.</p> <p>Provides capacity for clean-up of spills &amp; messes at job-sites and busy shops.</p> <p>Provide easy 360° mobility.</p> <p>Four built-in accessory storage pockets – 1 on each caster foot. No more searching or fumbling to find accessories.</p>
<ul style="list-style-type: none"><li>• Lower Center of Gravity</li><li>• 1-Layer Standard Filter</li><li>• Tug-A-Long® Locking Hose</li><li>• Top Carry Handle</li><li>• Included Accessories</li></ul>	<p>Design lowers the center of gravity to help prevent tipping. Compact design stores more easily.</p> <p>Pleated paper filter captures common everyday dirt.</p> <p>Positively locks 7-foot hose to the vac. Hose won't pull loose during use.</p> <p>Large top mounted carry handle for easy transporting.</p> <p>1-7/8" x 7' Tug-A-Long® Locking Hose, 2 Extension Wands, Utility Nozzle Wet Nozzle, Car Nozzle, Dusting Brush &amp; 1-Layer Paper Pleated Filter</p>




### SPECIFICATIONS

Drum Size	6 gal.
Motor	
- Peak Horsepower	2.5
- Air Watts	124
- Voltage	120
- Amps	5.8
Cord Length	10'
Construction	High Impact Polypropylene
U.L. Listed	Yes
Filter	Pleated Paper
Replacement Filters	VF4000 VF5000 VF6000
Optional Wet Filter	VF7000
Optional Filter Bag	VF3503
Accessory Size	1-7/8"
Shipping Weight	15.1 lbs.
Net Weight	12.6 lbs.



Tug-A-Long® Locking Hose



Qwik Lock Filter Fastening System



Vac with Accessories & Filter



Dry Pick-up - Workshop, Garage etc.