

强制性认证产品符合性自我声明



自我声明编号: 2020980305003328

TopWorx Inc. (生产者) 及世格流体控制(上海)有限公司(生产者授权代表) 确认知晓《强制性产品认证自我声明实施规则》以及相关产品强制性认证实施规则的要求, 对本声明承担全部法律责任。

TopWorx Inc. (生产者) 及世格流体控制(上海)有限公司(生产者授权代表) 声明以下产品已按照《强制性产品认证自我声明实施规则》以及相关产品强制性认证实施规则的要求进行检测, 符合相关标准要求; 自本声明签署之日起, 生产和销售的产品持续符合以下标准与实施规则的要求; 保存本声明涉及的技术文档至少10年; 正确使用强制性产品认证标志; 如产品或其符合性信息发生变更, 将及时更新技术文档并报送产品变更信息。


生产者名称: TopWorx Inc.
生产者地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
依据的强制性产品认证规则: CNCA-00C-008: 2019 强制性产品认证实施规则自我声明
产品名称: 磁性开关
产品系列、型号、规格: (见附页)
依据的标准: GB/T 14048.5-2017
生产企业名称: TopWorx Inc.
生产企业地址: 3300 Fern Valley Road, Louisville, KY 40213, USA

生产者联系信息

名称: TopWorx Inc.
地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
联系人: Robert Coale
电话: +1 502 873 4629
电子邮箱: Robert.Coale@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: Louisville
指定签字人:
签章:

授权代表信息

名称: 世格流体控制(上海)有限公司
地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
联系人: 刘钦海
电话: 18501785664
电子邮箱: QinHai.Liu@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: 上海市
指定签字人:
签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)




自我声明编号: 2020980305003328

产品系列、型号、规格:

7: Ui:480V; Uimp:2.5kV; Ith:4A; AC-12:Ue/Ie:240VAC/2A, 120VAC/4A; DC-12:Ue/Ie:24VDC/3A; IP66; 型号解释见附件


生产者联系信息

名称: TopWorx Inc.
地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
联系人: Robert Coale
电话: +1 502 873 4629
电子邮箱: Robert.Coale@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: Louisville
指定签字人:
签章:



授权代表信息

名称: 世格流体控制(上海)有限公司
地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
联系人: 刘钦海
电话: 18501785664
电子邮箱: QinHai.Liu@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: 上海市
指定签字人:
签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):

型号解释:

Go Switch Models 71, 71M, 73, 73M, 75, 75M and 77
E.g. Model No.: 71 1 3 5 2 2 F2 N xxxx
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

① Model 型号

71: 3/8" UNF external thread x 3-15/16" overall length, with 1/2NPT cable entry (3/8" UNF 外螺纹 x 3-15/16" 总长度, 带 1/2NPT 电缆入口)

71M: 12mm external thread x 3-15/16" overall length, with M20 cable entry (12mm 外螺纹 x 3-15/16" 总长度, 带 M20 电缆入口)

73: 5/8" UNF external thread x 3-5/8" overall length, with 1/2NPT cable entry (5/8" UNF 外螺纹 x 3-5/8" 总长度, 带 1/2NPT 电缆入口)

73M: 18mm external thread x 3-5/8" overall length, with M20 cable entry (18mm 外螺纹 x 3-5/8" 总长度, 带 M20 电缆入口)

75: 5/8" UNF external thread x 4-5/16" overall length, with 1/2NPT cable entry (5/8" UNF 外螺纹 x 4-5/16" 总长度, 带 1/2NPT 电缆入口)

75M: 18mm external thread x 4-5/16" overall length, with M20 cable entry (18mm 外螺纹 x 4-5/16" 总长度, 带 M20 电缆入口)

77: 3/4" UNF external thread x 5-13/16" overall length, with 1/2NPT cable entry (3/4" UNF 外螺纹 x 5-13/16" 总长度, 带 1/2NPT 电缆入口)

② Contact Form 连接类型

1: SPDT

③ Sensing Range 感应范围

3: 0.100" standard (Enclosure Type 2 or 6) (标准(外壳类型2或6))

4: 0.072" (Enclosure must be 3 or 7 and Approvals must be 2,3,7,8 or 9) ((外壳必须为3或7, Approvals必须为2,3,7,8或9))

5: 0.060" (Enclosure must be 4 and Approvals must be 2, 7, 8 or 9) ((外壳必须为4, Approvals必须为2,7,8或9))

6: 0.040" standard (Model 71) (标准(型号71))

④ Outlet Position 出口位置

5: Bottom, or opposite of the sensing face of switch 开关传感面的底部或对面

⑤ Enclosure Material 外壳材料

2: 303 stainless steel (rated 2,000 psi) (Sensing must be 3 or 6) (303 不锈钢(额定压力2,000 psi)(传感必须为3或6))

3: Hi Pressure-303 stainless steel (rated 5,000psi) (Models 73-77) (Sensing must be 4 and Approval must be 2, 7 or 8) (Hi Pressure-303 不锈钢(额定5,000psi)(型号73-77)(传感必须为4, 认证必须为2,7或8))

4: Hi Pressure-303 stainless steel (rated 10,000psi) (Models 73-77) (Sensing must be 5 and Approval must be 2, 7 or 8) (Hi Pressure-303 不锈钢(额定10,000psi)(型号73-77)(传感必须为5, 认证必须为2,7或8))

6: 316 Stainless steel (rated 2,000 psi) (316 不锈钢(额定压力2,000 psi))

7: Hi Pressure-303 stainless steel (rated 2,500psi) (Model 73, 75 or 77 14573-xx only) (Wiring must be A, B or F) (Hi Pressure-303 不锈钢(额定压力2,500psi)(仅适用于型号73,75或77 14573-xx)(接线必须为A, B或F))

⑥ Area Classification* 区域分类

2: Hi Temperature to 400°F (Wiring option F only)

3: UL / Class I, Div 1, GrABCD, Class II, Div 1, GrEFG, Class III (Wiring A,B,F)(lead seal req'd within 18")

4: cUL / Class I, Div 1, GrABCD, Class II, Div 1, GrEFG, Class III (Wiring A,B,F)(lead seal req'd within 18")

5: UL / Class I, Div 2, GrABCD, Class II, Div 2, GrFG, Class III (Wiring A,B,F)(lead seal req'd within 18")

6: cUL / Class I, Div 2, GrABCD, Class II, Div 2, GrFG, Class III (Wiring A,B,F)(lead seal req'd within 18")


7: cUL listed General Purpose

生产者联系信息

名称: TopWorx Inc.
地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
联系人: Robert Coale
电话: +1 502 873 4629
电子邮箱: Robert.Coale@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: Louisville
指定签字人:
签章:

授权代表信息

名称: 世格流体控制(上海)有限公司
地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
联系人: 刘钦海
电话: 18501785664
电子邮箱: QinHai.Liu@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: 上海市
指定签字人:
签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):



- 8 UL Listed General Purpose
- 9 IECEx/ATEX Zone 1, Ex db IIC T6 Gb, Ex tb IIIC T85°C Db, IP66 (-40°C to 50°C)(Wiring A,B)
IECEx/ATEX Zone 1, Ex db IIC T4/T3 Gb, Ex tb IIIC T135°C/T200°C Db, IP66 (-40°C to 100°C/150°C)(Wiring F,H)
- T Model 73, 73M only (Hermetically sealed)
IECEx/ATEX Zone 1, Ex db IIC T6 Gb, Ex tb IIIC T85°C Db, IP66 (-40°C to 50°C)(Wiring A,B)
IECEx/ATEX Zone 1, Ex db IIC T4/T3 Gb, Ex tb IIIC T135°C/T200°C Db, IP66 (-40°C to 100°C/150°C)(Wiring F,H)
- F IECEx/ATEX Zone 0, Ex ia IIC T6 Ga, Ex ia IIIC T85°C Da (-40°C to 50°C)(Wiring S)(IF 73,73M=hermetic seal)
- G IECEx/ATEX Zone 0, Ex ia IIC T4 Ga, Ex ia IIIC T135°C Da (-40°C to 100°C)(Wiring S)(IF 73,73M=hermetic seal)
- H IECEx/ATEX Zone 0, Ex ia IIC T3 Ga, Ex ia IIIC T200°C Da (-40°C to 150°C)(Wiring S)(IF 73,73M=hermetic seal)
- ⑦ Wiring / Termination 接线/触点
A2 thru A8 3ft up to 250ft length, 18GA, PVC insulated lead wires (3英尺至250英尺长, 18GA, 聚氯乙烯绝缘引线)
B2 thru B8 3ft up to 250ft length, 18GA, PVC insulated cable (3英尺至250英尺长, 18GA, 聚氯乙烯绝缘电缆)
F2 thru F8 3ft up to 250ft length, 18GA, Teflon™ insulated lead wires (3英尺至250英尺长, 18GA, Teflon™绝缘引线)
H2 thru H8 3ft up to 250ft length, 18GA, PEEK insulated lead wires (3英尺至250英尺长, 18GA, PEEK绝缘导线)
S2 thru S8 3ft up to 250ft length, 18GA, Silicone insulated cable (3英尺至250英尺长, 18GA, 硅胶绝缘电缆)
DBA 3-pin Micro connector, male (Area Class 8 only) (3针Micro连接器, 公头 (仅限Area Class 8))
DBD 4-pin Micro connector, male (Area Class 7 only) (4针微型连接器, 公头 (仅限Area Class 7))
DCA 3-pin male Mini Quick Disconnect (Approval must be 7 or 8) (3针公头小型快速断开 (必须为7或8))
DCD 4-pin male Mini Quick Disconnect (Approval must be 7 or 8) (4针公头小型快速断开 (必须为7或8))
DCG 5-pin male Mini Quick Disconnect (Approval must be 7 or 8) (5针公头小型快速断开 (必须为7或8))
DMD 4-pin male Micro Quick Disconnect (Approval must be 7 or 8) (4针公头微型快速断开 (必须为7或8))
3DD 3-pin male, straight, SubSea Connector (Approval must be 7 or 8) (3针公头, 直头, SubSea连接器 (必须为7或8))
4DD 4-pin male, straight, SubSea Connector (Approval must be 7 or 8) (4针公头, 直头, SubSea连接器 (必须为7或8))
3DE 3-pin male, 90degree, SubSea Connector ((Approval must be 7 or 8) (3针公头, 90度, SubSea连接器 (必须为7或8))
4DE 4-pin male, 90degree, SubSea Connector ((Approval must be 7 or 8) (4针公头, 90度, SubSea连接器 (必须为7或8))
- ⑧ Regional Certifications 区域认证
Blank, OR
N NEPSI certified Ex d IIC T* Gb, Ex d A21 IP66 T* (Area Class 9 & T only)(Ref current NEPSI certificate)
K KOSHA certified Ex d IIC T* (Ref cert#14-AV4BO-0160X), Ex d A21 IP68 T* (Ref current KOSHA certificate)(Area Class 9 & T only)
P PESO certified Ex db IIC T* Gb (Ref cert#P396877)(Area Class 9 & T only) OR, Ex ia IIC T* Ga (Ref current PESO certificate)(Area Class F,G,H only)
R EAC certified I Ex d IIC T* Gb X, Ex tb IIIC T* Db X (Ref current EAC certificate)(Area Class 9 & T only), OR 0 Ex ia IIC T* Ga X, Ex is IIIC T* Da X (Ref current EAC certificate)(Area Class F,G,H only)
- ⑨ Custom(Optional) 自定义 (可选)
Blank: No Custom number, OR 空白, 或者
May include 4 numbers indicating custom quote Does not affect protection method The 4 custom quote number is only for commercial use, does not affect product safety or production process. 可能包含4个数字, 表示自定义报价 不影响保护方法, 4个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

生产者联系信息

名称: TopWorx Inc.
 地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
 联系人: Robert Coale
 电话: +1 502 873 4629
 电子邮箱: Robert.Coale@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: Louisville
 指定签字人:
 签章:

授权代表信息

名称: 世格流体控制(上海)有限公司
 地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
 联系人: 刘钦海
 电话: 18501785664
 电子邮箱: QinHai.Liu@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: 上海市
 指定签字人:
 签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):


- Go Switch Models 72, 72M, 74, 74M, 76 and 76M
 E.g Model No.: 72 1 3 5 2 8 A2 N xxxx
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨
- ① Model 型号
 72: 3/8" UNF external thread x 3-3/8" overall length (3/8"UNF外螺纹x 3-3/8"总长度)
 72M: 12mm external thread x 3-3/8" overall length (12mm外螺纹x 3-3/8"总长度)
 74: 5/8" UNF external thread x 2-13/16" overall length (5/8"UNF外螺纹x 2-13/16"总长度)
 74M: 18mm external thread x 2-13/16" overall length (18mm外螺纹x 2-13/16"总长度)
 76: 5/8" UNF external thread x 3-1/4" overall length (5/8"UNF外螺纹x 3-1/4"总长度)
 76M: 18mm external thread x 3-1/4" overall length (18mm外螺纹x 3-1/4"总长度)
- ② Contact Form 连接类型
 1 SPDT
 ③ Sensing Range 感应范围
 3 0.100" standard (Enclosure Type 2 or 6)(Model 74, 74M, 76, 76M) 标准(外壳类型2或6)(型号74,74M,76,76M)
 4 0.072" (Enclosure Type 3 or 7, Approval must be 2, 7, 8 or 9)(Model 74, 74M, 76, 76M) (外壳类型3或7, Approval必须是2,7,8或9) (型号74,74M,76,76M)
 5 0.060" (Enclosure Type 4, Approval must be 2, 7, 8 or 9)(Model 74, 74M, 76, 76M) (外壳类型4, Approval必须是2,7,8或9) (型号74,74M,76,76M)
 6 0.040" standard (Model 72 only) (标准(仅限72型))
- ④ Outlet Position 出口位置
 2 Side outlet (Approval must be 2 or 8)(Wiring must be F) 侧出口(必须为2或8)(接线必须为F)
 5 Bottom, or opposite of the sensing face of switch 开关传感面的底部或对面
- ⑤ Enclosure Material 外壳材料
 2 303 stainless steel (rated 2kpsi)(Sensing must be 3 or 6) (303不锈钢(额定2kpsi)(传感必须为3或6))
 3 Hi-pressure 303/316 stainless steel (rated 5kpsi)(Models 74, 74M, 76, 76M)(Sensing must be 4, Approval must be 2, 7 or 8) (高压303/316不锈钢(额定5kpsi)(型号74,74M, 76,76M)(传感必须为4, 认证必须为2,7或8))
 4 Hi-pressure 303/316 stainless steel (rated 10kpsi)(Models 74, 74M, 76, 76M)(Sensing must be 5, Approval must be 2, 7 or 8) (高压303/316不锈钢(额定10kpsi)(型号74,74M, 76,76M)(传感必须为5, 认证必须为2,7或8))
 6 316 stainless steel (rated 2kpsi)(Model 72, 72M)
- ⑥ Area Classification* 区域分类
 2 Hi Temperature to 400°F (Wiring option F only)
 7 cUL listed General Purpose
 8 UL listed General Purpose
 9 IECEx/ATEX Zone 1, Ex db IIC T6/T4/T3 Gb, Ex tb IIIC T85°C/135°C/200°C Db, IP66 (-55°C to 50°C/100°C/100°C)(Model 74, 74M only)(Outlet 5 only)(Wiring R only)
 F IECEx/ATEX Zone 0, Ex ia T6 Ga, Ex ia IIIC T85°C Da (-40°C to 50°C)(Outlet 5 only)(Wiring S only)
 G IECEx/ATEX Zone 0, Ex ia T4 Ga, Ex ia IIIC T135°C Da (-40°C to 100°C)(Outlet 5 only)(Wiring S only)
 H IECEx/ATEX Zone 0, Ex ia T3 Ga, Ex ia IIIC T200°C Da (-40°C to 150°C)(Outlet 5 only)(Wiring S only)
- ⑦ Wiring Option 接线
 A2 thru A8: 3ft up to 250ft length, 18GA, PVC insulated lead wires (3英尺至250英尺长, 18GA, 聚氯乙烯绝缘引线)
 B2 thru B8: 3ft up to 250ft length, 18GA, PVC insulated cable (3英尺至250英尺长, 18GA, 聚氯乙烯绝缘电缆)
 C2 thru C8: 3ft up to 250ft length, 18GA, PVC insulated cable, water resistant (3英尺至250英尺长, 18GA, 聚氯乙烯绝缘电缆, 防水)
 F2 thru F8: 3ft up to 250ft length, 18GA, Teflon™ insulated lead wires (3英尺至250英尺长, 18GA, Teflon™绝缘引线)
 N2 thru N8: 3ft up to 250ft length, 18GA, Niltex™ cable (3英尺至250英尺长, 18GA, Niltex™电缆)
 R2 thru R8: 3ft up to 250ft, Raychem cable (model 72, 74, 76 only)(Area Class 9 only) (3英尺至250英尺长, Raychem电缆(仅限72,74,76型)(仅限Area Class 9))

生产者联系信息

名称: TopWorx Inc.
 地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
 联系人: Robert Coale
 电话: +1 502 873 4629
 电子邮箱: Robert.Coale@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: Louisville
 指定签字人:
 签章:

授权代表信息

名称: 世格流体控制(上海)有限公司
 地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
 联系人: 刘钦海
 电话: 18501785664
 电子邮箱: QinHai.Liu@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: 上海市
 指定签字人:
 签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):

- S2 thru S8: 3ft up to 250ft length, 18GA, Silicone insulated cable (3英尺至250英尺长, 18GA, 硅胶绝缘电缆)
- DBA: 3-pin male Micro Quick Disconnect (Approval must be 7 or 8) (3针公头微型快速连接器, 公头(必须为7或8))
- DBD: 4-pin male Micro Quick Disconnect (Approval must be 7 or 8) (4针公头微型快速连接器, 公头(必须为7或8))
- DBG: 5-pin male Micro Quick Disconnect (Approval must be 7 or 8) (5针公头微型快速连接器, 公头(必须为7或8))
- DMD: 4-pin male Micro Quick Disconnect (Approval must be 7 or 8) (4针公头微型快速连接器, 公头(必须为7或8))

⑧Regional Certs 区域认证

Blank or, N: NEPSI Ex d IIC T3/T4/T6 Gb, Ex tD A21 IP66 T200°C/T135°C/T85°C

⑨Custom model number 自定义编号

Blank, or May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use, does not affect the product safety or production process 空白, 或者可能包含4个数字, 表示自定义报价 不影响保护方法。4个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

Go Switch models 7 Series with Connection Head Terminals

E.g. Model No.: 7G 2 3 5 2 Y JAM xxxx

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

①Model 型号

- 73: 5/8 UNF external thread (5/8 UNF 外螺纹)
- 73M: 18mm external thread (18mm 外螺纹)
- 75: 5/8 UNF external thread (5/8 UNF 外螺纹)
- 75M: 18mm external thread (18mm 外螺纹)
- 77: 3/4 UNF external thread (3/4 UNF 外螺纹)
- 7G: 5/8 UNF external thread (5/8 UNF 外螺纹)
- 7GM: 18mm external thread (18mm 外螺纹)

②Contact Form 连接类型

- 1: SPDT (Model 73, 73M, 75, 75M, 77, 7G, 7GM)(7G-1, 7GM-1 = hermetic seal)
- 2: DPDT (Model 7G, 7GM only)

③Sensing Range 感应范围

- 3: 0.100" standard (Enclosure Type 2 or 6) 标准 (外壳类型 2 或 6)
- 4: 0.072" (Enclosure Type 3) (外壳类型 3)
- 5: 0.060" (Enclosure Type 4) (外壳类型 4)

④Outlet Position 出口位置

- 5: Bottom, or opposite of the sensing face of switch 开关传感面的底部或对面

⑤Enclosure Material 外壳材料

生产者联系信息

名称: TopWorx Inc.
 地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
 联系人: Robert Coale
 电话: +1 502 873 4629
 电子邮箱: Robert.Coale@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: Louisville
 指定签字人:

授权代表信息

名称: 世格流体控制(上海)有限公司
 地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
 联系人: 刘钦海
 电话: 18501785664
 电子邮箱: QinHai.Liu@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: 上海市
 指定签字人:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):

- 2. 303 stainless steel (rated 2kpsi)(Sensing must be 3) (303 不锈钢(额定 2kpsi) (传感必须为 3))
- 3. Hi-pressure 303/316 stainless steel (rated 5kpsi)(Sensing must be 4) (高压 303/316 不锈钢(额定 5kpsi)(传感必须为 4))
- 4. Hi-pressure 303/316 stainless steel (rated 10kpsi)(Sensing must be 5) (高压 303/316 不锈钢(额定 10kpsi) (传感必须为 5))
- 6. 316 stainless steel (rated 2kpsi)(Sensing must be 3) (316 不锈钢(额定 2kpsi) (传感必须为 3))
- ⑥ Area Classification* 区域分类
 - X IECEx/ATEX Zone 1, Ex de IIC T6/T4 Gb, Ex tb IIIC T85°C/135°C Db, IP66 (-40°C to 50°C/100°C)(Model 73, 73M, 7G-1, 7GM-1 only)(Hermetic Seal)
 - Y IECEx/ATEX Zone 1, Ex de IIC T6/T4 Gb, Ex tb IIIC T85°C/135°C Db, IP66 (-40°C to 50°C/100°C)
- ⑦ Wiring Option 接线
 - JAM Aluminum Connection Head, rated Ex e, M20 cable entry (铝制连接头, 额定 Ex e, M20 电缆入口)
 - JAP Aluminum Connection Head, rated Ex e, 1/2NPT cable entry (铝制连接头, 额定 Ex e, 1/2NPT 电缆入口)
 - JSM Stainless steel Connection Head, rated Ex e, M20 cable entry (不锈钢连接头, 额定 Ex e, M20 电缆入口)
 - JSP Stainless steel Connection Head, rated Ex e, 1/2NPT cable entry (不锈钢连接头, 额定 Ex e, 1/2NPT 电缆入口)
- ⑧ Custom(Optional) 自定义 (可选)

May include 4 numbers indicating custom quote Does not affect protection method. The 4 custom quote number is only for commercial use, does not affect the product safety or production process. 可能包含 4 个数字, 表示自定义报价, 不影响保护方法。4 个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

GO Switch Model 7L
E.g Model No. 7LG 1 3 5 6 8 A2 xxxx
① ② ③ ④ ⑤ ⑥ ⑦ ⑧
- ① Model 型号
 - 7LG 5/8 UNF external thread x 4-3/4 overall length, Green LED Indication(5/8 UNF 外螺纹 x 4-3/4: 总长度, 绿色 LED 指示)
 - 7LR 5/8 UNF external thread x 4-3/4 overall length, Red LED Indication (5/8 UNF 外螺纹 x 4-3/4: 总长度, 红色 LED 指示)
 - 7LY 5/8 UNF external thread x 4-3/4 overall length, Green/Red LED Indication(5/8 UNF 外螺纹 x 4-3/4: 总长度, 绿色/红色 LED 指示)
- ② Contact Form 连接类型
 - 1 SPDT
- ③ Sensing Range 感应范围
 - 3 0 100" standard
- ④ Outlet Position 出口位置
 - 5 Bottom, or opposite of the sensing face of switch 开关传感面的底部或对面
- ⑤ Enclosure Material 外壳材料
 - 6 316 stainless steel (rated 2kpsi) 316 不锈钢 (额定压力 2kpsi)
- ⑥ Area Classification* 区域分类
 - 8 UL/cUL listed General Purpose
 - E UL/cUL listed Class I, Div 2, GrABCD, Class II, Div 2, GrFG, Class III (Wiring A or B)(Lead seal req'd within 18")
- ⑦ Wiring Option 接线
 - A2 thru A8 3ft up to 250ft length, 18GA, PVC insulated lead wires (3 英尺至 250 英尺长, 18GA, 聚氨酯绝缘引线)
 - B2 thru B8 3ft up to 250ft length, 18GA, PVC insulated cable (3 英尺至 250 英尺长, 18GA, 聚氨酯乙炔绝缘电缆)
 - DCA 3-pin male Mini Quick Disconnect (Approval must be 8) (3 针公头迷你快速连接器 (必须为 8))
 - DCD 4-pin male Mini Quick Disconnect (Approval must be 8) (4 针公头迷你快速连接器 (必须为 8))
 - DCG 5-pin male Mini Quick Disconnect (Approval must be 8) (5 针公头迷你快速连接器 (必须为 8))
 - DMD 4-pin male Micro Quick Disconnect (Approval must be 8) (4 针公头微型快速连接器 (必须为 8))
- ⑧ Custom(Optional) 自定义 (可选)


May include 4 numbers indicating custom quote Does not affect protection method. The 4 custom quote number is only for commercial use, does not affect the product safety or production process. 可能包含 4 个数字, 表示自定义报价, 不影响保护方法。4 个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

生产者联系信息

名称: TopWorx Inc.
 地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
 联系人: Robert Coale
 电话: +1 502 873 4629
 电子邮箱: Robert.Coale@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: Louisville
 指定签字人:
 签章:

授权代表信息

名称: 世格流体控制(上海)有限公司
 地址: 上海市市辖区松江区新桥镇新庙三路 480号18幢号楼1楼、2楼和3楼B区
 联系人: 刘钦海
 电话: 18501785664
 电子邮箱: QinHai.Liu@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: 上海市
 指定签字人:
 签章:



强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):

GO Switch Models 7G, 7GM, 7H & 7I
E.g Model No: 7G 1 3 5 2 3 A2 N xxxx
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

①Model 型号

7G: 5/8" UNF external thread x 4" overall length, with 1/2NPT (SPDT) or 3/4NPT (DPDT) cable entry (Hermetic Seal) (5/8" UNF 外螺纹 x 4" 总长, 带 1/2NPT (SPDT) 或 3/4NPT (DPDT) 电缆入口 (密封))

7GM: 18mm external thread x 4" overall length, with M20 (SPDT) or M25 (DPDT) cable entry (18mm 外螺纹 x 4" 总长度, 带 M20 (SPDT) 或 M25 (DPDT) 电缆入口)

7H: 5/8" UNF external thread x 3-1/4" overall length, with only potted-in leads/cable, no conduit connection (5/8" UNF 外螺纹 x 3-1/4" 总长度, 仅带有封装引线/电缆, 无导管连接)

7I: 1" UNF external thread x 5-5/8" overall length, with 1/2NPT (SPDT) or 3/4NPT (DPDT) cable entry (Hermetic Seal) (1" UNF 外螺纹 x 5-5/8" 总长, 带 1/2NPT (SPDT) 或 3/4NPT (DPDT) 电缆入口 (密封))

②Contact Form 连接类型

1: SPDT

2: DPDT

③Sensing Range 感应范围

3: 0.100" standard (Enclosure Type 2 or 6)

④Outlet Position 出口位置

5: Bottom, or opposite of the sensing face of switch 开关传感面的底部或对面

⑤Enclosure Material 外壳材料

2: 303 stainless steel (rated 2kpsi) 303 不锈钢 (额定压力 2kpsi)

6: 316 stainless steel (rated 2kpsi) 316 不锈钢 (额定压力 2kpsi)

⑥Area Classification* 区域分类

2: Hi Temperature to 400°F (Wiring option F only)

3: UL / Class I, Div 1, GrABCD, Class II, Div 1, GrEFG, Class III (Model 7G, 7I only)(Wiring A,B,F)(lead seal req'd within 18")

4: cUL / Class I, Div 1, GrABCD, Class II, Div 1, GrEFG, Class III (Model 7G, 7I only)(Wiring A,B,F)(lead seal req'd within 18")

5: UL / Class I, Div 2, GrABCD, Class II, Div 2, GrFG, Class III (Model 7G, 7I only)(Wiring A,B,F)(lead seal req'd within 18")

6: cUL / Class I, Div 2, GrABCD, Class II, Div 2, GrFG, Class III (Model 7G, 7I only)(Wiring A,B,F)(lead seal req'd within 18")

7: cUL listed General Purpose

8: UL listed General Purpose

9: IECEx/ATEX Zone 1, Ex db IIC T6 Gb; Ex tb IIIC T85°C Db, IP66 (Model 7G, 7GM, 7I only) (-40°C to 50°C)(Wiring A,B)

IECEx/ATEX Zone 1, Ex tb IIC T4/T3 Gb; Ex tb IIIC T135°C/T200°C Db, IP66 (Model 7G, 7GM, 7I only) (-40°C to 100°C/150°C)(Wiring F,H)

T: Model 73, 73M only (Hermetically sealed)IECEx/ATEX Zone 1, Ex db IIC T6 Gb; Ex tb IIIC T85°C Db, IP66 (Model 7G, 7GM, 7I only) (-40°C to 50°C)(Wiring A,B)

IECEx/ATEX Zone 1, Ex tb IIC T4/T3 Gb; Ex tb IIIC T135°C/T200°C Db, IP66 (Model 7G, 7GM, 7I only) (-40°C to 100°C/150°C)(Wiring F,H)

F: IECEx/ATEX Zone 0, Ex ia IIC T6 Ga; Ex ia IIIC T85°C Da (-40°C to 50°C)(Wiring S)(IF 7G, 7I=hermetic seal)

G: IECEx/ATEX Zone 0, Ex ia IIC T4 Ga; Ex ia IIIC T135°C Da (-40°C to 100°C)(Wiring S)(IF 7G, 7I=hermetic seal)

H: IECEx/ATEX Zone 0, Ex ia IIC T3 Ga; Ex ia IIIC T200°C Da (-40°C to 150°C)(Wiring S)(IF 7G, 7I=hermetic seal)

生产者联系信息

名称: TopWorx Inc.
地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
联系人: Robert Coale
电话: +1 502 873 4629
电子邮箱: Robert.Coale@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: Louisville
指定签字人:
签章:

授权代表信息

名称: 世格流体控制(上海)有限公司
地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
联系人: 刘钦海
电话: 18501785664
电子邮箱: QinHai.Liu@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: 上海市
指定签字人:
签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):

⑦Wiring Option 接线

A2 thru A8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), PVC insulated lead wires(3英尺至250英尺长, 18GA (SPDT) 或 22GA (DPDT), 聚氯乙烯绝缘引线)

B2 thru B8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), PVC insulated cable (3英尺至250英尺长, 18GA (SPDT) 或 22GA (DPDT), 聚氯乙烯绝缘电缆)

F2 thru F8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), Teflon™ insulated lead wires (3英尺至250英尺长, 18GA (SPDT) 或 22GA (DPDT), 铁氟龙™绝缘导线)

H2 thru H8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), PEEK insulated lead wires (3英尺至250英尺长, 18GA (SPDT) 或 22GA (DPDT), PEEK 绝缘引线)

S2 thru S8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), Silicone insulated cable (3英尺至250英尺长, 18GA (SPDT) 或 22GA (DPDT), 硅胶绝缘电缆)

DCH: 7-pin male Mini Quick Disconnect (DPDT only)(Approval 7, 8, F, G, H only) (7针公头迷你快速连接器(仅限 DPDT) (仅限 7, 8, F, G, H))

DMD: 4-pin male Micro Quick Disconnect (SPDT only)(Approval 7, 8, F, G, H only)(4针公头微型快速连接器(仅限 SPDT) (仅限 7, 8, F, G, H))

⑧Regional Certs 区域认证

Blank OR,

B: InMetro. Ex d IIC T6... T3 Gb, Ex tb IIIC T85°C... T200°C Db, IP66

N: NEPSI. Ex d IIC T3/T4/T6 Gb, Ex tD A21 IP66 T200°C/T135°C/T85°C

P: PESO. Ex db IIC T* Gb

R: EAC. 1 Ex d IIC T3/T4/T6 Gb X, Ex tb IIIC T85°C/T135°C/T200°C Db X

⑨Custom model 自定义(可选)

Blank OR,

May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use, does not affect the product safety or production process. 可能包含4个数字, 表示自定义报价 不影响保护方法。4个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

GO Switch Models 7C, 7D, 7E & 7F

E.g. Model No.: 7C 2 3 2 5 8 A2 xxxx

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

①Model 型号

7C: 1.025" Probe length, 5/8" diameter, with cylinder mounting flange (1.025"探头长度, 直径5/8", 带气缸安装法兰)

7D: 1.250" Probe length, 5/8" diameter, with cylinder mounting flange (1.250"探头长度, 直径5/8", 带气缸安装法兰)

7E: 2.062" Probe length, 5/8" diameter, with cylinder mounting flange (2.062"探头长度, 直径5/8", 带气缸安装法兰)

7F*: 7F+probe code. Custom Probe Length from 1.00" up to 5.00" (** can be different for different probe length See Probe Selection Chart) E.g. 7FJ4 = 2.875" Probe length (7F+探头代码, 自定义探头长度从1.00"到5.00" (** 可以根据不同的探头长度而不同参见探头选择表) 例如。 7FJ4 = 2.875"探头长度)

7CX: 1.025" Probe Length, welded cylinder mounting flange (1.025"探头长度, 焊接气缸安装法兰)


7DX: 2.062" Probe Length, welded cylinder mounting flange (2.062"探头长度, 焊接气缸安装法兰)

生产者联系信息

名称: TopWorx Inc.
地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
联系人: Robert Coale
电话: +1 502 873 4629
电子邮箱: Robert.Coale@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: Louisville
指定签字人:
签章:

授权代表信息

名称: 世格流体控制(上海)有限公司
地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
联系人: 刘钦海
电话: 18501785664
电子邮箱: QinHai.Liu@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: 上海市
指定签字人:
签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):

探针选择列表

Probe Selection Chart

| "A" Range | | | | "B" Range | | | | "A" Range | | | |
|-----------|-------|--------|------|-----------|-------|--------|------|-----------|-------|--------|------|
| Min | Max | Length | Code | Min | Max | Length | Code | Min | Max | Length | Code |
| 1.015 | 1.040 | 1.200 | A3 | 2.305 | 2.300 | 2.300 | D1 | 3.715 | 3.740 | 3.750 | N1 |
| 1.040 | 1.065 | 1.225 | " | 2.300 | 2.315 | 2.375 | D2 | 3.740 | 3.765 | 3.775 | N2 |
| 1.085 | 1.090 | 1.250 | A3 | 2.315 | 2.340 | 2.400 | D3 | 3.765 | 3.790 | 3.795 | N3 |
| 1.090 | 1.115 | 1.275 | A4 | 2.440 | 2.465 | 2.425 | G4 | 3.790 | 3.815 | 3.775 | N4 |
| 1.115 | 1.140 | 1.300 | A5 | 2.465 | 2.490 | 2.450 | G5 | 3.815 | 3.840 | 3.800 | N5 |
| 1.140 | 1.165 | 1.325 | A6 | 2.480 | 2.515 | 2.475 | G6 | 3.840 | 3.865 | 3.825 | N6 |
| 1.165 | 1.190 | 1.350 | A7 | 2.515 | 2.540 | 2.500 | G7 | 3.865 | 3.890 | 3.850 | N7 |
| 1.190 | 1.215 | 1.375 | A8 | 2.540 | 2.565 | 2.525 | G8 | 3.900 | 3.915 | 3.875 | N8 |
| 1.215 | 1.240 | 1.400 | A9 | 2.565 | 2.590 | 2.550 | G9 | 3.915 | 3.940 | 3.900 | N9 |
| 1.240 | 1.265 | 1.425 | B1 | 2.590 | 2.615 | 2.575 | H1 | 3.940 | 3.965 | 3.925 | P1 |
| 1.265 | 1.290 | 1.450 | " | 2.615 | 2.640 | 2.600 | H2 | 3.965 | 3.990 | 3.950 | P2 |
| 1.290 | 1.315 | 1.475 | B3 | 2.640 | 2.665 | 2.625 | H3 | 3.990 | 4.015 | 3.975 | P3 |
| 1.315 | 1.340 | 1.500 | B4 | 2.665 | 2.690 | 2.650 | H4 | 4.015 | 4.040 | 4.000 | P4 |
| 1.340 | 1.365 | 1.525 | B5 | 2.690 | 2.715 | 2.675 | H5 | 4.040 | 4.065 | 4.025 | P5 |
| 1.365 | 1.390 | 1.550 | B6 | 2.715 | 2.740 | 2.700 | H6 | 4.065 | 4.090 | 4.050 | P6 |
| 1.390 | 1.415 | 1.575 | B7 | 2.740 | 2.765 | 2.725 | H7 | 4.090 | 4.115 | 4.075 | P7 |
| 1.415 | 1.440 | 1.600 | B8 | 2.765 | 2.790 | 2.750 | H8 | 4.115 | 4.140 | 4.100 | P8 |
| 1.440 | 1.465 | 1.625 | B9 | 2.790 | 2.815 | 2.775 | H9 | 4.140 | 4.165 | 4.125 | P9 |
| 1.465 | 1.490 | 1.650 | C1 | 2.815 | 2.840 | 2.800 | J1 | 4.165 | 4.190 | 4.150 | R1 |
| 1.490 | 1.515 | 1.675 | C2 | 2.840 | 2.865 | 2.825 | J2 | 4.190 | 4.215 | 4.175 | R2 |
| 1.515 | 1.540 | 1.700 | C3 | 2.865 | 2.890 | 2.850 | J3 | 4.215 | 4.240 | 4.200 | R3 |
| 1.540 | 1.565 | 1.725 | C4 | 2.890 | 2.915 | 2.875 | J4 | 4.240 | 4.265 | 4.225 | R4 |
| 1.565 | 1.590 | 1.750 | C5 | 2.915 | 2.940 | 2.900 | J5 | 4.265 | 4.290 | 4.250 | R5 |
| 1.590 | 1.615 | 1.775 | C6 | 2.940 | 2.965 | 2.925 | J6 | 4.290 | 4.315 | 4.275 | R6 |
| 1.615 | 1.640 | 1.800 | C7 | 2.965 | 2.990 | 2.950 | J7 | 4.315 | 4.340 | 4.300 | R7 |
| 1.640 | 1.665 | 1.825 | C8 | 2.990 | 3.015 | 2.975 | J8 | 4.340 | 4.365 | 4.325 | R8 |
| 1.665 | 1.690 | 1.850 | C9 | 3.015 | 3.040 | 3.000 | J9 | 4.365 | 4.390 | 4.350 | R9 |
| 1.690 | 1.715 | 1.875 | D1 | 3.040 | 3.065 | 3.025 | K1 | 4.390 | 4.415 | 4.375 | E1 |
| 1.715 | 1.740 | 1.900 | D2 | 3.065 | 3.090 | 3.050 | K2 | 4.415 | 4.440 | 4.400 | E2 |
| 1.740 | 1.765 | 1.925 | D3 | 3.090 | 3.115 | 3.075 | K3 | 4.440 | 4.465 | 4.425 | E3 |
| 1.765 | 1.790 | 1.950 | D4 | 3.115 | 3.140 | 3.100 | K4 | 4.465 | 4.490 | 4.450 | E4 |
| 1.790 | 1.815 | 1.975 | D5 | 3.140 | 3.165 | 3.125 | K5 | 4.490 | 4.515 | 4.475 | E5 |
| 1.815 | 1.840 | 2.000 | D6 | 3.165 | 3.190 | 3.150 | K6 | 4.515 | 4.540 | 4.500 | E6 |
| 1.840 | 1.865 | 2.025 | D7 | 3.190 | 3.215 | 3.175 | K7 | 4.540 | 4.565 | 4.525 | E7 |
| 1.865 | 1.890 | 2.050 | D8 | 3.215 | 3.240 | 3.200 | K8 | 4.565 | 4.590 | 4.550 | E8 |
| 1.890 | 1.915 | 2.075 | D9 | 3.240 | 3.265 | 3.225 | K9 | 4.590 | 4.615 | 4.575 | E9 |
| 1.915 | 1.940 | 2.100 | E1 | 3.265 | 3.290 | 3.250 | L1 | 4.615 | 4.640 | 4.600 | T1 |
| 1.940 | 1.965 | 2.125 | E2 | 3.290 | 3.315 | 3.275 | L2 | 4.640 | 4.665 | 4.625 | T2 |
| 1.965 | 1.990 | 2.150 | E3 | 3.315 | 3.340 | 3.300 | L3 | 4.665 | 4.690 | 4.650 | T3 |
| 1.990 | 2.015 | 2.175 | E4 | 3.340 | 3.365 | 3.325 | L4 | 4.690 | 4.715 | 4.675 | T4 |
| 2.015 | 2.040 | 2.200 | E5 | 3.365 | 3.390 | 3.350 | L5 | 4.715 | 4.740 | 4.700 | T5 |
| 2.040 | 2.065 | 2.225 | E6 | 3.390 | 3.415 | 3.375 | L6 | 4.740 | 4.765 | 4.725 | T6 |
| 2.065 | 2.090 | 2.250 | E7 | 3.415 | 3.440 | 3.400 | L7 | 4.765 | 4.790 | 4.750 | T7 |
| 2.090 | 2.115 | 2.275 | E8 | 3.440 | 3.465 | 3.425 | L8 | 4.790 | 4.815 | 4.775 | T8 |
| 2.115 | 2.140 | 2.300 | E9 | 3.465 | 3.490 | 3.450 | L9 | 4.815 | 4.840 | 4.800 | T9 |
| 2.140 | 2.165 | 2.325 | F1 | 3.490 | 3.515 | 3.475 | M1 | 4.840 | 4.865 | 4.825 | V1 |
| 2.165 | 2.190 | 2.350 | F2 | 3.515 | 3.540 | 3.500 | M2 | 4.865 | 4.890 | 4.850 | V2 |
| 2.190 | 2.215 | 2.375 | F3 | 3.540 | 3.565 | 3.525 | M3 | 4.890 | 4.915 | 4.875 | V3 |
| 2.215 | 2.240 | 2.400 | F4 | 3.565 | 3.590 | 3.550 | M4 | 4.915 | 4.940 | 4.900 | V4 |
| 2.240 | 2.265 | 2.425 | F5 | 3.590 | 3.615 | 3.575 | M5 | 4.940 | 4.965 | 4.925 | V5 |
| 2.265 | 2.290 | 2.450 | F6 | 3.615 | 3.640 | 3.600 | M6 | 4.965 | 4.990 | 4.950 | V6 |
| 2.290 | 2.315 | 2.475 | F7 | 3.640 | 3.665 | 3.625 | M7 | 4.990 | 5.015 | 4.975 | V7 |
| 2.315 | 2.340 | 2.500 | F8 | 3.665 | 3.690 | 3.650 | M8 | 5.015 | 5.040 | 5.000 | V8 |
| 2.340 | 2.365 | 2.525 | F9 | 3.690 | 3.715 | 3.675 | M9 | | | | |

② Contact Form 连接类型

2. SPST (Form A) N/O output with bi-color LED indication (N/O 输出, 带双色 LED 指示)
3. SPST (Form B) N/C output with bi-color LED indication (带有双色 LED 指示的 N/C 输出)
4. SPDT (Form C) without LED (Model 7CX, 7DX only) (不带 LED 的 (仅限 7CX 型, 7DX 型))
5. SPDT (Form C) with dual LED indication (具有双 LED 指示的)
7. SPST (Form A) N/O output without LED indication (N/O 输出, 无 LED 指示)
8. SPST (Form B) N/C output without LED indication (N/C 输出, 无 LED 指示)

生产者联系信息

名称: TopWorx Inc.
 地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
 联系人: Robert Coale
 电话: +1 502 873 4629
 电子邮箱: Robert.Coale@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: Louisville
 指定签字人:
 签章:

授权代表信息

名称: 世格流体控制(上海)有限公司
 地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
 联系人: 刘钦海
 电话: 18501785664
 电子邮箱: QinHai.Liu@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: 上海市
 指定签字人:
 签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):

- ③Sensing Range 感应范围
 - 3 0.090" standard
- ④Outlet Position 出口位置
 - 2. Side outlet, 360° adjustable (Wiring A, B, C, F only) No conduit connection (侧面插座, 360度可调(仅限A, B, C, F接线)无导管连接)
 - 5. Top outlet, or opposite of the sensing face of switch (Model 7CX, 7DX only) With 1/2NPT conduit connection (顶部插座, 或与开关传感面相对(仅限7CX型, 7DX型)带1/2NPT导管连接)
 - 6. Side outlet, 360° adjustable, no conduit connection (Approval 7 or 8 only)(Wiring D** or SubSea connectors only) (侧面插座, 360度可调, 无导管连接(仅限认证7或8)(仅限接线D**或SubSea接头))
 - 7. Side outlet, 360° adjustable, 1/2NPT conduit connection (Wiring A, B, F only) (侧面插座, 360度可调节, 1/2NPT导管连接(仅限A, B, F接线))
 - 8. Top outlet (Wiring SubSea connectors only) (顶部插座(仅接线SubSea连接器))
- ⑤Enclosure Material 外壳材料
 - 5. 303/316 stainless steel (rated 3kpsi with 3x safety factor) (303/316 不锈钢(额定3kpsi, 安全系数3倍))
- ⑥Area Classification* 区域分类
 - 2. Hi Temperature to 400°F (Contact Form 4, 7, 8 only)(Wiring option F only)
 - 3. UL / Class I, Div 1, GrABCD; Class II, Div 1, GrEFG; Class III (Model 7CX, 7DX only)
 - 4. cUL / Class I, Div 1, GrABCD; Class II, Div 1, GrEFG; Class III (Model 7CX, 7DX only)
 - 5. UL / Class I, Div 2, GrABCD; Class II, Div 2, GrFG; Class III (Model 7CX, 7DX only)
 - 6. cUL / Class I, Div 2, GrABCD; Class II, Div 2, GrFG; Class III (Model 7CX, 7DX only)
 - 7. eUL listed General Purpose
 - 8. UL listed General Purpose
 - 9. IECEx/ATEX Zone 1, Ex db IIC T6 Gb, Ex tb IIIC T85°C Db, IP66 (Model 7CX, 7DX only) (-40°C to 50°C)(Wiring A,B)
 - IECEx/ATEX Zone 1, Ex tb IIC T4/T3 Gb, Ex tb IIIC T135°C/T200°C Db, IP66 (Model 7CX, 7DX only) (-40°C to 100°C/150°C)(Wiring F,H)
 - T: Model 73, 73M only (Hermetically sealed)
 - IECEx/ATEX Zone 1, Ex db IIC T6 Gb, Ex tb IIIC T85°C Db, IP66 (Model 7CX, 7DX only) (-40°C to 50°C)(Wiring A,B)
 - IECEx/ATEX Zone 1, Ex tb IIC T4/T3 Gb, Ex tb IIIC T135°C/T200°C Db, IP66 (Model 7CX, 7DX only) (-40°C to 100°C/150°C)(Wiring F,H)
 - F: IECEx/ATEX Zone 0, Ex ia IIC T6 Ga, Ex ia IIIC T85°C Da (-40°C to 50°C)(Wiring S)(Model 7CX, 7DX only)
 - G: IECEx/ATEX Zone 0, Ex ia IIC T4 Ga, Ex ia IIIC T135°C Da (-40°C to 100°C)(Wiring S)(Model 7CX, 7DX only)
 - H: IECEx/ATEX Zone 0, Ex ia IIC T3 Ga, Ex ia IIIC T200°C Da (-40°C to 150°C)(Wiring S)(Model 7CX, 7DX only)
- ⑦Wiring Option 接线
 - A2 thru A8: 3ft up to 250ft length, 18GA, PVC insulated lead wires (3英尺至250英尺长, 18GA, 聚氯乙烯绝缘引线)
 - B2 thru B8: 3ft up to 250ft length, 18GA, PVC insulated cable (3英尺至250英尺长, 18GA, 聚氯乙烯绝缘电缆)
 - C2 thru C8: 3ft up to 250ft length, 18GA, PVC insulated cable, water resistant (3英尺至250英尺长, 18GA, 聚氯乙烯绝缘电缆, 防水)
 - F2 thru F8: 3ft up to 250ft length, 18GA, Teflon™ insulated lead wires (3英尺至250英尺长, 18GA, Teflon™绝缘引线)
 - S2 thru S8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), Silicone insulated cable (Model 7CX, 7DX only) (3英尺至250英尺长, 18GA (SPDT) 或 22GA (DPDT), 硅胶绝缘电缆(7CX型, 仅7DX))

生产者联系信息

名称: TopWorx Inc.
 地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
 联系人: Robert Coale
 电话: +1 502 873 4629
 电子邮箱: Robert.Coale@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: Louisville
 指定签字人:
 签章:

授权代表信息

名称: 世格流体控制(上海)有限公司
 地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
 联系人: 刘钦海
 电话: 18501785664
 电子邮箱: QinHai.Liu@Emerson.com
 自我声明时间: 2020-12-22
 自我声明地点: 上海市
 指定签字人:
 签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):

- DCA: 3-pin male Mini Quick Disconnect (Approval 7, 8 only) (3 针公头迷你快速连接器 (仅限 7,8))
- DCD: 4-pin male Mini Quick Disconnect (Approval 7, 8 only) (4 针公头迷你快速连接器 (仅限 7,8))
- DCH: 7-pin male Mini Quick Disconnect (Approval 7, 8 only) (7 针公头迷你快速连接器 (仅限 7,8))
- DMD: 4-pin male Micro Quick Disconnect (Approval 7, 8 only) (4 针公头微型快速连接器 (仅限 7,8))
- DBA: 3-pin male Micro Quick Disconnect (Approval 7, 8 only) (3 针公头微型快速连接器 (仅限 7,8))
- DBD: 4-pin male Micro Quick Disconnect (Approval 7, 8 only) (4 针公头微型快速连接器 (仅限 7,8))
- 3DD: 3-pin male, straight, SubSea Connector (Approval must be 7 or 8) (3 针公头, 直头, SubSea 连接器 (必须为 7 或 8))
- 4DD: 4-pin male, straight, SubSea Connector (Approval must be 7 or 8) (4 针公头, 直头, SubSea 连接器 (必须为 7 或 8))
- 3DE: 3-pin male, 90degree, SubSea Connector (Approval must be 7 or 8) (3 针公头, 90 度, SubSea 连接器 (必须为 7 或 8))
- 4DE: 4-pin male, 90degree, SubSea Connector (Approval must be 7 or 8) (4 针公头, 90 度, SubSea 连接器 (必须为 7 或 8))

⑧ Custom(Optional) 自定义 (可选)

May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use, does not affect the product safety or production process. 可能包含 4 个数字, 表示自定义报价 不影响保护方法。4 个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

GO Switch Models 7J

E.g. Model No.:

7J 1 3 5 6 4 JSP N xxxx
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

① Model 型号

7J: External thread 5/8-18UNF (外螺纹 5/8-18UNF)

7JM: External thread M18 metric (外螺纹 M18 公)

② Contact Form 连接类型

1: SPDT

③ Sensing Range 感应范围

3: 0.100" (2.5mm) standard

④ Outlet Position 出口位置

5: Bottom outlet, 1/2NPT or M20 conduit connection (底部插座, 1/2NPT 或 M20 导管连接)

⑤ Enclosure Type/Material 外壳材料

6: 316 stainless steel (316 不锈钢)

⑥ Approvals / Area Classification 区域分类

4: UL/cUL Class I, Div 1, GrABCD, Class II, Div 1, GrEFG

6: UL/cUL Class I, Div 2, GrABCD, Class II, Div 2, GrFG

7: UL/cUL General Purpose

9: Ex db IIC T6 Gb, Ex tb IIIC T85°C Db; IP66/68, Tamb: -40°C to +75°C

生产者联系信息

名称: TopWorx Inc.
地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
联系人: Robert Coale
电话: +1 502 873 4629
电子邮箱: Robert.Coale@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: Louisville
指定签字人:
签章:

授权代表信息

名称: 世格流体控制(上海)有限公司
地址: 上海市市辖区松江区新桥镇新庙三路 480 号 18 幢号楼 1 楼、2 楼和 3 楼 B 区
联系人: 刘钦海
电话: 18501785664
电子邮箱: QinHai.Liu@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: 上海市
指定签字人:
签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。

强制性认证产品符合性自我声明(附页)



自我声明编号: 2020980305003328

产品系列、型号、规格(附件):

Y: Ex db eb IIC T6 Gb, Ex tb IIIC T85°C Db; IP66/68, Tamb: -40°C to +75°C
F: Ex ia IIC T6 Ga; Ex ia IIIC T85°C Da, Tamb: -40°C to +50°C
G: Ex ia IIC T4 Ga; Ex ia IIIC T135°C Da, Tamb: -40°C to +100°C
H: Ex ia IIC T3 Ga; Ex ia IIIC T200°C Da, Tamb: -40°C to +150°C
⑦Wiring / Cable Entry (Terminal block is provided for field wiring) 接线
JSP: 1/2NPT cable entry (Model 7J) (1/2NPT 电缆入口 (型号 7J))
JSM: M20 cable entry (Model 7JM) (M20 电缆入口 (型号 7JM))
⑧Regional Approvals / Certifications 区域认证
N: NEPSI (Approval 9 only) Ex d IIC T3/T4/T6 Gb, Ex tD A21 IP66 T200°C/T135°C/T85°C (Ref current NEPSI certificate)
K: KOSHA (Approval 9 only) Ex d IIC T6 (ref current KOSHA certificate)
R: EAC (Approval 9) 1 Ex d IIC T6 Gb X, Ex tb IIIC T85°C Db X; (Approval Y) 1 Ex de IIC T6 Gb X, Ex tb IIIC T85°C Db X
Z: Canada Zone Equivalence (Approval 4 only) Class I, Zone 1, Ex d IIC; Class II, Zone 21, Ex tb IIIC
⑨Custom(Optional) 自定义 (可选)
Blank OR,
May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use, does not affect the product safety or production process. 可能包含 4 个数字, 表示自定义报价 不影响保护方法。4 个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

生产者联系信息

名称: TopWorx Inc.
地址: 3300 Fern Valley Road, Louisville, KY 40213, USA
联系人: Robert Coale
电话: +1 502 873 4629
电子邮箱: Robert.Coale@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: Louisville
指定签字人:
签章:



授权代表信息

名称: 世格流体控制(上海)有限公司
地址: 上海市市辖区松江区新桥镇新庙三路480号18幢号楼1楼、2楼和3楼B区
联系人: 刘钦海
电话: 18501785664
电子邮箱: QinHai.Liu@Emerson.com
自我声明时间: 2020-12-22
自我声明地点: 上海市
指定签字人:
签章:



注: 有关本声明信息真伪可登录全国认证认可信息公共服务平台 (cx.cnca.cn) 或扫描右上角二维码查询。