



产品认证证书

证书编号: CQC20107279174

II 型自愿认证

申请人名称及地址

TopWorx Inc.

3300 Fern Valley Road, Louisville, KY 40213, USA

制造商名称及地址

TopWorx Inc.

3300 Fern Valley Road, Louisville, KY 40213, USA

生产企业名称及地址

TopWorx Inc. (V059165)

3300 Fern Valley Road, Louisville, KY 40213, USA

产品名称和系列、规格、型号

磁性开关

7: Ui:480V; Uimp:2.5kV; Ith:4A; AC-12:Ue/Ie:240VAC/2A, 120VAC/4A; DC-12:Ue/Ie:24VDC/3A;
IP66; 型号解释见附件

产品标准和技术要求

GB/T 14048.5-2017

认证模式

产品型式试验+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

发证日期: 2020 年 12 月 21 日 有效期至: 2025 年 12 月 21 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任: _____

陆楠



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

C 0445561



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC20107279174

Type II CQC Certification

NAME AND ADDRESS OF THE APPLICANT

TopWorx Inc.
3300 Fern Valley Road, Louisville, KY 40213, USA

NAME AND ADDRESS OF THE MANUFACTURER

TopWorx Inc.
3300 Fern Valley Road, Louisville, KY 40213, USA

NAME AND ADDRESS OF THE FACTORY

TopWorx Inc. (V059165)
3300 Fern Valley Road, Louisville, KY 40213, USA

PRODUCT NAME, MODEL AND SPECIFICATION

Magnetic Switch

7: Ui:480V; Uimp:2.5kV; Ith:4A; AC-12:Ue/Ie:240VAC/2A, 120VAC/4A; DC-12:Ue/Ie:24VDC/3A; IP66 See the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.5-2017

TYPE OF CERTIFICATION SCHEMES

Type Testing of Product + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020 .

Valid from: Dec.21,2020

Valid until: Dec.21,2025

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

President: _____

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>

C 0445561



产品认证证书

附 录

第 1 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

型号解释:

Go Switch Models 71, 71M, 73, 73M, 75, 75M and 77

E.g. Model No.: 71 1 3 5 2 2 F2 N xxxx

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

① Model 型号

71: 3/8" UNF external thread x 3-15/16" overall length, with 1/2NPT cable entry (3/8" UNF 外螺纹 x 3-15 / 16" 总长度, 带 1 / 2NPT 电缆入口)

71M: 12mm external thread x 3-15/16" overall length, with M20 cable entry (12mm 外螺纹 x 3-15 / 16" 总长度, 带 M20 电缆入口)

73: 5/8" UNF external thread x 3-5/8" overall length, with 1/2NPT cable entry (5/8" UNF 外螺纹 x 3-5 / 8" 总长度, 1 / 2NPT 电缆入口)

73M: 18mm external thread x 3-5/8" overall length, with M20 cable entry (18mm 外螺纹 x 3-5 / 8" 总长度, 带 M20 电缆入口)

75: 5/8" UNF external thread x 4-5/16" overall length, with 1/2NPT cable entry (5/8" UNF 外螺纹 x 4-5 / 16" 总长度, 带 1 / 2NPT 电缆入口)

75M: 18mm external thread x 4-5/16" overall length, with M20 cable entry (18mm 外螺纹 x 4-5 / 16" 总长, 带 M20 电缆入口)

77: 3/4 UNF external thread x 5-13/16" overall length, with 1/2NPT cable entry (3/4 UNF 外螺纹 x 5-13 / 16" 总长度, 1 / 2NPT 电缆入口)

② Contact Form 连接类型

1: SPDT

③ Sensing Range 感应范围

3: 0.100" standard (Enclosure Type 2 or 6) (标准 (外壳类型 2 或 6))

注: 此附录与证书同时使用时有效。

主任: _____

陆杨



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 2 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

- 4: 0.072" (Enclosure must be 3 or 7 and Approvals must be 2,3,7,8 or 9) ((外壳必须为3或7, Approvals必须为2,3,7,8或9))
- 5: 0.060" (Enclosure must be 4 and Approvals must be 2, 7, 8 or 9) ((外壳必须为4, Approvals必须为2,7,8或9))
- 6: 0.040" standard (Model 71) (标准 (型号71))
- ④Outlet Position 出口位置
- 5: Bottom, or opposite of the sensing face of switch 开关传感面的底部或对面
- ⑤Enclosure Material 外壳材料
- 2: 303 stainless steel (rated 2,000 psi) (Sensing must be 3 or 6) (303不锈钢 (额定压力2,000 psi) (传感必须为3或6))
- 3: Hi Pressure-303 stainless steel (rated 5,000psi) (Models 73-77) (Sensing must be 4 and Approval must be 2, 7 or 8) (Hi Pressure-303不锈 钢 (额定5,000psi) (型号73-77) (传感必须为4, 认证必须为2,7或8))
- 4: Hi Pressure-303 stainless steel (rated 10,000psi) (Models 73-77) (Sensing must be 5 and Approval must be 2, 7 or 8) (Hi Pressure-303不锈 钢 (额定10,000psi) (型号73-77) (传感必须为5, 认证必须为2,7或8))
- 6: 316 Stainless steel (rated 2,000 psi) (316不锈钢 (额定压力2,000 psi))
- 7: Hi Pressure-303 stainless steel (rated 2,500psi) (Model 73, 75 or 77 14573-xx only) (Wiring must be A, B or F) (Hi Pressure-303不锈 钢 (额定压力2,500psi) (仅适用于型号73,75或77 14573-xx) (接线必须为A, B或F))
- ⑥Area Classification* 区域分类
- 2: Hi Temperature to 400°F (Wiring option F only)
- 3: UL / Class I, Div 1, GrABCD; Class II, Div 1, GrEFG; Class III (Wiring A,B,F)(lead seal req'd within 18")
- 4: cUL / Class I, Div 1, GrABCD; Class II, Div 1, GrEFG; Class III (Wiring A,B,F)(lead seal req'd within 18")
- 5: UL / Class I, Div 2, GrABCD; Class II, Div 2, GrFG; Class III (Wiring A,B,F)(lead seal req'd within 18")
- 6: cUL / Class I, Div 2, GrABCD; Class II, Div 2, GrFG; Class III (Wiring A,B,F)(lead seal req'd within 18")
- 7: cUL listed General Purpose

注: 此附录与证书同时使用时有效。

主任: 陆梅



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 3 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

- 8: UL listed General Purpose
9: IECEX/ATEX Zone 1, Ex db IIC T6 Gb; Ex tb IIIC T85°C Db; IP66
(-40°C to 50°C)(Wiring A,B)
IECEX/ATEX Zone 1, Ex db IIC T4/T3 Gb; Ex tb IIIC T135°C/T200°C Db; IP66
(-40°C to 100°C/150°C)(Wiring F,H)
T: Model 73, 73M only (Hermetically sealed)
IECEX/ATEX Zone 1, Ex db IIC T6 Gb; Ex tb IIIC T85°C Db; IP66
(-40°C to 50°C)(Wiring A,B)
IECEX/ATEX Zone 1, Ex db IIC T4/T3 Gb; Ex tb IIIC T135°C/T200°C Db; IP66
(-40°C to 100°C/150°C)(Wiring F,H)
F: IECEX/ATEX Zone 0, Ex ia IIC T6 Ga; Ex ia IIIC T85°C Da (-40°C to 50°C)(Wiring S)(IF 73,73M=hermetic seal)
G: IECEX/ATEX Zone 0, Ex ia IIC T4 Ga; Ex ia IIIC T135°C Da (-40°C to 100°C)(Wiring S)(IF 73,73M=hermetic seal)
H: IECEX/ATEX Zone 0, Ex ia IIC T3 Ga; Ex ia IIIC T200°C Da (-40°C to 150°C)(Wiring S)(IF 73,73M=hermetic seal)
⑦Wiring / Termination 接线/触点
A2 thru A8: 3ft up to 250ft length, 18GA, PVC insulated lead wires (3英尺至250英尺长, 18GA, 聚氯乙烯绝缘引线)
B2 thru B8: 3ft up to 250ft length, 18GA, PVC insulated cable (3英尺至250英尺长, 18GA, 聚氯乙烯绝缘电缆)
F2 thru F8: 3ft up to 250ft length, 18GA, Teflon™ insulated lead wires (3英尺至250英尺长, 18GA, Teflon™绝缘引线)

注: 此附录与证书同时使用时有效。

主任: _____

陆杨



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 4 页 共 23 页

证书编号：CQC20107279174

纸 号：445561

- H2 thru H8: 3ft up to 250ft length, 18GA, PEEK insulated lead wires (3英尺至250英尺长, 18GA, PEEK绝缘导线)
- S2 thru S8: 3ft up to 250ft length, 18GA, Silicone insulated cable (3英尺至250英尺长, 18GA, 硅胶绝缘电缆)
- DBA: 3-pin Micro connector, male (Area Class 8 only) (3针Micro连接器, 公头 (仅限Area Class 8))
- DBD: 4-pin Micro connector, male (Area Class 7 only) (4针微型连接器, 公头 (仅限Area Class 7))
- DCA: 3-pin male Mini Quick Disconnect (Approval must be 7 or 8) (3针公头小型快速断开 (必须为7或8))
- DCD: 4-pin male Mini Quick Disconnect (Approval must be 7 or 8) (4针公头小型快速断开 (必须为7或8))
- DCG: 5-pin male Mini Quick Disconnect (Approval must be 7 or 8) (5针公头小型快速断开 (必须为7或8))
- DMD: 4-pin male Micro Quick Disconnect (Approval must be 7 or 8) (4针公头微型快速断开 (必须为7或8))
- 3DD: 3-pin male, straight, SubSea Connector (Approval must be 7 or 8) (3针公头, 直头, SubSea连接器 (必须为7或8))
- 4DD: 4-pin male, straight, SubSea Connector (Approval must be 7 or 8) (4针公头, 直头, SubSea连接器 (必须为7或8))
- 3DE: 3-pin male, 90degree, SubSea Connector ((Approval must be 7 or 8) (3针公头, 90度, SubSea连接器 (必须为7或8))
- 4DE: 4-pin male, 90degree, SubSea Connector ((Approval must be 7 or 8) (4针公头, 90度, SubSea连接器 (必须为7或8))

注：此附录与证书同时使用时有效。

主任：

陆梅



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 5 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

⑧. Regional Certifications 区域认证

Blank, OR

N : NEPSI certified Ex d IIC T* Gb; Ex tD A21 IP66 T* (Area Class 9 & T only)(Ref current NEPSI certificate)

K : KOSHA certified Ex d IIC T* (Ref cert#14-AV4BO-0160X), Ex tD A21 IP68 T* (Ref current KOSHA certificate)(Area Class 9 & T only)

P : PESO certified Ex db IIC T* Gb (Ref cert#P396877)(Area Class 9 & T only) OR, Ex ia IIC T* Ga (Ref current PESO certificate)(Area Class F,G,H only)

R : EAC certified I Ex d IIC T* Gb X, Ex tb IIIC T* Db X (Ref current EAC certificate)(Area Class 9 & T only), OR 0 Ex ia IIC T* Ga X, Ex is IIIC T* Da X

(Ref current EAC certificate)(Area Class F,G,H only)

⑨. Custom(Optional) 自定义 (可选)

Blank: No Custom number, OR 空白, 或者

May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use , does not affect product safety or production process. 可能包含 4 个数字, 表示自定义报价 不影响保护方法。 4 个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

Go Switch Models 72, 72M, 74, 74M, 76 and 76M

E.g. Model No.: 72 1 3 5 2 8 A2 N xxxx

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

① Model 型号

72: 3/8" UNF external thread x 3-3/8" overall length (3/8"UNF外螺纹x 3-3/8"总长度)

72M: 12mm external thread x 3-3/8" overall length (12mm外螺纹x 3-3/8"总长度)

74: 5/8" UNF external thread x 2-13/16" overall length (5/8"UNF外螺纹x 2-13/16"总长度)

74M: 18mm external thread x 2-13/16" overall length (18mm外螺纹x 2-13/16"总长度)

76: 5/8" UNF external thread x 3-1/4" overall length (5/8"UNF外螺纹x 3-1/4"总长度)

76M: 18mm external thread x 3-1/4" overall length (18mm外螺纹x 3-1/4"总长度)

注: 此附录与证书同时使用时有效。

主任: _____

陆杨



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 6 页 共 23 页

证书编号：CQC20107279174

纸 号：445561

②Contact Form 连接类型

1: SPDT

③Sensing Range 感应范围

3: 0.100" standard (Enclosure Type 2 or 6)(Model 74, 74M, 76, 76M) 标准(外壳类型2或6)(型号74,74M,76,76M)

4: 0.072" (Enclosure Type 3 or 7, Approval must be 2, 7, 8 or 9)(Model 74, 74M, 76, 76M) (外壳类型3或7, Approval必须是2,7,8或9) (型号74,74M,76,76M)

5: 0.060" (Enclosure Type 4, Approval must be 2, 7, 8 or 9)(Model 74, 74M, 76, 76M) (外壳类型4, Approval必须是2,7,8或9) (型号74,74M,76,76M)

6: 0.040" standard (Model 72 only) (标准(仅限72型))

④Outlet Position 出口位置

2: Side outlet (Approval must be 2 or 8)(Wiring must be F) 侧出口(必须为2或8)(接线必须为F)

5: Bottom, or opposite of the sensing face of switch 开关传感面的底部或对面

⑤Enclosure Material 外壳材料

2: 303 stainless steel (rated 2kpsi)(Sensing must be 3 or 6) (303不锈钢(额定2kpsi)(传感必须为3或6))

3: Hi-pressure 303/316 stainless steel (rated 5kpsi)(Models 74, 74M, 76, 76M)(Sensing must be 4, Approval must be 2, 7 or 8)(高压 303/316不锈钢(额定5kpsi)(型号74,74M, 76,76M)(传感必须为4, 认证必须为2,7或8))

注：此附录与证书同时使用时有效。

主任：_____

陆梅



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 8 页 共 23 页

证书编号：CQC20107279174

纸 号：445561

S2 thru S8: 3ft up to 250ft length, 18GA, Silicone insulated cable (3英尺至250英尺长, 18GA, 硅胶绝缘电缆)
DBA: 3-pin male Micro Quick Disconnect (Approval must be 7 or 8) (3针公头微型快速连接器, 公头(必须为7或8))
DBD: 4-pin male Micro Quick Disconnect (Approval must be 7 or 8) (4针公头微型快速连接器, 公头(必须为7或8))
DBG: 5-pin male Micro Quick Disconnect (Approval must be 7 or 8) (5针公头微型快速连接器, 公头(必须为7或8))
DMD: 4-pin male Micro Quick Disconnect (Approval must be 7 or 8) (4针公头微型快速连接器, 公头(必须为7或8))

⑧Regional Certs 区域认证

Blank or,

N: NEPSI Ex d IIC T3/T4/T6 Gb, Ex tD A21 IP66 T200°C/T135°C/T85°C

⑨Custom model number 自定义编号

Blank, or May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use, does not affect the product safety or production process 空白, 或者可能包含4个数字, 表示自定义报价 不影响保护方法。4个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

注：此附录与证书同时使用时有效。

主任：



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 9 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

Go Switch models 7 Series with Connection Head Terminals
E.g. Model No.: 7G 2 3 5 2 Y JAM xxxx

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

① Model 型号

73: 5/8 UNF external thread (5/8 UNF 外螺纹)
73M: 18mm external thread (18mm 外螺纹)
75: 5/8 UNF external thread (5/8 UNF 外螺纹)
75M: 18mm external thread (18mm 外螺纹)
77: 3/4 UNF external thread (3/4 UNF 外螺纹)
7G: 5/8 UNF external thread (5/8 UNF 外螺纹)
7GM: 18mm external thread (18mm 外螺纹)

② Contact Form 连接类型

1: SPDT (Model 73, 73M, 75, 75M, 77, 7G, 7GM)(7G-1, 7GM-1 = hermetic seal)
2: DPDT (Model 7G, 7GM only)

③ Sensing Range 感应范围

3: 0.100" standard (Enclosure Type 2 or 6) 标准 (外壳类型 2 或 6)
4: 0.072" (Enclosure Type 3) (外壳类型 3)
5: 0.060" (Enclosure Type 4) (外壳类型 4)

④ Outlet Position 出口位置

5: Bottom, or opposite of the sensing face of switch 开关传感面的底部或对面

⑤ Enclosure Material 外壳材料

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 10 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

- 2: 303 stainless steel (rated 2kpsi)(Sensing must be 3) (303 不锈钢(额定 2kpsi) (传感必须为 3))
- 3: Hi-pressure 303/316 stainless steel (rated 5kpsi)(Sensing must be 4) (高压 303/316 不锈钢(额定 5kpsi)(传感必须为 4))
- 4: Hi-pressure 303/316 stainless steel (rated 10kpsi)(Sensing must be 5) (高压 303/316 不锈钢(额定 10kpsi) (传感必须为 5))
- 6: 316 stainless steel (rated 2kpsi)(Sensing must be 3) (316 不锈钢(额定 2kpsi) (传感必须为 3))

⑥Area Classification* 区域分类

- X: IECEx/ATEX Zone 1, Ex de IIC T6/T4 Gb; Ex tb IIIC T85°C/135°C Db; IP66
(-40°C to 50°C/100°C)(Model 73, 73M, 7G-1, 7GM-1 only)(Hermetic Seal)
- Y: IECEx/ATEX Zone 1, Ex de IIC T6/T4 Gb; Ex tb IIIC T85°C/135°C Db; IP66
(-40°C to 50°C/100°C)

⑦Wiring Option 接线

- JAM: Aluminum Connection Head, rated Ex e, M20 cable entry (铝制连接头, 额定 Ex e, M20 电缆入口)
- JAP: Aluminum Connection Head, rated Ex e, 1/2NPT cable entry (铝制连接头, 额定 Ex e, 1/2NPT 电缆入口)
- JSM: Stainless steel Connection Head, rated Ex e, M20 cable entry (不锈钢连接头, 额定 Ex e, M20 电缆入口)
- JSP: Stainless steel Connection Head, rated Ex e, 1/2NPT cable entry (不锈钢连接头, 额定 Ex e, 1/2NPT 电缆入口)

⑧Custom(Optional) 自定义 (可选)

May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use, does not affect the product safety or production process. 可能包含 4 个数字, 表示自定义报价 不影响保护方法。4 个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 11 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

GO Switch Model 7L

E.g. Model No.: 7LG 1 3 5 6 8 A2 xxxx
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

① Model 型号

7LG: 5/8 UNF external thread x 4-3/4: overall length, Green LED Indication(5/8 UNF 外螺纹 x 4-3 / 4: 总长度, 绿色 LED 指示)

7LR: 5/8 UNF external thread x 4-3/4: overall length, Red LED Indication (5/8 UNF 外螺纹 x 4-3 / 4: 总长度, 红色 LED 指示)

7LY: 5/8 UNF external thread x 4-3/4: overall length, Green/Red LED Indication(5/8 UNF 外螺纹 x 4-3 / 4: 总长度, 绿色/红色 LED 指示)

② Contact Form 连接类型

1: SPDT

③ Sensing Range 感应范围

3: 0.100" standard

④ Outlet Position 出口位置

5: Bottom, or opposite of the sensing face of switch 开关传感面的底部或对面

⑤ Enclosure Material 外壳材料

6: 316 stainless steel (rated 2kpsi) 316 不锈钢 (额定压力 2kpsi)

⑥ Area Classification* 区域分类

8: UL/cUL listed General Purpose

E: UL/cUL listed Class I, Div 2, GrABCD; Class II, Div 2, GrFG; Class III (Wiring A or B)(Lead seal req'd within 18")

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 12 页 共 23 页

证书编号：CQC20107279174

纸 号：445561

⑦Wiring Option 接线

A2 thru A8: 3ft up to 250ft length, 18GA, PVC insulated lead wires (3 英尺至 250 英尺长, 18GA, 聚氯乙烯绝缘引线)

B2 thru B8: 3ft up to 250ft length, 18GA, PVC insulated cable (3 英尺至 250 英尺长, 18GA, 聚氯乙烯绝缘电缆)

DCA: 3-pin male Mini Quick Disconnect (Approval must be 8) (3 针公头迷你快速连接器 (必须为 8))

DCD: 4-pin male Mini Quick Disconnect (Approval must be 8) (4 针公头迷你快速连接器 (必须为 8))

DCG: 5-pin male Mini Quick Disconnect (Approval must be 8) (5 针公头迷你快速连接器 (必须为 8))

DMD: 4-pin male Micro Quick Disconnect (Approval must be 8) (4 针公头微型快速连接器 (必须为 8))

⑧Custom(Optional) 自定义 (可选)

May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use, does not affect the product safety or production process. 可能包含 4 个数字, 表示自定义报价 不影响保护方法。4 个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

注：此附录与证书同时使用时有效。

主任：_____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 13 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

GO Switch Models 7G, 7GM , 7H & 7I

E.g. Model No.: 7G 1 3 5 2 3 A2 N xxxx
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

① Model 型号

7G: 5/8" UNF external thread x 4" overall length, with 1/2NPT (SPDT) or 3/4NPT (DPDT) cable entry (Hermetic Seal) (5/8" UNF 外螺纹 x 4" 总长, 带 1/2NPT (SPDT) 或 3/4NPT (DPDT) 电缆入口 (密封))

7GM: 18mm external thread x 4" overall length, with M20 (SPDT) or M25 (DPDT) cable entry (18mm 外螺纹 x 4" 总长度, 带 M20 (SPDT) 或 M25 (DPDT) 电缆入口)

7H: 5/8" UNF external thread x 3-1/4" overall length, with only potted-in leads/cable, no conduit connection (5/8" UNF 外螺纹 x 3-1/4" 总长度, 仅带有封装引线/电缆, 无导管连接)

7I: 1" UNF external thread x 5-5/8" overall length, with 1/2NPT (SPDT) or 3/4NPT (DPDT) cable entry (Hermetic Seal) (1" UNF 外螺纹 x 5-5/8" 总长, 带 1/2NPT (SPDT) 或 3/4NPT (DPDT) 电缆入口 (密封))

② Contact Form 连接类型

1: SPDT

2: DPDT

③ Sensing Range 感应范围

3: 0.100" standard (Enclosure Type 2 or 6)

④ Outlet Position 出口位置

5: Bottom, or opposite of the sensing face of switch 开关传感面的底部或对面

⑤ Enclosure Material 外壳材料

2: 303 stainless steel (rated 2kpsi) 303 不锈钢 (额定压力 2kpsi)

6: 316 stainless steel (rated 2kpsi) 316 不锈钢 (额定压力 2kpsi)

注: 此附录与证书同时使用时有效。

主任: 陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 14 页 共 23 页

证书编号: CQC20107279174

纸号: 445561

⑥Area Classification* 区域分类

- 2: Hi Temperature to 400°F (Wiring option F only)
- 3: UL / Class I, Div 1, GrABCD; Class II, Div 1, GrEFG; Class III (Model 7G, 7I only)(Wiring A,B,F)(lead seal req'd within 18")
- 4: cUL / Class I, Div 1, GrABCD; Class II, Div 1, GrEFG; Class III (Model 7G, 7I only)(Wiring A,B,F)(lead seal req'd within 18")
- 5: UL / Class I, Div 2, GrABCD; Class II, Div 2, GrFG; Class III (Model 7G, 7I only)(Wiring A,B,F)(lead seal req'd within 18")
- 6: cUL / Class I, Div 2, GrABCD; Class II, Div 2, GrFG; Class III (Model 7G, 7I only)(Wiring A,B,F)(lead seal req'd within 18")
- 7: cUL listed General Purpose
- 8: UL listed General Purpose
- 9: IECEx/ATEX Zone 1, Ex db IIC T6 Gb; Ex tb IIIC T85°C Db; IP66 (Model 7G, 7GM, 7I only) (-40°C to 50°C)(Wiring A,B)
IECEx/ATEX Zone 1, Ex tb IIC T4/T3 Gb; Ex tb IIIC T135°C/T200°C Db; IP66 (Model 7G, 7GM, 7I only) (-40°C to 100°C/150°C)(Wiring F,H)
- T: Model 73, 73M only (Hermetically sealed)IECEx/ATEX Zone 1, Ex db IIC T6 Gb; Ex tb IIIC T85°C Db; IP66 (Model 7G, 7GM, 7I only)(-40°C to 50°C)(Wiring A,B)
IECEx/ATEX Zone 1, Ex tb IIC T4/T3 Gb; Ex tb IIIC T135°C/T200°C Db; IP66 (Model 7G, 7GM, 7I only) (-40°C to 100°C/150°C)(Wiring F,H)
- F: IECEx/ATEX Zone 0, Ex ia IIC T6 Ga; Ex ia IIIC T85°C Da (-40°C to 50°C)(Wiring S)(IF 7G, 7I=hermetic seal)
- G: IECEx/ATEX Zone 0, Ex ia IIC T4 Ga; Ex ia IIIC T135°C Da (-40°C to 100°C)(Wiring S)(IF 7G, 7I=hermetic seal)
- H: IECEx/ATEX Zone 0, Ex ia IIC T3 Ga; Ex ia IIIC T200°C Da (-40°C to 150°C)(Wiring S)(IF 7G, 7I=hermetic seal)

注: 此附录与证书同时使用时有效。

主任: 陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 15 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

⑦Wiring Option 接线

A2 thru A8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), PVC insulated lead wires(3 英尺至 250 英尺长, 18GA (SPDT) 或 22GA (DPDT), 聚氯乙烯绝缘引线)

B2 thru B8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), PVC insulated cable (3 英尺至 250 英尺长, 18GA (SPDT) 或 22GA (DPDT), 聚氯乙烯绝缘电缆)

F2 thru F8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), Teflon™ insulated lead wires (3 英尺至 250 英尺长, 18GA (SPDT) 或 22GA (DPDT), 铁氟龙™绝缘导线)

H2 thru H8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), PEEK insulated lead wires (3 英尺至 250 英尺长, 18GA (SPDT) 或 22GA (DPDT), PEEK 绝缘引线)

S2 thru S8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), Silicone insulated cable (3 英尺至 250 英尺长, 18GA (SPDT) 或 22GA (DPDT), 硅胶绝缘电缆)

DCH: 7-pin male Mini Quick Disconnect (DPDT only)(Approval 7, 8, F, G, H only) (7 针公头迷你快速连接器 (仅限 DPDT) (仅限 7,8, F, G, H))

DMD: 4-pin male Micro Quick Disconnect (SPDT only)(Approval 7, 8, F, G, H only)(4 针公头微型快速连接器(仅限 SPDT) (仅限 7,8, F, G, H))

⑧Regional Certs 区域认证

Blank OR,

B: InMetro. Ex d IIC T6... T3 Gb, Ex tb IIIC T85°C... T200°C Db, IP66

N: NEPSI. Ex d IIC T3/T4/T6 Gb, Ex tD A21 IP66 T200°C/T135°C/T85°C

P: PESO. Ex db IIC T* Gb

R: EAC. 1 Ex d IIC T3/T4/T6 Gb X, Ex tb IIIC T85°C/T135°C/T200°C Db X

⑨Custom model 自定义 (可选)

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 16 页 共 23 页

证书编号：CQC20107279174

纸 号：445561

Blank OR,

May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use , does not affect the product safety or production process. 可能包含 4 个数字，表示自定义报价 不影响保护方法。 4 个自定义报价编号仅用于商业用途，不影响产品安全或生产过程。

GO Switch Models 7C, 7D, 7E & 7F

E.g. Model No.: 7C 2 3 2 5 8 A2 xxxx
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

① Model 型号

7C: 1.025" Probe length, 5/8" diameter, with cylinder mounting flange (1.025"探头长度，直径 5/8"，带气缸安装法兰)

7D: 1.250" Probe length, 5/8" diameter, with cylinder mounting flange (1.250"探头长度，直径 5/8"，带气缸安装法兰)

7E: 2.062" Probe length, 5/8" diameter, with cylinder mounting flange (2.062"探头长度，直径 5/8"，带气缸安装法兰)

7F**: 7F+probe code, Custom Probe Length from 1.00" up to 5.00" (** can be different for different probe length See Probe Selection Chart) E.g. 7FJ4 = 2.875" Probe length (7F+探头代码，自定义探头长度从 1.00"到 5.00" (** 可以根据不同的探头长度而不同参见探头选择表) 例如。 7FJ4 = 2.875"探头长度)

7CX: 1.025" Probe Length, welded cylinder mounting flange (1.025"探头长度，焊接气缸安装法兰)

7DX: 2.062" Probe Length, welded cylinder mounting flange (2.062"探头长度，焊接气缸安装法兰)

注：此附录与证书同时使用时有效。

主任： 陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 17 页 共 23 页

证书编号: CQC20107279174

纸号: 445561

探针选择列表

Probe Selection Chart

| "A" Range Probe | | | | "A" Range Probe | | | | "A" Range Probe | | | |
|-----------------|-------|--------|------|-----------------|-------|--------|------|-----------------|-------|--------|------|
| Min | Max | Length | Code | Min | Max | Length | Code | Min | Max | Length | Code |
| 1.015 | 1.040 | 1.000 | A1 | 2.365 | 2.390 | 2.350 | G1 | 3.715 | 3.740 | 3.700 | N1 |
| 1.040 | 1.065 | 1.025 | * | 2.390 | 2.415 | 2.375 | G2 | 3.740 | 3.765 | 3.725 | N2 |
| 1.065 | 1.090 | 1.050 | A3 | 2.415 | 2.440 | 2.400 | G3 | 3.765 | 3.790 | 3.750 | N3 |
| 1.090 | 1.115 | 1.075 | A4 | 2.440 | 2.465 | 2.425 | G4 | 3.790 | 3.815 | 3.775 | N4 |
| 1.115 | 1.140 | 1.100 | A5 | 2.465 | 2.490 | 2.450 | G5 | 3.815 | 3.840 | 3.800 | N5 |
| 1.140 | 1.165 | 1.125 | A6 | 2.490 | 2.515 | 2.475 | G6 | 3.840 | 3.865 | 3.825 | N6 |
| 1.165 | 1.190 | 1.150 | A7 | 2.515 | 2.540 | 2.500 | G7 | 3.865 | 3.890 | 3.850 | N7 |
| 1.190 | 1.215 | 1.175 | A8 | 2.540 | 2.565 | 2.525 | G8 | 3.890 | 3.915 | 3.875 | N8 |
| 1.215 | 1.240 | 1.200 | A9 | 2.565 | 2.590 | 2.550 | G9 | 3.915 | 3.940 | 3.900 | N9 |
| 1.240 | 1.265 | 1.225 | B1 | 2.590 | 2.615 | 2.575 | H1 | 3.940 | 3.965 | 3.925 | P1 |
| 1.265 | 1.290 | 1.250 | ** | 2.615 | 2.640 | 2.600 | H2 | 3.965 | 3.990 | 3.950 | P2 |
| 1.290 | 1.315 | 1.275 | B3 | 2.640 | 2.665 | 2.625 | H3 | 3.990 | 4.015 | 3.975 | P3 |
| 1.315 | 1.340 | 1.300 | B4 | 2.665 | 2.690 | 2.650 | H4 | 4.015 | 4.040 | 4.000 | P4 |
| 1.340 | 1.365 | 1.325 | B5 | 2.690 | 2.715 | 2.675 | H5 | 4.040 | 4.065 | 4.025 | P5 |
| 1.365 | 1.390 | 1.350 | B6 | 2.715 | 2.740 | 2.700 | H6 | 4.065 | 4.090 | 4.050 | P6 |
| 1.390 | 1.415 | 1.375 | B7 | 2.740 | 2.765 | 2.725 | H7 | 4.090 | 4.115 | 4.075 | P7 |
| 1.415 | 1.440 | 1.400 | B8 | 2.765 | 2.790 | 2.750 | H8 | 4.115 | 4.140 | 4.100 | P8 |
| 1.440 | 1.465 | 1.425 | B9 | 2.790 | 2.815 | 2.775 | H9 | 4.140 | 4.165 | 4.125 | P9 |
| 1.465 | 1.490 | 1.450 | C1 | 2.815 | 2.840 | 2.800 | J1 | 4.165 | 4.190 | 4.150 | R1 |
| 1.490 | 1.515 | 1.475 | C2 | 2.840 | 2.865 | 2.825 | J2 | 4.190 | 4.215 | 4.175 | R2 |
| 1.515 | 1.540 | 1.500 | C3 | 2.865 | 2.890 | 2.850 | J3 | 4.215 | 4.240 | 4.200 | R3 |
| 1.540 | 1.565 | 1.525 | C4 | 2.890 | 2.915 | 2.875 | J4 | 4.240 | 4.265 | 4.225 | R4 |
| 1.565 | 1.590 | 1.550 | C5 | 2.915 | 2.940 | 2.900 | J5 | 4.265 | 4.290 | 4.250 | R5 |
| 1.590 | 1.615 | 1.575 | C6 | 2.940 | 2.965 | 2.925 | J6 | 4.290 | 4.315 | 4.275 | R6 |
| 1.615 | 1.640 | 1.600 | C7 | 2.965 | 2.990 | 2.950 | J7 | 4.315 | 4.340 | 4.300 | R7 |
| 1.640 | 1.665 | 1.625 | C8 | 2.990 | 3.015 | 2.975 | J8 | 4.340 | 4.365 | 4.325 | R8 |
| 1.665 | 1.690 | 1.650 | C9 | 3.015 | 3.040 | 3.000 | J9 | 4.365 | 4.390 | 4.350 | R9 |
| 1.690 | 1.715 | 1.675 | D1 | 3.040 | 3.065 | 3.025 | K1 | 4.390 | 4.415 | 4.375 | S1 |
| 1.715 | 1.740 | 1.700 | D2 | 3.065 | 3.090 | 3.050 | K2 | 4.415 | 4.440 | 4.400 | S2 |
| 1.740 | 1.765 | 1.725 | D3 | 3.090 | 3.115 | 3.075 | K3 | 4.440 | 4.465 | 4.425 | S3 |
| 1.765 | 1.790 | 1.750 | D4 | 3.115 | 3.140 | 3.100 | K4 | 4.465 | 4.490 | 4.450 | S4 |
| 1.790 | 1.815 | 1.775 | D5 | 3.140 | 3.165 | 3.125 | K5 | 4.490 | 4.515 | 4.475 | S5 |

注: 此附录与证书同时使用时有效。

主任: 陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附录

第 18 页 共 23 页

证书编号: CQC20107279174

纸号: 445561

| | | | | | | | | | | | |
|-------|-------|-------|----|-------|-------|-------|----|-------|-------|-------|----|
| 1.815 | 1.840 | 1.850 | D6 | 3.165 | 3.190 | 3.150 | K6 | 4.515 | 4.540 | 4.500 | S6 |
| 1.840 | 1.865 | 1.825 | D7 | 3.190 | 3.215 | 3.175 | K7 | 4.540 | 4.565 | 4.525 | S7 |
| 1.955 | 1.990 | 1.950 | D8 | 3.215 | 3.240 | 3.200 | K8 | 4.565 | 4.590 | 4.550 | S8 |
| 1.990 | 1.915 | 1.875 | D9 | 3.240 | 3.265 | 3.225 | K9 | 4.590 | 4.615 | 4.575 | S9 |
| 1.915 | 1.940 | 1.900 | E1 | 3.265 | 3.290 | 3.250 | L1 | 4.615 | 4.640 | 4.600 | T1 |
| 1.940 | 1.965 | 1.925 | E2 | 3.290 | 3.315 | 3.275 | L2 | 4.640 | 4.665 | 4.625 | T2 |
| 1.965 | 1.990 | 1.950 | E3 | 3.315 | 3.340 | 3.300 | L3 | 4.665 | 4.690 | 4.650 | T3 |
| 1.990 | 2.015 | 1.975 | E4 | 3.340 | 3.365 | 3.325 | L4 | 4.690 | 4.715 | 4.675 | T4 |
| 2.015 | 2.040 | 2.000 | E5 | 3.365 | 3.390 | 3.350 | L5 | 4.715 | 4.740 | 4.700 | T5 |
| 2.040 | 2.065 | 2.025 | E6 | 3.390 | 3.415 | 3.375 | L6 | 4.740 | 4.765 | 4.725 | T6 |
| 2.065 | 2.090 | 2.050 | E7 | 3.415 | 3.440 | 3.400 | L7 | 4.765 | 4.790 | 4.750 | T7 |
| 2.090 | 2.115 | 2.075 | E8 | 3.440 | 3.465 | 3.425 | L8 | 4.790 | 4.815 | 4.775 | T8 |
| 2.115 | 2.140 | 2.100 | E9 | 3.465 | 3.490 | 3.450 | L9 | 4.815 | 4.840 | 4.800 | T9 |
| 2.140 | 2.165 | 2.125 | F1 | 3.490 | 3.515 | 3.475 | M1 | 4.840 | 4.865 | 4.825 | V1 |
| 2.165 | 2.190 | 2.150 | F2 | 3.515 | 3.540 | 3.500 | M2 | 4.865 | 4.890 | 4.850 | V2 |
| 2.190 | 2.215 | 2.175 | F3 | 3.540 | 3.565 | 3.525 | M3 | 4.890 | 4.915 | 4.875 | V3 |
| 2.215 | 2.240 | 2.200 | F4 | 3.565 | 3.590 | 3.550 | M4 | 4.915 | 4.940 | 4.900 | V4 |
| 2.240 | 2.265 | 2.225 | F5 | 3.590 | 3.615 | 3.575 | M5 | 4.940 | 4.965 | 4.925 | V5 |
| 2.265 | 2.290 | 2.250 | F6 | 3.615 | 3.640 | 3.600 | M6 | 4.965 | 4.990 | 4.950 | V6 |
| 2.290 | 2.315 | 2.275 | F7 | 3.640 | 3.665 | 3.625 | M7 | 4.990 | 5.015 | 4.975 | V7 |
| 2.315 | 2.340 | 2.300 | F8 | 3.665 | 3.690 | 3.650 | M8 | 5.015 | 5.040 | 5.000 | V8 |
| 2.340 | 2.365 | 2.325 | F9 | 3.690 | 3.715 | 3.675 | M9 | | | | |

②Contact Form 连接类型

- 2: SPST (Form A) N/O output with bi-color LED indication (N/O 输出, 带双色 LED 指示)
- 3: SPST (Form B) N/C output with bi-color LED indication (带有双色 LED 指示的 N/C 输出)
- 4: SPDT (Form C) without LED (Model 7CX, 7DX only) (不带 LED 的 (仅限 7CX 型, 7DX 型))
- 5: SPDT (Form C) with dual LED indication (具有双 LED 指示的)
- 7: SPST (Form A) N/O output without LED indication (N/O 输出, 无 LED 指示)
- 8: SPST (Form B) N/C output without LED indication (N/C 输出, 无 LED 指示)

注: 此附录与证书同时使用时有效。

主任: 陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 19 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

③Sensing Range 感应范围

3: 0.090" standard

④Outlet Position 出口位置

2: Side outlet, 360° adjustable (Wiring A, B, C, F only) No conduit connection (侧面插座, 360 度可调 (仅限 A, B, C, F 接线) 无导管连接)

5: Top outlet, or opposite of the sensing face of switch (Model 7CX, 7DX only) With 1/2NPT conduit connection (顶部插座, 或与开关传感面相对 (仅限 7CX 型, 7DX 型) 带 1/2NPT 导管连接)

6: Side outlet, 360° adjustable, no conduit connection (Approval 7 or 8 only)(Wiring D** or SubSea connectors only) (侧面插座, 360 度可调, 无导管连接 (仅限认证 7 或 8) (仅限接线 D **或 SubSea 接头))

7: Side outlet, 360° adjustable, 1/2NPT conduit connection (Wiring A, B, F only) (侧面插座, 360 度可调节, 1/2NPT 导管连接 (仅限 A, B, F 接线))

8: Top outlet (Wiring SubSea connectors only) (顶部插座 (仅接线 SubSea 连接器))

⑤Enclosure Material 外壳材料

5: 303/316 stainless steel (rated 3kpsi with 3x safety factor) (303/316 不锈钢 (额定 3kpsi, 安全系数 3 倍))

⑥Area Classification* 区域分类

2: Hi Temperature to 400°F (Contact Form 4, 7, 8 only)(Wiring option F only)

3: UL / Class I, Div 1, GrABCD; Class II, Div 1, GrEFG; Class III (Model 7CX, 7DX only)

4: cUL / Class I, Div 1, GrABCD; Class II, Div 1, GrEFG; Class III (Model 7CX, 7DX only)

5: UL / Class I, Div 2, GrABCD; Class II, Div 2, GrFG; Class III (Model 7CX, 7DX only)

6: cUL / Class I, Div 2, GrABCD; Class II, Div 2, GrFG; Class III (Model 7CX, 7DX only)

7: cUL listed General Purpose

8: UL listed General Purpose

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 20 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

- 9: IECEX/ATEX Zone 1, Ex db IIC T6 Gb; Ex tb IIIC T85°C Db; IP66 (Model 7CX, 7DX only)
(-40°C to 50°C)(Wiring A,B)
IECEX/ATEX Zone 1, Ex tb IIC T4/T3 Gb; Ex tb IIIC T135°C/T200°C Db; IP66 (Model 7CX, 7DX only)
(-40°C to 100°C/150°C)(Wiring F,H)
- T: Model 73, 73M only (Hermetically sealed)
IECEX/ATEX Zone 1, Ex db IIC T6 Gb; Ex tb IIIC T85°C Db; IP66 (Model 7CX, 7DX only)
(-40°C to 50°C)(Wiring A,B)
- IECEX/ATEX Zone 1, Ex tb IIC T4/T3 Gb; Ex tb IIIC T135°C/T200°C Db; IP66 (Model 7CX, 7DX only)
(-40°C to 100°C/150°C)(Wiring F,H)
- F: IECEX/ATEX Zone 0, Ex ia IIC T6 Ga; Ex ia IIIC T85°C Da (-40°C to 50°C)(Wiring S)(Model 7CX, 7DX only)
- G: IECEX/ATEX Zone 0, Ex ia IIC T4 Ga; Ex ia IIIC T135°C Da (-40°C to 100°C)(Wiring S)(Model 7CX, 7DX only)
- H: IECEX/ATEX Zone 0, Ex ia IIC T3 Ga; Ex ia IIIC T200°C Da (-40°C to 150°C)(Wiring S)(Model 7CX, 7DX only)
- ⑦Wiring Option 接线
- A2 thru A8: 3ft up to 250ft length, 18GA, PVC insulated lead wires (3 英尺至 250 英尺长, 18GA, 聚氯乙烯绝缘引线)
- B2 thru B8: 3ft up to 250ft length, 18GA, PVC insulated cable (3 英尺至 250 英尺长, 18GA, 聚氯乙烯绝缘电缆)
- C2 thru C8: 3ft up to 250ft length, 18GA, PVC insulated cable, water resistant (3 英尺至 250 英尺长, 18GA, 聚氯乙烯绝缘电缆, 防水)
- F2 thru F8: 3ft up to 250ft length, 18GA, Teflon™ insulated lead wires (3 英尺至 250 英尺长, 18GA, Teflon™绝缘引线)
- S2 thru S8: 3ft up to 250ft length, 18GA (SPDT) or 22GA (DPDT), Silicone insulated cable (Model 7CX, 7DX only)
(3 英尺至 250 英尺长, 18GA (SPDT) 或 22GA (DPDT), 硅胶绝缘电缆 (7CX 型, 仅 7DX))

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 22 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

GO Switch Models 7J

E.g. Model No.:

7J 1 3 5 6 4 JSP N xxxx
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

① Model 型号

7J: External thread 5/8-18UNF (外螺纹 5/8-18UNF)

7JM: External thread M18 metric (外螺纹 M18 公)

② Contact Form 连接类型

1: SPDT

③ Sensing Range 感应范围

3: 0.100" (2.5mm) standard

④ Outlet Position 出口位置

5: Bottom outlet, 1/2NPT or M20 conduit connection (底部插座, 1/2NPT 或 M20 导管连接)

⑤ Enclosure Type/Material 外壳材料

6: 316 stainless steel (316 不锈钢)

⑥ Approvals / Area Classification 区域分类

4: UL/cUL Class I, Div 1, GrABCD; Class II, Div 1, GrEFG

6: UL/cUL Class I, Div 2, GrABCD; Class II, Div 2, GrFG

7: UL/cUL General Purpose

9: Ex db IIC T6 Gb, Ex tb IIIC T85°C Db; IP66/68, Tamb: -40°C to +75°C

注: 此附录与证书同时使用时有效。

主任: _____

陆杨



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>



产品认证证书

附 录

第 23 页 共 23 页

证书编号: CQC20107279174

纸 号: 445561

Y: Ex db eb IIC T6 Gb, Ex tb IIIC T85°C Db; IP66/68, Tamb: -40°C to +75°C

F: Ex ia IIC T6 Ga; Ex ia IIIC T85°C Da, Tamb: -40°C to +50°C

G: Ex ia IIC T4 Ga; Ex ia IIIC T135°C Da, Tamb: -40°C to +100°C

H: Ex ia IIC T3 Ga; Ex ia IIIC T200°C Da, Tamb: -40°C to +150°C

⑦Wiring / Cable Entry (Terminal block is provided for field wiring) 接线

JSP: 1/2NPT cable entry (Model 7J) (1 / 2NPT 电缆入口 (型号 7J))

JSM: M20 cable entry (Model 7JM) (M20 电缆入口 (型号 7JM))

⑧Regional Approvals / Certifications 区域认证

N: NEPSI (Approval 9 only) Ex d IIC T3/T4/T6 Gb, Ex tD A21 IP66 T200°C/T135°C/T85°C (Ref current NEPSI certificate)

K: KOSHA (Approval 9 only) Ex d IIC T6 (ref current KOSHA certificate)

R: EAC (Approval 9) 1 Ex d IIC T6 Gb X, Ex tb IIIC T85°C Db X; (Approval Y) 1 Ex de IIC T6 Gb X, Ex tb IIIC T85°C Db X

Z: Canada Zone Equivalence (Approval 4 only) Class I, Zone 1, Ex d IIC; Class II, Zone 21, Ex tb IIIC

⑨Custom(Optional) 自定义 (可选)

Blank OR,

May include 4 numbers indicating custom quote. Does not affect protection method. The 4 custom quote number is only for commercial use , does not affect the product safety or production process. 可能包含 4 个数字, 表示自定义报价 不影响保护方法。 4 个自定义报价编号仅用于商业用途, 不影响产品安全或生产过程。

注: 此附录与证书同时使用时有效。

主任: _____

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>