



Fast - Accurate - Reliable

The Flexim FLUXUS® F/G731 is a technological breakthrough in the clampon ultrasonic flow measurement of liquids and gases. With its new hardware design and improved, powerful digital signal processing it surpasses any other non-intrusive ultrasonic flow meter in terms of accuracy, reliability and versatility.

Clamp-On Saves Cost and Time

From the smallest tubing to the largest penstock, independent from the pressure inside the pipe and over a very wide temperature range, the Flexim FLUXUS® F/G731 saves time and money! Whether it is gas or liquid, no process interruption is required for installation. The signal processing increases robustness even in challenging conditions with entrained gas or solids or liquid in the gas stream. Even low flows down to only a few liters per hour can be recorded accurately. As the flow meter of choice for a very wide range of applications in virtually any industrial sector, the FLUXUS® F/G731 is available with two different housing types: aluminum enclosure for standard applications and stainless steel enclosure for operation in highly corrosive environments.


Ready for Industry 4.0

The Flexim FLUXUS® F/G731 comes with all common communication protocols - HART, Modbus, Foundation Fieldbus, Profibus PA and BACnet allow field communication, parameterization and online diagnostics. The FLUXUS® F/G731 is also one step ahead in terms of user guidance and diagnostics. It can be easily parameterized via USB. Its Ethernet connectivity provides additional bidirectional communication capabilities. The Advanced Meter Verification tool enables the user to prove the meter performance at any time.

Key Features

- Fully compliant with ISO 24062
- Advanced Meter Verification provides continuous meter status check
- Integrated Flow Disturbance Correction allows installations with a short inlet run down to 2x pipe diameter length
- Transducer calibration according to ISO 17025
- Permanent transducer coupling reduces the maintenance efforts to virtually zero
- Synchronized multi-channel processor for instant flow disturbance compensation
- Matched transducers, built-in temperature compensation (according to ANSI/ASME MFC-5.1-2011 regulations) and digital signal processing guarantee excellent zero-point flow measurement stability

 Instantaneous flow compensation of averaging (Y) channel with F/G731 Synchronized Channel Averaging ultrasonic flow meter





Instantaneous Flow Compensation

Flow profile changes or disturbances inside the pipe are the result of multiple factors: high flow velocities, pressure and temperature fluctuations, inadequate inflow conditions (straight runs), and adjacent instrumentation such as valves, gauges, etc. Minimizing the effects of these disturbances makes all the difference when it comes to accurate and reliable flow measurement. While optimal inflow conditions, flow conditioners and other design measures can solve these issues, in real-world applications, the opposite is often the case, resulting in a trade-off between response time and performance.

With Flexim FLUXUS® F/G731 there is no compromise. The faster processor reduces fluctuations and lag time in the meter reading, thus resulting in better and more stable outputs.

Superior Performance


The new Flexim FLUXUS® F/G731 leverages the already superior capabilities and advanced signal processing techniques pioneered by Flexim's clamp-on measurement solutions, while introducing an even faster DSP processing module that enables Synchronized Channel Averaging measurement.

Operational Safety
 The measurement system can't cause pipe leaks, be prone to clogging or any other related issues that can compromise


process integrity.

- Economical Solution
 An externally mounted system means there's no need for process interruptions or additional engineering costs.
- Maintenance-Free
 No contact with flowing
 fluids results in a completely
 maintenance-free and durable
 metering solution suitable for
 the harshest environments.
- Standard Volumetric Flow Rate and Mass Flow Rate Compensation
 Pressure and temperature inputs for built-in standard volumetric and/or mass flow rate measurement.

2. Disturbed flow profile and flow velocity vector composition



3. Cross flow compensation with X arrangement or reflection arrangement



TECHNICAL FACTS Flexim FLUXUS® F/G731 Measurement uncertainty (volumetric flow rate) FLUXUS® F731 (liquids) \pm 1% MV \pm 0.02 ft/s (\pm 0.005 m/s) FLUXUS® G731 (gases) $\pm 1...2\%$ MV ± 0.02 ft/s (± 0.005 m/s) Transmitter Response time 1 s (2 channels) Repeatability $0.15 \% MV \pm 0.02 ft/s (\pm 0.005 m/s)$ Number of measuring channels 1 or 2 Explosion protection of ATEX/IECEx Zone 2, FM Class I / Div. 2 transmitter Power supply 90...264 V/50...60 Hz or 11...32 V DC 4...20 mA active/passive 4...20 mA HART active/passive Outputs Pulse/frequency/binary Digital outputs Pulse/frequency/binary Pt100/Pt1000 Inputs 4...20 mA active/passive Modbus RTU/TCP, BACnet MSTP/IP, Profibus PA, Digital communication Foundation Fieldbus Available transducers Pipe size range (inner diameter) FLUXUS® F731 0.24...256 in (6 mm...6500 mm) FLUXUS® G731 0.28...64 in (7 mm...1600 mm) Temperature range (pipe wall) -40...+392 °F / WI: -328...+1166 °F FLUXUS® F/G731

(-40...+ 240 °C / WI: -200...+630 °C)

- Fast measurement dynamics thanks to high sampling rates
- Certified for use in hazardous areas ATEX/IECEx Zone 2, FM Class I Div. 2
- High operational safety with no risk of leakage
- Independent of pipe material, diameter, wall thickness and internal pressure and temperature
- Accurate and repeatable measurement readings even at extremely low flow rates (high turndown ratio)
- Highly cost-effective compared to wetted instrumentation



FLUXUS® F/G731 aluminum housing



FLUXUS® F/G731 stainless steel housing





The Emerson logo is a trademark and service mark of Emerson Electric Co. FLUXUS® is a registered trademark of one of the Emerson family of companies. All other marks are the property of their respective owners.

© 2024 Emerson Electric Co.

All rights reserved.

For more information, visit

Emerson.com/Flexim

BUFG731V1-0EN 0924



