


XL Pneumatic Actuators

High on Quality... High on Reliability... High on Service



Hytork –High on Quality

- Reduce capital cost
- Reduce installation cost
- Reduce maintenance cost
- Increase plant uptime
- Increased plant and operator safety

“Hytork has combined quality with reliability and economy in a single package”

“Heavy duty cast construction provides maximum protection for harsh service”

“Only three moving parts make operation highly dependable”

The XL actuator range of actuators is the result of Hytork’s 30-plus years of field-proven experience. The actuators have numerous features that add reliability. Its rugged heavy duty body is made from a high strength LM25 aluminum casting designed to prevent damage from dents, shock or fatigue. The XL is modular in design and is field convertible from double-acting to spring-return configurations and vice versa.

1 NAMUR Mounting

This mounting configuration allows standardization of mounting hardware for a wide range of accessories.

2 CERAMIGARD

The spring chambers of spring return actuators often have an open connection to the environment. To protect the bore and other internals against wear and corrosion, all XL actuator bodies have a hard corrosion resistant ceramic-like finish of Di-Aluminum Tri-oxide (Al_2O_3).

3 Large Internal Air Passages

This feature maximizes valve operating speeds and adds reliability by reducing potential blockage.

4 DURASTRIP Bearings


All moving parts are protected by permanently lubricated and long-lasting DURASTRIP bearings. It reduces friction and leads to longer life.

5 ISO 5211 Mounting Pad

Hytork XL actuator pinion drives are manufactured to ISO 5211 with a star drive to provide extra flexibility and simplicity for direct mounting to a valve.

6 Accessory Mounting Holes

On the smaller sizes there are extra mounting holes near NAMUR solenoid pad to facilitate filter/regulator bracket installation.



Hytorch –High on Reliability

7 Visual Position Indicator

The visual position indicator is designed for indication at a glance and can easily be converted from across-line to in-line indication.

8 Corrosion Resistant Pinion

Plated with cobalt zinc, the steel pinion is protected from corrosion. Actuator has experienced a salt spray test up to 1,000 hours. The pinion also features a unique stop design.

9 Bi-Directional Travel Stops

XL actuators have two travel stops. (See page 4)

10 Rack and Pinion Design


Extra large rack and pinion tooth design promotes full tooth engagement. Assists gear tooth life by reducing stress and having precise gear tooth mesh.

11 End Caps

A polyester powder-coated surface treatment as standard on end caps and housing provides extra protection against aggressive environments. (See page 4)

12 Spring Package

XL Springs are designed and manufactured never to break. The nested design provides a balanced concentric force on the pistons. They are coated with an electrophoretic finish to protect against corrosion, are guaranteed for life and backed by a free complete actuator replacement.



13 SAFEKEY System

The patented SAFEKEY method of end cap assembly to the actuator eliminates dangerous disassembly. (See page 4)

14 Cast-in identification

The unique cast body and end caps allow cast-in identification model numbers, port identifications and safety instructions and are therefore permanently readable. No lost identification due to weathering or paint.

Superior design and construction

The XL series is engineered and manufactured to the highest quality and tolerance standards. Site proven DURASTRIP bearings protect all moving parts for guaranteed high cycle life. Unbreakable Springs, with a unique lifetime warranty, assure Fail Safe action when it is needed. **Increase process safety and plant uptime.**

Easy maintenance

Change a solenoid or positioner, adjust a switch, alter a spring rating or install a new set of bearings and seals (never a spring set) – in just minutes. **Lower maintenance costs.**

Safety first

Hytorch XL actuators comply to the European safety and health requirements as required by the ATEX, PED and Machine Directives. Rugged, heavy duty body casting, patented SAFEKEY, unbreakable springs and HYTORK'S safety retractor rod system for disassembly of spring return actuators. All these features provide **increased personnel and plant safety.** Hytorch XL actuators are only intended for use in large-scale fixed installations excluded from the scope of Directive 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment (RoHS 2).

Wide torque range

Hytorch's 12 actuator sizes cover a wide torque range (19 to 3232 Nm @ 5.5 Barg; 167 to 28500 in/.lbs @ 80 PSIG). With up to 7 spring sets per actuator size, this allows the correct selection of the actuator size you need, all to **reduce procurement costs.**

Additional Hytorch XL features

All the Hytorch XL features provide:

Reduced capital cost

Reduced installation cost

Reduced maintenance cost

Reduced assembly cost

Increased process safety

Increased plant uptime


Increased plant and operator safety

Hytork – High on Service


SAFEKEY System

The SAFEKEY system (patented) uses a flexible stainless steel key in an internal machined keyway. Completely sealed with o-rings to prevent external contamination, the SAFEKEY system eliminates stress concentrations caused by point loading. It is stronger than conventional bolting and is impossible to remove when pressurized or with springs under tension. It is a proven means of eliminating potentially dangerous disassembly.

With the SAFEKEY method, cap screws are not needed to retain the end caps to the actuator body. With other methods, galling can occur and fasteners can break. Competitor models often use Helicoils™ that can turnout or rip out if over-torqued. SAFEKEY is yet another Hytork advantage.




SAFEKEY System eliminates conventional screws and tierods.



Bi-Directional Travel Stops

Hytork XL actuators are provided with bi-directional travel stops. This feature provides rotational adjustment on the actuator in both travel directions. The stops provide precise travel control. This is particularly important when used with special duty, high precision valves, such as metal seated or high performance butterfly valves needing exact rotation stopping. Models XL2586 and XL4581 have a bottom mounted travel stop plate.





Valvetop T-Series

- **Rugged enclosures for demanding environments**
 - NEMA 4, 4X / IP66/67
 - UL Certification C11 Div 1 Grps C,D
 - TVA, Composite Resin
 - TXP, Aluminium
 - TXS, Stainless Steel
- **Stainless Steel Shaft & Fasteners**
- **Variety of integral pilot valves available**
 - Low-Power Solenoid
 - Single Coil
 - High flow rate of 1.0 Cv
 - Integrally mounted for extra protection
- **Low-profile impact resistant poly carbonate visual display, available with intuitive colors and customizable to your application**
- **Suitable for extreme operating temperatures from -50°C to 80°C (-58°F to 176°F)**

Valvetop D-Series

- **Rugged enclosures for demanding environments**
 - NEMA Type 4, 4X, 7 plus IP66/67
 - DXP, Tropicalized Aluminium
 - DXS, 316L Stainless Steel
 - DXR, Composite Resin
- **Stainless Steel Shaft & Fasteners**
- **Variety of integral pilot valves available**
 - Aluminium, 304, 316 Stainless Steel
 - Low-Power Solenoid or Ultra-Low Power Piezo
 - Single or Dual Coil
 - High flow rates of 1.2 Cv or 3.0 Cv
- **Impact resistant poly carbonate visual display, available with intuitive colors and customizable to your application**
- **Suitable for extreme operating temperatures from -50°C to 80°C (-58°F to 176°F)**



Value-Added Accessories

Hytork XL with Valvetop™ Discrete Valve Controllers


Valvetop Discrete Valve Controllers from TopWorx™ are engineered to provide superior performance in the most demanding conditions. With a variety of bus networking and sensor options such as FOUNDATION™ fieldbus, DeviceNet, AS-interface, Profibus, HART, GO Switch, and inductive proximity and mechanical switches, Valvetop is flexible enough for any valve application.

Each Valvetop model carries global certifications such as IECEx, ATEX, UL, CSA, NEPSI, KOSHA, InMetro, and GOST, allowing them to be used anywhere in the world.

Hytork XL the starting point for Valve Operating System™ (VOS)

Hytork XL actuators come with solenoid and accessory mounting interfaces that comply with internationally accepted standards like EN15714-3 and VDE/VDI 3845 (NAMUR). Due to these standardized interfaces, Hytork XL actuators can be packaged together with a range of control and feedback accessories.

Emerson, with all its control and feedback accessories, makes sure you have a reliable (VOS) from a single source supplier.



XL Commando for Corrosion Resistance



The XL Commando range solves aggressive corrosion problems. It works where stainless doesn't. A proprietary heat treatment with CG941 fluoropolymer impregnates the body making it impervious to corrosion. The steel pinion is also fluoropolymer coated. Field service has shown that the Commando actuators outperform other actuators in corrosive environments.

World Area Configuration Centers (WACC) offer sales support, service, inventory and commissioning to our global customers. Choose the WACC or sales office nearest you:

NORTH & SOUTH AMERICA

19200 Northwest Freeway
Houston TX 77065
USA
T +1 281 477 4100

Av. Hollingsworth
325 Iporanga Sorocaba
SP 18087-105
Brazil
T +55 15 3413 8888

ASIA PACIFIC

No. 9 Gul Road
#01-02 Singapore 629361
T +65 6777 8211

No. 1 Lai Yuan Road
Wuqing Development Area
Tianjin 301700
P. R. China
T +86 22 8212 3300

MIDDLE EAST & AFRICA

P. O. Box 17033
Jebel Ali Free Zone
Dubai
T +971 4 811 8100

P. O. Box 10305
Jubail 31961
Saudi Arabia
T +966 3 340 8650

24 Angus Crescent
Longmeadow Business Estate East
P.O. Box 6908 Greenstone
1616 Modderfontein Extension 5
South Africa
T +27 11 451 3700

EUROPE

Holland Fazor 6
Székesfehérvár 8000
Hungary
T +36 22 53 09 50

Strada Biffi 165
29017 Fiorenzuola d'Arda (PC)
Italy
T +39 0523 944 411

For complete list of sales and manufacturing sites, please visit www.emerson.com/actuationtechnologieslocations or contact us at info.actuationtechnologies@emerson.com

©2019 Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Hytork™ is a mark of the Emerson family of companies. All other marks are property of their respective owners.



www.emerson.com/hytork