

Refinery Increases Profitability by Pushing Production Limits while Controlling for Piping and Equipment Damage

RESULTS

- Increased facility profit by increasing production without capital spending
- Verified the viability of equipment condition to avoid unnecessary shutdowns
- Quantified the wear-and-tear on piping and equipment to determine higher production limits



APPLICATION

Rosemount™ Wireless Permasense Corrosion and Erosion Monitoring Probes and Analytic Software used to monitor refinery equipment.

CUSTOMER

European refiner operated by integrated major oil and gas producer

CHALLENGE

Refineries wanting to increase profitability can try to reduce production costs – or increase production levels, provided there is sufficient market demand. Pushing for increased production may require capital projects to remove bottlenecks, but determining how much production can be driven up usually begins with gradual increases until bottlenecks emerge.

Corporate management challenged this refinery to increase production by 30 percent without launching any major capital improvements.

Faced with such a challenge, one approach is to simply run pumps faster, open valves wider, and go past normal limits in an effort to increase production. Naturally, the effects vary greatly depending on the nature of the plant, but here are a few typical effects:

- Heating stages must run hotter to transfer heat more quickly
- Fluid flows through pipes and valves increase with higher velocities
- Residence time in reactors is reduced
- The separating efficiency of fractionation distillation processes is lowered

One of the bottlenecks that soon emerged was in the refinery's hydrocracker unit, which was already running at a high conversion rate. Some effectiveness of the process would be lost by forcing a higher amount of unconverted oil out with the propane and light-ends stream into the hydrocracker stabilizer. This stream was cooled in a series of heat exchangers and then split into three streams: propane, unconverted oil, and sour water.

The unit ran for about four years at the new production rate and seemed to be working well. Unknown to the operators, the increased flow of propane was eroding a complex header system designed to collect propane from the heat exchangers. One day operators discovered a plume of liquid propane with high H₂S content shooting out of a newly formed leak in the header, creating serious safety and environmental issues, not to mention product loss.

“The total sensor installation project cost was approximately 25,000 €, however, given the production value of the unit of about one million € per day, it was regarded as a minor expense.”

Fortunately, the problem was discovered before the propane found an ignition source. The unit was shut down briefly so an externally mounted clamp could be installed before resuming operation. This solved the immediate problem, but engineers feared more leaks were likely to occur.

SOLUTION

The refinery's evaluation engineering team installed five Rosemount Wireless Permasense transmitters, mounted at strategic points around the header. After some analysis, they determined the carbon steel header pipe wall was thinning at a rate of 2 mm (0.08-in.) per year due to the erosion caused by the increased flow combined with high H2S levels resulting from higher sour water carry-over.

The total transmitter installation project cost was approximately 25,000 €, however, given the production value of the unit of about one million € per day, it was regarded as a minor expense. Permasense transmitters are permanently mounted, make continuous metal-thickness readings, and send the data to a monitoring and historizing system via a WirelessHART® network. Readings from individual transmitters can be analyzed over time, making it possible to monitor metal loss as it happens.

While damage to the header was severe, engineers determined that enough integrity remained to allow the header to continue operating safely until a new header could be fabricated from stainless steel and installed during a scheduled turnaround. The new header would be more expensive than its carbon steel predecessor, but engineers anticipated a much longer service life and, since it could be manufactured in a reasonable amount of time, rush-premium charges were avoided.

The true value of the Permasense installation and its data was in avoiding the potential disaster of a major header failure and catastrophic hydrocarbon release. It also avoided costs for expedited design and fabrication of a new header, and eliminated production disruptions for an unwarranted shutdown. Had the engineers not been able to determine the true condition of the header, a shutdown would have been required for safety reasons.



Five Rosemount Wireless Permasense ultrasonic thickness measuring sensors, mounted at strategic points around the header, helped determine the carbon steel header pipe wall was thinning at a rate of 2 mm (0.08-in.) per year.

RESOURCES

Rosemount Wireless Permasense Corrosion and Erosion Monitoring Systems

[Emerson.com/Automation/Permasense](https://www.emerson.com/Automation/Permasense)

Emerson Terms and Conditions of Sale are available upon request.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount is a mark of one of the Emerson family of companies. All other marks are the property of their respective owners.

© 2019 Emerson. All rights reserved.

[LinkedIn.com/company/Emerson-Automation-Solutions](https://www.linkedin.com/company/Emerson-Automation-Solutions)

[Twitter.com/Rosemount_News](https://twitter.com/Rosemount_News)

[Facebook.com/Rosemount](https://www.facebook.com/Rosemount)

[Youtube.com/user/RosemountMeasurement](https://www.youtube.com/user/RosemountMeasurement)

Global Headquarters

Emerson Automation Solutions

6021 Innovation Blvd.

Shakopee, MN 55379, USA

+1 800 999 9307 or +1 952 906 8888

+1 952 949 7001

RFQ.RMD-RCC@Emerson.com

Europe Region

Emerson Automation Solutions Europe GmbH

Neuhofstrasse 19a P.O. Box 1046

CH 6340 Baar, Switzerland

+41 (0) 41 768 6111

+41 (0) 41 768 6300

RFQ.RMD-RCC@Emerson.com

Middle East and Africa Region

Emerson Automation Solutions

Emerson FZE P.O. Box 17033,

Jebel Ali Free Zone - South 2

Dubai, United Arab Emirates

+971 4 8118100

+971 4 8865465

RFQ.RMTMEA@Emerson.com

Asia Pacific Region

Emerson Automation Solutions

1 Pandan Crescent

Singapore 128461

+65 6777 8211

+65 6777 0947

Enquiries@AP.Emerson.com

00830-0200-4210, Rev AB