Rosemount[™] X-well[™] Technology saves significant operational costs, improves product quality

RESULTS

- Reduced annual operational cost by more than \$57,000
- Improved process efficiencies
- Improved product quality and document contracted agreement for product delivery



A cogeneration power and heating plant using gas turbine, steam turbine, heat recovery steam generator and control systems.

CUSTOMER

DS Power Company, Ltd is a highly efficient, eco-friendly cogeneration plant. The company produces a stable power supply for the growing city of Osan, South Korea, district heating and cooling for 42,000 households and process steam to eight nearby factories. The company prides itself on its ability to provide environmentally friendly products using clean burning LNG fuel.

CHALLENGE

DS Power Operations and Maintenance Teams spent over 160 hours a month doing manual rounds to visually check temperature gauges installed around the plant to ensure efficient operation and proper water temperature. To optimize the plants operations, DS Power wanted to automate temperature measurement for their multifunctional plant to help reduce the manual labor hours required to fulfill their contract to provide hot water at 100 °C to their local utility.

With their existing temperature measurement system installed, their Instrument Technicians spend 5 hours a day making manual rounds to record temperature measurement data from temperature gauges. Additionally, the maintenance team spent 2 hours each week visually checking the gauges for proper operation. DS Power also wanted an automated system to ensure that water delivered to the local utility was at the proper temperature of 100 °C and that the system was optimized to efficiently deliver products without wasting energy.

SOLUTION

Emerson recommended Rosemount 648 X-well Technology temperature transmitters. X-well Technology's non-intrusive temperature measurement was easy to install and commission



"X-well Technology can be commissioned in less than one hour per temperature point."



Rosemount X-well Technology can be configured to fit pipe sizes from half inch to four foot diameters.



Cogeneration Plant - Power and Heating

without the need for cutting and welding pipes or worrying about wake frequency calculations. Plus, simple bolt-on installation allowed DS Power Maintenance Engineers to install the temperature points without process shut down and without the additional costs of hiring outside contractors for piping work. Because the plant is scheduled for expansion, future needs for temperature measurement can be easily added to seamlessly integrate into the plant's infrastructure.

The plant's immediate benefit is the ability to collect accurate temperature measurement that can be monitored from the control room, eliminating manual rounds and saving an estimated \$57,000 (USD) annually in unnecessary operational costs.

The new X-well transmitters were connected wirelessly using DS Power's existing Ovation Distributed Control System (DCS). Ovation's embedded advanced applications and proven industry-specific control routines assures optimized operations to maximize plant reliability and profitability.

RESOURCES

White Paper

Get a copy of our White Paper at <u>http://emr.sn/NM27</u> Flyer

https://www.emerson.com/documents/automation/flyertemperature-measurement-assembly-rosemount-x-well-technologyaccurately-measure-process-temperature-without-a-thermowellprocess-penetration-en-80370.pdf

Videos

Rosemount X-well How it Works Rosemount X-well Overview Rosemount X-well Non-intrustise Temperature Measurement

Emerson Terms and Conditions of Sale are available upon request. The Emerson logo is a trademark and service mark of Emerson Electric Co. Rosemount is a mark of one of the Emerson family of companies. All other marks are the property of their respective owners. © 2019 Emerson. All rights reserved.

Global Headquarters Emerson Automation Solutions

6021 Innovation Blvd.

Shakopee, MN 55379, USA

+1 800 999 9307 or +1 952 906 8888

(2) +1 952 949 7001

C RFQ.RMD-RCC@Emerson.com

00830-0800-4648_RevAA

Europe Region Emerson Automation Solutions Europe GmbH

Neuhofstrasse 19a P.O. Box 1046 CH 6340 Baar, Switzerland

- +41 (0) 41 768 6111
- +41 (0) 41 768 6300
- RFQ.RMD-RCC@Emerson.com

X-well Technology is available in wired and wireless versions and can easily integrate into an existing process without shut down or production loss.



- In Linkedin.com/company/Emerson-Automation-Solutions
- Twitter.com/Rosemount_News
- Facebook.com/Rosemount
- Youtube.com/user/RosemountMeasurement
- B Google.com/+RosemountMeasurement

Middle East and Africa Region Emerson Automation Solutions

Emerson FZE P.O. Box 17033, Jebel Ali Free Zone - South 2 Dubai, United Arab Emirates +971 4 8118100 +971 4 8865465 RFQ.RMTMEA@Emerson.com

Asia Pacific Region Emerson Automation Solutions

1 Pandan Crescent Singapore 128461

+65 6777 0947 Enquiries@AP.Emerson.com



ROSEMOUNT