



2410 TANK HUB



- ③ IT IS RECOMMENDED TO USE A 120Ω TERMINATION RESISTOR
- ② K2-ADE SHOULD ONLY BE USED FOR SERVICE PURPOSE.
- ① SETTINGS SHOWN FOR 2410 WITH RS485 ON PRIMARY BUS AND DEFAULT SETTINGS; 9600 BAUD, RTS/CTS, 2-WIRE HALF DUPLEX, 1 STOP BIT, NO PARITY

ISSUED BY TP-CH	WEEK 1403	PRODUCT CODE RAPTOR	FILE ACAD	INSTALLATION DRAWING TITLE			
APPROVED BY TSe-AH	WEEK 1403	ORIGINAL DWG NO. 9261065-058	SCALE -	EL INST. DWG 2410 TANK HUB K2-ADE RS232-RS485 CONVERTER			
ROSEMOUNT			1 ST ANGLE 	DOC TYPE 2	DWG NO. 9261095-013	ISSUE 1	SHEET 1/1

THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. SAAB MARINE ELECTRONICS AB.