

What if You Could Make Tank Level Measurements Easy Every Step of The Way?

Introducing Rosemount 520 Level Transmitter

- Ensure safe vessel operation
- Meet marine requirements easily with one transmitter
- Install and configure easily
- Reduce maintenance frustrations



Suitable for all marine tank applications

Designed especially for harsh marine environments

Increased safety for installers and operators

Get support quickly and easily anytime, anywhere

Compliance to marine requirements

Compatible with all commonly used liquids

Emerson Tank Level Gauging

Rosemount 520 Level Transmitter

You will gain exclusive benefits from working with Emerson and by choosing our new Level Transmitter. Taking on your toughest challenges:

Safety

With the Rosemount 520 Level Transmitter you can re-range and commission it with digital commands which means it can be accessed and configured remotely from the control room, removing any risks associated with manual handling on location in the hazardous environments.

Compliance


With compliance to marine requirements the vetting inspections will go smoother. Knowing that if your transmitter fails a vetting inspection this could postpone operations until you resolve the inspector's concerns, which costs you operational days and service expenses. In the long term, failed vetting inspections can sour business relationships, and even take a vessel out of operation.

Performance

Sensors can drift over time, leading to measurement inaccuracies and requiring a technician's time to recalibrate equipment. The sensors that make up the Rosemount 520 Level Transmitter are tested repeatedly against the extremes of humidity, temperature, and pressure. Because of this rigorous testing, the Rosemount 520 comes standard with superior overpressure protection and readjustment is only needed every fifth year due to high stability.

Flexibility

The Rosemount 520 Level Transmitter is suitable for installation in virtually any tank gauging application with a comprehensive offering of installation kits. The transmitter is available as gauge or absolute type to fit all applications. Selecting the Rosemount 520 Level Transmitter gives you a transmitter designed especially for harsh marine environments, giving you a robust transmitter with all-welded titanium housing, compatible with all commonly used liquids. You will get a extremely flexible transmitter 100% dedicated for marine usage.



CONTACT US

Please contact us for further information:

Emerson's
Marine Solutions

©2020 Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Co. Damcos trademark and logotype are trademarks of Damcos A/S. LevelDatic is a trademark of Rosemount TankRadar AB. Rosemount and Rosemount logotype are trademarks of Rosemount Inc. All rights reserved. The contents of this publication are presented for informational purposes only, and while efforts have been made to ensure their accuracy, they are not to be construed as warranties or guarantees, expressed or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice. Emerson Process Management accepts no responsibility for any errors that may appear in this publication.

Version 03, November 2020, Marine Integrated Marketing