
Fisher[™] i2P-100 Electro-Pneumatic Transducer

The Fisher i2P-100 electro-pneumatic transducer, uses a converter module that converts a milliampere input to a proportional pressure output. Both the current input and pressure output range are user-configurable in the field. The converter module uses small parts of minimum mass, which are balanced symmetrically around a pivot point at the center of the mass. This balanced arrangement results in a high performance instrument that reduces sensitivity to vibration.

An integral pneumatic relay provides the high capacity necessary to drive pneumatic control valve/actuator assemblies without additional boosters or positioners. The transducer also provides stable, accurate operation when its output is transmitted to small volume chambers, such as a pneumatic positioner or other pneumatic instrument. Reduced sensitivity to vibration, combined with high capacity and first order lag characteristics, make the i2P-100 transducer suitable for direct mounting on control valve/actuator combinations.

Features

- Approved for use with Natural Gas—The i2P-100 is approved for use with natural gas as the pneumatic supply.
- Low Pneumatic Supply Consumption—The transducer has low pneumatic supply consumption which lowers operating costs. Maximum steady state consumption is less than the 6 SCFH requirement set for the oil and gas industry by the US Environmental Protection Agency (New Source Performance Standards Subpart OOOO, EPA-HQ-QAR-2010-0505).
- Single Sealed Device— The i2P-100 has been tested in accordance with ANSI/ISA Standard 12.27.01 (Requirements for Process Sealing Between Electrical Systems and Flammable or Combustible Process Fluids) as a single sealed device.



- High Output Capability and Rangeability— The integral output relay volume of the transducer is adequate to drive valve/actuator combinations without requiring a positioner or volume booster. Selectable user field-configurable dip switch setting for output range of 0.14 to 2.3 bar (2 to 33 psi).
- Split Range—Selectable user field-configurable two-way split range, using either half of the standard input signal.
- Corrosion Resistant—Separate housing compartments isolate the electronics from the pneumatic process. The electronics module is encased in a rugged plastic shell which helps to prevent damage to the electronics. The printed wiring board and dip switches are conformal coated to help prevent corrosion. Converter module coils have corrosion resistant coating and all flexures are gold plated to provide protection from hostile environments.
- Tolerant of Dirty Supply Medium—Free-flow pilot stage design and large internal air passages provide excellent tolerance to dirty pneumatic supply, by reducing the effects of contaminant buildup and erosion. The removable primary orifice and replaceable 5 micrometer filter are easy to remove for service and maintenance.





Product Bulletin 62.1:i2P-100 October 2022

Figure 1. Fisher i2P-100 Electro-Pneumatic Transducer Mounted on a Rotary Actuator



W8693-1

- Easy Maintenance—Modular electronics and converter modules contained in separate housing compartments, isolating the electronics from the process, allow for easy replacement in the field for reduced maintenance time and costs.
- Vibration Resistance—The transducer, used in a standard valve/actuator mounted application, exhibits an output shift of less than 1 percent of span when tested to ISA S75.13.

Valve Stroking Time

W8723-1

Figure 3 shows relative times for loading and exhausting an actuator. Stroking time depends upon the size of the actuator, travel, relay characteristics and the magnitude and rate of change of the input signal. If stroking time is critical, contact your Emerson sales office.

Table of Contents

Features	1
Valve Stroking Time	2
Specifications	

Installation	6
Ordering Information	6

Figure 2. Fisher i2P-100 Electro-Pneumatic Transducer Mounted on a Sliding-Stem Actuator

Specifications

Input Signal

Available as standard with 4-20 mA. User configurable by dip switch for split ranging, see table below.

Output Signal

Available as standard 0.2 to 1.0 bar (3 to 15 psig), 0.4 to 2.0 bar (6 to 30 psig), or 0.14 to 2.3 bar (2 to 33 psig). User configurable by dip switch selection and zero and span potentiometer adjustment, see table below.

	OUTPUT PRESSURE			
INPUT SIGNAL	Bar	Psig		
	0.2 to 1.0	3 to 15		
4 to 20 mA DC	0.4 to 2.0	6 to 30		
	0.14 to 2.3	2 to 33		
4 to 12 mA DC	0.2 to 1.0	3 to 15		
12 to 20 mA DC	0.2 to 1.0	3 to 15		

Equivalent Circuit

The i2P-100 equivalent circuit is a series circuit consisting of a constant voltage drop (battery) of approximately 4 VDC and a total resistance of 40 ohms. Input is shunted by two 6.8 V zener diodes (see figure 4).

Supply Pressure⁽¹⁾

Recommended: 0.34 bar (5 psi) higher than upper range limit of output signal

Maximum: 3.4 bar (50 psig)

Medium: Air or Non-Corrosive Natural Gas

Maximum Steady-State Flow Rate⁽²⁾⁽³⁾

Refer to tables 2 and 3

Maximum Output Air Capacity⁽³⁾

8.04 m³/hr (300 scfh) at 1.4 bar (20 psig) supply pressure

Performance⁽⁴⁾

Reference Accuracy: $\pm 1.0\%$ of full scale output span; includes combined effects of hysteresis, linearity, and deadband

Independent Linearity: ±0.5% of full scale output span **Hysteresis:** 0.4% of full scale output span **Frequency Response:** Gain is attenuated 3 dB at 3 Hz with transducer output signal piped to a typical instrument input

Temperature Effect: $\pm 0.14\%$ per degrees Celsius (± 0.075 per degrees Fahrenheit) of span

Supply Pressure Effect: 0.2% of full scale output span per psi supply pressure change)

Vibration Effect: Less than 1% of full scale output span when tested to ISA S75.13

Electromagnetic Compatibility Meets EN 61326-1:2013 Immunity—Industrial locations per Table 2 of EN 61326-1 Standard. Performance is shown in table 1 below. Emissions—Class A ISM equipment rating: Group 1, Class A

Operating Ambient Temperature Limits⁽¹⁾

-40 to 85°C (-40 to +185°F)

Electrical Seal

Single sealed device per ANSI/ISA 12.27.01

Electrical Classification

Hazardous Area Approvals

CSA — Intrinsically Safe, Explosion proof, Type n, Dust-Ignition proof

FM— Intrinsically Safe, Explosion proof, Type n, Non-incendive, Dust-Ignition proof

ATEX— Intrinsically Safe, Flameproof, Type n

IECEx— Intrinsically Safe, Flameproof, Type n

CUTR—Customs Union Technical Regulations (Russia, Kazakhstan, Belarus, and Armenia)

(continued on next page)

-continued-

Specifications (continued)

Hazardous Area Approvals (continued)	Adjustments ⁽⁵⁾
INMETRO— National Institute of Metrology, Qualit and Technology (Brazil)	y, Zero and Span: Trim potentiometers (20 turn) for zero and span adjustments are located under the housing cap.
KTL—Korea Testing Laboratory (South Korea)	Switch: Allows input signal split range and
NEPSI— National Supervision and Inspection Centr for Explosion Protection and Safety of Instrumentation (China)	e user-configurable 0.14 to 2.3 bar (2 to 33 psig) output.
	Connections
Contact your <u>Emerson sales office</u> for classification/certification specific information	Supply and Output Pressure: 1/4 NPT internal connection
Electrical Housing:	Vent: 1/4 NPT internal
When Remotely Vented No Remote Venting	Electrical: ■ Standard 1/2 NPT Wire Size: 18 to 22 AWG
CSA—Type 4X Encl.CSA—Type 3 Encl.FM— NEMA 4XFM— NEMA 3ATEX—IP66ATEX—IP64IECEx—IP66IECEx—IP64	Mounting Position ■ Actuator ■ pipestand or ■ surface
	Approximate Weight
Construction Materials	2.5 kg (5.5 lbs)
Housing: ASTM: A03600 material composition alloy	Options
O-rings: Nitrile Diaphragms: Nitrile	■ Output pressure gauge ■ M20 or PG13 conduit adapter
NOTE: Specialized instrument terms are defined in ANSI/ISA Standard 51.1 - Process Ins 1. The pressure and temperature limits in this document and any applicable standard or 2. Average flow rate determined at 12 mA and 0.6 bar (9 psig) output. 3. Normal m ³ /hour-Normal cubic meters per hour (0° c. and 1.01325 bar, absolute). Sc 4. Performance values are obtained using a transducer with a 4 to 20 mA DC input signa 5. For other ranges, zero and span adjustments needed.	r code limitation should not be exceeded.

Table 1. EMC Summary Results—Immunity

Port	Phenomenon	Basic Standard	Test Level	Performance Criteria ⁽¹⁾
	Electrostatic discharge (ESD)	IEC 61000-4-2	4kV Contact 8kV Air	А
Enclosure	Radiated EM field	IEC 61000-4-3	80 to 1000 MHz @ 10V/m with 1 kHz AM at 80% 1400 to 2000 MHz @ 3V/m with 1 kHz AM at 80% 2000 to 2700 MHz @ 1V/m with 1 kHz AM at 80%	A
	Burst (fast transients)	IEC 61000-4-4	1 kV	A
I/O signal/control	Surge	IEC 61000-4-5	1 kV (line to ground only, each)	A
	Conducted RF	IEC 61000-4-6	150 kHz to 80 MHz at 3 Vrms	A
Specification limit = 1. A=No degradation	±1% of span n during testing. B = Temporary degradation during	testing, but is self-recovering.		

Figure 3. Output-Time Relationships




Table 2. Maximum Steady-State Flow Rate (Air)


SUPPLY P	RESSURE	OUTPUT F	PRESSURE	STEAD FLOW I	
Bar	Psi	Bar Psi		m³/hr	Scfh
	20	0.2 - 1.0	3 - 15		
1.4		0.2	3	0.04	1.5
1.4		0.62	9	0.06	2.0
		1.0	15	0.07	2.6
		0.4 - 2.0	6 - 30		
2.4	35	0.4	6	0.05	1.7
2.4		1.2	18	0.08	2.9
		2	30	0.12	4.1
		0.1 - 2.3	2 - 33		
2.6	20	0.1	2	0.04	1.5
2.0	38	1.2	17.5	0.08	2.9
		2.3	33	0.12	4.3
	 Normal m3/hour - Normal cubic meters per hour (0C and 1.0135 bar, absolute). Scfh - Standard cubic feet per hour (60F and 14.7psig). 				

Table 3. Maximum Steady-State Flow Rate (Natural Gas)

Scfh 1.95
1.95
1.95
2.6
3.38
2.21
3.77
5.33
1.94
3.74
5.55
-

Normal m3/hour - Normal cubic meters per hour (0C and 1.0135 bar, absolute).
 Scfh - Standard cubic feet per hour (60F and 14.7psig).
 Natural gas steady state flow based on natural gas specific gravity of 0.6.
 Flow decreases as specific gravity increases.

Figure 4. Equivalent Circuit




Installation

Refer to figure 5 for location of standard mounting holes in the housing. See figures 1 and 2 for typical mounting configurations. Standard mounting hardware is provided for mounting on the actuator, a pipestand, or surface mount. Field wiring connections are made to the terminal block accessible under the housing cap, via the 1/2 NPT conduit connection. Dimensions are shown in figures 5, 6, 7, and 8.

Ordering Information

To determine what ordering information is required, refer to the Specifications table. Carefully review the description of each specification. Specify the desired choice whenever there is a selection available. Also, specify options that are applicable to the application.

Figure 5. Dimensions









Figure 6. Dimensions with Optional Fisher 67 Filter-Regulator (Yoke/Bracket Mounted)







mm (INCH)

Product Bulletin 62.1:i2P-100 October 2022




Figure 8. Dimensions with Optional Fisher 67 Filter-Regulator (Pipestand Mounted)

Neither Emerson, Emerson Automation Solutions, nor any of their affiliated entities assumes responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use, and maintenance of any product remains solely with the purchaser and end user.

Fisher is a mark owned by one of the companies in the Emerson Automation Solutions business unit of Emerson Electric Co. Emerson Automation Solutions, Emerson, and the Emerson logo are trademarks and service marks of Emerson Electric Co. All other marks are the property of their respective owners.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Automation Solutions Marshalltown, Iowa 50158 USA Sorocaba, 18087 Brazil Cernay 68700 France Dubai, United Arab Emirates Singapore 128461 Singapore

www.Fisher.com

