# FloBoss<sup>™</sup> 107 LCD Touchpad

The FloBoss™ 107 LCD Touchpad is a transreflective user interface that provides touch screen access to the process and operational information contained in a FloBoss 107 Flow Computer (FB107). It allows you to view and change parameters in the unit directly from the touch-sensitive display. The Touchpad displays real-time and historical charts to provide a visual representation of data contained in the FB107.


### **Touchpad**

The Touchpad consists of an 8-line by 21-character display. The Touchpad is transreflective for improved sunlight readability, and backlit for enhanced ambient light readability.

You can browse through lists or screens and enter numeric values by simply touching the LCD. The Touchpad shows measurement values in real-time. You can make configuration changes to numeric values through the Touchpad.

### **Modes**

You can configure the Touchpad to display information in two different modes – Normal and BLM (Basic List Mode). Under Normal mode, a logon prompt displays before any data is viewable. With BLM mode, a user-configured autoscrolling list of read-only data displays before you are required to logon.



FloBoss 107 LCD Touchpad

#### **Charts**

You can configure real-time dynamic and historical charts to display on the Touchpad using ROCLINK™ 800. Additionally, by simply touching the engineering units in the menu or user lists displayed on the Touchpad, you can view real-time charts for most values.

#### Screens

Easy-to-navigate menus and screens allow access to the most commonly used parameters. You can add, delete, and modify viewed items using ROCLINK 800 Configuration Software.

The default screens of the main menu provide the following:

- User list information.
- Meter run information.
- Proportion, Integral, and Derivative (PID) loop and Function Sequence Table (FST) control.
- History charts and graphing.
- Input and Output (I/O) information.
- System information.
- Integrity and alarm conditions.
- Contrast Control.

### Security

Configure security for the Touchpad in ROCLINK 800, which allows individual user access customization. Set user access to view and edit parameters, to view parameters only, or to not view parameters for up to 16 users. Typically, user access assignment is based on an individual user's preferences.

### **Connections to FloBoss**

The FB107 communicates with and powers the Touchpad through the Display port on the FB107 unit.

### Mounting

The Touchpad has CSA Class I, Division 2 approval and can be mounted on a panel or on a Type 4 enclosure.

### **Option**

The Touchpad may be installed on an optional enclosure available from Remote Automation Solutions. For more information, contact your local sales representative.



FB107:LCD August 2017

## FB107 LCD Touchpad

Physical		
Touchpad	128 x 64 pixel, backlit, liquid crystal display.	
LEDs	Red LED	Displays alarm or integrity alerts
	Green LED	Displays positive key press indication
Communications	Connects to the FB107's Display port, maximum cable length of 15 m (50 ft)	
Housing	PBT/Polypropylene, UV stabilized	
Dimensions	111 mm H x 140 mm W x 25 mm D (4.38 in. H x 5.5 in. W x 1.0 in. D)	
Weight	0.23 kg (0.51 lbs)	
Mounting	Suitable for panel or enclosure mounting	
Power		
Input Power (from the FB107's display port)	Normal Idle Mode	120 mW
	Low Power Mode	42 mW
	Input Voltage	8 to 30 Vdc
Environmental		
Operating Temperature	-20 to 70 °C (-4 to 158 °F)	
Storage Temperature	-30 to 85 °C (-22 to 185 °F)	
Operating Humidity	0 to 95% relative humidity, non-condensing	
Radiated/Conducted Transmissions	Meets the requirements of IEC 61326 Electrical equipment for use in industrial locations	
Radiated Emissions	Meets FCC Part 15, Class A	
Vibration	Tested to ISA 75.13 1996 with an abbreviated endurance dwell test	
Approvals		
Product Markings for Hazardous Locations (North America)	Class I, Division 2, Groups A, B, C, and D CSA Type 4 rating when installed on enclosure per included installation sheet <i>Form A6236</i> .	
Miscellaneous Approvals	RoHS2	RoHS (2) EU Directive 2011/65/EU: This product may be considered out- of-scope when used for the intended design purpose in a Large Scale Fixed Installation (LSFI). Consult <a href="https://www.emerson.com/compliance">https://www.emerson.com/compliance</a> for up-to-date product information.
	RoHS (China)	<b>25</b>

August 2017 FB107:LCD

For customer service and technical support, visit <a href="https://www.EmersonProcess.com/Remote/Support">www.EmersonProcess.com/Remote/Support</a>.

#### Global Headquarters, North America, and Latin America:

Emerson Automation Solutions Remote Automation Solutions 6005 Rogerdale Road Houston, TX 77072 U.S.A. T +1 281 879 2699 | F +1 281 988 4445 www.EmersonProcess.com/Remote

#### Europe:

Emerson Automation Solutions Remote Automation Solutions Unit 8, Waterfront Business Park Dudley Road, Brierley Hill Dudley UK DY5 1LX T +44 1384 487200 | F +44 1384 487258

#### Middle East/Africa:

Emerson Automation Solutions Remote Automation Solutions Emerson FZE P.O. Box 17033 Jebel Ali Free Zone – South 2 Dubai U.A.E. T +971 4 8118100 | F +971 4 8865465

#### Asia-Pacific:

Emerson Automation Solutions Remote Automation Solutions 1 Pandan Crescent Singapore 128461 T +65 6777 8211 | F +65 6777 0947  $\ \ \, \mathbb{C}$  2007–2017 Remote Automation Solutions, a business unit of Emerson Automation Solutions. All rights reserved.

This publication is for informational purposes only. While every effort has been made to ensure accuracy, this publication shall not be read to include any warranty or guarantee, express or implied, including as regards the products or services described or their use or applicability. Remote Automation Solutions (RAS) reserves the right to modify or improve the designs or specifications of its products at any time without notice. All sales are governed by RAS terms and conditions which are available upon request. RAS accepts no responsibility for proper selection, use or maintenance of any product, which remains solely with the purchaser and/or end-user.

