M-series Traditional I/O



The DeltaV[™] I/O subsystem is easy to install and maintain.

- Decreases capital equipment costs
- Decreases installation time and expense
- Increases productivity
- Increases process availability

Introduction

Traditional I/O is a modular subsystem that offers flexibility during installation. It's designed to be installed in the field, near your devices. Traditional I/O is equipped with *function and field wiring protection keys* to ensure that the correct I/O card is always plugged into the corresponding terminal block. Modularity, protection keys, and plug and play capabilities make DeltaVTM Traditional I/O a smart choice for your process control system.





February 2016 - Page 2

Benefits

Decreases capital equipment costs

Full system modularity. The Traditional I/O subsystem was designed with your investment in mind. All components are fully modular and may be installable under power.¹ You add I/O interface carriers and I/O interfaces in groups of 4, 8, 16, or 32 channels as you need them. The modular design enables you to purchase the exact amount of I/O cards, 8-wide carriers, power/controllers, and 2-wide carriers you need and add more DeltaV I/O as your system grows.

Reduced system footprint. The DeltaV system's state-of-the-art form factor design of the I/O components enables you to mount the I/O interface carrier in a junction box in the field so you significantly reduce the footprint of your equipment and increase valuable control room space for other uses.

Installation. Save on wiring expenses by installing Classic Instrumentation in the field, near the actual field devices. Mounting the controller with the I/O further reduces your wiring expenditures by eliminating the need for long runs of multi-cores. The integrated design of the Traditional I/O subsystem can eliminate the need for marshaling panels. This saves you even more in your total capital costs.

The provision of in-line fuses and bussed power saves on installation costs compared with external fuses and power distribution.

Decreases installation time and expense

Plug-and-play installation saves money. All Traditional I/O components plug into the I/O interface carrier. You can install the I/O interface carriers to manage anticipated growth and postpone the I/O interfaces until you're ready to install your additional field devices.

Phased installation saves time. As soon as you mount the I/O interface carrier, you're ready to begin installing the field devices. I/O terminal blocks plug directly onto the I/O interface carrier. There is no need to have the I/O cards installed.



Traditional I/O terminal block.

Keys. Traditional I/O interfaces and terminal blocks have I/O function keys. These keys ensure that the correct I/O card is always plugged into the corresponding terminal block. It's incredibly easy to use and gives you time to *do more*.

This design enables you to initially install Traditional I/O quickly and efficiently. When you need to replace an I/O card, the function key design ensures that you will always install it correctly. This keying system provides a safety measure by preventing the wrong I/O interface's being installed.

Increases productivity

Real-time, online equipment additions. Online addition of new I/O interfaces means your process does not get interrupted. As new equipment is added, the DeltaV Explorer acknowledges it and assigns it basic configuration.

Increases process availability

1:1 Redundancy for Traditional and HART I/O

cards. DeltaV redundant I/O uses the same Series 2 I/O cards as non-redundant I/O. This allows you to leverage your investment in installed I/O and in I/O spares. No additional configuration is needed when using a redundant channel. The redundant terminal blocks provide the same field wiring connections as simplex blocks, so there is no extra wiring needed.

¹ Refer to Zone 2 installation instructions (12P2046) and/or Class 1 Division 2 installation instructions (12P1293) for details.

Autosense of redundancy. DeltaV autosenses redundant I/O, which greatly simplifies the task of adding redundancy to the system. The redundant pair of cards is treated as one card in the system tools.

Automatic Switchover. Should a primary I/O card fail, the system automatically switches to the "standby" card without user intervention. The operator is given clear notification of a switchover at the operator display

Product Description

The Traditional I/O subsystem includes:

- I/O interface carrier (a DIN rail surface mounted) on which all I/O related components are installed.
- Bulk AC to 24 VDC power supply for field devices.
- An I/O interface consisting of an I/O card and an I/O terminal block.
- A variety of analog and discrete I/O cards enclosed in a common form factor that easily plugs into the I/O interface carrier.
- A variety of I/O terminal blocks mounted on the I/O interface carrier that can be pre-wired before I/O card installation.



A Traditional I/O card easily plugs into an I/O carrier

I/O Cards

A variety of analog and discrete I/O cards are available to meet your specific requirements. The following cards support simplex or redundant installation:

- AI 4-20 mA HART 8 channels
- AI 4-20 mA HART 16 channels
- AO-4-20 mA HART 8 channels
- AO-4-20mA HART 16 channels
- DI, 24 VDC Dry Contact, 8-channels
- DI, High Density, 32-channels
- DO 24 VDC High Side, 8-channels
- DO,High Density, 32-channels

The following I/O cards are supported in simplex format to meet your field wiring needs.

- AI 4-20 mA HART 16 channels
- Al Isolated, 4 channels
- RTD, 8-channels
- Thermocouple, 8- channels
- Millivolt, 8-channels
- DI, High Density, 32-channels
- DI 24 VDC Isolated, 8-channels
- Multi-Function, 4 channels (Isolated DI)
- Sequence of Event, 16 channels (DI 24 VDC)
- DI 120 VAC Low Side Detection, 8-channels
- DI 120 VAC Isolated , 8-channels
- DO, High Density, 32-channels
- DO 24 VDC Isolated, 8-channels
- DO 120/230 VAC High Side, 8 channels
- DO 120/230 Isolated, 8 channels

All I/O cards are enclosed in a common form factor that plugs into the I/O interface carrier. The housing is clearly labeled with the enclosed I/O card type. All cards have power and internal error indicators. Eight channel cards have clearly visible channel status LEDs.

All cards meet ISA G3 corrosion specifications by the careful selection of superior electronic components and the use of conformal coating.

Pulse Counters are available on most DI cards. The supported maximum frequency varies from 0.1 Hz on AC signals to 75 or 120 Hz on 24 VDC inputs. For higher pulse counts up to 50 KHz, use the Multi-Function card's high speed pulse input.

DeltaV provides control module level time stamping for log events and alarms. For greater event resolution the 16 channel Sequence of Events DI card can provide signal driven events to a resolution of +/- 0.25 ms per card, or within 1 ms per controller. Please refer to the Sequence of Events PDS for more information on Sequence of Event data collection and system options for this feature. February 2016 - Page 4

I/O Card Redundancy

Redundant I/O cards are available for critical applications. The same card can be used in simplex or redundant applications. When installed on a two-wide redundant terminal block, the cards are recognized as a redundant pair by the controller. The controller scans each card and determines which card is acting as the active interface. When a fault is detected, the system automatically switches to the standby I/O card.

DeltaV Control modules reference simplex and redundant I/O channels identically and there is no special configuration required to take advantage of redundancy.

Switchover of a redundant I/O card is completed within two scans of the I/O bus. Make-before-break contacts ensure digital field instruments remain powered and the process is undisturbed. Analog output signals are briefly driven by both cards for < 5 ms during switchover of the card.

Hardware Alerts automatically report hardware integrity errors for both the primary and secondary cards. Any event that causes a switchover is also reported automatically through the system hardware alerts and is logged in the Event Chronicle. Events that can cause a switchover include.

- Hardware failure within the active card.
- Communications failure between the active card and the controller.
- Detection of a fault in the field wiring

A switchover may also be initiated from the diagnostics explorer, and the health and status of both cards and their channels are available in the diagnostics explorer.

The system automatically commissions a new standby card. In safe areas, failed cards can be replaced under power. In hazardous areas, appropriate installation procedures must be followed.

February 2016 - Page 5

Hardware Specifications

Common Environmental Specifications for all I/O Interfaces			
Category	Specifications:		
Operating temperature*	0 to 60 °C (32 to 140 °F)		
Operating temperature	-40 to 70 °C (-40 to 158 °F)		
Storage temperature	-40 to 85 °C (-40 to 185 °F)		
Relative humidity	5 to 95%, non-condensing		
Airborne contaminants	ISA-S71.04-1985 Airborne Contaminants Class G3 Conformal coating		
Protection rating	IP 20, NEMA 12		
Hazardous area/location**	ATEX 3 G IIC T4 Class 1, Div 2, Groups A, B, C, D, T4		
Shock	10 g ¹ / ₂ -sine wave for 11 ms		
Vibration	1 mm peak-to-peak from 2 to 13.2 Hz; 0.7 g from 13.2 to 150 Hz		
Dimensions	H 10.7 cm (4.2 in.) W 4.1 cm (1.6 in.) Depth 10.5 cm (4.1 in.)		

*Applies to the following I/O cards:

Analog Input Card: 16 Channels 4-20 mA, HART, Series 2 Plus

Analog Output Card: 16 Channels 4-20 mA, HART, Series 2 Plus

Discrete Input Card: 32 Channels, 24Vdc, Dry Contact, Series 2 Plus Discrete Output Card, 32 Channels, 24Vdc, High Side, Series 2 Plus

**Refer to Zone 2 installation instructions (12P2046) and/or Class 1 Division 2 installation instructions (12P1293) for information on installing in hazardous areas.

Analog Input I/O Cards

Specifications	Specifications for HART Al-Card, 8 channel, 4 to 20 mA			
Number of channels	8			
Isolation	Each channel is optically isolated from the system and factory tested to 1500 VDC.			
Nominal signal range (span)	4 to 20 mA			
Full signal range	1 to 22.5 mA, with over range checking			
LocalBus current (12 VDC nominal) per card	120 mA typical, 150 mA maximum			
Field circuit power per card	300 mA maximum at 24 VDC (<u>+</u> 10%)			
Accuracy over temperature range	0.1% of span			
Resolution	16 bits			
Repeatability	0.05% of span			
Roll off frequency	-3 dB at 2.7 Hz; -20.5 dB at $\frac{1}{2}$ the sampling frequency			
Calibration	None required			
Optional fuse	2.0 A			
Field wiring	Class 1, Div 2, Groups A, B, C, D, T4 2-wire—non-incendive ² 4-wire—non-arcing 2-wire— ATEX 3 G IIC T4 -nL 4-wire— ATEX 3 G IIC T4 -nA			

² Non-incendive field circuits are designed such that under normal operating conditions energy is limited.

Specifications for HART AI-Card 16 Channel, 4 to 20 mA				
Number of channels	16			
Isolation	Each channel is optically isolated from the system and factory tested to 1000 VDC.			
Nominal signal range (span)	4 to 20 mA			
Full signal range	2 to 22 mA, with over range checking			
LocalBus current (12 VDC nominal) per Card	110 mA typical, 150 mA maximum			
Field circuit power per Card	500 mA maximum at 24 VDC			
Accuracy over temperature range	0.2% of span			
Resolution	16 bits			
Repeatability	0.05% of span			
Roll off frequency	-3 dB at 2.7 Hz; -20.5 dB at ½ the sampling frequency			
Calibration	None required			
Communications support	HART pass-through request/response HART variable reporting Field device status reporting			
Hart Scan Time	600 – 800 ms (typical) per enabled channel			

February 2016 - Page 8

Specifications for RTD Input Card, 8 channel			
RTD channels per card	8		
Sensor types	2 wire, 3 wire, or 4 wire		
Sensor Configuration	Resistance, Pt100, Pt200, Pt500, Ni120, Cu10, User Defined		
Full Scale signal range	See Table next page		
Accuracy	See Table next page		
Repeatability	0.05% of span		
A/D Resolution	16 bit		
Calibration	None required		
Units	Degrees C, Degrees F		
Sensor excitation current	100 μΑ		
Common mode rejection	120 dB at 50/60 Hz		
Common mode impedance	> 10 megohms		
Roll off Frequency	-3db at 3 Hz, -25 db at 30 Hz		
LocalBus current (12 VDC nominal)	160 mA		
Open sensor detection time	1 second		
Open mV Lead detection time	15 second		

RTD, ohms Sensor Type Specifications					
Sensor Type	Full Scale	Operating Range	25° Reference Accuracy	Temperature Drift	Resolution
Resistance	0 to 2,000 Ω	0 to 2,000 Ω	± 6.2 Ω	± 0.112 Ω/°C	~0.02 Ω
Pt100	-200 to 850°C	-200 to 850°C	± 0.5° C	± 0.018° C/°C	~0.05° C
Pt200	-200 to 850°C	-200 to 850°C	± 0.5° C	± 0.012° C/°C	~0.05° C
Pt500	-200 to 850°C	-200 to 850°C	± 3.5° C	± 0.063° C/°C	~0.18° C
Ni120	-70 to 300°C	70 to 300°C	± 0.2° C	± 0.006° C/°C	~0.02° C
Cu10	-30 to 140°C	-30 to 140°C	± 2.0° C	± 0.157° C/°C	~0.23° C
User Defined*	0 to 1000 Ω	0 to 1000 Ω	± 0.4 Ω	± 0.009 Ω/°C	~0.05 Ω

* The Callendar-Van Dusen linearization equation can be used with user defined Pt RTDs. Refer to Recommended I/O Practices in DeltaV Books online for usage information.

Specifications for	Thermocouple/mV Input Card, 8 channel
Channels per card	8
Sensor types Thermocouple mV	B, E, J, K, N, R, S, T, uncharacterized Low level voltage source
Sensor Ranges	See table next page
Repeatability	0.05% of span
A/D Resolution	16 bit
Calibration	None required
Units	Degrees C Degrees F
Cold junction compensation (Not available on mV channels)	Local: Integrally mounted in terminal block External: Configure one channel as external cold junction compensation for remaining inputs
Isolation	Each channel is optically isolated from the system and factory tested to 1500 VDC. Channels 1, 2, 3, and 4 are isolated from channels 5, 6, 7, and 8 (verified by 1500 VDC factory test). Thermocouples attached to channels 1, 2, 3, and 4 are not electrically isolated and should be within \pm 0.7 VDC of each other. Thermocouples attached to channels 5, 6, 7, and 8 are not electrically isolated and should be within \pm 0.7 VDC of each other.
Common mode rejection	120 dB at DC/50/60 Hz
Common mode impedance	> 10 megohms
Normal mode rejection	60 dB at 60 Hz
Roll off frequency Thermocouple mV	-3 dB at 3 Hz, -25 dB at 30 Hz -100 dB at 50/60 Hz, -200 dB at ½ the sample frequency -25 dB at 50/60 Hz, -20 dB at ½ the sample frequency
LocalBus current (12 VDC nominal)	210 mA
Open sensor detection	Yes (< 70 nA)
Open sensor detection time	10 second

Thermocouple Sensor Type Specifications					
Sensor Type	Full Scale	Operating Range	25° Reference Accuracy	Temperature Drift	Resolution
Uncharacterized (no linearization, no cold junction compensation.)	-100 to 100 mV	-100 to 100 mV	0.1 mV	± 0.002 mV/ °C	~ 0.003mV
В	250 to 1810° C	500 to 1810° C	± 2.4° C	± 0.056 ° C/ °C	~ 0.18° C
E	-200 to 1000° C	-200 to 1000° C	± 0.6° C	± 0.008° C/ °C	~ 0.07° C
J	-210 to 1200° C	-190 to 1200° C	± 0.8° C	± 0.011° C/ °C	~ 0.05° C
к	-270 to 1372° C	-200 to 1372° C	± 0.5° C	± 0.016° C/ °C	~ 0.18° C
N	-270 to 1300° C	-190 to 1300° C	± 1.0° C	± 0.007° C/ °C	~ 0.10° C
R	-50 to 1768° C	-50 to 1768° C	± 2.1° C	± 0.013° C/ °C	~ 0.14° C
S	-50 to 1768° C	-40 to 1768° C	± 2.2° C	± 0.067° C/ °C	~ 0.24° C
Т	-270 to 400° C	-200 to 400° C	± 0.7° C	± 0.001° C/ °C	~ 0.04° C

mV Sensor Type Specifications					
Sensor Type	Full Scale	Operating Range	25° Reference Accuracy	Temperature Drift	Resolution
Low-level voltage source	-100 to 100 mV	-100 to 100 mV	0.1 mV	0.002 mV/° C	~ 0.003 mV°

February 2016 - Page 11

Specifications for Isolated Input Card,4 channel ³			
Number of channels	4		
Isolation CAN/CSA-C22.2 No.1010.1-	Installation Cat II, Pollution degree 2		
92*	Channel to system - 600 VAC double insulation. Each channel is optically isolated from the system and factory tested to 5000 VDC.		
	Channel to channel - 600 V basic insulation. Each channel is optically isolated from each other and factory tested to 3100 VDC.		
Dielectric strength	Channel to system - 3700 V RMS		
	Channel to channel - 2200 V RMS		
ADC Resolution	16 bit		
-3dB Filter Frequency	2.7 Hz		
DC/50/60 Hz Common Mode Rejection	120 dB		
Input Impedance	10 Megaohms		
Thermocouple Sensor Types	B, E, J, K, N, R, S, T, Uncharacterized		
RTD Sensor Types	PT100, PT200, Ni120, Cu10, Resistance/User Defined		
mV and V ranges	Refer to following tables.		
Input type mix	Independently configurable		
Ambient temperature	-40° to 70°C		
Calibration	None required		
Mounting	Assigned slot of I/O carrier		
LocalBus power rating	12 VDC, 350 mA, no field power required		

Isolated Input Card, Thermocouple and MilliVolt Input Specifications

Item	Specification
Linearization error	±0.003% full scale
Cold Junction Compensation Accuracy	±1.0°C
Cold Junction Compensation types	Off, local, remote
Cold Junction Compensation range	-40 to 85°C
Temperature scale	ITS90
Open circuit detection (Thermocouple only)	0.4 µA DC
Detection time	1 second

 ³ DeltaV version 7.3 is required for this card.
 ⁴Warning: When hazardous live voltages are present on a channel, adjacent channel wiring must be inaccessible.

Isolated Input Thermocouple Sensor Type Specifications					
Sensor Types	25°C Reference Accuracy	Temperature Drift	Nominal Resolution	Full Scale	Operating Range
В	±1.2° C	±0.116 ° C/ °C	0.09° C	250 to 1810° C	500 to 1810° C
E	±0.5° C	±0.004° C/ °C	0.05° C	-200 to 1000° C	-200 to 1000° C
J	±0.6° C	±0.005° C/ °C	0.06° C	-210 to 1200° C	-190 to 1200° C
к	±0.5° C	±.013° C/ °C	0.05° C	-270 to 1372° C	-140 to 1372° C
Ν	±1.0° C	±.015° C/ °C	0.05° C	-270 to 1300° C	-190 to 1300° C
R	±1.7° C	±.083° C/ °C	0.06° C	-50 to 1768° C	0 to 1768° C
S	±1.8° C	±.095° C/ °C	0.08° C	-50 to 1768° C	0 to 1768° C
т	±0.7° C	±.025° C/ °C	0.04° C	-270 to 400° C	-200 to 400° C
Uncharacterized no linearization or CJC	±0.05 mV	±.0003 mV/ °C	.0031 mV	-100 to 100 mV	-100 to 100 mV

Isolated Input Millivolt Input Range Specifications					
Sensor Type	Input Ranges	25 C° Reference Accuracy	Temperature Drift	Maximum Resolution	
20 mV	±20 mV	±0.02 mV	0.001 mV/° C	0.0008 mV	
50 mV	±50 mV	±0.03 mV	0.0005 mV/° C	0.0017 mV	
100 mV	±100 mV	±0.05 mV	0.0003 mV/° C	0.0031 mV	

Isolated Input Card, RTD, ohms Input Specifications

Item	Specification
Measurement configurations	2, 3, and 4 wire
Excitation current	100 µA DC
Temperature scale	ITS90
Open sensor detection time	1 second
Short circuit detection time	1 second
Pt 100 and Pt 200 alpha	0.00385

Isolated Input Card, RTD, ohms Input Range Specifications

Sensor Type	25°C Reference Accuracy	Temperature Drift	Resolution	Sensor Input Range
Pt100	± 0.5° C	± 0.018° C/°C	0.05° C	-200 to 850° C
Pt200	± 0.5° C	± 0.012° C/°C	0.05° C	-200 to 850° C
Ni120	± 0.2° C	± 0.006° C/°C	0.02° C	-70 to 300° C
Cu10	± 2.0° C	± 0.076° C/°C	0.23° C	-30 to 140° C
Resistance	± 0.5 ohms	± 0.018 ohms/°C	0.02 ohms	1 to 1000 ohm
User Defined*	±0.4 ohms	±0.009 ohms/°C	~0.05 ohms	0 to 1000 ohms

* The Callendar-Van Dusen linearization equation can be used with user defined Pt RTDs.

Refer to Recommended I/O Practices in DeltaV Books online for usage information.

Isolated Input Card, Voltage Input Range Specifications

Sensor Type	Sensor Range	25°C Reference Accuracy	Temperature Drift	Maximum Resolution
0 - 5 V	0 - 5 V	0.005 V	0.0002 V° C	0.00009 V
0 - 10 V	0 - 10 V	± 0.010 V	0.0004 V° C	0.00016 V
1 - 5 V	1 - 5 V	0.0005 V	0.0002 V° C	0.00009 V
1 V	+/- 1 V	0.0025 V	0.0002 V° C	0.00015 V
5 V	+/- 5 V	0.005 V	0.0002 V° C	0.00017 V
10 V	+/- 10 V	0.010 V	0.0004 V° C	0.0003 V

February 2016 – Page 14

Analog Output I/O Cards

Specifications for HART AO Card, 8 channel, 4 to 20 mA		
Number of channels	8	
Isolation	Each channel is optically isolated from the system and factory tested to 1500 VDC.	
Nominal signal range (span)	4 to 20 mA	
Full signal range	1 to 23 mA	
LocalBus current (12 VDC nominal) per card	100 mA typical, 150 mA maximum	
Field circuit power per card	300 mA maximum @ 24 VDC (+/-10%)	
Accuracy over temperature range	0.25% of span	
Resolution	12 bits	
Output compliance	20 mA at 21.6 VDC supply into 700 Ω load	
Calibration	Information stored on card.	
Optional fuse	2.0 A	
Field wiring	Class I, Div 2, Groups A, B, C, D T4 non-incendive ATEX 3 G IIC T4 -nL	

Specifications for HART AO Card, 16 channel, 4 to 20 mA		
Number of channels	16	
Isolation	Each channel is optically isolated from the system and factory tested to 1000 VDC.	
Nominal signal range (span)	4 to 20 mA	
Full signal range	1 to 23 mA	
LocalBus current (12 VDC nominal) per card	110 mA typical, 160 mA maximum	
Field circuit power per card	400 mA maximum @ 24 VDC (+/-10%)	
Accuracy over temperature range	0.25% of span	
Resolution	14 bits	
Output compliance	20 mA at 14 VDC supply into 700 Ω load	
Calibration	Information stored on card.	
Optional fuse	2.0 A	
Field wiring	Class I, Div 2, Groups A, B, C, D T4 non-incendive ATEX 3 G IIC T4 -nL	

February 2016 – Page 15

Discrete Input I/O Cards

Specifications for DI Card, 8 channel, 24 VDC, Dry Contact		
Number of channels	8	
Isolation	Each channel is optically isolated from the system and factory tested to 1500 VDC.	
Detection level for On	> 2.2 mA	
Detection level for Off	< 1 mA	
Output Impedance	5 KΩ (approximate)	
LocalBus current (12 VDC nominal) per card	75 mA typical, 100 mA maximum	
Field circuit power per card	40 mA at 24 VDC	
Optional fuse	2.0 A	
Field wiring	Class 1, Div 2, Groups A, B, C, D, T4 non-incendive ATEX 3 G IIC T4 -nL	

Specifications for DI Card, 8 channel, 24 VDC, Isolated		
Number of channels	8	
Isolation	Each channel is optically isolated from the system and from each other and factory tested to 1500 VDC.	
Detection level for On	> 10 VDC	
Detection level for Off	< 5 VDC	
Input impedance	5 mA at 24 V	
LocalBus current (12 VDC nominal) per card	75 mA typical, 100 mA maximum	
Field circuit power per card	None	
Optional fuse	2.0 A	
Field wiring	Class 1, Div 2, Groups A, B, C, D, T4 non-arcing ATEX 3 G IIC T4 -nA	

Specifications for DI Card, 32 channel, 24 VDC, Dry Contact		
Number of channels	32	
Isolation	Each channel is optically isolated from the system and factory tested to 1000 VDC.	
Detection level for On	> 2 mA	
Detection level for Off	< 0.25 mA	
Input impedance	5K ohm (approximate)	
LocalBus current (12 VDC nominal) per card	50 mA typical,	
	75 mA maximum	
Field circuit power per card	150 mA at 24 VDC	
Return	Uses common return	
Terminal block	32-screw termination block	
Field wiring	Class 1, Div 2, Groups A, B, C, D, T4 non-arcing ⁵ ATEX 3 G IIC T4 -nA ⁶	

Specifications for DI Card, 8 channel, 120 VAC, Isolated		
Number of channels	8	
Isolation	Each channel is optically isolated from the system at 250 VAC and from other channels at 250 VAC.	
Detection level for On	84 to 130 VAC	
Detection level for Off	0 to 34 VAC	
Input load (contact cleaning)	2 mA at 120 VAC	
Input Impedance	60 ΚΩ	
LocalBus current (12 VDC nominal) per card	75 mA typical, 100 mA maximum	
Field circuit power per card	None	
Optional fuse	2.0 A	
Field wiring	Class 1, Div 2, IIC T4 non-arcing	

 ⁵ Non-arcing field circuits are designed so that ignition does not occur during normal operation.
 ⁶ Non-sparking circuits (-nA) are designed to minimize the risk of occurrence of arcs, sparks, or hot spots capable of creating ignition hazards during normal operation. Normal operation excludes the removal or insertion of field wiring with circuits energized.

Specifications for DI Card, 8 channel, 120 VAC, Dry Contact		
Number of channels	8	
Isolation	Each channel is optically isolated from the system at 250 VAC	
Detection level for On	> 1.4 mA	
Detection level for Off	< 0.56 mA	
Output Impedance	60 ΚΩ	
LocalBus current (12 VDC nominal) per	75 mA typical,	
Cald	100 mA maximum	
Field circuit power per card	15 mA at 120 VAC	
Optional fuse	2.0 A	
Field wiring	Class 1, Div 2 IIC T4 non-arcing	

Specifications for PCI Card, 4 channel, 24 VDC, Dry Contact		
Number of channels	4	
Detection level for ON (min.)	>4.8 VDC (>5 mA)	
Detection level for OFF (max.)	<1.0 VDC (< 1 mA)	
Input impedance	25 mA at 24 VDC (960 Ohms)	
Input accuracy	0.1% reading (over 0.1 Hz to 50 kHz)	
Resolution	+/- 1 pulse	
Minimum pulse width	10 μS	
Maximum input voltage	24 VDC +20%	
Resolution counter	32 BITS	
Input frequency	Sine wave 10 Hz to 50kHz	
	Square wave 0.1 Hz to 50 kHz	
Wetting Voltage	24 VDC	
LocalBus current (12 VDC nominal)	150 mA maximum	
Field circuit power per card	25 mA at 24 VDC (1 A resettable fuse)	
Isolation	Each channel is optically isolated from the system at 250 VAC and from other channels at 100 VAC.	
Hazardous areas/location	ATEX: II 3G EEx nL IIC T4	
	FM: Class 1, Div 2, Groups A, B, C, D; Haz. Loc.; T4	
Field wiring	ATEX: II 3G EEx nL IIC T4	
	FM: Class 1, Div 2, Groups A, B, C, D; Haz. Loc.; T4	

Specifications for SOE Card, 16 channel, 24 VDC, Dry Contact		
Number of channels	16	
Detection level for On	> 2 mA	
Detection level for Off	< 0.25 mA	
Input impedance	5K ohm (approximate)	
Wetting Voltage	24 VDC	
Channel Scan Rate	0.25 msec for all 16 channels	
Time Stamp Accuracy (for SOE enabled	0.25 msec from same card	
channels only)7	1 msec from same controller	
LocalBus current (12 VDC nominal)	75 mA typical, 100 mA maximum	
Field circuit power per card	75 mA at 24 VDC	
Isolation	Each channel is optically isolated from the system and factory tested to 1500 VDC.	
Hazardous areas/location	ATEX: II 3G EEx nL IIC T4	
	FM: Class 1, Div 2, Groups A, B, C, D; Haz. Loc.; T4	
Field wiring	ATEX: II 3G EEx nL IIC T4	
	FM: Class 1, Div 2, Groups A, B, C, D; Haz. Loc.; T4	

⁷ Refer to Sequence of Event Product Data Sheet for more information on System capabilities and Sequence of Event data collection.

February 2016 – Page 19

Discrete Output I/O Cards

Specifications for DO Card, 8 channel, 24 VDC, Isolated		
Number of channels	8	
Isolation	Each channel is optically isolated from the system and from each other and factory tested to 1500 VDC.	
Output range	2 VDC to 60 VDC	
Output rating	1.0 A	
Off state leakage	1.2 mA maximum	
LocalBus current (12 VDC nominal) per card	100 mA typical, 150 mA maximum	
Field circuit power per card	None	
Configurable Channel Types:	Output	
Discrete output	Output stays in last state submitted by the controller.	
Momentary output	Output is active for a pre-configured time period (100 ms to 100 s).	
Continuous pulse output	Output is active as a percentage of a pre-configured base time period (100 ms to 100 s). Resolution = 5 ms	
Field wiring	Class I, Div 2 Groups A, B, C, D, T4 non-arcing ATEX 3 G IIC T4 -nA	

Specifications for DO Card, 8 channel, 24 VDC, High Side		
Number of channels	8	
Isolation	Each channel is optically isolated from the system and factory tested to 1500 VDC.	
Output range	2 VDC to 60 VDC	
Output rating	1.0 A continuous per channel; 3.0 A maximum per I/O Interface	
Off state leakage	1.2 mA maximum	
LocalBus current (12 VDC nominal) per card	100 mA typical, 150 mA maximum	
Field circuit power per card	3.0 A at 24 VDC per I/O Interface	
Configurable channel types:	Output	
Discrete output	Output stays in last state submitted by the controller.	
Momentary output	Output is active for a pre-configured time period (100 ms to 100 s).	
Continuous pulse output	Output is active as a percentage of a pre-configured base time period (100 ms to 100 s). Resolution = 5 ms	
Optional fuse	2.0 A	
Field wiring	Class I, Div 2 Groups A, B, C, D, T4 non-arcing ATEX 3 G IIC T4 -nA	

Specifications for DO Card, 32 channel, 24 VDC, High Side		
Number of channels	32	
Isolation	Each channel is optically isolated from the system and factory tested to 1000 VDC.	
Output range	24 VDC ± 10%	
Output rating	100 mA per channel	
Off-state leakage	0.1 mA maximum	
LocalBus current (12 VDC nominal) per card	100 mA typical, 150 mA maximum	
Field circuit power per card	3.2 A at 24 VDC per I/O interface	
Return	Uses common return	
Terminal block	32-screw termination block	
Field wiring	Class 1, Div 2, Groups A, B, C, D, T4 non-arcing ATEX 3 G IIC T4 -nA	

Specifications for DO Card, 8 channel, 120/230 VAC, Isolated		
Number of channels	8	
Isolation	Each channel is optically isolated from system at 250 VAC and from other channels at 250 VAC	
Output range	20 to 250 VAC	
Output rating	 1.0 A continuous per channel; 2.0 A maximum per card up to 60 C° (140 F°) 3.0 A maximum per card up to 50 C° (122 F°) 	
Off state leakage	2 mA maximum at 120 VAC 4 mA maximum at 230 VAC	
LocalBus current (12 VDC nominal) per card	100 mA typical,150 mA maximum	
Field circuit power per card	None	
Configurable channel types:	Output	
Discrete output	Output stays in last state submitted by the controller.	
Momentary output	Output is active for a pre-configured time period (100 ms to 100 s).	
Continuous pulse output	Output is active as a percentage of a pre-configured base time period (100 ms to 100 s). Resolution = 5 ms	
Optional fuse	2.0 A	
Field wiring	Class 1, Div 2 IIC T4 non-arcing	

Specifications for DO Card, 8 channel, 120/230 VAC, High Side ⁸		
Number of channels	8	
Isolation	Each channel is optically isolated from the system at 250 VAC	
Output range	20 to 250 VAC	
Output rating	 1.0 A continuous per channel; 2.0 A maximum per card up to 60 C° (140 F°) 3.0 A maximum per card up to 50 C° (122 F°) 	
Off state leakage	2 mA maximum at 120 VAC 4 mA maximum at 230 VAC	
LocalBus current (12 VDC nominal) per card	100 mA typical, 150 mA maximum	
Field circuit power per card	3.0 A at 120 VAC or 230 VAC	
Configurable channel types:	Output	
Discrete output	Output stays in last state submitted by the controller	
Momentary output	Output is active for a pre-configured time period (100 ms to 100 s).	
Continuous pulse output	Output is active as a percentage of a pre-configured base time period (100 ms to 100 s). Resolution = 5 ms	
Optional fuse	2.0 A	
Field wiring	Class 1, Div 2 IIC T4 non-arcing	

⁸ High-side means the output signal is switched on the positive leg. Switching on the positive leg avoids current in field wiring when there is no output signal.

February 2016 - Page 23

I/O Terminal Blocks

A variety of I/O terminal blocks are available to meet specific functionality and environmental requirements of the installation. The I/O interface is a combination of the I/O card and the I/O terminal block. Each I/O interface is uniquely keyed so that once installed in a carrier slot with a terminal block, that terminal block will only accept a replacement card.



8 channel standard Terminal block

The keying mechanism consists of two keying posts that rotate and lock into the terminal block base. Each post has 6 positions: A-F and 1-6. Each card is assigned a unique key which is marked on the side of the I/O card:



Terminal Block keying example

The keys prevent installation of an incorrect card, and the graphical information on the card makes it easy to determine if a keyed slot will accept a particular card.

There are 8 different I/O terminal blocks available to meet the wiring needs of field signals.

- 8-Channel Terminal Block
- Fused 8-Channel Terminal Block
- AI 8-Channel Terminal Block
- Al 16-channel Terminal Block
- Discrete 32-Channel Terminal Block
- Isolated Input Terminal Block
- RTD/Resistance Terminal Block
- Thermocouple Terminal Block

The following redundant I/O terminal blocks are available on some I/O interfaces, allowing a pair of cards to be installed as a redundant pair.

- Redundant AI 8-Channel Terminal Block
- Redundant AO 8-Channel Terminal Block
- Redundant Discrete 8-Channel Terminal Block

The table on the following page lists the compatible terminal blocks for each card, along with the cards unique key positions. The first terminal block listed is the recommended terminal block.

In addition to standard signal wiring, some cards may also be ordered with Mass Terminal blocks that allow these cards to be connected to a third party wiring solution, mounted in an adjacent cabinet in order to meet special signal conditioning or for optimizing field wiring solutions. Please refer to the Alliance Program website for details on approved 3rd party products.

- 10-pin Mass Terminal Block
- 16-pin Mass Terminal Block
- 24-pin Mass Terminal Block
- 40-pin Mass Terminal Block

February 2016 – Page 24

Traditional I/O and terminal block compatibility:

I/O Card	I/O Card Keying	Traditional I/O Terminal Blocks	Mass Terminal Blocks
AI, 8-channel, 4–20 mA, HART	A1	I/O Terminal Block Fused I/O Terminal Block	16-pin Mass Terminal Block (Supports 2-wire Devices)
		4-wire I/O terminal Block	24-pin Mass Terminal Block (Supports 4-wire Devices)
Al, 16-channel, 4-20 mA HART (Simplex mode)	A2	2-wire I/O Terminal Block 4-wire I/O Terminal Block	NA
AI, 16-channel, 4-20 mA HART (red. mode)	A6	I/O Terminal Block (supports 2- and 4-wire)	NA
AO, 8-channel,4–20 mA, HART	A4	I/O Terminal Block Fused Terminal Block	16-pin Mass Termination Block
AO, 16-channel,4–20 mA, HART (red. mode)	A5	I/O Terminal Block	NA
Thermocouple, mV	C1	I/O Terminal Block Cold Junction Compensated (CJC) Termination Block	NA
RTD, 8-channel	C3	Resistant Temperature Device (RTD) Termination Block	NA
Isolated Input Card	C2	Isolated Input Terminal Block	NA

February 2016 – Page 25

I/O Card	I/O Card Keying	Traditional I/O Terminal Blocks	Mass Terminal Blocks
DI, 8-channel, 24 VDC, dry contact	B1	I/O Terminal Block Fused Terminal Block	16-pin Mass Termination Block
DI, 8-channel, 24 VDC, Isolated	B2	I/O Terminal Block Fused Terminal Block	16-pin Mass Termination Block
DI, 32-channel, 24 VDC dry contact (simplex mode)	B3	32-Channel Terminal Block	40-pin Mass Termination Block
DI, 32-channel, 24 VDC dry contact (red. Mode)	E3	32-Channel Terminal Block	NA
PCI, 4-channel	C6	32-Channel Terminal Block	NA
SOE, 16-channel,24 VDC	C5	32-Channel Terminal Block	40-pin Mass Termination Block
DO, 8-channel, 24 VDC, High Side	B6	I/O Terminal Block Fused Terminal Block	10-pin Mass Termination Block 16-pin Mass Termination Block
DO, 8-channel, 24 VDC, isolated	B5	I/O Terminal Block Fused Terminal Block	16-pin Mass Termination Block
DO, 32-channel, 24 VDC high-side (simplex mode)	B4	32-Channel Terminal Block	40-pin Mass Termination Block
DO, 32-channel, 24 VDC high-side (red. Mode)	B4	NA	40-pin Mass Termination Block
DI, 8-channel, 120 VAC, dry contact	E1	I/O Terminal Block Fused Terminal Block	NA
DI, 8-channel, 120 VAC, isolated	E4	I/O Terminal Block Fused Terminal Block	NA
DO, 8-channel, 120 VAC/ 230 VAC, high side	F1	I/O Terminal Block Fused Terminal Block	NA
DO, 8-channel, 120 VAC/ 230 VAC, isolated	F4	I/O Terminal Block Fused Terminal Block	NA

February 2016 – Page 26

System Compatibility

■ M-series Traditional I/O cards are not physically compatible with S-series controller carriers

Ordering Information

Analog Input Cards and Termination Blocks		
Description	Model Number	
Analog Input Card: 8 Channels 4-20 mA, HART		
Standard I/O Termination Block	CE4003S2B1	
Redundant Standard I/O Termination Block	CE4033S2B1	
Fused I/O Termination Block	CE4003S2B2	
4-wire I/O Termination Block	CE4003S2B3	
16-Pin Mass I/O Termination Block	CE4003S2B4	
24-Pin Mass I/O Termination Block	CE4003S2B5	
Analog Input Card: 16 Channels 4-20 mA, HART		
Standard I/O Termination Block	CE4003S2B6	
4-wire I/O Termination Block	CE4003S2B7	
Analog Input Card: 16 Channels 4-20 mA, HART, Series 2 Plus		
Redundant Standard I/O Termination Block (supports 2- and 4-wire)	CE4033S2B10	
2-wire, Standard I/O Termination Block, Simplex	CE4003S2B9	
4-wire, Standard I/O Termination Block, Simplex	CE4003S2B10	
Analog Input Card: 8 Channels Thermocouple,mV		
Standard I/O Termination Block	CE4003S4B1	
Cold Junction Compensated (CJC) Termination Block	CE4003S5B1	
Analog Input Card: 8 Channels RTD		
Resistant Temperature Device (RTD) Termination Block	CE4003S6B1	
Isolated Input Card		
Isolated Input terminal Block	CE4003S7B1	

Analog Output Cards and Termination Blocks		
Description	Model Number	
Analog Output Card: 8 Channels 4-20 mA, HART		
Standard I/O Termination Block	CE4005S2B1	
Redundant Standard I/O Termination Block	CE4035S2B1	
Fused I/O Termination Block	CE4005S2B2	
16-Pin Mass I/O Termination Block	CE4005S2B3	
Analog Output Card: 16 Channels 4-20 mA, HART, Series 2 Plus		

February 2016 – Page 27

Analog Output Cards and Termination Blocks		
Description	Model Number	
Redundant Standard I/O Termination Block	CE4035S2B4	
Standard I/O Termination Block, Simplex	CE4005S2B4	

February 2016 – Page 28

Discrete Input Cards and Termination Blocks		
Description	Model Number	
Discrete Input Card: 8 Channels, 24Vdc, Isolated		
Standard I/O Termination Block	CE4001S2T1B1	
Fused I/O Termination Block	CE4001S2T1B2	
16-Pin Mass I/O Termination Block	CE4001S2T1B3	
Discrete Input Card: 8 Channels, 24Vdc, Dry Contact		
Standard I/O Termination Block	CE4001S2T2B1	
Redundant Standard I/O Termination Block	CE4031S2T2B1	
Fused I/O Termination Block	CE4001S2T2B2	
16-Pin Mass I/O Termination Block	CE4001S2T2B3	
Discrete Input Card: 32 Channels, 24 Vdc, Dry Contact		
Standard Termination Block	CE4001S2T2B4	
40-pin Mass Termination Block	CE4001S2T2B5	
40-pin Mass Termination Block and DI Mass Connection Solution	CE4051S2T2B5	
Discrete Input Card: 32 Channels, 24 Vdc, Dry Contact, Series 2 Plus		
Redundant Standard I/O Termination Block	CE4031S2T2B6	
Mass Termination Block, Simplex	CE4001S2T2B7	
Redundant Mass Termination Block	CE4031S2T2B7	
Discrete Input Card: 8 Channels, 120Vac, Isolated		
Standard I/O Termination Block	CE4001S3T1B1	
Fused I/O Termination Block	CE4001S3T1B2	
Discrete Input Card: 8 Channels, 120Vac, Dry Contact		
Standard I/O Termination Block	CE4001S3T2B1	
Fused I/O Termination Block	CE4001S3T2B2	
Pulse Count Input Card: 4-Channels, 24 Vdc, Dry Contact		
Discrete 32 Channel Terminal Block	CE4015	
Sequence of Event Input Card: 16 Channels, 24 Vdc Dry Contact		
Discrete 32-Channel Terminal Block	CE4001S5T2B4	
40-pin Mass Terminal Block	CE4001S5T2B5	

February 2016 – Page 29

Discrete Output Cards and Termination Blocks		
Description	Model Number	
Discrete Output Card: 8 Channels 24Vdc, Isolated		
Standard I/O Termination Block	CE4002S1T1B1	
Fused I/O Termination Block	CE4002S1T1B2	
16-Pin Mass I/O Termination Block	CE4002S1T1B3	
Discrete Output Card: 8 Channels 24Vdc, High Side		
Standard I/O Termination Block	CE4002S1T2B1	
Redundant Standard I/O Termination Block	CE4032S1T2B1	
Fused I/O Termination Block	CE4002S1T2B2	
16-Pin Mass I/O Termination Block	CE4002S1T2B3	
10-Pin Mass I/O Termination Block	CE4002S1T2B4	
Discrete Output Card, 32 Channels, 24Vdc, High Side		
Standard I/O Termination Block	CE4002S1T2B5	
40-Pin Mass I/O Termination Block	CE4002S1T2B6	
40-pin Mass Termination Block and DO Mass Connection Solution	CE4052S1T2B6	
Discrete Output Card, 32 Channels, 24Vdc, High Side, Series 2 Plus		
Redundant 40-pin Mass Termination Block	CE4032S1T2B8	
Redundant 40-pin Mass Termination Block and DO Mass Connection Solution	CE4082S1T2B8	
Mass Termination Block, Simplex	CE4002S1T2B8	
Discrete Output Card: 8 Channels 115/230Vac, Isolated		
Standard I/O Termination Block	CE4002S2T1B1	
Fused I/O Termination Block	CE4002S2T1B2	
Discrete Output Card: 8 Channels 115/230Vac, High Side		
Standard I/O Termination Block	CE4002S2T2B1	
Fused I/O Termination Block	CE4002S2T2B2	

Spare part ordering Information

Spare Parts	
Description	Model Number
250V 2A Fuse for Fused Terminal Block; Box of 20	KJ4010X1-BC1

To locate a sales office near you, visit our website at: www.EmersonProcess.com Or call us at: India: +91 22 66620566 Asia Pacific: 65.6777.8211 Office Address: Emerson Process Management (India) Pvt. Ltd. Delphi B-Wing, 601-602, 6th Floor, Central Avenue, Hiranandani Business Park, Mumbai-400076

© Emerson Process Management 2016. All rights reserved. For Emerson Process Management trademarks and service marks, go to: http://www.emersonprocess.com/home/news/resources/marks.pdf.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warrantees or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the design or specification of such products at any time without notice.





