

8

7

6

5

4

3

2



1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

Sensor Terminals:


Sensor Types:

CMF010	T075	F025	H025
CMF025	T100	F050	H050
CMF050	T150	F100	H100
CMF100		F200	H200
CMF200			
CMF300 (excluding CMF300A)			



NOTE: PREPARE CABLE PER THE INSTRUCTIONS PROVIDED WITH THE CABLE.

3700 IS TERMINAL (BLUE)



D

D

C

C

B

B

A

A

8

7

6



5

4

3

2

1

		 MICRO MOTION, INC. BOULDER, COLORADO	
 THIRD ANGLE PROJECTION		WIRING, 3700 TO CMF/T/F/H	
NAME	DATE	SIZE	DWG. NO.
DRAWN DJS	11/13/97	D	EW-3300526
CHKD. RBG	12/30/97	SCALE NONE	DO NOT SCALE DRAWING
APVD. RBG	12/30/97	SHEET 1 OF 1	

COPYRIGHT 2005 MICRO MOTION, INC.
ALL RIGHTS RESERVED