

8

7

6

5

4

3

2

1

GENERAL NOTES (UNLESS OTHERWISE SPECIFIED)

REVISIONS						
REV	ECN	DESCRIPTION OF CHANGE	DRAWN	CHKD	APVD	DATE

D

D

Sensor Terminals

Sensor Types:

- CMF010
- CMF025
- CMF050
- CMF100
- CMF200
- CMF300
- CMF400

C

C


Transmitter:

3500
IS CONNECTOR

	C	D	
	2	2	
VDC+	4	4	VDC-
RS485A	6	6	RS485B
	8	8	
	10	10	
	12	12	
	14	14	
	16	16	
	18	18	
	20	20	
	22	22	
	24	24	
	26	26	
	28	28	
	30	30	
	32	32	

B

B



CUSTOMER SUPPLIED CABLE
 MAXIMUM LENGTH:
 1000 ft (300m) OF 18 AWG(0.8 mm²)
 300 ft (100m) OF 22 AWG(0.35 mm²)

A

A

COPYRIGHT 2006 MICRO MOTION, INC.
ALL RIGHTS RESERVED

ITEM	DESCRIPTION	PART OR REF. NO.	MATL. OR MFR	QTY.
THIRD ANGLE PROJECTION		MICRO MOTION, INC. BOULDER, COLORADO		
WIRING ENHANCED CORE TO 3500		SIZE DWG. NO. REV. D 20006809 A		
DRAWN	WJB	4/27/06		
CHKD.	SAD	5/19/06		
APVD.	ER	5/19/06	SCALE NONE	DO NOT SCALE DRAWING SHEET 1 OF 1

8

7

6

5

4

3

2

1