



WHY PROTEAM

Game-Changing Design Innovation

In 1987, ProTeam revolutionized the commercial cleaning world by introducing the lightweight backpack vacuum.

ProTeam's backpack vacuum dramatically improves worker productivity, effectiveness and ergonomic comfort.

Scientific studies and end-users consistently find ProTeam vacuums save time, money and resources while improving Indoor Air Quality (IAQ).

With durable materials and fewer moving parts, ProTeam vacuums last for years, while reducing repair and maintenance issues.

ProTeam's legacy of engineering innovative cleaning solutions continues with its latest lineup — the GoFit® Series. Using decades of learned knowledge and user insight, the GoFit Series delivers maximum comfort, productivity and now cordless efficiency. From fit to function, GoFit gives you more.



“The GoFit backpack was lighter, quieter, and more comfortable to use.”

- Chris F., Glenale, WI

WHY PROTEAM?

PRODUCTIVITY



COST OF OWNERSHIP



ERGONOMICS



SUSTAINABILITY



INDOOR AIR QUALITY



CLEANING FOR HEALTH






- ProTeam backpack vacuums clean more than 3 times faster than commercial uprights.
- Backpack vacuuming is a faster, healthier, more efficient way to clean.
- ProTeam backpack vacuums clean 52% faster than a dust mop.
- Dust bunnies reappear in 24 hours when a floor has been dust mopped as compared to 72 hours when cleaned with a ProTeam backpack vacuum.

In 5 passes, the ProTeam backpack vacuum is:

- 43% more efficient than a commercial upright vacuum.
- 30% more efficient than a canister in removing soil.

Source—
Quality Environmental Services & Technologies, 1996; APC Filtration, Inc., 1996; An Evaluation of ProTeam's QuarterVac and CoachVac in a School Environment, Dr. Eric Brown, Cleaning Research International, UK, 1994



CORDLESS CLEANING IS 30% MORE EFFICIENT THAN A BACKPACK AND 5x FASTER THAN AN UPRIGHT

A cordless backpack vacuum increases efficiencies by saving approximately 1-1.5 hours per a 4-hour vacuum shift.

COST OF OWNERSHIP



- For more than 30 years, ProTeam has designed vacuums with durability and quality in mind.
- ProTeam vacuums are low maintenance and long lasting, with multi-year warranties to back them up.



BACKPACK VACUUM CLEANER ROI ANALYSIS

20% In Savings Every Hour

- In about 9 vacuuming hours, you have recouped your additional investment required to purchase a backpack over an upright.
- In less than 17 vacuuming hours, you have recouped your entire investment required to purchase a backpack.

50,000 SF FACILITY

	AVERAGE PRICE	TIME TO VACUUM	COST TO VACUUM*
ProTeam Backpack	\$550	6.1 Hrs	\$79.30
Single Motor	\$300	16.3 Hrs	\$211.90
Upright Difference	<\$250>	10.2 Hrs	\$132.60

*Using \$13.00/Hr Labor Rate
Source – Bureau of Labor Statistics (<http://www.bls.gov/ooh/>)

Annual savings using a ProTeam Backpack Vacuum versus a 14" upright: \$35,350

*based on The Official ISSA Cleaning Times (www.issa.com). Used with permission.



- Backpack vacuums are lightweight. When worn properly, the effect of the backpack on body joints and posture is negligible and similar to walking.
- When working near or on stairs, using a backpack improves mobility and is recommended to reduce the risk of falling.
- Backpack vacuum users maintain a more neutral posture compared to frequent extreme arm and leg extensions seen when using an upright.
- Results in less body stress due to the use of larger muscle groups by minimizing “hunching over” often associated with upright and canister vacuum.

“The easy self adjusting harness fits any user’s body. The harness is very padded and super comfortable.”

Courtney C., University of Utah



1/2

the energy and effort to clean the same area as an upright.

Source – Battelle Memorial Institute, Ohio State University, Columbus, Ohio, 1998. Reviewed by Jim Fullmer, Certified Human Factors Professional, 2009. The Official ISSA Cleaning Times.

ProTeam backpack vacuums ergonomic design allowed end-users to vacuum more than twice the area in half the time with less fatigue and body strain.

These findings are the results of two studies completed by the Department of Surgery, Division of Orthopedics, at Ohio State University and the Battelle Memorial Institute.

SUSTAINABILITY



Environmental Impact

For more than 30 years our innovative products have led the market in efficient cleaning with less user effort or strain. Our vacuums require fewer repairs and replacement parts and improve cost savings and IAQ.

Product Design

Our vacuums are built to last, and they have – for many years – which reduces items headed to waste landfills.

Plus, with fewer moveable parts and washable vacuum body parts and filters, fewer replacement materials are thrown away.

ProTeam’s Environmental Responsibility

- Commitment to provide products and services that improve energy efficiencies and reduce potential harm to the environment.
- Applying cost-effective and energy-efficient manufacturing processes.
- Reducing energy consumption and waste.



The air we breathe is full of particles that trigger asthma and allergic reactions. Dust, mold, pollen and bacteria, invisible to the human eye, come from many different sources and quickly travel from one environment to the next. The ProTeam exclusive suction only system successfully contains microscopic debris.

WHY is it important to filter out particles down to such a microscopic size?



FACT

ProTeam's exclusive filtration system capture particulates and pollutants both visible and invisible that can harm health and trigger asthma or allergies.

Around 300 million people worldwide have asthma and likely by 2025 a further 100 million may be affected according to National Library of Medicine leading to increasing health care costs and lost productivity.

Approximately 13.8 million school days and 14.2 million work days are missed each year due to asthma, according to the CDC National Center for Health Statistics.

PROTEAM'S UNIQUE SUCTION METHOD OF CLEANING:

- **Cleans carpet & hard surfaces** without stirring up dust.
- **Air stays cleaner reducing** the need to dust as often.
- **Operators can work** without breathing unhealthy air.



ProTeam vacuums have earned Seal of Approval from the Carpet and Rug Institute (CRI) signifying the vacuum systems meet higher standards for carpet cleaning effectiveness and Indoor Air Quality.

ProTeam backpack vacuums meet the vacuum cleaner requirements for green cleaning credits under LEED v4.1 Building Operations and Maintenance.

CLEANING FOR HEALTH[®]



ProTeam is a proud partner of the American Lung Association. Together, we fight for clean indoor air so that we all can breathe easier. We spend the majority of our time indoors, so breathing healthy air where we live, work and play is critical.

For more information from the American Lung Association, call 1-800-LUNG USA, or visit their website at www.lung.org.

*The American Lung Association does not endorse product, device or service.

PROTEAM GOFIT SERIES

This reimagined, reshaped and remarkable lineup includes corded and cordless versions, featuring our ProLevel Filtration® system and a quick-adjust harness for unparalleled productivity and comfort. The GoFit Series is designed with the user in mind to accommodate users of all sizes and all cleaning needs. The GoFit Corded units are available in 3, 6, 6 PLUS and 10-quart size. The GoFit 3 delivers big power for those with a smaller frame while the GoFit 6 PLUS features a filter change indicator light for maintenance alerts. The GoFit Cordless units come in 3 and 6-quart sizes and are ideal for navigating freely without potential tripping hazards, offering extended runtimes with 4Ah or 8Ah batteries and a high/low power switch for tailored cleaning power.



Stay comfortable while being more productive.

- **INCREASED BREATHABILITY**

Increases air circulation, reducing warmth and moisture accumulation.

- **QUICK-ADJUST SYSTEM**

No tools required - quick adjust system moves upper harness up and down to fit user height perfectly

- **INTERCHANGEABLE HARNESS**

Allows each user to have their own custom-fitted harness.

- **WIDER AND LONGER LOWER HARNESS**

Distributes the weight of the unit for greater comfort.

ProTeam GoFit 6 Cordless



13.5 lbs. / 6.1 kg. (w/ 4Ah) | 16.4 lbs. / 7.4 kg. (w/ 8Ah)

65 CFM (low) | 70 CFM (high)

55 in. (low) | 63 in. (high) Static Lift

65 dBA (low) | 67 dBA (high)

4Ah Battery: 51 min. (low) | 39 min. (high)

8Ah Battery: 106 min. (low) | 83 min. (high)

ProTeam GoFit 3 Cordless



12.8 lbs. / 5.8 kg. (w/ 4Ah) | 15.7 lbs. / 7.1 kg. (w/ 8Ah)

65 CFM (low) | 70 CFM (high)

55 in. (low) | 63 in. (high) Static Lift

63 dBA (low) | 66 dBA (high)


4Ah Battery: 51 min. (low) | 39 min. (high)

8Ah Battery: 106 min. (low) | 83 min. (high)

PROTEAM GOFIT SERIES

ProTeam GoFit 3/6/10 Corded

Packed with the same power and efficiency. Get a customized fit with the vacuum's quick-adjust harness, making it easy to adjust the height to personalized needs.



- 11.4 lbs. / 5.17 kg. (GoFit 3)
- 12 lbs. / 5.44 kg. (GoFit 6 / 6 PLUS)
- 12.9 lbs. / 5.85 kg. (GoFit 10)
- 153 CFM
- 91 in. Static Lift
- 68 dBA (GoFit 3)
- 67.9 dBA (GoFit 6)
- 67.2 dBA (GoFit 10)

**ProLevel Filtration System with HEPA Media

Captures 99.79% (GoFit 3), 99.82% (GoFit 6) & 99.86% (GoFit 10) at 0.3-.5 microns per ASTM F3150

BACKPACK VACUUMS



ProTeam GoFree® Flex Pro II

With a high/low power switch, the GoFree Flex Pro II brings greater versatility & options to professional cleaners. Eliminate safety and tripping concerns when going cordless.

- 17.5 lbs. / 7.9 kg.
- 58 CFM (low) | 65 CFM (high)
- 67 in. (low) | 81 in. (high) Static Lift
- 63.9 dBA (low) | 65.9 dBA (high)
- 106 mins. (low) | 75 mins. (high)

**ProLevel Filtration System with HEPA Media

Captures 99.72% at 0.3-.5 microns per ASTM F3150



ProTeam Super Coach® Pro 6 & 10

A productive vacuum that features ProTeam's innovative articulating harness which provides comfort and ease of use.

- 11.8 lbs. / 5.35 kg. (SCP 6)
- 12.5 lbs. / 5.67 kg. (SCP 10)
- 153 CFM
- 91 in. Static Lift
- 69.7 dBA

**ProLevel Filtration System with HEPA Media

Captures 99.63% (SCP 6) & 99.84% (SCP 10) at 0.3-.5 microns per ASTM F3150



ProTeam ProVac® FS 6

This vacuum is designed to be virtually indestructible with no belts or beater bars to triumph over food service & hospitality industry demands.

- 11.8 lbs. / 5.35 kg.
- 153 CFM
- 91 in. Static Lift
- 69.7 dBA

**ProLevel Filtration System with HEPA Media

Captures 99.63% at 0.3-.5 microns per ASTM F3150



ProTeam LineVacer® HEPA / ULPA

Ideal for critical cleaning such as medical facilities & is appropriate for lead paint renovations under the EPA's RRP rule.

- 13 lbs. / 5.9 kg.
- 124 CFM
- 75 in. Static Lift
- 64 dBA

**HEPA/ULPA Filtration

Captures 99.97% at 0.3 microns (HEPA) & 99.999+% (ULPA) at 0.12 microns

TOOLS & FILTERS

High Dusting Tool Kit

Expand the reach of your ProTeam vacuum by 10-12 ft. of effective cleaning.



Intercept Micro® Filters

The first line of defense in our ProLevel Filtration System which reduces and controls indoor air pollutants.



UPRIGHT VACUUMS



ProTeam ProForce® 1200XP / 1500XP

12" - 15" path with on-board tools. High-performance dual motor system maintains power to both the brush roller and the suction motor.

18 lbs. / 8.17 kg.

Dual Motor System

96 CFM

84 in. Static Lift

67 dBA

****ProLevel Filtration System with HEPA Media**
Captures 97.33% (1200XP) & 98.73% (1500XP) at 0.3-5 microns per ASTM F3150



ProTeam ProGen® 12 / 15

Choose 12" or 15" width for productivity in a variety of applications. Ability to reach clogs in four easy access points provides quick and easy maintenance.

17 lbs. / 7.71 kg. (ProGen 12)

18 lbs. / 8.17 kg. (ProGen 15)

100 CFM

93 in. Static Lift

69 dBA

****ProLevel Filtration System with HEPA Media**
Captures 97.44% (PG 12) & 98.36% (PG 15) at 0.3-5 microns per ASTM F3150

WET/DRY VACUUMS



ProTeam ProGuard 10

With a heavy duty motor and commercial grade tools and hose, they will keep working even in the toughest environments.

28 lbs. / 12.7 kg.

10 gal. / 38 L

105 CFM

95 in. Static Lift

68 dBA



ProTeam ProGuard 4 Portable

Power and versatility come together in the portable ProGuard 4 wet/dry vacuum.

12 lbs. / 5.5 kg.

4 gal. / 15.2 L

142 CFM

51 in. Static Lift

76 dBA



ProTeam ProGuard 15 / 20*

Variable wheel pattern allows for increased maneuverability. Large tank capacity for major spills & messes.

68 lbs. / 31 kg. (PG 15)

70 lbs. / 32 kg. (PG 20)

15 gal. / 57 L (PG 15)

20 gal. / 76 L (PG 20)

105 CFM

95 in. Static Lift

69 dBA



ProTeam ProGuard 16

Has a removable handle allowing for easy storage and is equipped with a convenient tool bag to hold all necessary hand tools within reach.

29 lbs. / 13.2 kg.

16 gal. / 60.6 L

105 CFM

95 in. Static Lift

66 dBA

*Sold with or without Front Mount Squeegee



ProTeam ProBlitz® AirMover

Quiet operation with multiple fan speeds & drying settings. Daisy chain capabilities on XP models.

28 lbs. / 12.7 kg.

2200 CFM (max)

Low, Medium, High Speeds

Three Drying Positions:

0°, 45°/60° (XP), 90°

*XP model w/ telescoping handle shown



FOR MORE INFORMATION ABOUT OUR COMPLETE LINE OF COMMERCIAL VACUUMS

CALL (866) 888-2168, EMAIL customerservice.proteam@emerson.com
OR VISIT proteam.emerson.com

ProTeam, GoFit, Super Coach Pro, ProVac, ProBlade, GoFree, ProForce, ProGen, ProGuard, ProBlitz, LineVacor, FlexFit, ProDuster, Intercept Micro, Cleaning for Health, ProLevel Filtration and Four Level are trademarks and registered trademarks of ProTeam, Inc. © 2024 ProTeam, Inc. All Rights Reserved.

Customer Success with our NEW GoFit Cordless Vacuums:

“Battery life is really good with a good rate of recharge. The two-speed motor is very helpful to extend battery life.”

- Richard S., Iowa City, IA

“I could vacuum the back corner I could never reach with a corded vacuum.”

- Pam W., Chesterfield, MO

“No need to locate outlets in unfamiliar spaces.”

- Dana K., Carrollton, GA

Contact us-



8100 West Florissant Ave, Building T
St. Louis, MO, 63136



Phone: 866-888-2168
Mondays to Fridays, 8AM-5PM



customerservice.proteam@emerson.com
proteam.emerson.com

